

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921396

Luminaire Tested: DFN2DIP-4P4F0-040D030US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921396
REPORT IS A COMBINATION OF REPORTS P899082 AND P895967
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-040D030US940-RLLFLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5399.3 lumens
Efficiency: N/A
Efficacy: 87.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 61.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921396

CATALOG NUMBER: DFN2DIP-4P4F0-040D030US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P921396

CATALOG NUMBER: DFN2DIP-4P4F0-040D030US940-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	55	54	53
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	49	47	46
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	30
6	65	53	46	40	61	50	43	38	44	38	34	38	34	31	33	30	27
7	61	48	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	956	956	956
5°	958	941	948
10°	949	923	917
15°	936	893	870
20°	918	851	812
25°	901	804	755
30°	877	756	684
35°	854	705	621
40°	830	651	549
45°	803	591	484
50°	774	531	420
55°	745	467	359
60°	711	400	296
65°	671	332	266
70°	624	268	242
75°	563	237	221
80°	476	199	193
85°	333	135	147

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 803 cd/sqm

TEST NUMBER: P921396

CATALOG NUMBER: DFN2DIP-4P4F0-040D030US940-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.2	2.6
10°-20°	379.3	7.0
20°-30°	532.5	9.9
30°-40°	580.5	10.8
40°-50°	533.5	9.9
50°-60°	419.0	7.8
60°-70°	272.7	5.1
70°-80°	140.4	2.6
80°-90°	38.2	0.7
90°-100°	52.3	1.0
100°-110°	166.3	3.1
110°-120°	284.7	5.3
120°-130°	374.4	6.9
130°-140°	420.2	7.8
140°-150°	412.1	7.6
150°-160°	345.7	6.4
160°-170°	229.2	4.2
170°-180°	80.1	1.5
0°-30°	1049.9	19.4
0°-40°	1630.4	30.2
0°-60°	2582.9	47.8
0°-90°	3034.2	56.2
90°-120°	503.4	9.3
90°-150°	1710.0	31.7
90°-180°	2365.0	43.8
0°-180°	5399.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1474	1474	1474	1474	1474	
5°	1474	1468	1450	1462	1458	140
15°	1402	1387	1342	1317	1304	395
25°	1273	1230	1142	1087	1067	585
35°	1097	1029	911	827	798	686
45°	896	807	667	572	540	692
55°	682	578	434	354	328	609
65°	460	352	232	187	183	456
75°	245	152	107	97	96	260
85°	57	29	25	25	25	66
90°	1	9	25	24	24	5
95°	37	44	46	46	44	41
105°	154	156	157	158	158	162
115°	286	290	288	288	286	283
125°	416	422	420	418	417	371
135°	537	545	547	546	544	415
145°	652	658	662	662	660	408
155°	746	748	750	754	752	343
165°	812	811	811	816	812	229
175°	844	842	841	846	842	80
180°	846	846	846	846	846	

TEST NUMBER: P921396

CATALOG NUMBER: DFN2DIP-4P4F0-040D030US940-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1474.2	1474.2	1474.2	1474.2	1474.2
2.5°	1480.9	1474.2	1459.5	1472.9	1470.2
5°	1474.2	1467.5	1450.1	1462.1	1458.2
7.5°	1462.1	1454.2	1435.6	1440.7	1434.1
10°	1446.2	1436.8	1410.2	1406.0	1398.2
12.5°	1426.2	1414.2	1378.0	1370.1	1355.4
15°	1402.1	1387.4	1342.1	1316.8	1303.5
17.5°	1374.1	1352.7	1296.6	1267.4	1246.0
20°	1342.1	1315.4	1248.7	1215.4	1186.0
22.5°	1307.4	1276.8	1199.3	1154.0	1134.1
25°	1272.7	1230.0	1141.9	1087.4	1067.2
27.5°	1231.5	1186.0	1088.6	1025.9	995.1
30°	1187.4	1136.6	1029.8	961.9	925.9
32.5°	1144.7	1083.2	973.9	893.9	860.4
35°	1096.7	1028.6	911.2	827.2	797.7
37.5°	1050.0	976.5	852.5	760.4	727.1
40°	1000.6	920.6	791.1	696.4	661.7
42.5°	949.8	864.5	729.8	631.0	597.7
45°	896.5	807.1	667.1	572.3	540.3
47.5°	845.9	751.2	607.1	512.3	483.0
50°	789.8	695.1	548.3	456.2	428.3
52.5°	735.0	635.0	492.3	404.2	378.9
55°	681.7	577.6	433.5	353.6	328.2
57.5°	627.1	520.3	381.6	306.8	285.5
60°	571.0	464.2	326.8	258.9	237.6
62.5°	516.4	409.7	280.1	216.2	205.5
65°	460.3	352.1	232.1	186.8	182.7
67.5°	407.0	298.8	186.8	164.1	160.1
70°	350.9	246.8	154.7	141.4	136.0
72.5°	297.6	198.8	129.4	118.8	116.1
75°	245.4	152.0	106.7	97.4	96.1
77.5°	193.5	108.0	84.1	78.7	76.0
80°	145.3	77.4	63.9	58.8	58.8
82.5°	101.4	52.1	44.1	41.3	41.3
85°	57.3	29.3	25.3	25.3	25.3
87.5°	21.4	10.6	10.6	9.4	9.4
90°	0.8	9.2	25.0	23.5	24.3
92.5°	15.8	21.4	22.2	22.9	22.9
95°	37.3	44.4	45.7	45.7	44.4
97.5°	62.0	68.6	71.4	71.4	71.4
100°	90.5	96.4	98.4	98.4	97.7
102.5°	120.6	125.0	127.8	128.6	127.8
105°	153.6	155.6	157.1	158.4	158.4
107.5°	186.2	189.2	189.2	189.8	186.2
110°	217.8	221.9	221.9	221.9	219.9

TEST NUMBER: P921396

CATALOG NUMBER: DFN2DIP-4P4F0-040D030US940-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	252.0	256.4	255.6	253.5	252.0
115°	285.7	289.7	288.5	287.8	285.7
117.5°	319.1	324.7	321.1	319.1	317.0
120°	352.8	358.4	352.8	352.8	350.4
122.5°	383.3	390.5	386.9	384.9	383.3
125°	415.5	421.9	419.8	417.5	416.8
127.5°	446.8	454.8	452.0	448.9	446.8
130°	476.2	485.4	484.1	482.6	479.7
132.5°	509.1	516.2	516.7	513.2	511.1
135°	537.4	545.3	546.9	546.1	544.0
137.5°	569.0	575.4	576.7	576.2	573.1
140°	596.8	603.2	606.8	606.8	604.0
142.5°	625.4	631.8	633.8	634.6	631.8
145°	652.5	657.5	661.6	662.4	659.6
147.5°	676.7	683.1	686.1	687.4	684.6
150°	701.7	706.1	708.8	711.1	708.8
152.5°	723.9	728.2	731.7	734.6	731.7
155°	746.1	748.1	750.4	753.9	751.7
157.5°	765.2	766.7	768.0	773.1	769.5
160°	782.3	783.8	784.6	788.9	785.9
162.5°	798.1	798.1	798.9	803.7	800.1
165°	811.6	810.8	810.8	815.9	812.3
167.5°	823.9	821.5	821.5	826.6	823.0
170°	833.0	831.0	830.3	835.4	831.0
172.5°	839.4	837.4	836.6	841.7	837.4
175°	844.5	842.5	841.0	846.1	841.7
177.5°	847.3	845.3	843.7	848.1	843.7
180°	846.1	846.1	846.1	846.1	846.1

TEST NUMBER: P921396

CATALOG NUMBER: DFN2DIP-4P4F0-040D030US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.57	8.45	8.48	9.38	10.56	3.53	4.41	4.44	5.34	6.52
	3H	9.26	10.05	10.18	10.98	12.19	4.72	5.51	5.65	6.45	7.65
	4H	9.87	10.62	10.81	11.56	12.77	5.18	5.92	6.11	6.86	8.08
	6H	10.30	10.99	11.25	11.93	13.16	5.50	6.19	6.45	7.13	8.36
	8H	10.43	11.09	11.39	12.05	13.27	5.60	6.25	6.55	7.21	8.44
	12H	10.50	11.12	11.46	12.07	13.33	5.64	6.26	6.60	7.22	8.47
4H	2H	7.59	8.34	8.54	9.28	10.50	4.13	4.88	5.08	5.82	7.04
	3H	9.44	10.06	10.39	11.02	12.25	5.49	6.11	6.44	7.08	8.31
	4H	10.13	10.70	11.09	11.66	12.92	6.04	6.61	7.01	7.57	8.83
	6H	10.66	11.14	11.63	12.13	13.38	6.47	6.96	7.44	7.94	9.20
	8H	10.84	11.29	11.81	12.27	13.54	6.60	7.05	7.58	8.03	9.30
	12H	10.94	11.35	11.93	12.34	13.62	6.67	7.08	7.66	8.07	9.35
8H	4H	10.11	10.56	11.08	11.54	12.81	6.33	6.79	7.31	7.77	9.03
	6H	10.68	11.05	11.68	12.08	13.34	6.86	7.23	7.86	8.25	9.52
	8H	10.90	11.23	11.91	12.24	13.53	7.05	7.38	8.06	8.39	9.67
	12H	11.05	11.34	12.06	12.34	13.67	7.17	7.46	8.18	8.46	9.80
12H	4H	10.06	10.47	11.05	11.47	12.74	6.34	6.75	7.33	7.75	9.02
	6H	10.66	10.99	11.66	12.00	13.28	6.91	7.24	7.91	8.25	9.53
	8H	10.88	11.17	11.89	12.18	13.51	7.12	7.41	8.13	8.42	9.75