

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921508

Luminaire Tested: DFN2DIP-4P4F0-080D070US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921508
REPORT IS A COMBINATION OF REPORTS P899138 AND P895967
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-080D070US940-RLLFLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11587.8 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 146.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921508

CATALOG NUMBER: DFN2DIP-4P4F0-080D070US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P921508

CATALOG NUMBER: DFN2DIP-4P4F0-080D070US940-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	99	95	91	88	91	88	85	82	75	73	71	63	62	60	52	51	50
2	90	83	77	72	83	77	72	68	66	63	59	56	53	51	47	45	43
3	83	74	67	61	76	69	62	57	59	54	50	50	47	44	42	39	37
4	76	66	58	52	70	61	54	49	53	48	43	45	41	38	38	35	33
5	70	59	51	45	65	55	48	43	47	42	38	41	36	33	34	31	29
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	31	28	25
7	60	48	40	35	55	45	38	33	39	34	30	34	29	26	29	25	23
8	56	44	36	31	52	41	34	29	36	30	26	31	27	23	26	23	21
9	52	40	33	28	48	38	31	26	33	28	24	29	24	21	24	21	19
10	49	37	30	25	45	35	28	24	30	25	22	26	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1913	1913	1913
5°	1916	1883	1895
10°	1897	1847	1834
15°	1871	1786	1739
20°	1837	1703	1623
25°	1801	1609	1511
30°	1754	1513	1368
35°	1708	1409	1242
40°	1661	1302	1098
45°	1606	1183	968
50°	1549	1063	840
55°	1490	934	717
60°	1421	800	591
65°	1342	663	533
70°	1247	536	484
75°	1127	474	442
80°	953	400	385
85°	667	270	294

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1606 cd/sqm

TEST NUMBER: P921508

CATALOG NUMBER: DFN2DIP-4P4F0-080D070US940-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.3	2.4
10°-20°	758.6	6.5
20°-30°	1065.0	9.2
30°-40°	1160.9	10.0
40°-50°	1067.0	9.2
50°-60°	838.0	7.2
60°-70°	545.4	4.7
70°-80°	280.8	2.4
80°-90°	77.3	0.7
90°-100°	122.2	1.1
100°-110°	388.1	3.3
110°-120°	664.2	5.7
120°-130°	873.6	7.5
130°-140°	980.5	8.5
140°-150°	961.5	8.3
150°-160°	806.6	7.0
160°-170°	534.9	4.6
170°-180°	187.0	1.6
0°-30°	2099.9	18.1
0°-40°	3260.8	28.1
0°-60°	5165.8	44.6
0°-90°	6069.3	52.4
90°-120°	1174.5	10.1
90°-150°	3990.1	34.4
90°-180°	5519.0	47.6
0°-180°	11587.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2948	2948	2948	2948	2948	
5°	2948	2935	2900	2924	2916	280
15°	2804	2775	2684	2634	2607	790
25°	2546	2460	2284	2175	2134	1171
35°	2193	2057	1822	1654	1595	1373
45°	1793	1614	1334	1144	1081	1385
55°	1363	1155	867	707	656	1218
65°	921	704	464	374	365	913
75°	491	304	214	195	192	519
85°	115	59	51	51	51	132
90°	2	21	58	55	56	11
95°	87	104	107	107	104	97
105°	358	363	367	370	370	378
115°	667	676	673	671	667	659
125°	970	984	980	974	972	866
135°	1254	1272	1276	1274	1269	969
145°	1522	1534	1544	1546	1539	951
155°	1741	1746	1751	1759	1754	801
165°	1894	1892	1892	1904	1896	534
175°	1970	1966	1962	1974	1964	187
180°	1974	1974	1974	1974	1974	

TEST NUMBER: P921508

CATALOG NUMBER: DFN2DIP-4P4F0-080D070US940-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2948.4	2948.4	2948.4	2948.4	2948.4
2.5°	2961.6	2948.4	2918.9	2945.8	2940.4
5°	2948.4	2935.1	2900.2	2924.3	2916.3
7.5°	2924.3	2908.4	2871.0	2881.6	2868.2
10°	2892.3	2873.6	2820.4	2812.2	2796.3
12.5°	2852.4	2828.3	2756.1	2740.2	2710.8
15°	2804.3	2774.8	2684.2	2633.6	2606.9
17.5°	2748.2	2705.4	2593.4	2534.8	2492.0
20°	2684.2	2630.7	2497.4	2430.9	2371.9
22.5°	2614.9	2553.4	2398.6	2308.0	2268.1
25°	2545.5	2460.1	2283.9	2174.7	2134.5
27.5°	2462.8	2371.9	2177.2	2051.8	1990.4
30°	2374.8	2273.1	2059.8	1923.9	1851.6
32.5°	2289.3	2166.5	1947.9	1787.7	1720.9
35°	2193.3	2057.2	1822.5	1654.4	1595.4
37.5°	2099.9	1953.0	1705.0	1520.7	1454.2
40°	2001.2	1841.2	1582.2	1392.8	1323.4
42.5°	1899.8	1729.1	1459.6	1262.0	1195.4
45°	1793.1	1614.2	1334.2	1144.5	1080.6
47.5°	1691.8	1502.4	1214.2	1024.5	965.9
50°	1579.6	1390.3	1096.7	912.4	856.6
52.5°	1470.1	1269.9	984.5	808.5	757.9
55°	1363.3	1155.3	867.1	707.1	656.5
57.5°	1254.1	1040.6	763.2	613.8	571.0
60°	1141.9	928.5	653.6	517.7	475.0
62.5°	1032.7	819.2	560.3	432.3	411.1
65°	920.6	704.3	464.2	373.7	365.4
67.5°	813.9	597.6	373.7	328.1	320.2
70°	701.8	493.7	309.4	282.8	272.1
72.5°	595.0	397.4	258.8	237.6	232.1
75°	490.9	304.1	213.5	194.7	192.3
77.5°	387.0	216.0	168.2	157.4	152.0
80°	290.7	154.9	128.0	117.4	117.4
82.5°	202.7	104.2	88.0	82.7	82.7
85°	114.7	58.6	50.6	50.6	50.6
87.5°	42.7	21.2	21.2	18.7	18.7
90°	1.8	21.4	58.3	54.8	56.5
92.5°	36.9	50.0	51.8	53.6	53.6
95°	86.9	103.5	106.6	106.6	103.5
97.5°	144.6	160.1	166.7	166.7	166.7
100°	211.2	225.0	229.7	229.7	227.9
102.5°	281.5	291.6	298.2	300.0	298.2
105°	358.3	363.0	366.6	369.6	369.6
107.5°	434.4	441.6	441.6	442.8	434.4
110°	508.3	517.8	517.8	517.8	513.0

TEST NUMBER: P921508

CATALOG NUMBER: DFN2DIP-4P4F0-080D070US940-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	588.0	598.2	596.4	591.6	588.0
115°	666.6	676.1	673.2	671.4	666.6
117.5°	744.5	757.6	749.3	744.5	739.8
120°	823.0	836.2	823.0	823.0	817.7
122.5°	894.5	911.1	902.9	898.0	894.5
125°	969.5	984.4	979.6	974.3	972.5
127.5°	1042.7	1061.1	1054.6	1047.5	1042.7
130°	1111.2	1132.6	1129.6	1126.1	1119.5
132.5°	1187.9	1204.6	1205.8	1197.5	1192.7
135°	1254.0	1272.4	1276.0	1274.2	1269.4
137.5°	1327.8	1342.6	1345.6	1344.4	1337.3
140°	1392.7	1407.6	1415.9	1415.9	1409.3
142.5°	1459.3	1474.2	1478.9	1480.7	1474.2
145°	1522.4	1534.3	1543.8	1545.6	1539.1
147.5°	1579.0	1593.8	1601.0	1603.9	1597.4
150°	1637.3	1647.3	1653.9	1659.3	1653.9
152.5°	1689.0	1699.2	1707.4	1714.0	1707.4
155°	1740.8	1745.5	1751.0	1759.3	1753.9
157.5°	1785.5	1789.0	1792.0	1803.9	1795.5
160°	1825.3	1828.9	1830.7	1840.8	1833.6
162.5°	1862.2	1862.2	1864.0	1875.3	1867.0
165°	1893.7	1891.9	1891.9	1903.9	1895.5
167.5°	1922.3	1917.0	1917.0	1928.9	1920.6
170°	1943.8	1939.0	1937.2	1949.1	1939.0
172.5°	1958.6	1953.8	1952.0	1964.0	1953.8
175°	1970.5	1965.8	1962.2	1974.1	1964.0
177.5°	1977.1	1972.3	1968.7	1978.9	1968.7
180°	1974.1	1974.1	1974.1	1974.1	1974.1

TEST NUMBER: P921508

CATALOG NUMBER: DFN2DIP-4P4F0-080D070US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.64	10.49	10.58	11.44	12.68	5.60	6.45	6.54	7.40	8.64
	3H	11.32	12.08	12.28	13.05	14.31	6.79	7.55	7.75	8.51	9.78
	4H	11.94	12.65	12.90	13.62	14.89	7.24	7.96	8.21	8.93	10.20
	6H	12.36	13.02	13.34	14.00	15.28	7.57	8.23	8.55	9.20	10.49
	8H	12.49	13.12	13.48	14.11	15.39	7.66	8.29	8.64	9.28	10.56
	12H	12.56	13.16	13.55	14.14	15.45	7.70	8.30	8.69	9.29	10.59
4H	2H	9.66	10.38	10.63	11.35	12.62	6.20	6.92	7.17	7.89	9.16
	3H	11.50	12.09	12.48	13.09	14.38	7.55	8.15	8.54	9.15	10.43
	4H	12.19	12.74	13.19	13.73	15.04	8.10	8.65	9.10	9.64	10.95
	6H	12.71	13.18	13.72	14.20	15.51	8.53	8.99	9.53	10.01	11.32
	8H	12.89	13.33	13.90	14.34	15.66	8.66	9.09	9.66	10.10	11.42
	12H	12.99	13.39	14.02	14.41	15.74	8.72	9.12	9.75	10.14	11.47
8H	4H	12.16	12.60	13.17	13.61	14.93	8.39	8.83	9.39	9.83	11.16
	6H	12.74	13.10	13.77	14.15	15.47	8.91	9.27	9.94	10.32	11.64
	8H	12.96	13.27	13.99	14.31	15.65	9.10	9.42	10.14	10.46	11.80
	12H	13.10	13.38	14.14	14.41	15.79	9.22	9.50	10.27	10.54	11.92
12H	4H	12.12	12.51	13.14	13.53	14.86	8.40	8.79	9.42	9.81	11.14
	6H	12.71	13.03	13.75	14.07	15.40	8.96	9.28	10.00	10.32	11.65
	8H	12.94	13.22	13.98	14.25	15.63	9.17	9.45	10.22	10.49	11.87