

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908026

Luminaire Tested: DFN2DIP-HX3F0-050D040US840-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908026
REPORT IS A COMBINATION OF REPORTS P899219 AND P896089
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-050D040US840-FLLFLL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8573.8 lumens
Efficiency: N/A
Efficacy: 115.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 74.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908026
CATALOG NUMBER: DFN2DIP-HX3F0-050D040US840-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P908026
 CATALOG NUMBER: DFN2DIP-HX3F0-050D040US840-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58		
1	100	95	91	88	93	89	86	82	77	75	72	66	65	63	56	55	54	49		
2	91	83	77	72	84	78	72	68	68	64	60	58	55	52	50	47	45	41		
3	83	73	66	60	77	69	62	57	60	55	50	52	48	44	44	41	39	35		
4	76	65	57	51	70	61	54	48	53	47	43	46	42	38	39	36	33	30		
5	70	58	50	43	65	54	47	41	48	42	37	41	37	33	35	32	29	26		
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	29	26	23		
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	26	23	20		
8	55	43	35	29	51	40	33	28	36	30	26	31	26	23	27	23	20	18		
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18	16		
10	48	36	28	24	45	34	27	23	30	25	21	27	22	19	23	19	17	15		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2276	2276	2276
5°	2278	2242	2258
10°	2259	2211	2226
15°	2225	2173	2177
20°	2179	2121	2127
25°	2133	2059	2069
30°	2076	2001	1996
35°	2022	1933	1919
40°	1956	1864	1845
45°	1889	1795	1770
50°	1817	1723	1683
55°	1740	1639	1602
60°	1654	1539	1510
65°	1560	1436	1401
70°	1440	1311	1284
75°	1275	1160	1173
80°	1075	967	966
85°	763	640	626

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1889 cd/sqm



TEST NUMBER: P908026

CATALOG NUMBER: DFN2DIP-HX3F0-050D040US840-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.9	2.2
10°-20°	520.3	6.1
20°-30°	764.6	8.9
30°-40°	888.1	10.4
40°-50°	887.0	10.3
50°-60°	773.4	9.0
60°-70°	571.7	6.7
70°-80°	323.5	3.8
80°-90°	89.0	1.0
90°-100°	79.1	0.9
100°-110°	251.2	2.9
110°-120°	429.8	5.0
120°-130°	565.3	6.6
130°-140°	634.5	7.4
140°-150°	622.2	7.3
150°-160°	522.0	6.1
160°-170°	346.2	4.0
170°-180°	121.0	1.4
0°-30°	1469.8	17.1
0°-40°	2357.9	27.5
0°-60°	4018.3	46.9
0°-90°	5002.5	58.3
90°-120°	760.1	8.9
90°-150°	2582.2	30.1
90°-180°	3571.0	41.7
0°-180°	8573.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1965	1965	1965	1965	1965	
5°	1965	1957	1936	1952	1948	187
15°	1870	1859	1834	1842	1833	527
25°	1693	1678	1646	1649	1646	779
35°	1460	1442	1411	1400	1390	912
45°	1188	1175	1147	1126	1118	917
55°	899	888	865	843	833	804
65°	606	595	576	559	550	600
75°	317	314	304	293	297	339
85°	77	76	74	68	66	86
90°	1	14	38	35	37	8
95°	56	67	69	69	67	63
105°	232	235	237	239	239	245
115°	431	438	436	434	431	427
125°	627	637	634	630	629	561
135°	812	823	826	825	822	627
145°	985	993	999	1000	996	616
155°	1126	1130	1133	1138	1135	519
165°	1226	1224	1224	1232	1227	346
175°	1275	1272	1270	1278	1271	121
180°	1278	1278	1278	1278	1278	



TEST NUMBER: P908026

CATALOG NUMBER: DFN2DIP-HX3F0-050D040US840-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1964.7	1964.7	1964.7	1964.7	1964.7
2.5°	1976.1	1966.7	1945.9	1964.7	1961.2
5°	1964.7	1957.3	1936.4	1951.5	1947.9
7.5°	1951.5	1940.3	1919.5	1934.7	1930.9
10°	1930.9	1917.6	1895.0	1910.0	1904.4
12.5°	1902.4	1891.2	1868.6	1877.9	1874.1
15°	1870.3	1859.1	1834.4	1842.1	1832.6
17.5°	1830.6	1819.4	1794.7	1804.1	1794.7
20°	1787.2	1775.9	1749.5	1755.0	1747.7
22.5°	1743.8	1726.8	1702.1	1702.1	1698.3
25°	1692.7	1677.7	1645.6	1649.2	1645.6
27.5°	1636.0	1622.8	1598.3	1592.7	1583.3
30°	1579.4	1564.3	1536.0	1530.4	1522.8
32.5°	1518.9	1507.7	1477.4	1466.0	1458.4
35°	1460.4	1441.6	1411.3	1399.9	1390.5
37.5°	1394.2	1377.3	1347.0	1333.7	1324.3
40°	1326.4	1311.1	1280.8	1263.9	1256.4
42.5°	1260.2	1245.0	1214.9	1195.8	1184.6
45°	1188.4	1175.2	1146.7	1126.1	1118.4
47.5°	1118.4	1105.2	1075.0	1054.1	1042.9
50°	1044.7	1035.3	1008.9	982.4	972.9
52.5°	972.9	959.7	935.2	914.4	901.2
55°	899.4	888.0	865.3	842.6	833.2
57.5°	825.6	816.2	791.5	768.9	761.2
60°	751.8	744.5	718.0	697.1	691.6
62.5°	680.1	666.9	648.0	629.1	621.6
65°	606.5	595.1	576.2	559.3	549.8
67.5°	531.0	521.4	504.5	491.3	483.6
70°	461.0	453.4	436.4	423.1	415.8
72.5°	389.3	381.6	372.2	359.0	353.4
75°	317.3	313.7	304.1	292.9	296.7
77.5°	253.2	245.5	241.8	236.1	230.6
80°	189.0	187.0	183.2	177.6	173.8
82.5°	128.5	128.5	126.6	119.1	119.1
85°	77.4	75.5	73.7	68.0	66.1
87.5°	34.0	30.3	26.5	20.8	18.9
90°	1.1	13.8	37.8	35.4	36.6
92.5°	23.8	32.3	33.5	34.6	34.6
95°	56.2	67.1	69.0	69.0	67.1
97.5°	93.6	103.6	107.9	107.9	107.9
100°	136.7	145.6	148.7	148.7	147.5
102.5°	182.2	188.7	193.0	194.1	193.0
105°	231.9	234.9	237.2	239.1	239.1
107.5°	281.1	285.8	285.8	286.5	281.1
110°	328.9	335.1	335.1	335.1	332.0



TEST NUMBER: P908026

CATALOG NUMBER: DFN2DIP-HX3F0-050D040US840-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	380.5	387.1	385.9	382.8	380.5
115°	431.3	437.6	435.6	434.4	431.3
117.5°	481.8	490.3	484.9	481.8	478.8
120°	532.7	541.1	532.7	532.7	529.2
122.5°	578.9	589.7	584.3	581.2	578.9
125°	627.4	637.0	634.0	630.5	629.3
127.5°	674.8	686.7	682.5	677.8	674.8
130°	719.0	733.0	731.0	728.7	724.5
132.5°	768.7	779.5	780.3	774.9	771.8
135°	811.5	823.4	825.8	824.6	821.5
137.5°	859.3	868.9	870.8	870.0	865.5
140°	901.2	910.9	916.3	916.3	912.0
142.5°	944.4	954.0	957.0	958.3	954.0
145°	985.2	992.9	999.1	1000.3	996.0
147.5°	1021.8	1031.4	1036.0	1037.9	1033.7
150°	1059.6	1066.1	1070.4	1073.8	1070.4
152.5°	1093.1	1099.5	1105.0	1109.2	1105.0
155°	1126.5	1129.6	1133.1	1138.5	1135.0
157.5°	1155.5	1157.7	1159.6	1167.4	1162.0
160°	1181.2	1183.6	1184.7	1191.2	1186.6
162.5°	1205.1	1205.1	1206.3	1213.6	1208.2
165°	1225.6	1224.4	1224.4	1232.0	1226.7
167.5°	1244.1	1240.5	1240.5	1248.3	1242.8
170°	1257.9	1254.8	1253.6	1261.3	1254.8
172.5°	1267.5	1264.5	1263.2	1271.0	1264.5
175°	1275.3	1272.1	1269.8	1277.5	1271.0
177.5°	1279.5	1276.4	1274.0	1280.6	1274.0
180°	1277.5	1277.5	1277.5	1277.5	1277.5



TEST NUMBER: P908026
 CATALOG NUMBER: DFN2DIP-HX3F0-050D040US840-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.82	11.76	11.70	12.67	13.81	10.39	11.33	11.27	12.24	13.38
	3H	12.48	13.33	13.37	14.24	15.41	12.01	12.86	12.90	13.77	14.94
	4H	13.07	13.87	13.98	14.78	15.96	12.60	13.40	13.51	14.31	15.50
	6H	13.46	14.20	14.39	15.12	16.32	12.99	13.73	13.91	14.65	15.85
	8H	13.57	14.27	14.50	15.21	16.40	13.10	13.80	14.03	14.74	15.94
	12H	13.62	14.28	14.55	15.22	16.44	13.14	13.81	14.08	14.74	15.96
4H	2H	11.29	12.09	12.20	13.01	14.19	10.95	11.75	11.86	12.66	13.85
	3H	13.15	13.82	14.08	14.77	15.97	12.76	13.43	13.69	14.38	15.58
	4H	13.87	14.47	14.80	15.42	16.64	13.46	14.07	14.40	15.02	16.24
	6H	14.38	14.90	15.33	15.87	17.09	13.97	14.50	14.92	15.47	16.69
	8H	14.53	15.02	15.48	15.98	17.21	14.12	14.61	15.07	15.57	16.81
	12H	14.60	15.04	15.57	16.02	17.26	14.18	14.63	15.15	15.60	16.85
8H	4H	14.07	14.56	15.02	15.52	16.75	13.71	14.20	14.66	15.16	16.40
	6H	14.69	15.10	15.67	16.10	17.33	14.33	14.74	15.31	15.74	16.98
	8H	14.91	15.27	15.89	16.26	17.51	14.54	14.90	15.53	15.89	17.15
	12H	15.04	15.35	16.03	16.34	17.64	14.66	14.97	15.65	15.96	17.26
12H	4H	14.05	14.50	15.03	15.48	16.72	13.70	14.15	14.68	15.13	16.37
	6H	14.72	15.08	15.71	16.07	17.32	14.37	14.73	15.36	15.72	16.98
	8H	14.96	15.28	15.95	16.26	17.56	14.61	14.92	15.60	15.91	17.21