

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924136

Luminaire Tested: DFN2DIP-4P4F0-040D060US950-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P924136  
REPORT IS A COMBINATION OF REPORTS P899118 AND P895967  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-4P4F0-040D060US950-RLLFLL  
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8309.4 lumens  
Efficiency: N/A  
Efficacy: 93.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 89.1  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9968  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P924136  
CATALOG NUMBER: DFN2DIP-4P4F0-040D060US950-RLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P924136  
 CATALOG NUMBER: DFN2DIP-4P4F0-040D060US950-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39			
1	96	92	88	85	87	83	80	78	68	66	64	54	53	51	41	40	40	34			
2	87	80	75	70	79	73	68	64	60	57	54	48	46	44	37	35	34	29			
3	80	71	64	58	73	65	59	54	53	49	46	43	40	37	33	31	29	25			
4	73	63	55	50	66	58	51	46	48	43	39	38	35	32	30	27	26	22			
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	24	22	19			
6	62	51	43	37	56	46	40	35	39	33	30	31	28	25	25	22	20	17			
7	57	46	38	33	52	42	35	30	35	30	26	29	25	22	22	20	18	15			
8	53	41	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16	14			
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15	12			
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1023	1023	1023
5°	1025	1007	1014
10°	1015	988	981
15°	1001	955	931
20°	983	911	868
25°	964	861	808
30°	938	809	732
35°	914	754	664
40°	888	696	587
45°	859	633	518
50°	829	569	449
55°	797	500	384
60°	760	428	316
65°	718	355	285
70°	667	287	259
75°	603	253	236
80°	510	214	206
85°	356	144	158

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 1369 cd/sqm



TEST NUMBER: P924136

CATALOG NUMBER: DFN2DIP-4P4F0-040D060US950-RLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	147.8	1.8
10°-20°	405.8	4.9
20°-30°	569.7	6.9
30°-40°	621.0	7.5
40°-50°	570.8	6.9
50°-60°	448.2	5.4
60°-70°	291.8	3.5
70°-80°	150.2	1.8
80°-90°	43.5	0.5
90°-100°	112.0	1.3
100°-110°	355.9	4.3
110°-120°	609.1	7.3
120°-130°	801.1	9.6
130°-140°	899.2	10.8
140°-150°	881.7	10.6
150°-160°	739.6	8.9
160°-170°	490.5	5.9
170°-180°	171.4	2.1
0°-30°	1123.3	13.5
0°-40°	1744.3	21.0
0°-60°	2763.3	33.3
0°-90°	3248.8	39.1
90°-120°	1077.0	13.0
90°-150°	3659.0	44.0
90°-180°	5061.0	60.9
0°-180°	8309.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1577	1577	1577	1577	1577	
5°	1577	1570	1551	1564	1560	150
15°	1500	1484	1436	1409	1395	423
25°	1362	1316	1222	1163	1142	626
35°	1173	1100	975	885	853	734
45°	959	864	714	612	578	741
55°	729	618	464	378	351	652
65°	492	377	248	200	196	488
75°	262	163	114	104	103	278
85°	61	31	27	27	27	70
90°	2	20	54	50	52	8
95°	80	95	98	98	95	89
105°	329	333	336	339	339	347
115°	611	620	617	616	611	605
125°	889	903	898	893	892	794
135°	1150	1167	1170	1168	1164	889
145°	1396	1407	1416	1417	1411	872
155°	1596	1601	1606	1613	1608	735
165°	1737	1735	1735	1746	1738	490
175°	1807	1803	1799	1810	1801	172
180°	1810	1810	1810	1810	1810	



TEST NUMBER: P924136

CATALOG NUMBER: DFN2DIP-4P4F0-040D060US950-RLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1577.2	1577.2	1577.2	1577.2	1577.2
2.5°	1584.3	1577.2	1561.4	1575.8	1572.9
5°	1577.2	1570.0	1551.4	1564.3	1560.1
7.5°	1564.3	1555.8	1535.8	1541.4	1534.3
10°	1547.2	1537.2	1508.7	1504.3	1495.9
12.5°	1525.8	1512.9	1474.3	1465.8	1450.1
15°	1500.1	1484.3	1435.9	1408.8	1394.6
17.5°	1470.1	1447.2	1387.2	1355.9	1333.0
20°	1435.9	1407.2	1335.9	1300.3	1268.8
22.5°	1398.8	1365.9	1283.0	1234.6	1213.3
25°	1361.6	1315.9	1221.7	1163.3	1141.7
27.5°	1317.5	1268.8	1164.6	1097.6	1064.7
30°	1270.3	1216.0	1101.8	1029.1	990.5
32.5°	1224.6	1158.9	1042.0	956.3	920.5
35°	1173.3	1100.4	974.9	884.9	853.4
37.5°	1123.3	1044.7	912.0	813.5	777.9
40°	1070.5	984.9	846.4	745.1	708.0
42.5°	1016.2	924.9	780.8	675.1	639.5
45°	959.2	863.5	713.7	612.3	578.0
47.5°	905.0	803.6	649.5	548.1	516.7
50°	845.0	743.6	586.6	488.1	458.2
52.5°	786.4	679.3	526.7	432.4	405.4
55°	729.3	618.0	463.8	378.3	351.2
57.5°	670.9	556.7	408.2	328.3	305.5
60°	610.8	496.7	349.6	276.9	254.1
62.5°	552.5	438.3	299.7	231.2	219.9
65°	492.5	376.7	248.3	199.9	195.5
67.5°	435.4	319.7	199.9	175.5	171.2
70°	375.4	264.1	165.5	151.3	145.5
72.5°	318.3	212.6	138.4	127.1	124.2
75°	262.5	162.7	114.2	104.2	102.8
77.5°	207.0	115.5	90.0	84.2	81.3
80°	155.5	82.8	68.4	62.9	62.9
82.5°	108.5	55.7	47.1	44.2	44.2
85°	61.3	31.4	27.1	27.1	27.1
87.5°	22.9	11.4	11.4	10.0	10.0
90°	1.6	19.7	53.5	50.2	51.8
92.5°	33.9	45.9	47.5	49.1	49.1
95°	79.7	94.9	97.7	97.7	94.9
97.5°	132.6	146.8	152.8	152.8	152.8
100°	193.8	206.3	210.6	210.6	209.0
102.5°	258.2	267.4	273.4	275.0	273.4
105°	328.6	332.9	336.2	339.0	339.0
107.5°	398.4	405.0	405.0	406.0	398.4
110°	466.1	474.8	474.8	474.8	470.4



TEST NUMBER: P924136

CATALOG NUMBER: DFN2DIP-4P4F0-040D060US950-RLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	539.2	548.5	546.8	542.4	539.2
115°	611.2	620.0	617.2	615.6	611.2
117.5°	682.8	694.8	687.1	682.8	678.4
120°	754.8	766.8	754.8	754.8	749.8
122.5°	820.2	835.5	827.9	823.6	820.2
125°	889.0	902.7	898.3	893.4	891.8
127.5°	956.2	973.1	967.1	960.6	956.2
130°	1019.0	1038.6	1035.9	1032.6	1026.6
132.5°	1089.4	1104.6	1105.7	1098.1	1093.7
135°	1150.0	1166.8	1170.1	1168.5	1164.1
137.5°	1217.6	1231.2	1234.0	1232.9	1226.4
140°	1277.1	1290.8	1298.4	1298.4	1292.4
142.5°	1338.2	1351.8	1356.2	1357.8	1351.8
145°	1396.1	1407.0	1415.7	1417.4	1411.3
147.5°	1447.9	1461.5	1468.1	1470.8	1464.8
150°	1501.4	1510.7	1516.7	1521.5	1516.7
152.5°	1548.8	1558.2	1565.8	1571.8	1565.8
155°	1596.3	1600.7	1605.6	1613.3	1608.3
157.5°	1637.3	1640.6	1643.3	1654.2	1646.6
160°	1673.9	1677.1	1678.8	1688.0	1681.5
162.5°	1707.7	1707.7	1709.3	1719.7	1712.0
165°	1736.6	1734.9	1734.9	1745.9	1738.3
167.5°	1762.8	1757.9	1757.9	1768.8	1761.2
170°	1782.5	1778.1	1776.4	1787.3	1778.1
172.5°	1796.1	1791.7	1790.1	1801.0	1791.7
175°	1807.0	1802.7	1799.3	1810.3	1801.0
177.5°	1813.0	1808.7	1805.3	1814.6	1805.3
180°	1810.3	1810.3	1810.3	1810.3	1810.3



TEST NUMBER: P924136  
 CATALOG NUMBER: DFN2DIP-4P4F0-040D060US950-RLFL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.13	6.88	7.18	7.93	9.35	2.09	2.84	3.14	3.89	5.31
	3H	7.81	8.48	8.87	9.54	10.98	3.28	3.95	4.34	5.01	6.45
	4H	8.42	9.05	9.49	10.11	11.56	3.72	4.36	4.80	5.42	6.87
	6H	8.84	9.42	9.92	10.49	11.95	4.04	4.63	5.12	5.69	7.15
	8H	8.97	9.52	10.05	10.60	12.06	4.13	4.69	5.22	5.77	7.22
	12H	9.03	9.56	10.12	10.63	12.11	4.17	4.70	5.26	5.78	7.25
4H	2H	6.14	6.78	7.22	7.84	9.28	2.68	3.32	3.76	4.38	5.82
	3H	7.97	8.50	9.06	9.59	11.05	4.03	4.55	5.11	5.64	7.10
	4H	8.66	9.15	9.75	10.23	11.71	4.57	5.06	5.66	6.14	7.62
	6H	9.18	9.59	10.28	10.70	12.17	4.99	5.40	6.09	6.51	7.98
	8H	9.36	9.74	10.45	10.84	12.33	5.12	5.51	6.22	6.60	8.09
	12H	9.45	9.80	10.57	10.91	12.40	5.18	5.53	6.30	6.64	8.13
8H	4H	8.62	9.01	9.72	10.11	11.60	4.85	5.24	5.95	6.33	7.82
	6H	9.19	9.51	10.31	10.65	12.14	5.37	5.69	6.49	6.83	8.31
	8H	9.41	9.69	10.54	10.81	12.32	5.56	5.84	6.69	6.96	8.47
	12H	9.55	9.80	10.68	10.91	12.46	5.68	5.92	6.81	7.04	8.58
12H	4H	8.57	8.92	9.69	10.03	11.53	4.85	5.20	5.97	6.31	7.81
	6H	9.17	9.45	10.30	10.57	12.07	5.42	5.70	6.55	6.82	8.32
	8H	9.39	9.64	10.52	10.75	12.30	5.63	5.87	6.76	6.99	8.53