

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924149

Luminaire Tested: DFN2DIP-4P4F0-050D030US950-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924149
REPORT IS A COMBINATION OF REPORTS P900604 AND P897523
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-050D030US950-RLLONL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6887.9 lumens
Efficiency: N/A
Efficacy: 94.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 73.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924149
CATALOG NUMBER: DFN2DIP-4P4F0-050D030US950-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P924149

CATALOG NUMBER: DFN2DIP-4P4F0-050D030US950-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59			59
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	55	51			51
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	51	49	48	43			43
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	43	41	37			37
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36	33			33
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	34	32	29			29
6	66	54	46	40	61	51	44	38	45	39	35	40	35	32	35	31	28	26			26
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25	23			23
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23	21			21
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	23	21	19			19
10	50	38	31	26	46	36	29	25	32	27	23	29	24	21	25	22	19	17			17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1279	1279	1279
5°	1281	1259	1267
10°	1268	1235	1226
15°	1251	1194	1163
20°	1228	1138	1085
25°	1205	1076	1010
30°	1173	1011	914
35°	1142	942	831
40°	1110	871	734
45°	1074	791	647
50°	1036	711	562
55°	996	625	480
60°	950	535	395
65°	898	443	356
70°	834	358	323
75°	754	317	295
80°	638	267	257
85°	446	181	197

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1074 cd/sqm



TEST NUMBER: P924149

CATALOG NUMBER: DFN2DIP-4P4F0-050D030US950-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.8	2.7
10°-20°	507.2	7.4
20°-30°	712.1	10.3
30°-40°	776.3	11.3
40°-50°	713.5	10.4
50°-60°	560.3	8.1
60°-70°	364.7	5.3
70°-80°	187.7	2.7
80°-90°	49.6	0.7
90°-100°	31.9	0.5
100°-110°	118.7	1.7
110°-120°	314.9	4.6
120°-130°	522.3	7.6
130°-140°	554.8	8.1
140°-150°	515.6	7.5
150°-160°	414.5	6.0
160°-170°	267.1	3.9
170°-180°	91.9	1.3
0°-30°	1404.1	20.4
0°-40°	2180.4	31.7
0°-60°	3454.1	50.1
0°-90°	4056.2	58.9
90°-120°	465.5	6.8
90°-150°	2058.1	29.9
90°-180°	2832.0	41.1
0°-180°	6887.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1971	1971	1971	1971	1971	
5°	1971	1963	1939	1955	1950	187
15°	1875	1855	1795	1761	1743	528
25°	1702	1645	1527	1454	1427	783
35°	1467	1376	1219	1106	1067	918
45°	1199	1079	892	765	722	926
55°	912	772	580	473	439	815
65°	616	471	310	250	244	610
75°	328	203	143	130	128	347
85°	77	39	34	34	34	88
90°	1	8	14	18	19	7
95°	45	22	27	31	30	54
105°	212	233	43	50	53	227
115°	402	414	431	108	57	396
125°	568	577	591	596	598	507
135°	703	714	721	728	726	543
145°	816	815	827	832	828	510
155°	898	892	900	904	899	414
165°	946	942	944	949	944	267
175°	968	963	964	969	962	92
180°	966	966	966	966	966	



TEST NUMBER: P924149

CATALOG NUMBER: DFN2DIP-4P4F0-050D030US950-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1971.4	1971.4	1971.4	1971.4	1971.4
2.5°	1980.3	1971.4	1951.8	1969.7	1966.1
5°	1971.4	1962.6	1939.3	1955.3	1950.1
7.5°	1955.3	1944.7	1919.7	1926.8	1917.8
10°	1933.9	1921.5	1885.9	1880.4	1869.7
12.5°	1907.2	1891.2	1842.9	1832.3	1812.6
15°	1875.1	1855.4	1794.9	1761.0	1743.1
17.5°	1837.6	1809.1	1734.1	1694.9	1666.3
20°	1794.9	1759.1	1669.9	1625.4	1586.0
22.5°	1748.5	1707.4	1603.9	1543.3	1516.6
25°	1702.0	1644.9	1527.2	1454.1	1427.2
27.5°	1646.8	1586.0	1455.8	1371.9	1330.9
30°	1587.9	1520.0	1377.3	1286.4	1238.1
32.5°	1530.8	1448.6	1302.5	1195.4	1150.7
35°	1466.6	1375.6	1218.6	1106.2	1066.9
37.5°	1404.1	1305.9	1140.1	1016.9	972.4
40°	1338.1	1231.1	1057.9	931.3	884.9
42.5°	1270.3	1156.2	975.9	843.8	799.4
45°	1199.0	1079.4	892.1	765.3	722.5
47.5°	1131.2	1004.6	811.9	685.1	645.9
50°	1056.3	929.6	733.3	610.1	572.8
52.5°	983.0	849.2	658.4	540.6	506.8
55°	911.6	772.5	579.7	472.8	438.9
57.5°	838.6	695.8	510.3	410.4	381.8
60°	763.6	620.9	437.0	346.2	317.6
62.5°	690.5	547.8	374.6	289.1	274.8
65°	615.5	471.0	310.4	249.9	244.4
67.5°	544.2	399.6	249.9	219.4	214.1
70°	469.3	330.1	206.9	189.1	181.9
72.5°	397.9	265.8	173.1	158.8	155.2
75°	328.3	203.3	142.7	130.2	128.5
77.5°	258.7	144.4	112.5	105.2	101.6
80°	194.4	103.5	85.6	78.5	78.5
82.5°	135.6	69.6	58.9	55.2	55.2
85°	76.7	39.2	33.9	33.9	33.9
87.5°	28.6	14.2	14.2	12.5	12.5
90°	0.7	8.4	13.9	17.6	18.8
92.5°	17.6	14.7	16.8	18.2	18.8
95°	45.4	22.3	27.2	30.8	30.1
97.5°	81.8	24.5	35.6	37.8	38.4
100°	123.7	28.0	39.9	45.4	46.8
102.5°	169.8	168.5	41.2	48.8	51.0
105°	212.5	233.4	42.6	50.3	53.1
107.5°	262.1	279.5	44.1	51.7	54.6
110°	309.7	324.3	122.3	52.5	55.2



TEST NUMBER: P924149

CATALOG NUMBER: DFN2DIP-4P4F0-050D030US950-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	354.4	366.9	355.1	53.8	55.9
115°	401.8	413.7	431.2	107.6	57.3
117.5°	443.1	457.1	469.0	369.0	185.9
120°	489.2	499.7	512.3	520.7	426.3
122.5°	528.3	539.6	553.6	557.7	558.5
125°	568.2	577.3	590.6	595.5	597.6
127.5°	604.5	614.3	624.9	631.8	632.5
130°	638.8	650.1	657.7	665.3	664.7
132.5°	673.7	682.9	690.5	696.8	696.1
135°	703.1	714.4	720.6	727.6	726.2
137.5°	733.8	742.2	749.3	756.2	754.1
140°	763.9	769.5	777.1	783.4	780.0
142.5°	789.1	794.0	803.1	808.6	805.2
145°	815.7	814.9	826.8	831.7	828.2
147.5°	838.7	836.6	848.5	851.9	849.2
150°	861.1	856.2	867.4	871.5	868.0
152.5°	879.9	874.3	884.8	889.0	884.2
155°	898.1	891.9	900.2	904.4	898.9
157.5°	912.8	907.3	913.6	918.4	912.8
160°	925.4	921.2	925.4	929.6	924.6
162.5°	936.5	932.3	935.9	940.7	934.4
165°	946.3	942.2	944.3	949.1	944.3
167.5°	954.0	949.8	951.9	956.9	950.6
170°	960.3	956.1	957.5	962.4	956.1
172.5°	964.5	960.3	961.7	966.6	960.3
175°	967.9	963.1	964.5	969.4	962.4
177.5°	969.4	964.5	965.3	970.1	963.8
180°	965.9	965.9	965.9	965.9	965.9



TEST NUMBER: P924149
 CATALOG NUMBER: DFN2DIP-4P4F0-050D030US950-RLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.81	9.72	9.70	10.62	11.76	4.77	5.68	5.66	6.58	7.72
	3H	10.50	11.31	11.40	12.22	13.39	5.97	6.78	6.87	7.69	8.86
	4H	11.12	11.89	12.03	12.80	13.98	6.42	7.19	7.34	8.11	9.28
	6H	11.55	12.25	12.47	13.18	14.36	6.75	7.46	7.67	8.38	9.57
	8H	11.68	12.35	12.61	13.29	14.48	6.84	7.52	7.78	8.45	9.64
	12H	11.75	12.39	12.68	13.32	14.53	6.89	7.53	7.83	8.46	9.67
4H	2H	8.84	9.61	9.76	10.52	11.70	5.38	6.15	6.30	7.06	8.24
	3H	10.68	11.32	11.61	12.27	13.46	6.74	7.38	7.67	8.32	9.52
	4H	11.38	11.96	12.32	12.90	14.12	7.29	7.87	8.23	8.81	10.03
	6H	11.91	12.41	12.86	13.37	14.59	7.72	8.22	8.67	9.18	10.40
	8H	12.09	12.55	13.04	13.51	14.74	7.85	8.32	8.80	9.27	10.50
	12H	12.19	12.61	13.16	13.59	14.82	7.92	8.34	8.89	9.32	10.55
8H	4H	11.36	11.82	12.31	12.78	14.01	7.58	8.05	8.54	9.01	10.24
	6H	11.93	12.32	12.91	13.32	14.55	8.11	8.49	9.08	9.49	10.72
	8H	12.15	12.49	13.14	13.48	14.73	8.30	8.64	9.29	9.63	10.88
	12H	12.30	12.60	13.29	13.58	14.88	8.42	8.72	9.41	9.70	11.00
12H	4H	11.31	11.73	12.28	12.71	13.94	7.59	8.01	8.56	8.99	10.22
	6H	11.91	12.25	12.90	13.24	14.48	8.16	8.50	9.14	9.49	10.73
	8H	12.14	12.44	13.13	13.42	14.71	8.37	8.67	9.36	9.65	10.95