

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908038

Luminaire Tested: DFN2DIP-HX3F0-050D070US840-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908038
REPORT IS A COMBINATION OF REPORTS P899261 AND P896089
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-050D070US840-FLLFLL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11255.0 lumens
Efficiency: N/A
Efficacy: 114.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 98.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908038
CATALOG NUMBER: DFN2DIP-HX3F0-050D070US840-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P908038

CATALOG NUMBER: DFN2DIP-HX3F0-050D070US840-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44				44
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43	37				37
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36	31				31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	27				27
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	31	29	27	23				23
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	28	25	23	20				20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	17				17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15				15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14				14
9	49	37	30	25	45	35	28	23	29	24	20	24	20	18	20	17	15	12				12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11				11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2276	2276	2276
5°	2278	2242	2258
10°	2259	2211	2226
15°	2225	2173	2177
20°	2179	2121	2127
25°	2133	2059	2069
30°	2076	2001	1996
35°	2022	1933	1919
40°	1956	1864	1845
45°	1889	1795	1770
50°	1817	1723	1683
55°	1740	1639	1602
60°	1654	1539	1510
65°	1560	1436	1401
70°	1440	1311	1284
75°	1275	1160	1173
80°	1075	967	966
85°	763	640	626

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 2103 cd/sqm



TEST NUMBER: P908038

CATALOG NUMBER: DFN2DIP-HX3F0-050D070US840-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.9	1.6
10°-20°	520.3	4.6
20°-30°	764.6	6.8
30°-40°	888.1	7.9
40°-50°	887.0	7.9
50°-60°	773.4	6.9
60°-70°	571.7	5.1
70°-80°	323.5	2.9
80°-90°	91.7	0.8
90°-100°	138.3	1.2
100°-110°	439.6	3.9
110°-120°	752.2	6.7
120°-130°	989.3	8.8
130°-140°	1110.5	9.9
140°-150°	1088.9	9.7
150°-160°	913.5	8.1
160°-170°	605.8	5.4
170°-180°	211.7	1.9
0°-30°	1469.8	13.1
0°-40°	2357.9	20.9
0°-60°	4018.3	35.7
0°-90°	5005.2	44.5
90°-120°	1330.1	11.8
90°-150°	4518.8	40.1
90°-180°	6250.0	55.5
0°-180°	11255.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1965	1965	1965	1965	1965	
5°	1965	1957	1936	1952	1948	187
15°	1870	1859	1834	1842	1833	527
25°	1693	1678	1646	1649	1646	779
35°	1460	1442	1411	1400	1390	912
45°	1188	1175	1147	1126	1118	917
55°	899	888	865	843	833	804
65°	606	595	576	559	550	600
75°	317	314	304	293	297	339
85°	77	76	74	68	66	86
90°	2	24	66	62	64	11
95°	98	117	121	121	117	109
105°	406	411	415	419	419	428
115°	755	766	762	760	755	747
125°	1098	1115	1109	1103	1101	981
135°	1420	1441	1445	1443	1438	1098
145°	1724	1738	1748	1750	1743	1077
155°	1972	1977	1983	1992	1986	907
165°	2145	2143	2143	2156	2147	605
175°	2232	2226	2222	2236	2224	212
180°	2236	2236	2236	2236	2236	



TEST NUMBER: P908038

CATALOG NUMBER: DFN2DIP-HX3F0-050D070US840-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1964.7	1964.7	1964.7	1964.7	1964.7
2.5°	1976.1	1966.7	1945.9	1964.7	1961.2
5°	1964.7	1957.3	1936.4	1951.5	1947.9
7.5°	1951.5	1940.3	1919.5	1934.7	1930.9
10°	1930.9	1917.6	1895.0	1910.0	1904.4
12.5°	1902.4	1891.2	1868.6	1877.9	1874.1
15°	1870.3	1859.1	1834.4	1842.1	1832.6
17.5°	1830.6	1819.4	1794.7	1804.1	1794.7
20°	1787.2	1775.9	1749.5	1755.0	1747.7
22.5°	1743.8	1726.8	1702.1	1702.1	1698.3
25°	1692.7	1677.7	1645.6	1649.2	1645.6
27.5°	1636.0	1622.8	1598.3	1592.7	1583.3
30°	1579.4	1564.3	1536.0	1530.4	1522.8
32.5°	1518.9	1507.7	1477.4	1466.0	1458.4
35°	1460.4	1441.6	1411.3	1399.9	1390.5
37.5°	1394.2	1377.3	1347.0	1333.7	1324.3
40°	1326.4	1311.1	1280.8	1263.9	1256.4
42.5°	1260.2	1245.0	1214.9	1195.8	1184.6
45°	1188.4	1175.2	1146.7	1126.1	1118.4
47.5°	1118.4	1105.2	1075.0	1054.1	1042.9
50°	1044.7	1035.3	1008.9	982.4	972.9
52.5°	972.9	959.7	935.2	914.4	901.2
55°	899.4	888.0	865.3	842.6	833.2
57.5°	825.6	816.2	791.5	768.9	761.2
60°	751.8	744.5	718.0	697.1	691.6
62.5°	680.1	666.9	648.0	629.1	621.6
65°	606.5	595.1	576.2	559.3	549.8
67.5°	531.0	521.4	504.5	491.3	483.6
70°	461.0	453.4	436.4	423.1	415.8
72.5°	389.3	381.6	372.2	359.0	353.4
75°	317.3	313.7	304.1	292.9	296.7
77.5°	253.2	245.5	241.8	236.1	230.6
80°	189.0	187.0	183.2	177.6	173.8
82.5°	128.5	128.5	126.6	119.1	119.1
85°	77.4	75.5	73.7	68.0	66.1
87.5°	34.0	30.3	26.5	20.8	18.9
90°	2.0	24.2	66.0	62.0	64.0
92.5°	41.8	56.7	58.7	60.7	60.7
95°	98.4	117.2	120.7	120.7	117.2
97.5°	163.8	181.3	188.7	188.7	188.7
100°	239.2	254.8	260.1	260.1	258.1
102.5°	318.8	330.2	337.7	339.7	337.7
105°	405.8	411.1	415.2	418.6	418.6
107.5°	492.0	500.1	500.1	501.5	492.0
110°	575.6	586.4	586.4	586.4	581.0



TEST NUMBER: P908038

CATALOG NUMBER: DFN2DIP-HX3F0-050D070US840-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	665.9	677.4	675.4	669.9	665.9
115°	754.9	765.7	762.3	760.3	754.9
117.5°	843.1	858.0	848.6	843.1	837.8
120°	932.1	947.0	932.1	932.1	926.0
122.5°	1013.0	1031.9	1022.5	1017.0	1013.0
125°	1097.9	1114.8	1109.4	1103.4	1101.4
127.5°	1180.8	1201.7	1194.4	1186.3	1180.8
130°	1258.4	1282.6	1279.3	1275.3	1267.8
132.5°	1345.3	1364.2	1365.5	1356.1	1350.7
135°	1420.2	1441.0	1445.1	1443.0	1437.6
137.5°	1503.7	1520.6	1523.9	1522.6	1514.5
140°	1577.2	1594.1	1603.5	1603.5	1596.1
142.5°	1652.6	1669.5	1674.9	1676.9	1669.5
145°	1724.1	1737.6	1748.4	1750.4	1743.0
147.5°	1788.2	1805.0	1813.1	1816.4	1809.1
150°	1854.2	1865.6	1873.1	1879.2	1873.1
152.5°	1912.8	1924.3	1933.7	1941.2	1933.7
155°	1971.5	1976.8	1983.0	1992.4	1986.3
157.5°	2022.1	2026.1	2029.4	2043.0	2033.5
160°	2067.2	2071.2	2073.3	2084.7	2076.6
162.5°	2109.0	2109.0	2111.0	2123.7	2114.4
165°	2144.7	2142.6	2142.6	2156.2	2146.7
167.5°	2177.1	2171.0	2171.0	2184.4	2175.0
170°	2201.3	2196.0	2193.9	2207.4	2196.0
172.5°	2218.2	2212.7	2210.7	2224.2	2212.7
175°	2231.6	2226.2	2222.2	2235.6	2224.2
177.5°	2239.1	2233.6	2229.6	2241.1	2229.6
180°	2235.6	2235.6	2235.6	2235.6	2235.6



TEST NUMBER: P908038
 CATALOG NUMBER: DFN2DIP-HX3F0-050D070US840-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.55	10.36	10.55	11.38	12.73	9.12	9.93	10.12	10.95	12.30
	3H	11.20	11.93	12.21	12.95	14.32	10.73	11.46	11.74	12.48	13.85
	4H	11.78	12.47	12.81	13.50	14.87	11.31	12.00	12.34	13.03	14.40
	6H	12.17	12.81	13.21	13.84	15.23	11.70	12.34	12.74	13.37	14.76
	8H	12.27	12.88	13.31	13.92	15.31	11.80	12.41	12.84	13.45	14.84
	12H	12.31	12.89	13.36	13.93	15.34	11.84	12.42	12.89	13.46	14.86
4H	2H	10.00	10.69	11.04	11.72	13.10	9.66	10.35	10.69	11.38	12.75
	3H	11.86	12.43	12.90	13.49	14.88	11.47	12.04	12.51	13.10	14.49
	4H	12.56	13.09	13.61	14.14	15.55	12.16	12.69	13.21	13.73	15.15
	6H	13.07	13.52	14.12	14.59	16.00	12.66	13.12	13.72	14.19	15.59
	8H	13.21	13.64	14.27	14.70	16.12	12.80	13.23	13.86	14.29	15.71
	12H	13.28	13.66	14.36	14.74	16.17	12.86	13.25	13.94	14.32	15.75
8H	4H	12.75	13.18	13.81	14.24	15.66	12.39	12.82	13.45	13.88	15.30
	6H	13.37	13.72	14.45	14.83	16.25	13.01	13.36	14.09	14.47	15.89
	8H	13.59	13.89	14.68	14.98	16.42	13.22	13.53	14.31	14.62	16.06
	12H	13.71	13.98	14.80	15.06	16.54	13.33	13.60	14.42	14.68	16.16
12H	4H	12.73	13.12	13.81	14.19	15.62	12.38	12.77	13.46	13.84	15.27
	6H	13.40	13.71	14.49	14.79	16.23	13.05	13.36	14.14	14.45	15.89
	8H	13.63	13.90	14.73	14.99	16.47	13.28	13.55	14.37	14.63	16.11