

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924203

Luminaire Tested: DFN2DIP-4P4F0-070D050US950-FLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P924203  
REPORT IS A COMBINATION OF REPORTS P900631 AND P897523  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-4P4F0-070D050US950-FLLONL  
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11333.6 lumens  
Efficiency: N/A  
Efficacy: 99.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 114.5  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9789  
Total Harmonic Distortion (THDi): 0.074  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P924203  
CATALOG NUMBER: DFN2DIP-4P4F0-070D050US950-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P924203  
 CATALOG NUMBER: DFN2DIP-4P4F0-070D050US950-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58			58
1	100	95	91	88	93	89	86	82	77	75	72	66	65	63	56	55	54	49			49
2	91	83	77	72	84	78	72	68	68	64	60	58	55	53	50	47	45	41			41
3	83	73	66	60	77	69	62	57	60	55	50	52	48	44	44	41	39	35			35
4	76	65	57	51	70	61	54	48	53	47	43	46	42	38	39	36	33	30			30
5	70	58	50	43	65	54	47	41	48	42	37	41	37	33	35	32	29	26			26
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	29	26	23			23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	26	23	20			20
8	55	43	35	29	51	40	33	28	36	30	26	31	26	23	27	23	20	18			18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18	16			16
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	19	17	15			15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1686	1686	1686
5°	1688	1663	1674
10°	1675	1641	1652
15°	1650	1614	1617
20°	1617	1577	1582
25°	1584	1533	1540
30°	1543	1492	1488
35°	1504	1443	1432
40°	1456	1394	1379
45°	1407	1345	1325
50°	1355	1293	1262
55°	1300	1233	1204
60°	1238	1162	1138
65°	1170	1089	1060
70°	1083	999	977
75°	964	892	901
80°	820	756	754
85°	595	520	509

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1407 cd/sqm



TEST NUMBER: P924203

CATALOG NUMBER: DFN2DIP-4P4F0-070D050US950-FLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	244.6	2.2
10°-20°	688.1	6.1
20°-30°	1011.3	8.9
30°-40°	1174.5	10.4
40°-50°	1173.1	10.4
50°-60°	1022.9	9.0
60°-70°	756.1	6.7
70°-80°	427.8	3.8
80°-90°	115.8	1.0
90°-100°	53.1	0.5
100°-110°	197.9	1.7
110°-120°	524.8	4.6
120°-130°	870.4	7.7
130°-140°	924.6	8.2
140°-150°	859.3	7.6
150°-160°	690.9	6.1
160°-170°	445.2	3.9
170°-180°	153.2	1.4
0°-30°	1943.9	17.2
0°-40°	3118.5	27.5
0°-60°	5314.4	46.9
0°-90°	6614.1	58.4
90°-120°	775.8	6.8
90°-150°	3430.2	30.3
90°-180°	4719.0	41.6
0°-180°	11333.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2598	2598	2598	2598	2598	
5°	2598	2589	2561	2581	2576	247
15°	2474	2459	2426	2436	2424	697
25°	2239	2219	2176	2181	2176	1030
35°	1932	1907	1866	1851	1839	1206
45°	1572	1554	1517	1489	1479	1213
55°	1189	1174	1144	1114	1102	1063
65°	802	787	762	740	727	793
75°	420	415	402	387	392	448
85°	102	100	98	90	88	114
90°	1	14	23	29	31	10
95°	76	37	45	51	50	90
105°	354	389	71	84	88	378
115°	670	690	719	179	96	659
125°	947	962	984	992	996	845
135°	1172	1191	1201	1213	1210	905
145°	1359	1358	1378	1386	1380	850
155°	1497	1486	1500	1507	1498	690
165°	1577	1570	1574	1582	1574	446
175°	1613	1605	1608	1616	1604	154
180°	1610	1610	1610	1610	1610	



TEST NUMBER: P924203

CATALOG NUMBER: DFN2DIP-4P4F0-070D050US950-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2598.4	2598.4	2598.4	2598.4	2598.4
2.5°	2613.6	2601.1	2573.5	2598.4	2593.6
5°	2598.4	2588.7	2561.1	2581.0	2576.2
7.5°	2581.0	2566.1	2538.5	2558.7	2553.7
10°	2553.7	2536.1	2506.2	2526.1	2518.7
12.5°	2516.0	2501.2	2471.2	2483.6	2478.6
15°	2473.6	2458.7	2426.1	2436.2	2423.7
17.5°	2421.1	2406.3	2373.6	2386.1	2373.6
20°	2363.5	2348.7	2313.7	2321.2	2311.4
22.5°	2306.3	2283.8	2251.2	2251.2	2246.1
25°	2238.8	2218.8	2176.5	2181.2	2176.5
27.5°	2163.7	2146.2	2113.9	2106.4	2093.9
30°	2089.0	2068.7	2031.4	2024.0	2013.9
32.5°	2008.8	1994.1	1954.0	1938.9	1928.8
35°	1931.5	1906.6	1866.5	1851.4	1838.9
37.5°	1844.0	1821.5	1781.4	1763.9	1751.4
40°	1754.1	1734.0	1693.9	1671.7	1661.6
42.5°	1666.6	1646.5	1606.7	1581.5	1566.7
45°	1571.7	1554.3	1516.6	1489.3	1479.2
47.5°	1479.2	1461.7	1421.7	1394.1	1379.3
50°	1381.7	1369.2	1334.2	1299.3	1286.8
52.5°	1286.8	1269.3	1237.0	1209.4	1191.8
55°	1189.4	1174.4	1144.4	1114.5	1102.0
57.5°	1091.9	1079.5	1046.8	1016.9	1006.9
60°	994.4	984.5	949.6	922.0	914.6
62.5°	899.4	882.0	857.1	832.2	822.1
65°	802.2	787.0	762.2	739.6	727.1
67.5°	702.2	689.6	667.2	649.8	639.7
70°	609.7	599.7	577.1	559.6	549.8
72.5°	514.8	504.8	492.3	474.8	467.4
75°	419.7	414.9	402.1	387.3	392.4
77.5°	334.9	324.7	319.7	312.2	304.9
80°	249.9	247.4	242.3	234.9	229.8
82.5°	169.9	169.9	167.5	157.5	157.5
85°	102.4	100.0	97.6	89.9	87.5
87.5°	45.0	40.1	35.0	27.6	24.9
90°	1.1	13.9	23.3	29.2	31.4
92.5°	29.2	24.5	28.0	30.3	31.4
95°	75.7	37.2	45.4	51.3	50.1
97.5°	136.2	40.8	59.3	63.0	64.0
100°	206.3	46.7	66.4	75.7	78.0
102.5°	283.1	280.8	68.8	81.5	85.1
105°	354.1	389.1	71.1	83.9	88.5
107.5°	436.8	465.8	73.5	86.1	90.9
110°	516.1	540.4	203.9	87.4	92.0



TEST NUMBER: P924203

CATALOG NUMBER: DFN2DIP-4P4F0-070D050US950-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	590.6	611.5	591.8	89.7	93.2
115°	669.8	689.6	718.7	179.4	95.6
117.5°	738.5	761.8	781.7	614.9	309.9
120°	815.4	832.8	853.8	867.9	710.5
122.5°	880.5	899.2	922.6	929.6	930.8
125°	946.9	962.2	984.3	992.4	996.0
127.5°	1007.5	1023.8	1041.5	1053.0	1054.2
130°	1064.7	1083.4	1096.1	1108.9	1107.9
132.5°	1123.0	1138.1	1150.8	1161.4	1160.3
135°	1171.9	1190.6	1200.9	1212.7	1210.3
137.5°	1223.0	1237.1	1248.8	1260.4	1257.0
140°	1273.1	1282.6	1295.2	1305.7	1300.0
142.5°	1315.2	1323.4	1338.5	1347.7	1341.9
145°	1359.4	1358.2	1378.0	1386.2	1380.3
147.5°	1397.8	1394.3	1414.1	1419.9	1415.4
150°	1435.1	1427.0	1445.6	1452.6	1446.7
152.5°	1466.5	1457.2	1474.7	1481.8	1473.5
155°	1496.8	1486.4	1500.4	1507.3	1498.1
157.5°	1521.2	1512.0	1522.5	1530.7	1521.2
160°	1542.3	1535.3	1542.3	1549.2	1541.1
162.5°	1560.8	1554.0	1559.7	1567.9	1557.4
165°	1577.2	1570.3	1573.7	1581.8	1573.7
167.5°	1590.0	1583.0	1586.6	1594.7	1584.2
170°	1600.5	1593.5	1595.9	1604.0	1593.5
172.5°	1607.5	1600.5	1602.9	1611.0	1600.5
175°	1613.3	1605.1	1607.5	1615.6	1604.0
177.5°	1615.6	1607.5	1608.7	1616.8	1606.3
180°	1609.8	1609.8	1609.8	1609.8	1609.8



TEST NUMBER: P924203  
 CATALOG NUMBER: DFN2DIP-4P4F0-070D050US950-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.84	10.78	10.72	11.69	12.83	9.40	10.34	10.28	11.24	12.39
	3H	11.52	12.36	12.41	13.27	14.44	11.02	11.87	11.92	12.78	13.95
	4H	12.11	12.91	13.02	13.83	15.01	11.62	12.41	12.53	13.33	14.51
	6H	12.52	13.26	13.44	14.18	15.37	12.02	12.76	12.94	13.68	14.87
	8H	12.63	13.33	13.56	14.27	15.46	12.13	12.83	13.05	13.77	14.96
	12H	12.68	13.35	13.62	14.28	15.50	12.17	12.84	13.11	13.78	14.99
4H	2H	10.31	11.11	11.23	12.03	13.21	9.96	10.76	10.87	11.68	12.86
	3H	12.19	12.86	13.12	13.81	15.01	11.79	12.45	12.71	13.40	14.60
	4H	12.92	13.53	13.85	14.47	15.69	12.49	13.10	13.43	14.04	15.27
	6H	13.44	13.97	14.39	14.93	16.16	13.01	13.53	13.96	14.50	15.72
	8H	13.60	14.09	14.55	15.05	16.28	13.16	13.65	14.11	14.61	15.85
	12H	13.68	14.12	14.65	15.10	16.34	13.23	13.67	14.20	14.65	15.89
8H	4H	13.12	13.61	14.07	14.57	15.81	12.74	13.23	13.70	14.20	15.43
	6H	13.76	14.17	14.74	15.17	16.41	13.38	13.78	14.36	14.79	16.02
	8H	13.99	14.35	14.97	15.34	16.59	13.59	13.95	14.58	14.95	16.20
	12H	14.13	14.44	15.12	15.43	16.73	13.72	14.03	14.71	15.02	16.32
12H	4H	13.11	13.55	14.08	14.53	15.77	12.74	13.19	13.71	14.16	15.41
	6H	13.79	14.15	14.78	15.14	16.40	13.42	13.78	14.41	14.77	16.02
	8H	14.04	14.36	15.03	15.34	16.64	13.66	13.98	14.65	14.96	16.26