

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924214

Luminaire Tested: DFN2DIP-4P4F0-070D080US950-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924214
REPORT IS A COMBINATION OF REPORTS P899147 AND P895967
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-070D080US950-FLLFLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13365.6 lumens
Efficiency: N/A
Efficacy: 90.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 147.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924214
CATALOG NUMBER: DFN2DIP-4P4F0-070D080US950-FLLFL

Luminous Intensity Polar Plot





TEST NUMBER: P924214

CATALOG NUMBER: DFN2DIP-4P4F0-070D080US950-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	56	50
1	98	93	89	86	90	86	83	80	73	70	68	61	59	57	49	48	47	49	48	47	42
2	89	82	75	70	82	75	70	66	64	60	56	53	50	48	43	41	40	43	41	40	35
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	36	34	38	36	34	30
4	74	63	56	49	68	59	52	46	50	45	40	42	38	35	34	31	29	34	31	29	25
5	68	57	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25	31	28	25	22
6	63	51	43	37	58	47	40	35	40	35	30	34	30	26	28	25	22	28	25	22	19
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20	26	22	20	17
8	54	42	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18	24	20	18	15
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	18	16	22	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1686	1686	1686
5°	1688	1663	1674
10°	1675	1641	1652
15°	1650	1614	1617
20°	1617	1577	1582
25°	1584	1533	1540
30°	1543	1492	1488
35°	1504	1443	1432
40°	1456	1394	1379
45°	1407	1345	1325
50°	1355	1293	1262
55°	1300	1233	1204
60°	1238	1162	1138
65°	1170	1089	1060
70°	1083	999	977
75°	964	892	901
80°	820	756	754
85°	595	520	509

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 1829 cd/sqm



TEST NUMBER: P924214

CATALOG NUMBER: DFN2DIP-4P4F0-070D080US950-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	244.6	1.8
10°-20°	688.1	5.1
20°-30°	1011.3	7.6
30°-40°	1174.5	8.8
40°-50°	1173.1	8.8
50°-60°	1022.9	7.7
60°-70°	756.1	5.7
70°-80°	427.8	3.2
80°-90°	119.8	0.9
90°-100°	149.4	1.1
100°-110°	474.6	3.6
110°-120°	812.1	6.1
120°-130°	1068.1	8.0
130°-140°	1198.9	9.0
140°-150°	1175.6	8.8
150°-160°	986.2	7.4
160°-170°	654.0	4.9
170°-180°	228.6	1.7
0°-30°	1943.9	14.5
0°-40°	3118.5	23.3
0°-60°	5314.4	39.8
0°-90°	6618.1	49.5
90°-120°	1436.1	10.7
90°-150°	4878.6	36.5
90°-180°	6747.0	50.5
0°-180°	13365.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2598	2598	2598	2598	2598	
5°	2598	2589	2561	2581	2576	247
15°	2474	2459	2426	2436	2424	697
25°	2239	2219	2176	2181	2176	1030
35°	1932	1907	1866	1851	1839	1206
45°	1572	1554	1517	1489	1479	1213
55°	1189	1174	1144	1114	1102	1063
65°	802	787	762	740	727	793
75°	420	415	402	387	392	448
85°	102	100	98	90	88	114
90°	2	26	71	67	69	13
95°	106	127	130	130	127	118
105°	438	444	448	452	452	462
115°	815	827	823	821	815	806
125°	1185	1204	1198	1191	1189	1059
135°	1533	1556	1560	1558	1552	1185
145°	1861	1876	1888	1890	1882	1163
155°	2128	2134	2141	2151	2144	980
165°	2316	2313	2313	2328	2318	653
175°	2409	2404	2399	2414	2401	229
180°	2414	2414	2414	2414	2414	



TEST NUMBER: P924214

CATALOG NUMBER: DFN2DIP-4P4F0-070D080US950-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2598.4	2598.4	2598.4	2598.4	2598.4
2.5°	2613.6	2601.1	2573.5	2598.4	2593.6
5°	2598.4	2588.7	2561.1	2581.0	2576.2
7.5°	2581.0	2566.1	2538.5	2558.7	2553.7
10°	2553.7	2536.1	2506.2	2526.1	2518.7
12.5°	2516.0	2501.2	2471.2	2483.6	2478.6
15°	2473.6	2458.7	2426.1	2436.2	2423.7
17.5°	2421.1	2406.3	2373.6	2386.1	2373.6
20°	2363.5	2348.7	2313.7	2321.2	2311.4
22.5°	2306.3	2283.8	2251.2	2251.2	2246.1
25°	2238.8	2218.8	2176.5	2181.2	2176.5
27.5°	2163.7	2146.2	2113.9	2106.4	2093.9
30°	2089.0	2068.7	2031.4	2024.0	2013.9
32.5°	2008.8	1994.1	1954.0	1938.9	1928.8
35°	1931.5	1906.6	1866.5	1851.4	1838.9
37.5°	1844.0	1821.5	1781.4	1763.9	1751.4
40°	1754.1	1734.0	1693.9	1671.7	1661.6
42.5°	1666.6	1646.5	1606.7	1581.5	1566.7
45°	1571.7	1554.3	1516.6	1489.3	1479.2
47.5°	1479.2	1461.7	1421.7	1394.1	1379.3
50°	1381.7	1369.2	1334.2	1299.3	1286.8
52.5°	1286.8	1269.3	1237.0	1209.4	1191.8
55°	1189.4	1174.4	1144.4	1114.5	1102.0
57.5°	1091.9	1079.5	1046.8	1016.9	1006.9
60°	994.4	984.5	949.6	922.0	914.6
62.5°	899.4	882.0	857.1	832.2	822.1
65°	802.2	787.0	762.2	739.6	727.1
67.5°	702.2	689.6	667.2	649.8	639.7
70°	609.7	599.7	577.1	559.6	549.8
72.5°	514.8	504.8	492.3	474.8	467.4
75°	419.7	414.9	402.1	387.3	392.4
77.5°	334.9	324.7	319.7	312.2	304.9
80°	249.9	247.4	242.3	234.9	229.8
82.5°	169.9	169.9	167.5	157.5	157.5
85°	102.4	100.0	97.6	89.9	87.5
87.5°	45.0	40.1	35.0	27.6	24.9
90°	2.2	26.2	71.4	67.0	69.2
92.5°	45.1	61.2	63.3	65.4	65.4
95°	106.3	126.6	130.2	130.2	126.6
97.5°	176.9	195.8	203.8	203.8	203.8
100°	258.3	275.0	280.9	280.9	278.7
102.5°	344.2	356.6	364.5	366.7	364.5
105°	438.1	443.9	448.3	451.9	451.9
107.5°	531.2	540.0	540.0	541.4	531.2
110°	621.4	633.1	633.1	633.1	627.3



TEST NUMBER: P924214

CATALOG NUMBER: DFN2DIP-4P4F0-070D080US950-FLLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	718.9	731.3	729.1	723.3	718.9
115°	815.0	826.6	823.0	820.8	815.0
117.5°	910.3	926.3	916.1	910.3	904.5
120°	1006.4	1022.4	1006.4	1006.4	999.8
122.5°	1093.7	1114.1	1103.9	1098.1	1093.7
125°	1185.3	1203.6	1197.7	1191.2	1189.1
127.5°	1274.9	1297.4	1289.4	1280.7	1274.9
130°	1358.6	1384.7	1381.1	1376.8	1368.8
132.5°	1452.5	1472.8	1474.3	1464.1	1458.3
135°	1533.2	1555.8	1560.2	1558.0	1552.2
137.5°	1623.4	1641.6	1645.3	1643.8	1635.1
140°	1702.8	1720.9	1731.1	1731.1	1723.1
142.5°	1784.3	1802.5	1808.3	1810.5	1802.5
145°	1861.4	1875.9	1887.6	1889.8	1881.8
147.5°	1930.5	1948.7	1957.4	1961.1	1953.1
150°	2001.9	2014.2	2022.2	2028.8	2022.2
152.5°	2065.1	2077.5	2087.7	2095.7	2087.7
155°	2128.5	2134.3	2140.9	2151.0	2144.5
157.5°	2183.0	2187.4	2191.1	2205.6	2195.4
160°	2231.8	2236.2	2238.4	2250.7	2242.0
162.5°	2276.9	2276.9	2279.1	2292.9	2282.7
165°	2315.5	2313.3	2313.3	2327.9	2317.6
167.5°	2350.4	2343.9	2343.9	2358.4	2348.2
170°	2376.6	2370.8	2368.6	2383.2	2370.8
172.5°	2394.8	2389.0	2386.8	2401.3	2389.0
175°	2409.3	2403.5	2399.1	2413.7	2401.3
177.5°	2417.3	2411.5	2407.1	2419.5	2407.1
180°	2413.7	2413.7	2413.7	2413.7	2413.7



TEST NUMBER: P924214
 CATALOG NUMBER: DFN2DIP-4P4F0-070D080US950-FLLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.06	9.92	10.02	10.89	12.17	8.61	9.47	9.58	10.45	11.73
	3H	10.72	11.49	11.70	12.48	13.78	10.23	11.00	11.21	11.99	13.29
	4H	11.32	12.04	12.30	13.03	14.34	10.82	11.55	11.81	12.54	13.85
	6H	11.72	12.39	12.72	13.38	14.71	11.22	11.89	12.22	12.88	14.21
	8H	11.83	12.47	12.83	13.48	14.79	11.32	11.96	12.33	12.97	14.29
	12H	11.88	12.48	12.89	13.49	14.83	11.37	11.97	12.38	12.98	14.32
4H	2H	9.52	10.25	10.51	11.24	12.55	9.17	9.89	10.16	10.88	12.19
	3H	11.39	12.00	12.39	13.02	14.34	10.98	11.59	11.99	12.61	13.93
	4H	12.11	12.67	13.12	13.68	15.02	11.69	12.24	12.70	13.25	14.60
	6H	12.63	13.11	13.65	14.14	15.49	12.20	12.68	13.22	13.71	15.05
	8H	12.78	13.23	13.81	14.26	15.62	12.35	12.79	13.37	13.82	15.18
	12H	12.86	13.26	13.90	14.31	15.67	12.41	12.81	13.45	13.86	15.22
8H	4H	12.31	12.75	13.33	13.78	15.14	11.93	12.38	12.95	13.41	14.76
	6H	12.95	13.32	13.99	14.38	15.74	12.56	12.93	13.61	14.00	15.36
	8H	13.17	13.50	14.22	14.55	15.92	12.78	13.10	13.83	14.16	15.53
	12H	13.31	13.59	14.36	14.64	16.06	12.89	13.18	13.95	14.23	15.65
12H	4H	12.29	12.70	13.33	13.74	15.10	11.93	12.33	12.97	13.37	14.74
	6H	12.98	13.30	14.03	14.36	15.73	12.60	12.93	13.66	13.98	15.36
	8H	13.22	13.51	14.28	14.56	15.97	12.84	13.13	13.90	14.18	15.59