

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924227

Luminaire Tested: DFN2DIP-4P4F0-080D050US950-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924227
REPORT IS A COMBINATION OF REPORTS P900633 AND P897523
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-080D050US950-FLLONL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12278.0 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 126
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924227
CATALOG NUMBER: DFN2DIP-4P4F0-080D050US950-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P924227
 CATALOG NUMBER: DFN2DIP-4P4F0-080D050US950-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	67	67	67	62
1	100	96	92	88	94	90	87	83	79	76	74	69	67	65	59	58	56	56	56	56	52
2	91	84	78	72	85	79	73	69	69	65	61	60	57	54	52	50	48	48	48	48	43
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	40	40	40	40	37
4	76	65	57	51	71	61	54	49	54	48	44	47	43	39	41	38	35	35	35	35	32
5	70	58	50	44	65	55	47	42	49	43	38	43	38	34	37	33	30	30	30	30	27
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27	27	27	27	24
7	60	47	39	34	56	45	37	32	40	34	29	35	30	27	31	27	24	24	24	24	21
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	24	21	21	21	21	19
9	52	39	32	27	49	37	30	26	33	28	23	30	25	21	26	22	19	19	19	19	17
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	18	18	18	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1926	1926	1926
5°	1930	1900	1913
10°	1914	1875	1888
15°	1886	1845	1848
20°	1848	1803	1807
25°	1811	1752	1760
30°	1763	1705	1700
35°	1719	1649	1636
40°	1663	1593	1576
45°	1609	1537	1514
50°	1548	1478	1442
55°	1485	1409	1376
60°	1414	1328	1301
65°	1337	1244	1212
70°	1238	1142	1116
75°	1101	1020	1030
80°	937	864	861
85°	680	594	581

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1609 cd/sqm



TEST NUMBER: P924227

CATALOG NUMBER: DFN2DIP-4P4F0-080D050US950-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	279.5	2.3
10°-20°	786.4	6.4
20°-30°	1155.7	9.4
30°-40°	1342.3	10.9
40°-50°	1340.6	10.9
50°-60°	1169.0	9.5
60°-70°	864.1	7.0
70°-80°	488.9	4.0
80°-90°	131.9	1.1
90°-100°	53.1	0.4
100°-110°	197.9	1.6
110°-120°	524.8	4.3
120°-130°	870.4	7.1
130°-140°	924.6	7.5
140°-150°	859.3	7.0
150°-160°	690.9	5.6
160°-170°	445.2	3.6
170°-180°	153.2	1.2
0°-30°	2221.6	18.1
0°-40°	3563.9	29.0
0°-60°	6073.6	49.5
0°-90°	7558.5	61.6
90°-120°	775.8	6.3
90°-150°	3430.2	27.9
90°-180°	4719.0	38.4
0°-180°	12278.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2970	2970	2970	2970	2970	
5°	2970	2958	2927	2950	2944	282
15°	2827	2810	2773	2784	2770	796
25°	2558	2536	2487	2493	2487	1177
35°	2207	2179	2133	2116	2102	1378
45°	1796	1776	1733	1702	1691	1386
55°	1359	1342	1308	1274	1259	1215
65°	917	900	871	845	831	906
75°	480	474	460	443	448	512
85°	117	114	112	103	100	130
90°	1	14	23	29	31	11
95°	76	37	45	51	50	90
105°	354	389	71	84	88	378
115°	670	690	719	179	96	659
125°	947	962	984	992	996	845
135°	1172	1191	1201	1213	1210	905
145°	1359	1358	1378	1386	1380	850
155°	1497	1486	1500	1507	1498	690
165°	1577	1570	1574	1582	1574	446
175°	1613	1605	1608	1616	1604	154
180°	1610	1610	1610	1610	1610	



TEST NUMBER: P924227

CATALOG NUMBER: DFN2DIP-4P4F0-080D050US950-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2969.6	2969.6	2969.6	2969.6	2969.6
2.5°	2986.9	2972.7	2941.2	2969.6	2964.2
5°	2969.6	2958.4	2927.0	2949.7	2944.2
7.5°	2949.7	2932.7	2901.2	2924.2	2918.5
10°	2918.5	2898.4	2864.2	2886.9	2878.5
12.5°	2875.5	2858.5	2824.2	2838.4	2832.7
15°	2827.0	2810.0	2772.7	2784.2	2770.0
17.5°	2767.0	2750.0	2712.7	2727.0	2712.7
20°	2701.3	2684.3	2644.3	2652.8	2641.5
22.5°	2635.8	2610.0	2572.7	2572.7	2567.0
25°	2558.5	2535.8	2487.4	2492.8	2487.4
27.5°	2472.8	2452.8	2415.8	2407.3	2393.1
30°	2387.4	2364.3	2321.7	2313.2	2301.6
32.5°	2295.9	2278.9	2233.1	2215.9	2204.4
35°	2207.4	2178.9	2133.1	2115.9	2101.7
37.5°	2107.4	2081.6	2035.9	2015.9	2001.7
40°	2004.7	1981.6	1936.0	1910.5	1898.9
42.5°	1904.8	1881.7	1836.3	1807.4	1790.6
45°	1796.3	1776.3	1733.2	1702.0	1690.6
47.5°	1690.6	1670.5	1624.8	1593.3	1576.3
50°	1579.1	1564.8	1524.8	1484.8	1470.6
52.5°	1470.6	1450.6	1413.6	1382.2	1362.1
55°	1359.4	1342.1	1307.9	1273.7	1259.4
57.5°	1247.9	1233.7	1196.4	1162.2	1150.6
60°	1136.4	1125.2	1085.2	1053.7	1045.2
62.5°	1027.9	1008.0	979.5	951.0	939.5
65°	916.8	899.5	871.0	845.2	831.0
67.5°	802.5	788.0	762.5	742.6	731.1
70°	696.8	685.3	659.6	639.6	628.3
72.5°	588.3	576.9	562.6	542.6	534.1
75°	479.6	474.1	459.6	442.7	448.4
77.5°	382.6	371.1	365.4	356.9	348.4
80°	285.7	282.7	276.9	268.5	262.6
82.5°	194.2	194.2	191.5	179.9	179.9
85°	117.0	114.2	111.5	102.7	100.0
87.5°	51.5	45.8	40.0	31.5	28.5
90°	1.1	13.9	23.3	29.2	31.4
92.5°	29.2	24.5	28.0	30.3	31.4
95°	75.7	37.2	45.4	51.3	50.1
97.5°	136.2	40.8	59.3	63.0	64.0
100°	206.3	46.7	66.4	75.7	78.0
102.5°	283.1	280.8	68.8	81.5	85.1
105°	354.1	389.1	71.1	83.9	88.5
107.5°	436.8	465.8	73.5	86.1	90.9
110°	516.1	540.4	203.9	87.4	92.0



TEST NUMBER: P924227

CATALOG NUMBER: DFN2DIP-4P4F0-080D050US950-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	590.6	611.5	591.8	89.7	93.2
115°	669.8	689.6	718.7	179.4	95.6
117.5°	738.5	761.8	781.7	614.9	309.9
120°	815.4	832.8	853.8	867.9	710.5
122.5°	880.5	899.2	922.6	929.6	930.8
125°	946.9	962.2	984.3	992.4	996.0
127.5°	1007.5	1023.8	1041.5	1053.0	1054.2
130°	1064.7	1083.4	1096.1	1108.9	1107.9
132.5°	1123.0	1138.1	1150.8	1161.4	1160.3
135°	1171.9	1190.6	1200.9	1212.7	1210.3
137.5°	1223.0	1237.1	1248.8	1260.4	1257.0
140°	1273.1	1282.6	1295.2	1305.7	1300.0
142.5°	1315.2	1323.4	1338.5	1347.7	1341.9
145°	1359.4	1358.2	1378.0	1386.2	1380.3
147.5°	1397.8	1394.3	1414.1	1419.9	1415.4
150°	1435.1	1427.0	1445.6	1452.6	1446.7
152.5°	1466.5	1457.2	1474.7	1481.8	1473.5
155°	1496.8	1486.4	1500.4	1507.3	1498.1
157.5°	1521.2	1512.0	1522.5	1530.7	1521.2
160°	1542.3	1535.3	1542.3	1549.2	1541.1
162.5°	1560.8	1554.0	1559.7	1567.9	1557.4
165°	1577.2	1570.3	1573.7	1581.8	1573.7
167.5°	1590.0	1583.0	1586.6	1594.7	1584.2
170°	1600.5	1593.5	1595.9	1604.0	1593.5
172.5°	1607.5	1600.5	1602.9	1611.0	1600.5
175°	1613.3	1605.1	1607.5	1615.6	1604.0
177.5°	1615.6	1607.5	1608.7	1616.8	1606.3
180°	1609.8	1609.8	1609.8	1609.8	1609.8



TEST NUMBER: P924227
 CATALOG NUMBER: DFN2DIP-4P4F0-080D050US950-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.57	11.55	11.42	12.42	13.52	10.13	11.10	10.98	11.98	13.07
	3H	12.25	13.12	13.11	14.01	15.13	11.76	12.63	12.62	13.52	14.64
	4H	12.84	13.67	13.72	14.56	15.69	12.35	13.18	13.23	14.07	15.20
	6H	13.25	14.02	14.15	14.91	16.06	12.75	13.52	13.65	14.41	15.56
	8H	13.36	14.09	14.26	15.01	16.15	12.86	13.59	13.76	14.50	15.65
	12H	13.42	14.11	14.32	15.02	16.19	12.91	13.60	13.81	14.51	15.68
4H	2H	11.05	11.88	11.93	12.77	13.90	10.69	11.52	11.58	12.41	13.54
	3H	12.93	13.62	13.83	14.54	15.69	12.52	13.21	13.42	14.13	15.28
	4H	13.65	14.28	14.56	15.20	16.37	13.23	13.86	14.14	14.78	15.95
	6H	14.18	14.73	15.10	15.67	16.84	13.75	14.29	14.67	15.23	16.41
	8H	14.34	14.85	15.26	15.78	16.97	13.90	14.41	14.82	15.34	16.53
	12H	14.42	14.88	15.36	15.83	17.02	13.97	14.43	14.91	15.38	16.57
8H	4H	13.86	14.37	14.78	15.30	16.49	13.48	13.99	14.41	14.93	16.12
	6H	14.50	14.92	15.45	15.90	17.09	14.12	14.54	15.07	15.52	16.71
	8H	14.73	15.10	15.69	16.07	17.27	14.34	14.71	15.30	15.68	16.88
	12H	14.87	15.20	15.83	16.16	17.41	14.46	14.79	15.42	15.75	17.00
12H	4H	13.85	14.31	14.80	15.26	16.46	13.48	13.94	14.43	14.90	16.09
	6H	14.53	14.91	15.49	15.87	17.08	14.16	14.54	15.12	15.50	16.71
	8H	14.79	15.11	15.75	16.07	17.33	14.41	14.73	15.37	15.69	16.95