

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902425

Luminaire Tested: DFN2DIP-HX2F0-020D030US830-RLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P902425  
REPORT IS A COMBINATION OF REPORTS P900682 AND P897595  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX2F0-020D030US830-RLONL  
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4401.7 lumens  
Efficiency: N/A  
Efficacy: 119.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 37  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: 0.9968  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P902425  
CATALOG NUMBER: DFN2DIP-HX2F0-020D030US830-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P902425  
 CATALOG NUMBER: DFN2DIP-HX2F0-020D030US830-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36			36
1	95	91	87	84	86	83	80	77	67	65	63	52	51	50	39	38	38	31			31
2	87	80	74	69	78	73	68	63	59	56	53	46	44	42	35	33	32	27			27
3	79	70	63	58	72	64	58	53	52	48	45	41	38	36	31	29	28	23			23
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24	20			20
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	18			18
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19	16			16
7	57	45	38	32	52	41	35	30	34	29	26	28	24	21	21	19	17	14			14
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15	13			13
9	49	37	30	25	45	34	28	24	29	24	20	23	20	17	18	16	14	12			12
10	46	34	27	23	42	32	25	21	26	22	18	22	18	15	17	14	13	11			11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1836	1836	1836
5°	1836	1802	1815
10°	1815	1763	1753
15°	1787	1700	1658
20°	1751	1616	1543
25°	1714	1522	1433
30°	1665	1426	1294
35°	1618	1324	1171
40°	1569	1218	1032
45°	1513	1102	906
50°	1455	984	783
55°	1393	860	665
60°	1322	730	544
65°	1241	599	486
70°	1141	476	435
75°	1016	412	389
80°	836	333	327
85°	547	206	230

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1513 cd/sqm



TEST NUMBER: P902425

CATALOG NUMBER: DFN2DIP-HX2F0-020D030US830-RLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	73.0	1.7
10°-20°	200.4	4.6
20°-30°	281.4	6.4
30°-40°	306.8	7.0
40°-50°	282.0	6.4
50°-60°	221.4	5.0
60°-70°	144.1	3.3
70°-80°	74.2	1.7
80°-90°	20.6	0.5
90°-100°	31.5	0.7
100°-110°	117.3	2.7
110°-120°	311.1	7.1
120°-130°	516.0	11.7
130°-140°	548.1	12.5
140°-150°	509.4	11.6
150°-160°	409.6	9.3
160°-170°	263.9	6.0
170°-180°	90.8	2.1
0°-30°	554.9	12.6
0°-40°	861.7	19.6
0°-60°	1365.1	31.0
0°-90°	1604.0	36.4
90°-120°	459.9	10.4
90°-150°	2033.4	46.2
90°-180°	2798.0	63.6
0°-180°	4401.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	779	779	779	779	779	
5°	779	776	766	773	771	74
15°	741	733	709	696	689	209
25°	673	650	604	575	564	309
35°	580	544	482	437	422	363
45°	474	426	353	302	286	366
55°	360	305	229	187	173	322
65°	243	186	123	99	97	241
75°	130	80	56	52	51	137
85°	30	16	13	13	13	35
90°	1	8	14	17	19	4
95°	45	22	27	30	30	53
105°	210	231	42	50	52	224
115°	397	409	426	106	57	391
125°	561	570	584	588	590	501
135°	695	706	712	719	718	537
145°	806	805	817	822	818	504
155°	887	881	889	894	888	409
165°	935	931	933	938	933	264
175°	956	952	953	958	951	91
180°	954	954	954	954	954	



TEST NUMBER: P902425

CATALOG NUMBER: DFN2DIP-HX2F0-020D030US830-RLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	779.1	779.1	779.1	779.1	779.1
2.5°	782.6	779.1	771.3	778.4	777.0
5°	779.1	775.6	766.4	772.8	770.6
7.5°	772.8	768.5	758.7	761.5	757.9
10°	764.3	759.3	745.3	743.1	739.0
12.5°	753.8	747.3	728.3	724.2	716.3
15°	741.0	733.2	709.3	695.9	688.9
17.5°	726.2	714.9	685.3	669.8	658.6
20°	709.3	695.1	660.0	642.3	626.8
22.5°	691.0	674.8	633.9	609.9	599.4
25°	672.7	650.1	603.5	574.7	564.0
27.5°	650.8	626.8	575.3	542.2	525.9
30°	627.5	600.7	544.3	508.4	489.3
32.5°	604.9	572.5	514.7	472.4	454.8
35°	579.6	543.7	481.6	437.2	421.6
37.5°	554.9	516.0	450.5	401.9	384.3
40°	528.8	486.5	418.1	368.1	349.7
42.5°	502.0	456.9	385.7	333.5	315.9
45°	473.8	426.5	352.6	302.5	285.5
47.5°	447.0	397.0	320.8	270.7	255.2
50°	417.5	367.4	289.8	241.1	226.4
52.5°	388.4	335.5	260.1	213.7	200.3
55°	360.2	305.3	229.1	186.9	173.4
57.5°	331.4	274.9	201.7	162.2	150.9
60°	301.8	245.3	172.8	136.9	125.5
62.5°	272.9	216.5	148.1	114.2	108.6
65°	243.3	186.2	122.7	98.8	96.6
67.5°	215.1	157.9	98.8	86.7	84.6
70°	185.4	130.4	81.7	74.7	71.9
72.5°	157.2	105.0	68.3	62.8	61.4
75°	129.7	80.3	56.4	51.5	50.8
77.5°	102.3	57.1	44.4	41.6	40.2
80°	76.8	40.9	33.8	31.0	31.0
82.5°	53.5	27.5	23.3	21.9	21.9
85°	30.3	15.5	13.4	13.4	13.4
87.5°	11.3	5.7	5.7	4.9	4.9
90°	0.7	8.3	13.8	17.3	18.6
92.5°	17.3	14.5	16.6	18.0	18.6
95°	44.9	22.1	26.9	30.4	29.7
97.5°	80.8	24.2	35.2	37.3	38.0
100°	122.2	27.6	39.4	44.9	46.3
102.5°	167.8	166.5	40.7	48.3	50.4
105°	209.9	230.6	42.1	49.7	52.5
107.5°	258.9	276.2	43.5	51.1	53.9
110°	305.9	320.4	120.8	51.8	54.6



TEST NUMBER: P902425

CATALOG NUMBER: DFN2DIP-HX2F0-020D030US830-RLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	350.2	362.5	350.8	53.2	55.2
115°	397.0	408.8	426.0	106.3	56.6
117.5°	437.8	451.6	463.4	364.6	183.7
120°	483.3	493.7	506.1	514.4	421.2
122.5°	522.0	533.1	547.0	551.0	551.8
125°	561.4	570.3	583.5	588.3	590.4
127.5°	597.3	606.9	617.4	624.2	624.9
130°	631.1	642.2	649.8	657.3	656.8
132.5°	665.6	674.7	682.2	688.4	687.8
135°	694.7	705.8	711.9	718.9	717.5
137.5°	725.0	733.3	740.3	747.2	745.1
140°	754.7	760.3	767.8	774.0	770.6
142.5°	779.7	784.5	793.4	798.9	795.5
145°	805.9	805.1	816.9	821.7	818.2
147.5°	828.6	826.5	838.3	841.7	839.0
150°	850.7	845.9	857.0	861.0	857.6
152.5°	869.3	863.8	874.2	878.4	873.5
155°	887.3	881.2	889.4	893.5	888.1
157.5°	901.8	896.4	902.6	907.4	901.8
160°	914.3	910.1	914.3	918.4	913.5
162.5°	925.3	921.1	924.6	929.4	923.2
165°	934.9	930.9	932.9	937.7	932.9
167.5°	942.5	938.4	940.5	945.4	939.1
170°	948.8	944.6	946.0	950.8	944.6
172.5°	952.9	948.8	950.2	955.0	948.8
175°	956.3	951.5	952.9	957.7	950.8
177.5°	957.7	952.9	953.7	958.5	952.3
180°	954.3	954.3	954.3	954.3	954.3



TEST NUMBER: P902425  
 CATALOG NUMBER: DFN2DIP-HX2F0-020D030US830-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.70	8.43	8.78	9.50	10.96	3.69	4.42	4.76	5.49	6.94
	3H	9.35	10.00	10.43	11.08	12.55	4.85	5.51	5.93	6.58	8.06
	4H	9.94	10.55	11.03	11.63	13.11	5.29	5.91	6.38	6.99	8.46
	6H	10.33	10.90	11.43	11.98	13.47	5.59	6.16	6.69	7.24	8.73
	8H	10.44	10.99	11.55	12.08	13.57	5.67	6.21	6.77	7.31	8.79
	12H	10.49	11.01	11.60	12.10	13.61	5.70	6.22	6.81	7.31	8.81
4H	2H	7.71	8.33	8.80	9.40	10.88	4.26	4.88	5.36	5.96	7.44
	3H	9.50	10.01	10.60	11.12	12.61	5.58	6.09	6.68	7.20	8.69
	4H	10.17	10.64	11.28	11.73	13.25	6.11	6.58	7.22	7.68	9.19
	6H	10.65	11.06	11.77	12.18	13.68	6.50	6.91	7.62	8.03	9.53
	8H	10.81	11.19	11.93	12.30	13.82	6.62	7.00	7.74	8.11	9.63
	12H	10.89	11.23	12.02	12.35	13.88	6.67	7.01	7.81	8.14	9.66
8H	4H	10.12	10.50	11.24	11.61	13.13	6.37	6.74	7.48	7.85	9.38
	6H	10.66	10.97	11.80	12.12	13.64	6.86	7.17	7.99	8.32	9.84
	8H	10.86	11.13	12.00	12.26	13.80	7.04	7.31	8.18	8.44	9.98
	12H	10.97	11.21	12.12	12.34	13.92	7.14	7.38	8.28	8.51	10.08
12H	4H	10.07	10.41	11.20	11.53	13.06	6.36	6.70	7.50	7.83	9.35
	6H	10.63	10.90	11.78	12.04	13.58	6.90	7.17	8.04	8.31	9.84
	8H	10.83	11.07	11.98	12.20	13.77	7.09	7.33	8.24	8.46	10.03