

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910719

Luminaire Tested: DFN2DIP-HX3F0-030D070US850-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910719
REPORT IS A COMBINATION OF REPORTS P900777 AND P897645
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-030D070US850-FLLONL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10979.1 lumens
Efficiency: N/A
Efficacy: 142.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 77.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910719

CATALOG NUMBER: DFN2DIP-HX3F0-030D070US850-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P910719

CATALOG NUMBER: DFN2DIP-HX3F0-030D070US850-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38
1	93	89	85	82	84	80	77	74	63	61	59	48	46	45	33	33	32
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	29	28	27
3	77	68	61	56	69	62	56	51	49	45	41	37	34	32	26	24	23
4	71	60	53	47	63	54	48	43	43	39	35	33	30	27	23	21	20
5	65	54	46	40	58	48	42	37	39	34	30	29	26	23	21	19	17
6	60	48	40	35	53	43	37	32	35	30	26	27	23	20	19	17	15
7	55	43	35	30	49	39	32	28	31	26	23	24	21	18	17	15	13
8	51	39	32	26	46	35	29	24	28	24	20	22	19	16	16	14	12
9	47	36	28	23	42	32	26	22	26	21	18	20	17	14	15	12	11
10	44	32	26	21	40	30	23	19	24	19	16	19	15	13	14	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1499	1499	1499
5°	1501	1478	1488
10°	1488	1457	1467
15°	1466	1432	1434
20°	1436	1397	1401
25°	1405	1356	1363
30°	1368	1318	1315
35°	1332	1273	1264
40°	1288	1228	1216
45°	1245	1183	1166
50°	1197	1135	1109
55°	1147	1080	1056
60°	1090	1014	995
65°	1028	946	923
70°	949	864	846
75°	840	764	773
80°	708	637	637
85°	502	422	413

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1679 cd/sqm

TEST NUMBER: P910719

CATALOG NUMBER: DFN2DIP-HX3F0-030D070US850-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.8	1.1
10°-20°	342.8	3.1
20°-30°	503.8	4.6
30°-40°	585.2	5.3
40°-50°	584.4	5.3
50°-60°	509.6	4.6
60°-70°	376.7	3.4
70°-80°	213.1	1.9
80°-90°	60.9	0.6
90°-100°	86.4	0.8
100°-110°	322.1	2.9
110°-120°	854.1	7.8
120°-130°	1416.6	12.9
130°-140°	1504.8	13.7
140°-150°	1398.5	12.7
150°-160°	1124.4	10.2
160°-170°	724.5	6.6
170°-180°	249.4	2.3
0°-30°	968.5	8.8
0°-40°	1553.6	14.2
0°-60°	2647.7	24.1
0°-90°	3298.4	30.0
90°-120°	1262.6	11.5
90°-150°	5582.5	50.8
90°-180°	7681.0	70.0
0°-180°	10979.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1294	1294	1294	1294	1294	
5°	1294	1290	1276	1286	1283	123
15°	1232	1225	1209	1214	1208	347
25°	1115	1106	1084	1087	1084	513
35°	962	950	930	922	916	601
45°	783	774	756	742	737	604
55°	593	585	570	555	549	530
65°	400	392	380	368	362	395
75°	209	207	200	193	196	223
85°	51	50	49	45	44	57
90°	2	23	38	48	51	10
95°	123	61	74	84	82	146
105°	576	633	116	136	144	616
115°	1090	1122	1170	292	156	1073
125°	1541	1566	1602	1615	1621	1375
135°	1907	1938	1954	1974	1970	1473
145°	2212	2210	2243	2256	2246	1384
155°	2436	2419	2442	2453	2438	1123
165°	2567	2556	2561	2574	2561	725
175°	2626	2612	2616	2629	2610	250
180°	2620	2620	2620	2620	2620	

TEST NUMBER: P910719

CATALOG NUMBER: DFN2DIP-HX3F0-030D070US850-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1294.5	1294.5	1294.5	1294.5	1294.5
2.5°	1302.1	1295.9	1282.1	1294.5	1292.2
5°	1294.5	1289.7	1275.9	1285.9	1283.4
7.5°	1285.9	1278.5	1264.7	1274.8	1272.2
10°	1272.2	1263.5	1248.6	1258.5	1254.8
12.5°	1253.5	1246.1	1231.2	1237.3	1234.9
15°	1232.3	1225.0	1208.7	1213.7	1207.5
17.5°	1206.1	1198.8	1182.5	1188.7	1182.5
20°	1177.5	1170.1	1152.7	1156.4	1151.5
22.5°	1149.0	1137.8	1121.5	1121.5	1119.0
25°	1115.3	1105.5	1084.3	1086.7	1084.3
27.5°	1077.9	1069.2	1053.1	1049.4	1043.2
30°	1040.7	1030.7	1012.1	1008.3	1003.3
32.5°	1000.9	993.4	973.5	965.9	960.9
35°	962.3	949.9	929.9	922.4	916.1
37.5°	918.7	907.5	887.5	878.8	872.6
40°	873.9	863.9	843.9	832.9	827.9
42.5°	830.3	820.3	800.5	787.9	780.5
45°	783.1	774.3	755.6	741.9	736.9
47.5°	736.9	728.3	708.3	694.6	687.1
50°	688.4	682.1	664.7	647.3	641.1
52.5°	641.1	632.4	616.3	602.5	593.8
55°	592.6	585.1	570.1	555.3	549.1
57.5°	544.0	537.8	521.6	506.6	501.6
60°	495.4	490.5	473.1	459.3	455.7
62.5°	448.1	439.4	427.0	414.5	409.6
65°	399.7	392.1	379.7	368.5	362.3
67.5°	349.9	343.6	332.4	323.7	318.7
70°	303.8	298.8	287.6	278.8	273.9
72.5°	256.5	251.4	245.2	236.5	232.9
75°	209.0	206.7	200.4	193.0	195.5
77.5°	166.8	161.8	159.3	155.6	151.9
80°	124.5	123.2	120.7	117.0	114.6
82.5°	84.6	84.6	83.5	78.4	78.4
85°	51.0	49.8	48.6	44.8	43.6
87.5°	22.4	20.0	17.4	13.8	12.4
90°	1.8	22.7	37.8	47.5	51.1
92.5°	47.5	39.8	45.5	49.4	51.1
95°	123.1	60.6	73.9	83.5	81.5
97.5°	221.7	66.4	96.6	102.5	104.2
100°	335.7	75.9	108.0	123.1	127.0
102.5°	460.6	457.0	111.9	132.6	138.4
105°	576.3	633.2	115.7	136.4	144.1
107.5°	710.9	758.2	119.6	140.3	147.9
110°	840.0	879.5	331.8	142.3	149.7

TEST NUMBER: P910719

CATALOG NUMBER: DFN2DIP-HX3F0-030D070US850-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	961.3	995.2	963.1	145.8	151.7
115°	1090.0	1122.2	1169.7	292.0	155.6
117.5°	1201.9	1239.8	1272.1	1000.9	504.3
120°	1327.0	1355.4	1389.7	1412.4	1156.5
122.5°	1433.0	1463.4	1501.6	1512.8	1514.8
125°	1541.2	1565.9	1602.0	1615.3	1620.8
127.5°	1639.8	1666.3	1694.9	1713.8	1715.6
130°	1732.7	1763.1	1783.8	1804.8	1803.0
132.5°	1827.5	1852.3	1873.0	1890.1	1888.3
135°	1907.1	1937.5	1954.5	1973.6	1969.8
137.5°	1990.4	2013.3	2032.4	2051.3	2045.7
140°	2071.9	2087.2	2108.0	2125.1	2115.6
142.5°	2140.4	2153.7	2178.2	2193.3	2183.8
145°	2212.5	2210.5	2242.6	2255.9	2246.5
147.5°	2274.8	2269.2	2301.4	2310.8	2303.4
150°	2335.6	2322.4	2352.7	2363.9	2354.5
152.5°	2386.7	2371.6	2400.0	2411.4	2398.2
155°	2436.0	2419.1	2441.8	2453.1	2438.0
157.5°	2475.8	2460.8	2477.8	2491.1	2475.8
160°	2510.1	2498.6	2510.1	2521.3	2508.0
162.5°	2540.3	2529.0	2538.4	2551.7	2534.6
165°	2566.8	2555.6	2561.1	2574.4	2561.1
167.5°	2587.7	2576.2	2582.1	2595.4	2578.3
170°	2604.8	2593.4	2597.2	2610.5	2593.4
172.5°	2616.1	2604.8	2608.7	2621.9	2604.8
175°	2625.6	2612.2	2616.1	2629.3	2610.5
177.5°	2629.3	2616.1	2618.1	2631.4	2614.2
180°	2619.9	2619.9	2619.9	2619.9	2619.9

TEST NUMBER: P910719

CATALOG NUMBER: DFN2DIP-HX3F0-030D070US850-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.43	7.13	7.54	8.24	9.77	6.00	6.71	7.11	7.81	9.34
	3H	8.07	8.70	9.19	9.82	11.36	7.60	8.23	8.72	9.35	10.89
	4H	8.64	9.25	9.77	10.36	11.91	8.18	8.78	9.31	9.89	11.44
	6H	9.03	9.58	10.17	10.70	12.27	8.56	9.11	9.70	10.23	11.80
	8H	9.13	9.65	10.27	10.79	12.34	8.66	9.18	9.80	10.32	11.87
	12H	9.17	9.67	10.31	10.79	12.37	8.69	9.19	9.84	10.32	11.90
4H	2H	6.87	7.47	8.01	8.58	10.14	6.52	7.13	7.66	8.24	9.79
	3H	8.71	9.21	9.85	10.35	11.92	8.32	8.82	9.46	9.96	11.53
	4H	9.41	9.87	10.56	11.00	12.59	9.01	9.47	10.16	10.60	12.19
	6H	9.91	10.31	11.06	11.46	13.04	9.51	9.90	10.66	11.06	12.63
	8H	10.05	10.42	11.20	11.57	13.16	9.65	10.02	10.80	11.16	12.75
	12H	10.12	10.45	11.28	11.61	13.20	9.70	10.03	10.87	11.19	12.79
8H	4H	9.59	9.96	10.74	11.11	12.70	9.24	9.60	10.39	10.75	12.34
	6H	10.21	10.51	11.38	11.70	13.29	9.85	10.15	11.02	11.34	12.93
	8H	10.42	10.69	11.60	11.85	13.46	10.06	10.32	11.24	11.49	13.10
	12H	10.54	10.78	11.72	11.94	13.58	10.16	10.40	11.34	11.56	13.20
12H	4H	9.57	9.91	10.74	11.06	12.66	9.22	9.56	10.39	10.71	12.31
	6H	10.24	10.50	11.41	11.67	13.28	9.89	10.15	11.07	11.32	12.93
	8H	10.46	10.70	11.65	11.86	13.50	10.11	10.34	11.29	11.51	13.15

END OF REPORT