

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902444

Luminaire Tested: DFN2DIP-HX2F0-030D030US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902444
REPORT IS A COMBINATION OF REPORTS P899164 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-030D030US830-RLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4905.9 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 47
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902444

CATALOG NUMBER: DFN2DIP-HX2F0-030D030US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P902444

CATALOG NUMBER: DFN2DIP-HX2F0-030D030US830-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2754	2754	2754
5°	2754	2703	2722
10°	2722	2644	2629
15°	2680	2550	2487
20°	2626	2424	2315
25°	2571	2283	2149
30°	2498	2139	1941
35°	2427	1986	1757
40°	2354	1827	1548
45°	2270	1653	1359
50°	2182	1477	1174
55°	2090	1290	997
60°	1983	1095	816
65°	1861	898	729
70°	1711	714	652
75°	1523	617	584
80°	1255	500	492
85°	819	309	345

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2270 cd/sqm

TEST NUMBER: P902444

CATALOG NUMBER: DFN2DIP-HX2F0-030D030US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.5	2.2
10°-20°	300.7	6.1
20°-30°	422.1	8.6
30°-40°	460.2	9.4
40°-50°	422.9	8.6
50°-60°	332.2	6.8
60°-70°	216.2	4.4
70°-80°	111.3	2.3
80°-90°	31.0	0.6
90°-100°	55.3	1.1
100°-110°	175.8	3.6
110°-120°	300.9	6.1
120°-130°	395.7	8.1
130°-140°	444.2	9.1
140°-150°	435.6	8.9
150°-160°	365.4	7.4
160°-170°	242.3	4.9
170°-180°	84.7	1.7
0°-30°	832.3	17.0
0°-40°	1292.5	26.3
0°-60°	2047.6	41.7
0°-90°	2406.0	49.0
90°-120°	532.1	10.8
90°-150°	1807.5	36.8
90°-180°	2500.0	51.0
0°-180°	4905.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1169	1169	1169	1169	1169	
5°	1169	1163	1150	1159	1156	111
15°	1112	1100	1064	1044	1033	313
25°	1009	975	905	862	846	464
35°	869	815	722	656	632	544
45°	711	640	529	454	428	549
55°	540	458	344	280	260	483
65°	365	279	184	148	145	362
75°	194	121	85	77	76	206
85°	45	23	20	20	20	52
90°	1	10	26	25	26	5
95°	39	47	48	48	47	44
105°	162	164	166	167	167	171
115°	302	306	305	304	302	299
125°	439	446	444	441	440	392
135°	568	576	578	577	575	439
145°	690	695	699	700	697	431
155°	789	791	793	797	795	363
165°	858	857	857	862	859	242
175°	893	890	889	894	890	85
180°	894	894	894	894	894	

TEST NUMBER: P902444

CATALOG NUMBER: DFN2DIP-HX2F0-030D030US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1168.7	1168.7	1168.7	1168.7	1168.7
2.5°	1173.9	1168.7	1157.0	1167.6	1165.5
5°	1168.7	1163.4	1149.6	1159.1	1155.9
7.5°	1159.1	1152.8	1138.0	1142.2	1136.9
10°	1146.4	1139.1	1117.9	1114.7	1108.4
12.5°	1130.6	1121.1	1092.5	1086.2	1074.5
15°	1111.5	1099.9	1063.9	1043.9	1033.3
17.5°	1089.3	1072.4	1027.9	1004.8	987.8
20°	1063.9	1042.7	989.9	963.6	940.2
22.5°	1036.5	1012.1	950.7	914.8	899.0
25°	1009.0	975.1	905.3	862.0	846.0
27.5°	976.2	940.2	863.0	813.3	788.9
30°	941.3	901.1	816.4	762.6	734.0
32.5°	907.4	858.8	772.1	708.6	682.1
35°	869.4	815.4	722.4	655.7	632.4
37.5°	832.4	774.1	675.8	602.8	576.5
40°	793.2	729.8	627.2	552.0	524.6
42.5°	753.0	685.4	578.5	500.2	473.8
45°	710.8	639.8	528.9	453.6	428.3
47.5°	670.5	595.5	481.3	406.0	382.9
50°	626.1	551.0	434.7	361.7	339.5
52.5°	582.7	503.4	390.3	320.5	300.4
55°	540.4	457.9	343.7	280.3	260.2
57.5°	497.1	412.5	302.6	243.3	226.3
60°	452.6	368.1	259.1	205.2	188.3
62.5°	409.3	324.7	222.1	171.4	163.0
65°	364.9	279.2	184.0	148.1	144.9
67.5°	322.6	236.9	148.1	130.1	126.9
70°	278.1	195.7	122.6	112.1	107.8
72.5°	235.8	157.5	102.5	94.2	92.0
75°	194.5	120.6	84.6	77.2	76.2
77.5°	153.4	85.6	66.6	62.4	60.2
80°	115.3	61.4	50.7	46.6	46.6
82.5°	80.3	41.3	34.9	32.8	32.8
85°	45.4	23.2	20.1	20.1	20.1
87.5°	17.0	8.4	8.4	7.4	7.4
90°	0.8	9.7	26.4	24.8	25.6
92.5°	16.7	22.6	23.5	24.2	24.2
95°	39.4	46.9	48.3	48.3	46.9
97.5°	65.5	72.5	75.5	75.5	75.5
100°	95.7	101.9	104.1	104.1	103.3
102.5°	127.5	132.1	135.1	135.9	135.1
105°	162.3	164.5	166.1	167.4	167.4
107.5°	196.8	200.0	200.0	200.6	196.8
110°	230.3	234.6	234.6	234.6	232.4

TEST NUMBER: P902444

CATALOG NUMBER: DFN2DIP-HX2F0-030D030US830-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	266.4	271.0	270.1	268.0	266.4
115°	302.0	306.2	304.9	304.2	302.0
117.5°	337.2	343.2	339.4	337.2	335.1
120°	372.9	378.8	372.9	372.9	370.4
122.5°	405.2	412.7	409.0	406.8	405.2
125°	439.2	445.9	443.7	441.3	440.5
127.5°	472.3	480.7	477.8	474.5	472.3
130°	503.3	513.0	511.7	510.1	507.1
132.5°	538.1	545.6	546.2	542.4	540.3
135°	568.1	576.4	578.1	577.2	575.0
137.5°	601.4	608.2	609.5	609.1	605.8
140°	630.8	637.6	641.4	641.4	638.4
142.5°	661.1	667.8	670.0	670.8	667.8
145°	689.7	695.0	699.4	700.1	697.2
147.5°	715.3	722.0	725.2	726.6	723.6
150°	741.7	746.3	749.2	751.7	749.2
152.5°	765.2	769.7	773.5	776.5	773.5
155°	788.6	790.7	793.1	796.9	794.6
157.5°	808.8	810.4	811.8	817.2	813.4
160°	826.9	828.5	829.3	833.9	830.7
162.5°	843.6	843.6	844.4	849.5	845.7
165°	857.9	857.1	857.1	862.4	858.7
167.5°	870.8	868.4	868.4	873.7	870.0
170°	880.5	878.4	877.6	883.0	878.4
172.5°	887.2	885.1	884.3	889.7	885.1
175°	892.7	890.5	888.9	894.3	889.7
177.5°	895.6	893.4	891.8	896.5	891.8
180°	894.3	894.3	894.3	894.3	894.3

TEST NUMBER: P902444

CATALOG NUMBER: DFN2DIP-HX2F0-030D030US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.44	11.26	11.41	12.24	13.53	6.42	7.24	7.39	8.22	9.51
	3H	12.09	12.82	13.07	13.82	15.12	7.59	8.33	8.57	9.32	10.63
	4H	12.68	13.38	13.68	14.37	15.69	8.03	8.73	9.03	9.72	11.04
	6H	13.08	13.72	14.09	14.72	16.05	8.34	8.98	9.34	9.97	11.30
	8H	13.20	13.80	14.21	14.82	16.15	8.42	9.03	9.43	10.04	11.37
	12H	13.25	13.83	14.27	14.84	16.19	8.45	9.03	9.47	10.04	11.39
4H	2H	10.45	11.15	11.45	12.14	13.46	7.00	7.70	8.00	8.69	10.01
	3H	12.25	12.83	13.26	13.85	15.18	8.33	8.91	9.34	9.93	11.26
	4H	12.92	13.45	13.94	14.47	15.82	8.86	9.39	9.88	10.41	11.76
	6H	13.41	13.87	14.44	14.91	16.26	9.26	9.72	10.29	10.76	12.11
	8H	13.57	14.00	14.61	15.03	16.40	9.38	9.81	10.41	10.84	12.20
	12H	13.66	14.04	14.70	15.08	16.46	9.44	9.82	10.49	10.87	12.24
8H	4H	12.89	13.31	13.92	14.34	15.71	9.13	9.55	10.16	10.58	11.95
	6H	13.42	13.77	14.48	14.85	16.21	9.62	9.97	10.68	11.05	12.41
	8H	13.62	13.93	14.69	14.99	16.37	9.80	10.11	10.86	11.17	12.55
	12H	13.75	14.02	14.81	15.07	16.49	9.91	10.18	10.97	11.23	12.65
12H	4H	12.84	13.22	13.88	14.27	15.64	9.13	9.51	10.18	10.56	11.93
	6H	13.40	13.71	14.46	14.77	16.15	9.67	9.97	10.73	11.03	12.41
	8H	13.60	13.87	14.67	14.93	16.35	9.86	10.13	10.93	11.18	12.61