

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902451

Luminaire Tested: DFN2DIP-HX2F0-030D050US830-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902451
REPORT IS A COMBINATION OF REPORTS P900703 AND P897595
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-030D050US830-FLLONL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7465.0 lumens
Efficiency: N/A
Efficacy: 117.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 63.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902451

CATALOG NUMBER: DFN2DIP-HX2F0-030D050US830-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P902451

CATALOG NUMBER: DFN2DIP-HX2F0-030D050US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45
1	95	91	87	83	86	82	79	76	67	65	63	53	51	50	39	39	38
2	86	79	73	68	78	72	67	63	59	55	52	46	44	42	35	33	32
3	79	70	62	57	71	63	57	52	52	47	44	41	38	35	31	29	27
4	72	62	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20
6	61	49	41	35	55	45	38	33	37	32	28	29	26	23	22	20	18
7	56	44	36	31	51	40	34	29	33	28	24	27	23	20	20	18	16
8	52	40	32	27	47	37	30	25	30	25	22	24	21	18	19	16	14
9	48	36	29	24	44	33	27	23	28	23	19	22	19	16	17	15	13
10	45	33	26	22	41	31	24	20	26	21	17	21	17	14	16	13	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2592	2592	2592
5°	2592	2550	2569
10°	2567	2510	2529
15°	2525	2462	2470
20°	2470	2399	2410
25°	2415	2324	2341
30°	2347	2254	2254
35°	2283	2172	2163
40°	2204	2090	2076
45°	2125	2007	1987
50°	2039	1919	1884
55°	1948	1818	1789
60°	1845	1700	1679
65°	1732	1575	1550
70°	1589	1424	1409
75°	1392	1243	1274
80°	1151	1011	1028
85°	783	635	635

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2125 cd/sqm

TEST NUMBER: P902451

CATALOG NUMBER: DFN2DIP-HX2F0-030D050US830-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.6	1.4
10°-20°	291.4	3.9
20°-30°	428.2	5.7
30°-40°	497.3	6.7
40°-50°	496.7	6.7
50°-60°	433.1	5.8
60°-70°	320.2	4.3
70°-80°	181.1	2.4
80°-90°	50.6	0.7
90°-100°	52.5	0.7
100°-110°	195.5	2.6
110°-120°	518.5	6.9
120°-130°	860.0	11.5
130°-140°	913.5	12.2
140°-150°	849.0	11.4
150°-160°	682.6	9.1
160°-170°	439.8	5.9
170°-180°	151.4	2.0
0°-30°	823.1	11.0
0°-40°	1320.4	17.7
0°-60°	2250.3	30.1
0°-90°	2802.2	37.5
90°-120°	766.5	10.3
90°-150°	3389.0	45.4
90°-180°	4663.0	62.5
0°-180°	7465.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1100	1100	1100	1100	1100	
5°	1100	1096	1084	1093	1091	104
15°	1047	1041	1027	1032	1026	295
25°	948	940	922	924	922	436
35°	818	807	790	784	779	511
45°	666	658	642	631	626	514
55°	504	497	485	472	467	450
65°	340	333	323	313	308	336
75°	178	176	170	164	166	190
85°	43	42	41	38	37	48
90°	1	14	23	29	31	7
95°	75	37	45	51	50	89
105°	350	384	70	83	88	374
115°	662	681	710	177	94	651
125°	936	951	972	980	984	834
135°	1158	1176	1186	1198	1196	894
145°	1343	1342	1361	1370	1364	840
155°	1479	1469	1482	1489	1480	681
165°	1558	1551	1555	1563	1555	440
175°	1594	1586	1588	1596	1585	152
180°	1590	1590	1590	1590	1590	

TEST NUMBER: P902451

CATALOG NUMBER: DFN2DIP-HX2F0-030D050US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1100.2	1100.2	1100.2	1100.2	1100.2
2.5°	1106.6	1101.4	1089.7	1100.2	1098.3
5°	1100.2	1096.1	1084.4	1092.9	1090.8
7.5°	1092.9	1086.6	1074.9	1083.5	1081.3
10°	1081.3	1073.8	1061.2	1069.6	1066.5
12.5°	1065.4	1059.0	1046.4	1051.6	1049.5
15°	1047.4	1041.1	1027.3	1031.5	1026.2
17.5°	1025.1	1018.9	1005.0	1010.3	1005.0
20°	1000.8	994.5	979.7	982.8	978.6
22.5°	976.6	967.0	953.2	953.2	951.0
25°	947.9	939.5	921.5	923.6	921.5
27.5°	916.2	908.7	895.0	891.9	886.6
30°	884.5	876.0	860.2	857.0	852.7
32.5°	850.6	844.3	827.4	821.0	816.7
35°	817.8	807.3	790.3	783.9	778.6
37.5°	780.8	771.3	754.3	746.9	741.6
40°	742.7	734.2	717.3	707.8	703.6
42.5°	705.7	697.2	680.3	669.7	663.4
45°	665.5	658.1	642.2	630.6	626.3
47.5°	626.3	619.0	602.0	590.3	584.0
50°	585.0	579.8	565.0	550.2	544.9
52.5°	544.9	537.4	523.8	512.1	504.6
55°	503.7	497.3	484.6	471.9	466.7
57.5°	462.3	457.0	443.3	430.6	426.3
60°	421.0	416.9	402.1	390.4	387.3
62.5°	380.9	373.4	362.9	352.3	348.1
65°	339.7	333.3	322.7	313.2	307.9
67.5°	297.4	292.0	282.5	275.1	270.9
70°	258.2	253.9	244.4	237.0	232.8
72.5°	218.0	213.7	208.4	201.0	197.9
75°	177.7	175.7	170.3	164.0	166.2
77.5°	141.8	137.5	135.3	132.2	129.1
80°	105.8	104.7	102.5	99.4	97.4
82.5°	71.9	71.9	71.0	66.6	66.6
85°	43.4	42.3	41.3	38.1	37.0
87.5°	19.0	17.0	14.8	11.7	10.6
90°	1.1	13.8	23.0	28.8	31.0
92.5°	28.8	24.2	27.6	30.0	31.0
95°	74.7	36.8	44.9	50.7	49.5
97.5°	134.6	40.3	58.6	62.2	63.2
100°	203.8	46.1	65.6	74.7	77.1
102.5°	279.7	277.4	68.0	80.5	84.1
105°	349.9	384.5	70.2	82.8	87.5
107.5°	431.6	460.2	72.6	85.1	89.8
110°	509.9	534.0	201.4	86.3	90.9

TEST NUMBER: P902451

CATALOG NUMBER: DFN2DIP-HX2F0-030D050US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	583.5	604.2	584.7	88.6	92.1
115°	661.8	681.3	710.1	177.3	94.4
117.5°	729.6	752.6	772.3	607.6	306.1
120°	805.6	822.8	843.6	857.4	702.0
122.5°	870.0	888.4	911.5	918.4	919.6
125°	935.6	950.6	972.5	980.5	984.0
127.5°	995.4	1011.5	1029.0	1040.4	1041.5
130°	1051.9	1070.4	1082.9	1095.6	1094.6
132.5°	1109.5	1124.5	1137.0	1147.5	1146.3
135°	1157.8	1176.3	1186.5	1198.2	1195.8
137.5°	1208.3	1222.2	1233.8	1245.3	1241.9
140°	1257.8	1267.2	1279.7	1290.1	1284.4
142.5°	1299.4	1307.5	1322.4	1331.5	1325.8
145°	1343.1	1341.9	1361.4	1369.5	1363.8
147.5°	1381.0	1377.5	1397.1	1402.9	1398.4
150°	1417.9	1409.9	1428.2	1435.1	1429.4
152.5°	1448.9	1439.7	1457.0	1464.0	1455.9
155°	1478.8	1468.6	1482.3	1489.2	1480.1
157.5°	1503.0	1493.8	1504.2	1512.3	1503.0
160°	1523.8	1516.8	1523.8	1530.6	1522.6
162.5°	1542.1	1535.3	1541.0	1549.1	1538.7
165°	1558.2	1551.4	1554.8	1562.8	1554.8
167.5°	1570.9	1564.0	1567.5	1575.6	1565.2
170°	1581.3	1574.3	1576.7	1584.7	1574.3
172.5°	1588.2	1581.3	1583.7	1591.7	1581.3
175°	1593.9	1585.8	1588.2	1596.2	1584.7
177.5°	1596.2	1588.2	1589.4	1597.4	1587.1
180°	1590.4	1590.4	1590.4	1590.4	1590.4

TEST NUMBER: P902451

CATALOG NUMBER: DFN2DIP-HX2F0-030D050US830-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.17	9.93	10.23	10.99	12.43	8.75	9.51	9.80	10.57	12.01
	3H	10.80	11.48	11.86	12.55	14.00	10.34	11.02	11.40	12.09	13.54
	4H	11.36	12.01	12.44	13.08	14.54	10.90	11.55	11.98	12.62	14.08
	6H	11.74	12.33	12.83	13.41	14.88	11.28	11.87	12.37	12.95	14.42
	8H	11.83	12.40	12.92	13.49	14.96	11.37	11.94	12.46	13.03	14.50
	12H	11.87	12.40	12.96	13.49	14.98	11.40	11.94	12.50	13.03	14.52
4H	2H	9.61	10.25	10.69	11.32	12.79	9.27	9.92	10.35	10.99	12.45
	3H	11.44	11.97	12.53	13.07	14.55	11.05	11.59	12.14	12.69	14.17
	4H	12.13	12.62	13.22	13.71	15.21	11.73	12.23	12.83	13.32	14.81
	6H	12.61	13.04	13.72	14.15	15.64	12.22	12.64	13.32	13.75	15.24
	8H	12.75	13.14	13.85	14.25	15.75	12.35	12.75	13.46	13.85	15.36
	12H	12.80	13.16	13.93	14.28	15.79	12.40	12.76	13.52	13.87	15.39
8H	4H	12.30	12.70	13.41	13.80	15.31	11.95	12.35	13.06	13.45	14.96
	6H	12.90	13.23	14.03	14.37	15.88	12.55	12.88	13.68	14.02	15.53
	8H	13.10	13.39	14.24	14.52	16.04	12.75	13.03	13.88	14.16	15.68
	12H	13.21	13.47	14.35	14.59	16.15	12.85	13.10	13.98	14.22	15.78
12H	4H	12.28	12.64	13.40	13.76	15.27	11.94	12.30	13.06	13.41	14.93
	6H	12.92	13.21	14.06	14.34	15.86	12.58	12.87	13.72	14.00	15.52
	8H	13.14	13.39	14.28	14.52	16.08	12.80	13.05	13.94	14.17	15.73