

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902461

Luminaire Tested: DFN2DIP-HX2F0-040D020US830-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902461
REPORT IS A COMBINATION OF REPORTS P900676 AND P897595
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-040D020US830-RLLONL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5070.8 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902461

CATALOG NUMBER: DFN2DIP-HX2F0-040D020US830-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P902461

CATALOG NUMBER: DFN2DIP-HX2F0-040D020US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	61	60	59
2	93	86	80	75	87	81	75	71	71	67	64	63	60	57	55	52	51
3	85	76	69	63	80	72	65	60	63	58	54	56	52	49	49	46	44
4	78	68	60	54	73	64	57	52	57	51	47	50	46	43	44	41	38
5	72	61	53	47	67	57	50	45	51	45	41	46	41	37	40	37	34
6	67	55	47	41	62	52	45	39	46	41	36	41	37	33	37	33	30
7	62	50	42	36	58	47	40	35	42	36	32	38	33	30	34	30	27
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	24
9	54	42	34	29	51	40	33	28	36	30	26	32	27	24	29	25	22
10	50	38	31	26	47	37	30	25	33	28	24	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3671	3671	3671
5°	3671	3604	3629
10°	3629	3525	3505
15°	3574	3400	3316
20°	3501	3231	3087
25°	3428	3044	2865
30°	3331	2852	2587
35°	3236	2647	2343
40°	3138	2436	2064
45°	3026	2203	1812
50°	2909	1969	1566
55°	2787	1720	1330
60°	2644	1460	1088
65°	2481	1197	972
70°	2282	953	870
75°	2031	823	779
80°	1671	666	656
85°	1094	412	460

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3026 cd/sqm

TEST NUMBER: P902461

CATALOG NUMBER: DFN2DIP-HX2F0-040D020US830-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.0	2.9
10°-20°	400.9	7.9
20°-30°	562.8	11.1
30°-40°	613.5	12.1
40°-50°	563.9	11.1
50°-60°	442.9	8.7
60°-70°	288.3	5.7
70°-80°	148.4	2.9
80°-90°	39.0	0.8
90°-100°	21.0	0.4
100°-110°	78.2	1.5
110°-120°	207.4	4.1
120°-130°	344.0	6.8
130°-140°	365.4	7.2
140°-150°	339.6	6.7
150°-160°	273.0	5.4
160°-170°	175.9	3.5
170°-180°	60.6	1.2
0°-30°	1109.8	21.9
0°-40°	1723.3	34.0
0°-60°	2730.1	53.8
0°-90°	3205.7	63.2
90°-120°	306.6	6.0
90°-150°	1355.6	26.7
90°-180°	1865.0	36.8
0°-180°	5070.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1558	1558	1558	1558	1558	
5°	1558	1551	1533	1546	1541	148
15°	1482	1466	1419	1392	1378	418
25°	1345	1300	1207	1149	1128	619
35°	1159	1087	963	874	843	726
45°	948	853	705	605	571	732
55°	721	611	458	374	347	644
65°	486	372	245	198	193	482
75°	259	161	113	103	102	274
85°	61	31	27	27	27	70
90°	0	6	9	12	12	5
95°	30	15	18	20	20	35
105°	140	154	28	33	35	150
115°	265	272	284	71	38	261
125°	374	380	389	392	394	334
135°	463	470	475	479	478	358
145°	537	537	545	548	546	336
155°	592	587	593	596	592	273
165°	623	621	622	625	622	176
175°	638	634	635	638	634	61
180°	636	636	636	636	636	

TEST NUMBER: P902461

CATALOG NUMBER: DFN2DIP-HX2F0-040D020US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1558.2	1558.2	1558.2	1558.2	1558.2
2.5°	1565.3	1558.2	1542.7	1556.9	1554.0
5°	1558.2	1551.1	1532.8	1545.5	1541.3
7.5°	1545.5	1537.1	1517.4	1522.9	1515.9
10°	1528.6	1518.7	1490.5	1486.2	1477.9
12.5°	1507.5	1494.8	1456.6	1448.2	1432.7
15°	1482.1	1466.5	1418.6	1391.9	1377.8
17.5°	1452.5	1429.8	1370.6	1339.6	1317.0
20°	1418.6	1390.3	1319.8	1284.7	1253.6
22.5°	1382.0	1349.5	1267.6	1219.7	1198.7
25°	1345.3	1300.1	1207.0	1149.3	1128.0
27.5°	1301.7	1253.6	1150.7	1084.4	1051.9
30°	1255.1	1201.4	1088.5	1016.7	978.6
32.5°	1209.9	1145.0	1029.4	944.8	909.5
35°	1159.2	1087.2	963.2	874.3	843.2
37.5°	1109.8	1032.2	901.1	803.7	768.5
40°	1057.6	973.1	836.2	736.1	699.5
42.5°	1004.0	913.8	771.4	666.9	631.8
45°	947.6	853.1	705.1	604.9	571.1
47.5°	894.1	794.0	641.7	541.5	510.5
50°	834.8	734.7	579.6	482.2	452.7
52.5°	776.9	671.2	520.4	427.3	400.5
55°	720.6	610.6	458.3	373.7	346.9
57.5°	662.8	550.0	403.3	324.3	301.8
60°	603.5	490.7	345.4	273.6	251.1
62.5°	545.8	433.0	296.1	228.5	217.3
65°	486.5	372.2	245.3	197.5	193.1
67.5°	430.2	315.8	197.5	173.4	169.2
70°	370.9	260.9	163.5	149.5	143.7
72.5°	314.5	210.1	136.8	125.5	122.7
75°	259.4	160.7	112.8	102.9	101.6
77.5°	204.5	114.1	88.9	83.2	80.3
80°	153.6	81.8	67.6	62.1	62.1
82.5°	107.2	55.0	46.6	43.6	43.6
85°	60.6	31.0	26.8	26.8	26.8
87.5°	22.6	11.2	11.2	9.9	9.9
90°	0.5	5.6	9.1	11.5	12.4
92.5°	11.5	9.7	11.0	12.0	12.4
95°	29.9	14.7	17.9	20.3	19.8
97.5°	53.8	16.1	23.5	24.9	25.4
100°	81.5	18.4	26.2	29.9	30.8
102.5°	111.9	110.9	27.1	32.2	33.6
105°	140.0	153.7	28.1	33.1	35.0
107.5°	172.7	184.1	29.0	34.0	35.9
110°	204.0	213.6	80.6	34.6	36.4

TEST NUMBER: P902461

CATALOG NUMBER: DFN2DIP-HX2F0-040D020US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	233.4	241.7	233.8	35.4	36.9
115°	264.7	272.5	284.1	70.9	37.8
117.5°	291.8	301.0	308.9	243.1	122.4
120°	322.3	329.1	337.4	343.0	280.8
122.5°	348.0	355.3	364.6	367.3	367.9
125°	374.3	380.2	389.0	392.2	393.6
127.5°	398.2	404.6	411.6	416.1	416.6
130°	420.8	428.1	433.2	438.3	437.8
132.5°	443.7	449.8	454.8	458.9	458.5
135°	463.2	470.5	474.6	479.3	478.3
137.5°	483.3	488.9	493.5	498.1	496.7
140°	503.1	506.9	511.9	516.0	513.8
142.5°	519.7	523.0	529.0	532.6	530.3
145°	537.2	536.8	544.6	547.8	545.5
147.5°	552.4	551.0	558.8	561.1	559.3
150°	567.1	563.9	571.3	574.0	571.7
152.5°	579.6	575.9	582.8	585.6	582.3
155°	591.5	587.4	593.0	595.7	592.0
157.5°	601.2	597.6	601.7	604.9	601.2
160°	609.5	606.7	609.5	612.3	609.1
162.5°	616.8	614.1	616.4	619.6	615.5
165°	623.3	620.6	621.9	625.2	621.9
167.5°	628.4	625.6	627.0	630.3	626.0
170°	632.5	629.7	630.7	633.9	629.7
172.5°	635.3	632.5	633.5	636.7	632.5
175°	637.5	634.3	635.3	638.5	633.9
177.5°	638.5	635.3	635.7	638.9	634.8
180°	636.2	636.2	636.2	636.2	636.2

TEST NUMBER: P902461

CATALOG NUMBER: DFN2DIP-HX2F0-040D020US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.68	13.63	13.52	14.49	15.56	8.66	9.61	9.50	10.47	11.54
	3H	14.34	15.19	15.20	16.06	17.16	9.84	10.69	10.70	11.56	12.66
	4H	14.94	15.74	15.81	16.62	17.73	10.29	11.09	11.16	11.97	13.08
	6H	15.35	16.09	16.23	16.97	18.09	10.60	11.34	11.48	12.22	13.34
	8H	15.47	16.17	16.36	17.07	18.19	10.69	11.39	11.58	12.29	13.41
	12H	15.52	16.19	16.42	17.08	18.23	10.73	11.40	11.62	12.29	13.44
4H	2H	12.71	13.51	13.59	14.39	15.50	9.26	10.06	10.13	10.94	12.05
	3H	14.52	15.19	15.41	16.10	17.22	10.60	11.27	11.49	12.17	13.30
	4H	15.20	15.81	16.10	16.71	17.86	11.14	11.74	12.04	12.65	13.80
	6H	15.70	16.22	16.61	17.15	18.30	11.55	12.07	12.46	13.00	14.15
	8H	15.86	16.35	16.78	17.27	18.44	11.67	12.16	12.58	13.08	14.24
	12H	15.95	16.39	16.88	17.33	18.50	11.73	12.17	12.66	13.11	14.28
8H	4H	15.17	15.66	16.09	16.58	17.75	11.41	11.90	12.33	12.82	13.99
	6H	15.71	16.12	16.66	17.08	18.25	11.91	12.32	12.85	13.28	14.44
	8H	15.92	16.27	16.87	17.23	18.41	12.09	12.45	13.04	13.40	14.58
	12H	16.04	16.36	17.00	17.30	18.54	12.20	12.51	13.15	13.46	14.69
12H	4H	15.13	15.57	16.06	16.51	17.68	11.42	11.86	12.35	12.80	13.97
	6H	15.69	16.05	16.64	17.00	18.18	11.96	12.31	12.91	13.27	14.45
	8H	15.90	16.21	16.85	17.16	18.39	12.16	12.47	13.11	13.42	14.65