

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910785

Luminaire Tested: DFN2DIP-HX3F0-060D050US850-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910785
REPORT IS A COMBINATION OF REPORTS P900756 AND P897645
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-060D050US850-RLLONL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11145.5 lumens
Efficiency: N/A
Efficacy: 119.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 93.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910785

CATALOG NUMBER: DFN2DIP-HX3F0-060D050US850-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P910785

CATALOG NUMBER: DFN2DIP-HX3F0-060D050US850-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	57	57	51
1	98	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	49	49	44
2	90	83	77	72	83	77	72	67	66	62	59	55	52	50	45	44	42	42	42	37
3	82	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36	36	36	32
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32	32	32	28
5	70	58	50	45	64	54	47	42	47	41	37	40	36	33	33	30	28	28	28	25
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25	25	25	22
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22	22	22	20
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	23	20	20	20	18
9	52	40	32	27	48	37	31	26	32	27	23	28	24	21	24	21	18	18	18	16
10	48	36	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	17	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3186	3186	3186
5°	3189	3133	3153
10°	3156	3069	3049
15°	3111	2966	2889
20°	3052	2824	2693
25°	2992	2665	2504
30°	2911	2502	2264
35°	2833	2328	2054
40°	2752	2148	1813
45°	2659	1948	1595
50°	2562	1747	1382
55°	2461	1532	1177
60°	2344	1307	967
65°	2209	1079	869
70°	2045	867	783
75°	1840	759	709
80°	1542	630	609
85°	1053	410	447

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2659 cd/sqm

TEST NUMBER: P910785

CATALOG NUMBER: DFN2DIP-HX3F0-060D050US850-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	257.7	2.3
10°-20°	707.6	6.3
20°-30°	993.4	8.9
30°-40°	1082.8	9.7
40°-50°	995.2	8.9
50°-60°	781.6	7.0
60°-70°	508.8	4.6
70°-80°	261.9	2.3
80°-90°	70.1	0.6
90°-100°	61.7	0.6
100°-110°	230.0	2.1
110°-120°	610.1	5.5
120°-130°	1011.9	9.1
130°-140°	1074.8	9.6
140°-150°	999.0	9.0
150°-160°	803.1	7.2
160°-170°	517.5	4.6
170°-180°	178.1	1.6
0°-30°	1958.7	17.6
0°-40°	3041.5	27.3
0°-60°	4818.4	43.2
0°-90°	5659.2	50.8
90°-120°	901.9	8.1
90°-150°	3987.5	35.8
90°-180°	5486.0	49.2
0°-180°	11145.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2750	2750	2750	2750	2750	
5°	2750	2738	2705	2728	2720	261
15°	2616	2588	2504	2456	2432	737
25°	2374	2295	2130	2028	1991	1092
35°	2046	1919	1700	1543	1488	1281
45°	1672	1506	1244	1068	1008	1292
55°	1272	1078	809	660	612	1136
65°	859	657	433	349	341	851
75°	458	284	199	182	179	484
85°	107	55	47	47	47	123
90°	1	16	27	34	36	10
95°	88	43	53	60	58	104
105°	412	452	83	98	103	440
115°	779	802	836	209	111	767
125°	1101	1118	1144	1154	1158	982
135°	1362	1384	1396	1410	1407	1052
145°	1580	1579	1602	1611	1605	988
155°	1740	1728	1744	1752	1742	802
165°	1833	1825	1829	1839	1829	518
175°	1875	1866	1869	1878	1865	178
180°	1871	1871	1871	1871	1871	

TEST NUMBER: P910785

CATALOG NUMBER: DFN2DIP-HX3F0-060D050US850-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2750.1	2750.1	2750.1	2750.1	2750.1
2.5°	2762.5	2750.1	2722.6	2747.7	2742.7
5°	2750.1	2737.7	2705.2	2727.7	2720.3
7.5°	2727.7	2712.8	2678.0	2687.8	2675.4
10°	2697.8	2680.3	2630.8	2623.1	2608.3
12.5°	2660.6	2638.1	2570.8	2556.0	2528.5
15°	2615.7	2588.2	2503.7	2456.4	2431.6
17.5°	2563.5	2523.5	2419.0	2364.3	2324.5
20°	2503.7	2453.8	2329.5	2267.4	2212.5
22.5°	2439.0	2381.7	2237.3	2152.8	2115.5
25°	2374.4	2294.6	2130.4	2028.5	1991.0
27.5°	2297.3	2212.5	2030.8	1913.8	1856.6
30°	2215.1	2120.3	1921.2	1794.5	1727.2
32.5°	2135.4	2020.8	1817.0	1667.5	1605.2
35°	2045.9	1918.9	1700.0	1543.1	1488.2
37.5°	1958.7	1821.6	1590.4	1418.5	1356.4
40°	1866.6	1717.4	1475.7	1299.1	1234.4
42.5°	1772.1	1612.8	1361.4	1177.1	1115.1
45°	1672.5	1505.6	1244.5	1067.5	1007.9
47.5°	1578.0	1401.3	1132.5	955.6	901.0
50°	1473.4	1296.8	1022.9	851.0	799.0
52.5°	1371.2	1184.5	918.4	754.1	706.9
55°	1271.7	1077.6	808.8	659.6	612.3
57.5°	1169.8	970.6	711.9	572.5	532.5
60°	1065.2	866.1	609.7	483.0	443.0
62.5°	963.3	764.2	522.6	403.2	383.4
65°	858.7	657.0	433.1	348.6	340.9
67.5°	759.1	557.4	348.6	306.1	298.7
70°	654.5	460.5	288.6	263.8	253.7
72.5°	555.1	370.7	241.3	221.6	216.5
75°	457.9	283.6	199.1	181.7	179.3
77.5°	361.0	201.5	156.8	146.8	141.8
80°	271.2	144.4	119.3	109.6	109.6
82.5°	189.1	97.1	82.1	77.1	77.1
85°	106.9	54.7	47.2	47.2	47.2
87.5°	39.9	19.9	19.9	17.4	17.4
90°	1.3	16.2	27.1	33.9	36.5
92.5°	33.9	28.5	32.5	35.3	36.5
95°	87.9	43.3	52.8	59.7	58.2
97.5°	158.4	47.5	69.0	73.2	74.4
100°	239.8	54.2	77.2	87.9	90.7
102.5°	329.0	326.4	80.0	94.7	98.9
105°	411.7	452.4	82.6	97.5	102.9
107.5°	507.8	541.5	85.4	100.1	105.7
110°	600.0	628.2	237.0	101.6	106.9

TEST NUMBER: P910785

CATALOG NUMBER: DFN2DIP-HX3F0-060D050US850-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	686.6	710.9	687.9	104.2	108.3
115°	778.6	801.6	835.5	208.6	111.1
117.5°	858.5	885.5	908.7	714.9	360.2
120°	947.9	968.2	992.6	1008.9	826.0
122.5°	1023.6	1045.3	1072.5	1080.6	1082.1
125°	1100.8	1118.5	1144.3	1153.7	1157.8
127.5°	1171.2	1190.2	1210.7	1224.1	1225.4
130°	1237.6	1259.4	1274.1	1289.1	1287.9
132.5°	1305.4	1323.0	1337.8	1350.1	1348.8
135°	1362.3	1384.0	1396.0	1409.8	1407.0
137.5°	1421.7	1438.0	1451.7	1465.2	1461.2
140°	1480.0	1490.9	1505.7	1517.9	1511.2
142.5°	1528.9	1538.4	1555.9	1566.7	1559.9
145°	1580.3	1578.9	1601.8	1611.4	1604.6
147.5°	1624.9	1620.8	1643.9	1650.6	1645.3
150°	1668.3	1658.8	1680.5	1688.6	1681.8
152.5°	1704.8	1694.0	1714.3	1722.5	1713.0
155°	1740.0	1727.9	1744.1	1752.2	1741.5
157.5°	1768.4	1757.7	1769.9	1779.4	1768.4
160°	1792.9	1784.7	1792.9	1800.9	1791.5
162.5°	1814.4	1806.5	1813.1	1822.6	1810.4
165°	1833.4	1825.4	1829.4	1838.8	1829.4
167.5°	1848.4	1840.2	1844.4	1853.8	1841.6
170°	1860.6	1852.4	1855.1	1864.6	1852.4
172.5°	1868.7	1860.6	1863.3	1872.8	1860.6
175°	1875.4	1865.9	1868.7	1878.1	1864.6
177.5°	1878.1	1868.7	1870.1	1879.5	1867.3
180°	1871.3	1871.3	1871.3	1871.3	1871.3

TEST NUMBER: P910785

CATALOG NUMBER: DFN2DIP-HX3F0-060D050US850-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.20	12.04	12.16	13.01	14.27	7.18	8.01	8.14	8.98	10.25
	3H	12.87	13.62	13.84	14.60	15.88	8.36	9.11	9.33	10.09	11.37
	4H	13.48	14.18	14.46	15.16	16.46	8.81	9.52	9.79	10.50	11.79
	6H	13.89	14.54	14.88	15.53	16.83	9.13	9.78	10.12	10.76	12.07
	8H	14.01	14.63	15.01	15.64	16.94	9.22	9.84	10.22	10.84	12.14
	12H	14.07	14.66	15.08	15.66	16.98	9.26	9.85	10.26	10.84	12.17
4H	2H	11.22	11.93	12.21	12.91	14.20	7.77	8.48	8.76	9.46	10.75
	3H	13.04	13.63	14.04	14.64	15.95	9.12	9.70	10.11	10.71	12.02
	4H	13.73	14.26	14.73	15.27	16.60	9.66	10.20	10.67	11.20	12.53
	6H	14.24	14.70	15.25	15.72	17.05	10.07	10.54	11.09	11.56	12.89
	8H	14.41	14.84	15.42	15.86	17.20	10.20	10.63	11.22	11.65	12.99
	12H	14.50	14.89	15.53	15.92	17.27	10.26	10.65	11.30	11.69	13.04
8H	4H	13.69	14.12	14.71	15.14	16.49	9.94	10.37	10.95	11.39	12.73
	6H	14.25	14.61	15.29	15.67	17.01	10.45	10.80	11.49	11.87	13.21
	8H	14.46	14.78	15.51	15.82	17.18	10.64	10.95	11.69	12.00	13.36
	12H	14.60	14.87	15.65	15.91	17.32	10.75	11.03	11.80	12.07	13.47
12H	4H	13.65	14.03	14.68	15.07	16.42	9.94	10.33	10.98	11.36	12.71
	6H	14.23	14.54	15.28	15.59	16.95	10.50	10.81	11.54	11.86	13.22
	8H	14.44	14.72	15.49	15.76	17.16	10.70	10.98	11.75	12.02	13.42