

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910823

Luminaire Tested: DFN2DIP-HX3F0-080D030US850-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910823
REPORT IS A COMBINATION OF REPORTS P900731 AND P897645
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-080D030US850-FLLONL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12077.0 lumens
Efficiency: N/A
Efficacy: 117.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 102.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910823

CATALOG NUMBER: DFN2DIP-HX3F0-080D030US850-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P910823

CATALOG NUMBER: DFN2DIP-HX3F0-080D030US850-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77
1	103	98	94	91	97	94	90	87	84	82	79	76	74	72	68	67	65
2	94	86	80	74	89	82	76	71	74	69	66	67	63	60	60	57	55
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47
4	78	67	59	53	74	64	57	51	58	52	47	53	48	44	48	44	40
5	72	60	51	45	68	57	50	44	52	46	41	47	42	38	43	39	35
6	67	54	45	39	63	52	44	38	47	41	36	43	37	33	39	35	31
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28
8	57	44	36	31	54	43	35	30	39	33	28	36	30	27	33	28	25
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22
10	50	38	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3999	3999	3999
5°	4003	3940	3967
10°	3969	3884	3912
15°	3909	3818	3825
20°	3828	3726	3737
25°	3748	3617	3636
30°	3648	3516	3507
35°	3553	3396	3372
40°	3436	3275	3242
45°	3319	3154	3110
50°	3192	3026	2956
55°	3058	2879	2815
60°	2907	2705	2653
65°	2741	2523	2462
70°	2531	2303	2255
75°	2240	2038	2061
80°	1888	1699	1697
85°	1340	1125	1101

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3319 cd/sqm

TEST NUMBER: P910823

CATALOG NUMBER: DFN2DIP-HX3F0-080D030US850-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	324.9	2.7
10°-20°	914.2	7.6
20°-30°	1343.5	11.1
30°-40°	1560.4	12.9
40°-50°	1558.4	12.9
50°-60°	1358.9	11.3
60°-70°	1004.5	8.3
70°-80°	568.4	4.7
80°-90°	152.0	1.3
90°-100°	37.0	0.3
100°-110°	138.0	1.1
110°-120°	366.1	3.0
120°-130°	607.1	5.0
130°-140°	644.9	5.3
140°-150°	599.4	5.0
150°-160°	481.9	4.0
160°-170°	310.5	2.6
170°-180°	106.9	0.9
0°-30°	2582.6	21.4
0°-40°	4143.0	34.3
0°-60°	7060.4	58.5
0°-90°	8785.3	72.7
90°-120°	541.1	4.5
90°-150°	2392.5	19.8
90°-180°	3292.0	27.3
0°-180°	12077.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3452	3452	3452	3452	3452	
5°	3452	3439	3402	3429	3423	328
15°	3286	3267	3223	3237	3220	926
25°	2974	2948	2892	2898	2892	1369
35°	2566	2533	2480	2460	2443	1602
45°	2088	2065	2015	1979	1965	1612
55°	1580	1560	1520	1481	1464	1413
65°	1066	1046	1012	983	966	1054
75°	558	551	534	515	521	595
85°	136	133	130	119	116	152
90°	1	10	16	20	22	11
95°	53	26	32	36	35	63
105°	247	271	50	58	62	264
115°	467	481	501	125	67	460
125°	660	671	687	692	695	589
135°	817	830	838	846	844	631
145°	948	947	961	967	963	593
155°	1044	1037	1046	1051	1045	481
165°	1100	1095	1098	1103	1098	311
175°	1125	1120	1121	1127	1119	107
180°	1123	1123	1123	1123	1123	

TEST NUMBER: P910823

CATALOG NUMBER: DFN2DIP-HX3F0-080D030US850-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3452.1	3452.1	3452.1	3452.1	3452.1
2.5°	3472.2	3455.6	3419.0	3452.1	3445.8
5°	3452.1	3439.1	3402.5	3428.9	3422.6
7.5°	3428.9	3409.2	3372.6	3399.3	3392.7
10°	3392.7	3369.4	3329.6	3355.9	3346.2
12.5°	3342.6	3322.9	3283.1	3299.6	3293.0
15°	3286.3	3266.6	3223.2	3236.6	3220.1
17.5°	3216.5	3196.8	3153.4	3170.1	3153.4
20°	3140.1	3120.4	3073.9	3083.8	3070.7
22.5°	3064.1	3034.1	2990.8	2990.8	2984.1
25°	2974.2	2947.8	2891.5	2897.8	2891.5
27.5°	2874.5	2851.3	2808.3	2798.5	2781.9
30°	2775.3	2748.4	2698.9	2689.0	2675.6
32.5°	2668.9	2649.2	2595.9	2575.9	2562.6
35°	2566.0	2533.0	2479.7	2459.7	2443.1
37.5°	2449.8	2419.8	2366.7	2343.4	2326.9
40°	2330.5	2303.6	2250.5	2220.9	2207.5
42.5°	2214.2	2187.4	2134.6	2101.1	2081.5
45°	2088.1	2064.8	2014.8	1978.6	1965.3
47.5°	1965.3	1942.0	1888.7	1852.1	1832.4
50°	1835.6	1819.1	1772.5	1726.0	1709.5
52.5°	1709.5	1686.2	1643.3	1606.7	1583.4
55°	1580.2	1560.1	1520.4	1480.6	1464.0
57.5°	1450.7	1434.2	1390.8	1351.0	1337.6
60°	1321.0	1308.1	1261.5	1224.9	1215.0
62.5°	1194.9	1171.8	1138.6	1105.6	1092.1
65°	1065.7	1045.7	1012.5	982.6	966.0
67.5°	932.9	916.0	886.4	863.2	849.8
70°	810.0	796.6	766.8	743.5	730.4
72.5°	683.9	670.6	654.0	630.8	620.9
75°	557.5	551.2	534.3	514.6	521.2
77.5°	444.8	431.4	424.7	414.9	405.0
80°	332.1	328.6	321.9	312.1	305.3
82.5°	225.8	225.8	222.6	209.2	209.2
85°	136.0	132.7	129.6	119.4	116.2
87.5°	59.9	53.2	46.5	36.6	33.2
90°	0.8	9.8	16.2	20.4	21.8
92.5°	20.4	17.1	19.5	21.2	21.8
95°	52.8	26.0	31.6	35.8	34.9
97.5°	95.0	28.5	41.4	43.9	44.7
100°	143.8	32.5	46.4	52.8	54.5
102.5°	197.4	195.8	47.9	56.8	59.3
105°	247.0	271.4	49.6	58.4	61.8
107.5°	304.6	324.9	51.2	60.1	63.4
110°	360.0	376.9	142.2	61.0	64.2

TEST NUMBER: P910823

CATALOG NUMBER: DFN2DIP-HX3F0-080D030US850-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	412.0	426.5	412.8	62.5	65.0
115°	467.1	481.0	501.3	125.1	66.7
117.5°	515.1	531.3	545.2	429.0	216.1
120°	568.7	580.9	595.5	605.3	495.6
122.5°	614.2	627.3	643.6	648.3	649.2
125°	660.5	671.1	686.6	692.2	694.7
127.5°	702.8	714.1	726.4	734.5	735.3
130°	742.6	755.7	764.5	773.4	772.8
132.5°	783.2	793.8	802.7	810.0	809.2
135°	817.3	830.4	837.6	845.8	844.2
137.5°	853.0	862.8	871.0	879.1	876.7
140°	888.0	894.5	903.4	910.7	906.7
142.5°	917.4	923.0	933.6	940.0	936.0
145°	948.2	947.3	961.2	966.8	962.7
147.5°	974.9	972.5	986.3	990.3	987.1
150°	1001.0	995.3	1008.3	1013.1	1009.1
152.5°	1022.8	1016.4	1028.6	1033.5	1027.8
155°	1044.0	1036.8	1046.5	1051.3	1044.9
157.5°	1061.1	1054.7	1062.0	1067.6	1061.1
160°	1075.7	1070.9	1075.7	1080.6	1074.8
162.5°	1088.7	1083.8	1087.9	1093.6	1086.3
165°	1100.0	1095.2	1097.7	1103.3	1097.7
167.5°	1109.0	1104.1	1106.6	1112.3	1105.0
170°	1116.3	1111.4	1113.1	1118.8	1111.4
172.5°	1121.2	1116.3	1118.0	1123.6	1116.3
175°	1125.2	1119.5	1121.2	1126.9	1118.8
177.5°	1126.9	1121.2	1122.1	1127.7	1120.4
180°	1122.9	1122.9	1122.9	1122.9	1122.9

TEST NUMBER: P910823

CATALOG NUMBER: DFN2DIP-HX3F0-080D030US850-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.92	15.03	14.66	15.79	16.69	13.49	14.60	14.23	15.36	16.26
	3H	15.59	16.59	16.34	17.36	18.29	15.12	16.12	15.87	16.89	17.82
	4H	16.19	17.13	16.95	17.90	18.85	15.72	16.66	16.48	17.43	18.38
	6H	16.59	17.46	17.37	18.25	19.21	16.12	16.99	16.90	17.78	18.74
	8H	16.70	17.53	17.49	18.33	19.30	16.23	17.06	17.02	17.86	18.83
	12H	16.75	17.55	17.55	18.34	19.33	16.28	17.07	17.07	17.87	18.86
4H	2H	14.41	15.35	15.18	16.13	17.07	14.07	15.01	14.84	15.78	16.73
	3H	16.29	17.08	17.07	17.89	18.85	15.90	16.69	16.68	17.50	18.46
	4H	17.01	17.72	17.80	18.53	19.53	16.61	17.32	17.40	18.13	19.12
	6H	17.53	18.15	18.34	18.98	19.98	17.12	17.74	17.94	18.58	19.58
	8H	17.68	18.26	18.50	19.09	20.10	17.27	17.85	18.09	18.68	19.69
	12H	17.76	18.28	18.60	19.13	20.15	17.35	17.87	18.18	18.72	19.74
8H	4H	17.22	17.80	18.04	18.63	19.64	16.86	17.44	17.68	18.27	19.28
	6H	17.85	18.33	18.70	19.20	20.22	17.49	17.97	18.34	18.85	19.86
	8H	18.07	18.50	18.93	19.37	20.39	17.71	18.13	18.56	19.00	20.03
	12H	18.21	18.59	19.07	19.44	20.53	17.83	18.21	18.69	19.06	20.15
12H	4H	17.22	17.74	18.05	18.59	19.61	16.87	17.39	17.71	18.24	19.26
	6H	17.88	18.31	18.74	19.18	20.21	17.53	17.96	18.39	18.83	19.86
	8H	18.13	18.51	18.99	19.37	20.45	17.78	18.15	18.64	19.01	20.10