

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905157

Luminaire Tested: DFN2DIP-HX2F0-020D040US835-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905157
REPORT IS A COMBINATION OF REPORTS P900692 AND P897595
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-020D040US835-RLLONL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5660.0 lumens
Efficiency: N/A
Efficacy: 126.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 44.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905157

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P905157

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38
1	94	90	86	83	84	81	77	75	64	62	60	48	47	46	34	33	32
2	85	78	73	68	76	71	66	62	56	53	50	43	40	39	30	29	28
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21
5	66	55	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15
8	52	40	33	28	46	36	30	25	29	25	21	23	20	17	17	15	13
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12
10	45	33	27	22	40	30	24	20	25	20	17	20	16	14	14	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1948	1948	1948
5°	1948	1912	1925
10°	1925	1870	1859
15°	1896	1803	1759
20°	1857	1714	1637
25°	1818	1615	1520
30°	1767	1513	1372
35°	1716	1405	1243
40°	1665	1292	1095
45°	1605	1169	961
50°	1543	1045	831
55°	1478	912	705
60°	1403	775	577
65°	1316	635	516
70°	1210	505	462
75°	1078	436	413
80°	887	354	347
85°	579	218	244

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1605 cd/sqm

TEST NUMBER: P905157

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US835-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.5	1.4
10°-20°	212.7	3.8
20°-30°	298.6	5.3
30°-40°	325.5	5.8
40°-50°	299.1	5.3
50°-60°	234.9	4.2
60°-70°	152.9	2.7
70°-80°	78.7	1.4
80°-90°	22.5	0.4
90°-100°	44.5	0.8
100°-110°	165.9	2.9
110°-120°	440.1	7.8
120°-130°	729.9	12.9
130°-140°	775.4	13.7
140°-150°	720.6	12.7
150°-160°	579.4	10.2
160°-170°	373.3	6.6
170°-180°	128.5	2.3
0°-30°	588.7	10.4
0°-40°	914.2	16.2
0°-60°	1448.3	25.6
0°-90°	1702.4	30.1
90°-120°	650.5	11.5
90°-150°	2876.4	50.8
90°-180°	3958.0	69.9
0°-180°	5660.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	827	827	827	827	827	
5°	827	823	813	820	818	78
15°	786	778	752	738	731	222
25°	714	690	640	610	598	328
35°	615	577	511	464	447	385
45°	503	452	374	321	303	388
55°	382	324	243	198	184	342
65°	258	198	130	105	102	256
75°	138	85	60	55	54	146
85°	32	16	14	14	14	37
90°	1	12	20	24	26	5
95°	63	31	38	43	42	75
105°	297	326	60	70	74	317
115°	562	578	603	150	80	553
125°	794	807	825	832	835	708
135°	983	998	1007	1017	1015	759
145°	1140	1139	1156	1162	1158	713
155°	1255	1246	1258	1264	1256	578
165°	1323	1317	1320	1326	1320	374
175°	1353	1346	1348	1355	1345	129
180°	1350	1350	1350	1350	1350	

TEST NUMBER: P905157

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	826.6	826.6	826.6	826.6	826.6
2.5°	830.3	826.6	818.3	825.9	824.4
5°	826.6	822.9	813.1	819.9	817.6
7.5°	819.9	815.4	804.9	807.9	804.1
10°	810.9	805.6	790.7	788.4	784.0
12.5°	799.7	792.9	772.7	768.3	760.0
15°	786.2	777.9	752.5	738.3	730.9
17.5°	770.5	758.5	727.1	710.6	698.7
20°	752.5	737.5	700.2	681.5	665.0
22.5°	733.1	715.9	672.5	647.1	635.9
25°	713.7	689.7	640.3	609.7	598.4
27.5°	690.5	665.0	610.4	575.2	558.0
30°	665.8	637.3	577.5	539.4	519.1
32.5°	641.8	607.4	546.1	501.2	482.5
35°	614.9	576.8	511.0	463.8	447.3
37.5°	588.7	547.5	478.0	426.4	407.7
40°	561.0	516.2	443.6	390.5	371.0
42.5°	532.6	484.8	409.2	353.8	335.2
45°	502.7	452.5	374.1	320.9	302.9
47.5°	474.3	421.2	340.4	287.2	270.8
50°	442.9	389.8	307.5	255.8	240.2
52.5°	412.1	356.0	276.0	226.7	212.5
55°	382.2	323.9	243.1	198.3	184.0
57.5°	351.6	291.7	214.0	172.1	160.1
60°	320.2	260.3	183.3	145.2	133.2
62.5°	289.5	229.7	157.1	121.2	115.2
65°	258.1	197.5	130.2	104.8	102.5
67.5°	228.2	167.5	104.8	92.0	89.8
70°	196.7	138.4	86.7	79.3	76.3
72.5°	166.8	111.4	72.5	66.6	65.1
75°	137.6	85.2	59.8	54.6	53.9
77.5°	108.5	60.6	47.1	44.1	42.6
80°	81.5	43.4	35.9	32.9	32.9
82.5°	56.8	29.2	24.7	23.2	23.2
85°	32.1	16.4	14.2	14.2	14.2
87.5°	12.0	6.0	6.0	5.2	5.2
90°	0.9	11.7	19.5	24.5	26.3
92.5°	24.5	20.5	23.4	25.4	26.3
95°	63.4	31.2	38.0	43.0	42.0
97.5°	114.3	34.2	49.8	52.8	53.7
100°	172.9	39.1	55.7	63.4	65.4
102.5°	237.3	235.5	57.6	68.3	71.3
105°	296.9	326.3	59.6	70.3	74.2
107.5°	366.3	390.7	61.6	72.3	76.2
110°	432.8	453.2	171.0	73.3	77.1

TEST NUMBER: P905157

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	495.3	512.8	496.2	75.2	78.2
115°	561.6	578.2	602.7	150.4	80.2
117.5°	619.3	638.8	655.5	515.7	259.8
120°	683.8	698.4	716.0	727.8	595.9
122.5°	738.4	754.1	773.7	779.5	780.5
125°	794.1	806.9	825.4	832.3	835.2
127.5°	844.9	858.6	873.3	883.1	884.0
130°	892.8	908.5	919.1	929.9	929.0
132.5°	941.6	954.4	965.1	973.9	973.0
135°	982.7	998.4	1007.1	1016.9	1015.0
137.5°	1025.6	1037.3	1047.2	1056.9	1054.0
140°	1067.6	1075.5	1086.2	1095.0	1090.1
142.5°	1102.9	1109.7	1122.4	1130.1	1125.3
145°	1140.0	1139.0	1155.5	1162.4	1157.5
147.5°	1172.1	1169.2	1185.8	1190.7	1186.9
150°	1203.4	1196.6	1212.3	1218.1	1213.2
152.5°	1229.8	1222.0	1236.6	1242.5	1235.7
155°	1255.2	1246.5	1258.2	1264.0	1256.2
157.5°	1275.7	1267.9	1276.8	1283.6	1275.7
160°	1293.3	1287.4	1293.3	1299.1	1292.3
162.5°	1308.9	1303.1	1308.0	1314.8	1306.0
165°	1322.6	1316.8	1319.7	1326.5	1319.7
167.5°	1333.4	1327.4	1330.5	1337.3	1328.5
170°	1342.2	1336.3	1338.2	1345.1	1336.3
172.5°	1348.0	1342.2	1344.2	1351.0	1342.2
175°	1352.8	1346.0	1348.0	1354.8	1345.1
177.5°	1354.8	1348.0	1349.0	1355.9	1347.1
180°	1350.0	1350.0	1350.0	1350.0	1350.0

TEST NUMBER: P905157

CATALOG NUMBER: DFN2DIP-HX2F0-020D040US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.10	7.79	8.22	8.90	10.43	3.09	3.78	4.20	4.89	6.42
	3H	8.75	9.36	9.87	10.48	12.03	4.25	4.87	5.37	5.98	7.53
	4H	9.33	9.92	10.46	11.03	12.59	4.68	5.27	5.82	6.38	7.94
	6H	9.72	10.26	10.87	11.38	12.95	4.98	5.52	6.12	6.64	8.20
	8H	9.84	10.35	10.98	11.48	13.04	5.06	5.57	6.20	6.71	8.26
	12H	9.88	10.37	11.03	11.50	13.08	5.09	5.58	6.24	6.70	8.28
4H	2H	7.10	7.69	8.24	8.80	10.36	3.65	4.24	4.79	5.35	6.91
	3H	8.89	9.38	10.04	10.52	12.08	4.97	5.46	6.12	6.60	8.17
	4H	9.56	10.00	10.71	11.13	12.72	5.50	5.95	6.65	7.08	8.66
	6H	10.04	10.42	11.19	11.58	13.15	5.89	6.27	7.05	7.43	9.00
	8H	10.20	10.56	11.35	11.70	13.29	6.01	6.36	7.16	7.51	9.10
	12H	10.27	10.60	11.44	11.75	13.35	6.06	6.38	7.23	7.54	9.13
8H	4H	9.51	9.87	10.66	11.01	12.60	5.75	6.11	6.91	7.26	8.85
	6H	10.04	10.34	11.22	11.53	13.12	6.24	6.54	7.42	7.72	9.31
	8H	10.24	10.50	11.42	11.67	13.28	6.42	6.68	7.60	7.84	9.45
	12H	10.36	10.58	11.54	11.75	13.39	6.52	6.74	7.70	7.91	9.55
12H	4H	9.45	9.78	10.62	10.93	12.53	5.75	6.07	6.92	7.23	8.83
	6H	10.02	10.27	11.20	11.44	13.05	6.28	6.54	7.46	7.71	9.32
	8H	10.21	10.44	11.40	11.60	13.25	6.47	6.70	7.66	7.86	9.51

END OF REPORT