

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905163

Luminaire Tested: DFN2DIP-HX2F0-020D060US835-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905163
REPORT IS A COMBINATION OF REPORTS P900711 AND P897595
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-020D060US835-FLLONL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7920.0 lumens
Efficiency: N/A
Efficacy: 124.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 63.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905163

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US835-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P905163

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US835-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	51	51	51	33	33	33
1	92	88	84	81	82	79	75	73	61	59	57	44	43	42	29	29	28
2	84	77	71	66	74	69	64	59	53	50	47	39	37	35	26	25	24
3	76	67	60	55	68	60	54	50	47	43	39	34	32	30	23	21	20
4	70	60	52	46	62	53	47	42	42	37	33	31	28	25	20	19	17
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15
6	59	47	40	34	52	42	36	31	33	28	25	25	21	19	17	15	13
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12
8	50	38	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10
9	47	35	28	23	41	31	25	21	25	20	17	19	15	13	13	11	9
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1834	1834	1834
5°	1834	1804	1817
10°	1816	1775	1789
15°	1786	1741	1747
20°	1747	1696	1704
25°	1708	1644	1656
30°	1660	1594	1595
35°	1615	1536	1530
40°	1559	1478	1469
45°	1503	1419	1405
50°	1442	1357	1333
55°	1378	1286	1265
60°	1305	1202	1187
65°	1225	1114	1096
70°	1124	1007	997
75°	984	879	901
80°	815	716	726
85°	552	449	450

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1851 cd/sqm

TEST NUMBER: P905163

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US835-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.2	0.9
10°-20°	206.1	2.6
20°-30°	302.9	3.8
30°-40°	351.8	4.4
40°-50°	351.3	4.4
50°-60°	306.3	3.9
60°-70°	226.5	2.9
70°-80°	128.1	1.6
80°-90°	37.4	0.5
90°-100°	66.8	0.8
100°-110°	248.9	3.1
110°-120°	660.2	8.3
120°-130°	1094.9	13.8
130°-140°	1163.0	14.7
140°-150°	1080.9	13.6
150°-160°	869.0	11.0
160°-170°	560.0	7.1
170°-180°	192.7	2.4
0°-30°	582.2	7.4
0°-40°	934.0	11.8
0°-60°	1591.6	20.1
0°-90°	1983.6	25.0
90°-120°	975.8	12.3
90°-150°	4314.7	54.5
90°-180°	5936.0	74.9
0°-180°	7920.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	778	778	778	778	778	
5°	778	775	767	773	772	74
15°	741	736	727	730	726	209
25°	670	664	652	653	652	309
35°	578	571	559	554	551	361
45°	471	466	454	446	443	363
55°	356	352	343	334	330	318
65°	240	236	228	222	218	238
75°	126	124	120	116	118	134
85°	31	30	29	27	26	34
90°	1	18	29	37	40	7
95°	95	47	57	65	63	113
105°	445	489	89	105	111	476
115°	842	867	904	226	120	829
125°	1191	1210	1238	1248	1253	1062
135°	1474	1498	1511	1525	1522	1139
145°	1710	1708	1733	1744	1736	1069
155°	1883	1870	1887	1896	1884	868
165°	1984	1975	1980	1990	1980	560
175°	2029	2019	2022	2032	2018	193
180°	2025	2025	2025	2025	2025	

TEST NUMBER: P905163

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	778.2	778.2	778.2	778.2	778.2
2.5°	782.7	779.0	770.7	778.2	776.8
5°	778.2	775.3	767.0	773.0	771.5
7.5°	773.0	768.5	760.3	766.3	764.8
10°	764.8	759.6	750.6	756.5	754.3
12.5°	753.5	749.1	740.1	743.8	742.3
15°	740.8	736.4	726.6	729.6	725.9
17.5°	725.1	720.7	710.9	714.6	710.9
20°	707.9	703.4	692.9	695.2	692.2
22.5°	690.7	684.0	674.2	674.2	672.7
25°	670.5	664.5	651.8	653.2	651.8
27.5°	648.0	642.8	633.1	630.9	627.1
30°	625.6	619.6	608.4	606.2	603.1
32.5°	601.6	597.2	585.2	580.7	577.7
35°	578.5	571.0	559.0	554.5	550.7
37.5°	552.3	545.5	533.5	528.3	524.5
40°	525.3	519.3	507.3	500.7	497.6
42.5°	499.1	493.1	481.2	473.7	469.2
45°	470.7	465.5	454.2	446.0	443.0
47.5°	443.0	437.8	425.8	417.5	413.1
50°	413.8	410.1	399.6	389.1	385.4
52.5°	385.4	380.1	370.4	362.2	357.0
55°	356.2	351.7	342.7	333.8	330.0
57.5°	327.0	323.3	313.5	304.6	301.5
60°	297.8	294.9	284.4	276.1	273.9
62.5°	269.4	264.1	256.7	249.2	246.2
65°	240.2	235.7	228.3	221.5	217.8
67.5°	210.3	206.5	199.8	194.6	191.6
70°	182.6	179.6	172.8	167.6	164.7
72.5°	154.2	151.2	147.4	142.2	140.0
75°	125.7	124.3	120.4	116.0	117.5
77.5°	100.3	97.3	95.7	93.5	91.3
80°	74.9	74.1	72.6	70.3	68.8
82.5°	50.9	50.9	50.2	47.2	47.2
85°	30.6	29.9	29.2	26.9	26.2
87.5°	13.5	12.0	10.5	8.3	7.5
90°	1.4	17.6	29.2	36.7	39.5
92.5°	36.7	30.8	35.1	38.1	39.5
95°	95.2	46.8	57.1	64.6	63.0
97.5°	171.4	51.3	74.6	79.2	80.6
100°	259.4	58.6	83.5	95.2	98.1
102.5°	356.0	353.2	86.5	102.5	107.0
105°	445.4	489.4	89.4	105.4	111.4
107.5°	549.5	586.0	92.4	108.4	114.3
110°	649.2	679.8	256.5	110.0	115.7

TEST NUMBER: P905163

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	742.9	769.2	744.3	112.7	117.3
115°	842.5	867.4	904.1	225.7	120.2
117.5°	928.9	958.2	983.2	773.6	389.7
120°	1025.7	1047.6	1074.1	1091.6	893.8
122.5°	1107.6	1131.1	1160.5	1169.2	1170.8
125°	1191.2	1210.3	1238.1	1248.4	1252.7
127.5°	1267.4	1287.9	1310.0	1324.6	1326.0
130°	1339.2	1362.7	1378.7	1394.9	1393.5
132.5°	1412.5	1431.6	1447.6	1460.8	1459.4
135°	1474.1	1497.6	1510.6	1525.4	1522.4
137.5°	1538.4	1556.0	1570.8	1585.4	1581.1
140°	1601.4	1613.3	1629.3	1642.5	1635.2
142.5°	1654.3	1664.6	1683.6	1695.2	1687.9
145°	1710.0	1708.4	1733.3	1743.6	1736.3
147.5°	1758.2	1753.8	1778.7	1786.0	1780.3
150°	1805.2	1794.9	1818.4	1827.1	1819.8
152.5°	1844.7	1833.0	1854.9	1863.8	1853.5
155°	1882.8	1869.7	1887.3	1896.0	1884.3
157.5°	1913.6	1901.9	1915.1	1925.4	1913.6
160°	1940.0	1931.1	1940.0	1948.7	1938.5
162.5°	1963.3	1954.6	1961.9	1972.2	1959.0
165°	1983.9	1975.2	1979.5	1989.8	1979.5
167.5°	2000.0	1991.2	1995.7	2006.0	1992.7
170°	2013.3	2004.4	2007.4	2017.6	2004.4
172.5°	2022.0	2013.3	2016.2	2026.5	2013.3
175°	2029.3	2019.0	2022.0	2032.2	2017.6
177.5°	2032.2	2022.0	2023.5	2033.8	2020.6
180°	2024.9	2024.9	2024.9	2024.9	2024.9

TEST NUMBER: P905163

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US835-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.30	6.97	7.45	8.11	9.70	5.88	6.55	7.02	7.69	9.27
	3H	7.92	8.52	9.07	9.67	11.27	7.46	8.06	8.61	9.21	10.81
	4H	8.48	9.06	9.64	10.20	11.81	8.02	8.60	9.19	9.74	11.35
	6H	8.85	9.38	10.02	10.53	12.15	8.39	8.92	9.56	10.07	11.69
	8H	8.94	9.45	10.12	10.61	12.22	8.48	8.99	9.66	10.15	11.76
	12H	8.98	9.45	10.15	10.61	12.24	8.51	8.99	9.69	10.14	11.78
4H	2H	6.73	7.30	7.90	8.44	10.05	6.39	6.96	7.56	8.11	9.71
	3H	8.55	9.03	9.72	10.19	11.81	8.16	8.64	9.34	9.81	11.43
	4H	9.23	9.68	10.41	10.83	12.47	8.84	9.28	10.02	10.44	12.08
	6H	9.72	10.09	10.90	11.27	12.90	9.32	9.70	10.50	10.88	12.50
	8H	9.85	10.20	11.03	11.37	13.02	9.45	9.80	10.63	10.97	12.62
	12H	9.90	10.22	11.10	11.40	13.05	9.50	9.82	10.69	11.00	12.65
8H	4H	9.40	9.76	10.58	10.93	12.57	9.05	9.41	10.23	10.58	12.22
	6H	10.00	10.29	11.20	11.50	13.14	9.65	9.94	10.85	11.15	12.79
	8H	10.20	10.45	11.41	11.64	13.31	9.84	10.10	11.05	11.29	12.95
	12H	10.31	10.53	11.52	11.72	13.41	9.94	10.16	11.15	11.35	13.04
12H	4H	9.38	9.70	10.57	10.88	12.53	9.03	9.35	10.23	10.54	12.19
	6H	10.02	10.28	11.23	11.47	13.13	9.68	9.93	10.88	11.12	12.79
	8H	10.24	10.46	11.44	11.65	13.34	9.89	10.11	11.10	11.30	12.99

END OF REPORT