

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913451

Luminaire Tested: DFN2DIP-HX3F0-030D080US927-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913451
REPORT IS A COMBINATION OF REPORTS P899272 AND P896089
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-030D080US927-RLLFLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7628.7 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 85
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913451

CATALOG NUMBER: DFN2DIP-HX3F0-030D080US927-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P913451

CATALOG NUMBER: DFN2DIP-HX3F0-030D080US927-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35
1	93	89	85	82	83	79	76	74	62	60	58	46	44	43	31	30	30
2	85	78	72	67	75	70	65	61	54	51	48	40	38	37	27	26	25
3	77	68	62	56	69	61	56	51	48	44	41	36	33	31	25	23	22
4	71	61	53	48	63	54	48	43	43	38	35	32	29	27	22	20	19
5	65	54	46	41	58	49	42	37	38	34	30	29	26	23	20	18	17
6	60	48	41	35	53	44	37	32	35	30	26	26	23	20	18	16	15
7	55	44	36	31	49	39	33	28	31	27	23	24	21	18	17	15	13
8	51	39	32	27	46	36	29	25	28	24	20	22	18	16	15	13	12
9	48	36	29	24	42	33	26	22	26	21	18	20	17	14	14	12	11
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1138	1138	1138
5°	1139	1119	1126
10°	1127	1096	1089
15°	1111	1059	1032
20°	1090	1008	962
25°	1069	952	894
30°	1040	894	809
35°	1012	831	734
40°	983	767	648
45°	950	696	570
50°	915	624	493
55°	879	547	420
60°	837	467	346
65°	789	385	310
70°	731	310	280
75°	657	271	253
80°	551	225	217
85°	376	147	160

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1886 cd/sqm

TEST NUMBER: P913451

CATALOG NUMBER: DFN2DIP-HX3F0-030D080US927-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.1	1.2
10°-20°	252.7	3.3
20°-30°	354.8	4.7
30°-40°	386.8	5.1
40°-50°	355.5	4.7
50°-60°	279.2	3.7
60°-70°	181.7	2.4
70°-80°	93.5	1.2
80°-90°	29.6	0.4
90°-100°	124.0	1.6
100°-110°	394.1	5.2
110°-120°	674.4	8.8
120°-130°	886.9	11.6
130°-140°	995.5	13.0
140°-150°	976.2	12.8
150°-160°	818.9	10.7
160°-170°	543.1	7.1
170°-180°	189.8	2.5
0°-30°	699.6	9.2
0°-40°	1086.3	14.2
0°-60°	1720.9	22.6
0°-90°	2025.8	26.6
90°-120°	1192.5	15.6
90°-150°	4051.1	53.1
90°-180°	5603.0	73.4
0°-180°	7628.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	982	982	982	982	982	
5°	982	978	966	974	972	93
15°	934	924	894	877	868	263
25°	848	820	761	724	711	390
35°	731	685	607	551	532	457
45°	597	538	444	381	360	461
55°	454	385	289	236	219	406
65°	307	235	155	124	122	304
75°	164	101	71	65	64	173
85°	38	20	17	17	17	44
90°	2	22	59	56	57	8
95°	88	105	108	108	105	98
105°	364	369	372	375	375	384
115°	677	686	683	682	677	669
125°	984	999	995	989	987	880
135°	1273	1292	1296	1294	1289	984
145°	1546	1558	1567	1569	1563	966
155°	1767	1772	1778	1786	1781	813
165°	1923	1921	1921	1933	1924	542
175°	2001	1996	1992	2004	1994	190
180°	2004	2004	2004	2004	2004	

TEST NUMBER: P913451

CATALOG NUMBER: DFN2DIP-HX3F0-030D080US927-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	982.2	982.2	982.2	982.2	982.2
2.5°	986.7	982.2	972.4	981.4	979.6
5°	982.2	977.8	966.2	974.2	971.5
7.5°	974.2	968.9	956.5	960.0	955.5
10°	963.5	957.4	939.6	936.8	931.6
12.5°	950.2	942.2	918.2	912.9	903.1
15°	934.2	924.4	894.2	877.3	868.5
17.5°	915.5	901.3	864.0	844.5	830.2
20°	894.2	876.4	831.9	809.8	790.2
22.5°	871.2	850.6	799.1	768.9	755.6
25°	848.0	819.5	760.9	724.4	711.1
27.5°	820.5	790.2	725.3	683.6	663.1
30°	791.2	757.3	686.2	641.0	616.9
32.5°	762.6	721.8	649.0	595.6	573.3
35°	730.7	685.3	607.1	551.1	531.6
37.5°	699.6	650.6	568.0	506.6	484.5
40°	666.7	613.4	527.1	464.0	440.9
42.5°	632.9	576.1	486.2	420.4	398.2
45°	597.4	537.7	444.5	381.3	360.0
47.5°	563.6	500.5	404.5	341.3	321.8
50°	526.2	463.1	365.4	304.0	285.3
52.5°	489.7	423.1	328.0	269.3	252.5
55°	454.2	384.8	288.8	235.6	218.7
57.5°	417.8	346.7	254.3	204.5	190.2
60°	380.4	309.3	217.8	172.5	158.3
62.5°	344.0	272.9	186.6	144.0	137.0
65°	306.7	234.6	154.6	124.5	121.8
67.5°	271.2	199.1	124.5	109.3	106.6
70°	233.8	164.5	103.1	94.2	90.6
72.5°	198.2	132.4	86.2	79.1	77.3
75°	163.5	101.3	71.1	64.9	64.0
77.5°	128.9	71.9	56.0	52.4	50.6
80°	96.9	51.6	42.6	39.1	39.1
82.5°	67.5	34.7	29.3	27.6	27.6
85°	38.2	19.5	16.9	16.9	16.9
87.5°	14.3	7.1	7.1	6.3	6.3
90°	1.8	21.8	59.3	55.6	57.4
92.5°	37.5	50.8	52.6	54.3	54.3
95°	88.2	105.1	108.1	108.1	105.1
97.5°	146.9	162.6	169.2	169.2	169.2
100°	214.5	228.4	233.2	233.2	231.4
102.5°	285.8	296.1	302.7	304.5	302.7
105°	363.8	368.6	372.2	375.3	375.3
107.5°	441.1	448.4	448.4	449.6	441.1
110°	516.0	525.7	525.7	525.7	520.9

TEST NUMBER: P913451

CATALOG NUMBER: DFN2DIP-HX3F0-030D080US927-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	597.0	607.3	605.5	600.6	597.0
115°	676.8	686.4	683.4	681.6	676.8
117.5°	755.9	769.2	760.7	755.9	751.1
120°	835.7	849.0	835.7	835.7	830.2
122.5°	908.2	925.1	916.6	911.8	908.2
125°	984.3	999.4	994.6	989.1	987.4
127.5°	1058.7	1077.4	1070.7	1063.5	1058.7
130°	1128.1	1149.9	1146.8	1143.3	1136.6
132.5°	1206.1	1223.0	1224.2	1215.8	1210.9
135°	1273.1	1291.9	1295.5	1293.7	1288.9
137.5°	1348.1	1363.2	1366.2	1365.0	1357.7
140°	1414.0	1429.0	1437.5	1437.5	1430.8
142.5°	1481.6	1496.7	1501.6	1503.4	1496.7
145°	1545.7	1557.7	1567.4	1569.2	1562.6
147.5°	1603.1	1618.2	1625.4	1628.5	1621.8
150°	1662.3	1672.5	1679.2	1684.7	1679.2
152.5°	1714.8	1725.1	1733.6	1740.3	1733.6
155°	1767.4	1772.3	1777.7	1786.1	1780.7
157.5°	1812.7	1816.4	1819.4	1831.4	1823.0
160°	1853.2	1856.9	1858.7	1868.9	1861.7
162.5°	1890.7	1890.7	1892.5	1904.0	1895.5
165°	1922.7	1920.9	1920.9	1933.0	1924.5
167.5°	1951.7	1946.3	1946.3	1958.4	1949.9
170°	1973.5	1968.6	1966.8	1978.9	1968.6
172.5°	1988.6	1983.8	1982.0	1994.0	1983.8
175°	2000.7	1995.8	1992.2	2004.3	1994.0
177.5°	2007.3	2002.5	1998.8	2009.1	1998.8
180°	2004.3	2004.3	2004.3	2004.3	2004.3

TEST NUMBER: P913451

CATALOG NUMBER: DFN2DIP-HX3F0-030D080US927-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.82	5.49	5.96	6.62	8.19	0.80	1.47	1.94	2.59	4.17
	3H	6.48	7.08	7.62	8.21	9.80	1.97	2.57	3.11	3.70	5.29
	4H	7.07	7.64	8.23	8.78	10.37	2.41	2.97	3.56	4.11	5.70
	6H	7.48	8.00	8.64	9.14	10.74	2.71	3.24	3.88	4.37	5.98
	8H	7.60	8.09	8.76	9.25	10.84	2.80	3.30	3.97	4.45	6.04
	12H	7.65	8.12	8.82	9.27	10.89	2.83	3.31	4.01	4.45	6.07
4H	2H	4.82	5.38	5.98	6.52	8.11	1.37	1.93	2.53	3.07	4.66
	3H	6.62	7.10	7.79	8.26	9.86	2.70	3.17	3.86	4.33	5.93
	4H	7.30	7.74	8.47	8.89	10.51	3.23	3.67	4.40	4.82	6.44
	6H	7.80	8.17	8.98	9.35	10.96	3.64	4.01	4.81	5.18	6.80
	8H	7.97	8.32	9.14	9.48	11.11	3.76	4.11	4.94	5.27	6.90
	12H	8.05	8.37	9.24	9.54	11.18	3.82	4.13	5.01	5.31	6.94
8H	4H	7.26	7.60	8.43	8.77	10.40	3.50	3.84	4.67	5.01	6.64
	6H	7.81	8.09	9.00	9.30	10.93	4.00	4.29	5.20	5.49	7.12
	8H	8.02	8.27	9.22	9.45	11.10	4.19	4.44	5.39	5.62	7.27
	12H	8.14	8.36	9.35	9.54	11.22	4.30	4.52	5.50	5.70	7.38
12H	4H	7.20	7.52	8.39	8.69	10.33	3.49	3.81	4.68	4.98	6.62
	6H	7.78	8.03	8.98	9.22	10.86	4.05	4.30	5.25	5.48	7.13
	8H	7.99	8.21	9.19	9.39	11.07	4.25	4.47	5.45	5.65	7.33

END OF REPORT