

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913463

Luminaire Tested: DFN2DIP-HX3F0-040D050US927-FLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P913463  
REPORT IS A COMBINATION OF REPORTS P900751 AND P897645  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX3F0-040D050US927-FLLONL  
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7058.3 lumens  
Efficiency: N/A  
Efficacy: 99.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 71.1  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9968  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P913463  
CATALOG NUMBER: DFN2DIP-HX3F0-040D050US927-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P913463

CATALOG NUMBER: DFN2DIP-HX3F0-040D050US927-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44				44
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43	37				37
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36	31				31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	27				27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	31	29	27	23				23
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	28	25	23	20				20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	17				17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15				15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14				14
9	49	37	30	25	45	35	28	23	29	24	20	25	20	18	20	17	15	12				12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11				11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1428	1428	1428
5°	1430	1407	1417
10°	1418	1387	1397
15°	1396	1364	1366
20°	1367	1331	1335
25°	1339	1292	1299
30°	1303	1256	1253
35°	1269	1213	1204
40°	1227	1170	1158
45°	1186	1126	1111
50°	1140	1081	1056
55°	1092	1028	1005
60°	1038	966	948
65°	979	901	879
70°	904	823	806
75°	800	728	736
80°	674	606	607
85°	479	402	393

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1186 cd/sqm



TEST NUMBER: P913463

CATALOG NUMBER: DFN2DIP-HX3F0-040D050US927-FLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	116.0	1.6
10°-20°	326.5	4.6
20°-30°	479.8	6.8
30°-40°	557.3	7.9
40°-50°	556.6	7.9
50°-60°	485.3	6.9
60°-70°	358.8	5.1
70°-80°	203.0	2.9
80°-90°	55.9	0.8
90°-100°	44.1	0.6
100°-110°	164.3	2.3
110°-120°	435.8	6.2
120°-130°	722.8	10.2
130°-140°	767.8	10.9
140°-150°	713.6	10.1
150°-160°	573.7	8.1
160°-170°	369.7	5.2
170°-180°	127.2	1.8
0°-30°	922.4	13.1
0°-40°	1479.7	21.0
0°-60°	2521.7	35.7
0°-90°	3139.4	44.5
90°-120°	644.2	9.1
90°-150°	2848.4	40.4
90°-180°	3919.0	55.5
0°-180°	7058.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1233	1233	1233	1233	1233	
5°	1233	1228	1215	1225	1222	117
15°	1174	1167	1151	1156	1150	331
25°	1062	1053	1033	1035	1033	489
35°	916	905	886	878	873	572
45°	746	738	720	707	702	576
55°	564	557	543	529	523	505
65°	381	373	362	351	345	376
75°	199	197	191	184	186	213
85°	49	48	46	43	42	54
90°	1	12	19	24	26	7
95°	63	31	38	43	42	74
105°	294	323	59	70	74	314
115°	556	573	597	149	79	548
125°	786	799	817	824	827	701
135°	973	989	997	1007	1005	752
145°	1129	1128	1144	1151	1146	706
155°	1243	1234	1246	1252	1244	573
165°	1310	1304	1307	1314	1307	370
175°	1340	1333	1335	1342	1332	127
180°	1337	1337	1337	1337	1337	



TEST NUMBER: P913463

CATALOG NUMBER: DFN2DIP-HX3F0-040D050US927-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1233.0	1233.0	1233.0	1233.0	1233.0
2.5°	1240.2	1234.2	1221.1	1233.0	1230.7
5°	1233.0	1228.3	1215.2	1224.6	1222.4
7.5°	1224.6	1217.6	1204.5	1214.1	1211.7
10°	1211.7	1203.4	1189.2	1198.6	1195.1
12.5°	1193.8	1186.8	1172.6	1178.5	1176.1
15°	1173.7	1166.6	1151.2	1156.0	1150.1
17.5°	1148.8	1141.8	1126.3	1132.2	1126.3
20°	1121.5	1114.4	1097.9	1101.4	1096.8
22.5°	1094.3	1083.6	1068.2	1068.2	1065.8
25°	1062.2	1052.8	1032.7	1035.0	1032.7
27.5°	1026.7	1018.3	1003.1	999.5	993.6
30°	991.2	981.7	963.9	960.4	955.6
32.5°	953.2	946.2	927.2	920.0	915.2
35°	916.5	904.7	885.7	878.5	872.6
37.5°	875.0	864.3	845.3	837.0	831.1
40°	832.3	822.8	803.7	793.2	788.5
42.5°	790.8	781.2	762.4	750.4	743.4
45°	745.8	737.5	719.6	706.7	701.9
47.5°	701.9	693.6	674.6	661.6	654.5
50°	655.6	649.7	633.1	616.5	610.5
52.5°	610.5	602.3	586.9	573.9	565.5
55°	564.4	557.2	543.0	528.8	522.9
57.5°	518.1	512.2	496.7	482.5	477.8
60°	471.8	467.1	450.6	437.5	434.0
62.5°	426.8	418.5	406.7	394.8	390.1
65°	380.6	373.4	361.6	350.9	345.1
67.5°	333.2	327.2	316.6	308.3	303.6
70°	289.3	284.6	273.9	265.5	260.9
72.5°	244.3	239.5	233.6	225.3	221.7
75°	199.2	196.9	190.8	183.8	186.2
77.5°	158.8	154.1	151.7	148.1	144.7
80°	118.6	117.3	114.9	111.5	109.1
82.5°	80.6	80.6	79.5	74.7	74.7
85°	48.6	47.5	46.3	42.6	41.5
87.5°	21.4	19.0	16.6	13.1	11.8
90°	1.0	11.6	19.3	24.2	26.1
92.5°	24.2	20.4	23.2	25.2	26.1
95°	62.8	30.9	37.7	42.6	41.6
97.5°	113.1	33.9	49.3	52.3	53.2
100°	171.3	38.7	55.1	62.8	64.8
102.5°	235.0	233.1	57.1	67.7	70.7
105°	294.1	323.1	59.0	69.6	73.5
107.5°	362.7	386.8	61.0	71.5	75.5
110°	428.6	448.8	169.3	72.6	76.4



TEST NUMBER: P913463

CATALOG NUMBER: DFN2DIP-HX3F0-040D050US927-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	490.4	507.8	491.4	74.5	77.4
115°	556.2	572.6	596.8	149.0	79.4
117.5°	613.2	632.6	649.1	510.6	257.3
120°	677.1	691.6	709.0	720.6	590.0
122.5°	731.2	746.7	766.1	771.9	772.9
125°	786.3	799.0	817.4	824.1	827.0
127.5°	836.6	850.2	864.8	874.4	875.4
130°	884.1	899.6	910.1	920.8	920.0
132.5°	932.5	945.1	955.6	964.4	963.5
135°	973.1	988.6	997.2	1007.0	1005.0
137.5°	1015.6	1027.2	1037.0	1046.6	1043.8
140°	1057.2	1065.0	1075.5	1084.3	1079.5
142.5°	1092.1	1098.9	1111.4	1119.1	1114.3
145°	1128.9	1127.8	1144.2	1151.0	1146.2
147.5°	1160.7	1157.8	1174.3	1179.1	1175.3
150°	1191.7	1184.9	1200.4	1206.2	1201.3
152.5°	1217.7	1210.1	1224.6	1230.4	1223.6
155°	1242.9	1234.3	1245.9	1251.6	1244.0
157.5°	1263.2	1255.5	1264.2	1271.1	1263.2
160°	1280.7	1274.9	1280.7	1286.4	1279.7
162.5°	1296.1	1290.4	1295.1	1301.9	1293.2
165°	1309.6	1303.9	1306.8	1313.5	1306.8
167.5°	1320.3	1314.5	1317.5	1324.2	1315.5
170°	1329.0	1323.2	1325.2	1331.9	1323.2
172.5°	1334.8	1329.0	1331.0	1337.8	1329.0
175°	1339.7	1332.8	1334.8	1341.6	1331.9
177.5°	1341.6	1334.8	1335.9	1342.6	1333.9
180°	1336.7	1336.7	1336.7	1336.7	1336.7



TEST NUMBER: P913463  
 CATALOG NUMBER: DFN2DIP-HX3F0-040D050US927-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.93	8.75	8.94	9.76	11.11	7.50	8.32	8.51	9.33	10.68
	3H	9.58	10.31	10.60	11.34	12.70	9.11	9.84	10.13	10.87	12.23
	4H	10.16	10.85	11.19	11.88	13.26	9.69	10.39	10.72	11.41	12.79
	6H	10.55	11.19	11.59	12.22	13.61	10.08	10.72	11.12	11.75	13.14
	8H	10.65	11.26	11.70	12.31	13.69	10.19	10.79	11.23	11.84	13.22
	12H	10.70	11.27	11.75	12.31	13.72	10.22	10.80	11.27	11.84	13.25
4H	2H	8.39	9.08	9.42	10.10	11.48	8.04	8.73	9.08	9.76	11.14
	3H	10.24	10.82	11.28	11.87	13.26	9.85	10.43	10.89	11.48	12.87
	4H	10.95	11.47	11.99	12.52	13.93	10.54	11.07	11.59	12.12	13.53
	6H	11.45	11.91	12.51	12.97	14.38	11.05	11.50	12.10	12.57	13.98
	8H	11.60	12.02	12.65	13.08	14.50	11.19	11.61	12.25	12.67	14.10
	12H	11.66	12.05	12.74	13.12	14.55	11.25	11.63	12.32	12.71	14.13
8H	4H	11.14	11.56	12.19	12.62	14.04	10.78	11.20	11.84	12.26	13.69
	6H	11.76	12.11	12.84	13.21	14.63	11.40	11.75	12.48	12.85	14.27
	8H	11.97	12.28	13.06	13.36	14.80	11.61	11.91	12.69	13.00	14.44
	12H	12.09	12.37	13.19	13.45	14.93	11.72	11.99	12.81	13.07	14.55
12H	4H	11.12	11.50	12.19	12.58	14.01	10.77	11.15	11.84	12.23	13.66
	6H	11.78	12.09	12.87	13.18	14.62	11.44	11.74	12.52	12.83	14.27
	8H	12.02	12.29	13.11	13.37	14.85	11.66	11.93	12.76	13.02	14.50