

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913477

Luminaire Tested: DFN2DIP-HX3F0-040D090US927-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913477
REPORT IS A COMBINATION OF REPORTS P899288 AND P896089
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-040D090US927-RLLFLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9003.1 lumens
Efficiency: N/A
Efficacy: 85.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 105.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913477

CATALOG NUMBER: DFN2DIP-HX3F0-040D090US927-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P913477

CATALOG NUMBER: DFN2DIP-HX3F0-040D090US927-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38
1	94	89	86	83	84	80	77	75	64	62	60	48	47	46	34	33	32
2	85	78	73	68	76	71	66	62	56	53	50	43	40	38	30	29	28
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21
5	66	55	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16
7	56	44	37	31	50	40	33	29	32	27	24	25	22	19	18	16	14
8	52	40	33	28	46	36	30	25	29	25	21	23	20	17	17	15	13
9	48	36	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12
10	45	33	27	22	40	30	24	20	25	20	17	19	16	14	14	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1517	1517	1517
5°	1519	1492	1502
10°	1503	1462	1452
15°	1482	1412	1376
20°	1454	1345	1282
25°	1425	1269	1192
30°	1387	1192	1078
35°	1349	1109	978
40°	1311	1023	863
45°	1266	928	760
50°	1220	832	658
55°	1172	729	561
60°	1116	622	461
65°	1052	514	414
70°	974	413	373
75°	876	362	338
80°	734	300	290
85°	502	195	213

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2123 cd/sqm

TEST NUMBER: P913477

CATALOG NUMBER: DFN2DIP-HX3F0-040D090US927-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.7	1.4
10°-20°	336.9	3.7
20°-30°	473.1	5.3
30°-40°	515.7	5.7
40°-50°	473.9	5.3
50°-60°	372.2	4.1
60°-70°	242.3	2.7
70°-80°	124.7	1.4
80°-90°	38.2	0.4
90°-100°	139.5	1.5
100°-110°	443.3	4.9
110°-120°	758.7	8.4
120°-130°	997.8	11.1
130°-140°	1120.0	12.4
140°-150°	1098.2	12.2
150°-160°	921.3	10.2
160°-170°	611.0	6.8
170°-180°	213.5	2.4
0°-30°	932.7	10.4
0°-40°	1448.4	16.1
0°-60°	2294.6	25.5
0°-90°	2699.8	30.0
90°-120°	1341.5	14.9
90°-150°	4557.5	50.6
90°-180°	6303.0	70.0
0°-180°	9003.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1310	1310	1310	1310	1310	
5°	1310	1304	1288	1299	1296	124
15°	1246	1233	1192	1170	1158	351
25°	1131	1093	1014	966	948	520
35°	974	914	810	735	709	610
45°	796	717	593	508	480	615
55°	606	513	385	314	292	541
65°	409	313	206	166	162	405
75°	218	135	95	86	85	231
85°	51	26	22	22	22	58
90°	2	24	67	62	65	9
95°	99	118	122	122	118	110
105°	409	415	419	422	422	432
115°	761	772	769	767	761	753
125°	1107	1124	1119	1113	1111	990
135°	1432	1453	1458	1455	1450	1107
145°	1739	1752	1763	1765	1758	1086
155°	1988	1994	2000	2009	2003	915
165°	2163	2161	2161	2175	2165	610
175°	2251	2245	2241	2255	2243	214
180°	2255	2255	2255	2255	2255	

TEST NUMBER: P913477

CATALOG NUMBER: DFN2DIP-HX3F0-040D090US927-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1309.6	1309.6	1309.6	1309.6	1309.6
2.5°	1315.6	1309.6	1296.6	1308.5	1306.1
5°	1309.6	1303.7	1288.2	1298.9	1295.5
7.5°	1298.9	1291.9	1275.3	1279.9	1274.1
10°	1284.8	1276.4	1252.8	1249.1	1242.1
12.5°	1267.0	1256.3	1224.2	1217.2	1204.1
15°	1245.6	1232.6	1192.3	1169.8	1158.0
17.5°	1220.8	1201.7	1151.9	1125.9	1106.9
20°	1192.3	1168.5	1109.3	1079.7	1053.6
22.5°	1161.5	1134.2	1065.4	1025.2	1007.5
25°	1130.7	1092.7	1014.5	966.0	948.1
27.5°	1094.0	1053.6	967.1	911.4	884.1
30°	1054.9	1009.7	914.9	854.5	822.5
32.5°	1016.9	962.3	865.2	794.1	764.4
35°	974.3	913.8	809.5	734.8	708.7
37.5°	932.8	867.5	757.3	675.5	645.9
40°	888.9	817.8	702.8	618.7	587.9
42.5°	843.8	768.0	648.3	560.5	531.0
45°	796.5	717.0	592.6	508.4	480.0
47.5°	751.5	667.3	539.3	455.1	429.0
50°	701.6	617.5	487.1	405.3	380.5
52.5°	653.0	564.1	437.4	359.1	336.6
55°	605.6	513.2	385.2	314.1	291.6
57.5°	557.1	462.2	339.0	272.6	253.7
60°	507.2	412.4	290.3	230.0	211.0
62.5°	458.8	363.9	248.8	192.0	182.6
65°	408.9	312.8	206.2	166.0	162.3
67.5°	361.6	265.5	166.0	145.8	142.2
70°	311.7	219.3	137.4	125.6	120.8
72.5°	264.4	176.6	114.9	105.5	103.1
75°	218.0	135.1	94.8	86.5	85.4
77.5°	171.9	95.9	74.7	69.9	67.5
80°	129.1	68.8	56.8	52.2	52.2
82.5°	90.1	46.3	39.1	36.7	36.7
85°	50.9	26.1	22.5	22.5	22.5
87.5°	19.0	9.4	9.4	8.3	8.3
90°	2.1	24.5	66.6	62.5	64.6
92.5°	42.1	57.1	59.2	61.2	61.2
95°	99.3	118.3	121.7	121.7	118.3
97.5°	165.2	182.8	190.4	190.4	190.4
100°	241.3	257.0	262.4	262.4	260.4
102.5°	321.5	333.1	340.6	342.6	340.6
105°	409.2	414.6	418.7	422.2	422.2
107.5°	496.2	504.4	504.4	505.7	496.2
110°	580.5	591.4	591.4	591.4	586.0

TEST NUMBER: P913477

CATALOG NUMBER: DFN2DIP-HX3F0-040D090US927-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	671.6	683.2	681.1	675.7	671.6
115°	761.4	772.2	768.8	766.8	761.4
117.5°	850.4	865.4	855.9	850.4	844.9
120°	940.2	955.1	940.2	940.2	934.0
122.5°	1021.7	1040.8	1031.3	1025.8	1021.7
125°	1107.4	1124.3	1119.0	1112.8	1110.8
127.5°	1191.0	1212.0	1204.6	1196.4	1191.0
130°	1269.2	1293.6	1290.2	1286.1	1278.7
132.5°	1356.8	1375.9	1377.2	1367.7	1362.3
135°	1432.3	1453.3	1457.5	1455.4	1450.0
137.5°	1516.6	1533.6	1537.0	1535.6	1527.5
140°	1590.7	1607.7	1617.2	1617.2	1609.7
142.5°	1666.8	1683.8	1689.2	1691.3	1683.8
145°	1738.9	1752.5	1763.3	1765.4	1757.9
147.5°	1803.5	1820.4	1828.6	1832.0	1824.6
150°	1870.1	1881.7	1889.1	1895.2	1889.1
152.5°	1929.2	1940.8	1950.3	1957.8	1950.3
155°	1988.4	1993.8	1999.9	2009.4	2003.3
157.5°	2039.3	2043.4	2046.8	2060.4	2050.9
160°	2084.9	2089.0	2091.0	2102.5	2094.4
162.5°	2127.0	2127.0	2129.1	2142.0	2132.5
165°	2163.1	2161.0	2161.0	2174.6	2165.1
167.5°	2195.7	2189.6	2189.6	2203.1	2193.6
170°	2220.2	2214.7	2212.7	2226.3	2214.7
172.5°	2237.1	2231.7	2229.7	2243.3	2231.7
175°	2250.7	2245.3	2241.2	2254.9	2243.3
177.5°	2258.2	2252.8	2248.7	2260.3	2248.7
180°	2254.9	2254.9	2254.9	2254.9	2254.9

TEST NUMBER: P913477

CATALOG NUMBER: DFN2DIP-HX3F0-040D090US927-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.31	7.00	7.43	8.11	9.64	2.29	2.98	3.41	4.09	5.62
	3H	7.97	8.59	9.10	9.71	11.26	3.46	4.08	4.59	5.20	6.75
	4H	8.57	9.16	9.70	10.27	11.83	3.90	4.49	5.04	5.61	7.16
	6H	8.98	9.52	10.12	10.64	12.20	4.21	4.75	5.36	5.87	7.44
	8H	9.10	9.61	10.24	10.74	12.30	4.30	4.81	5.44	5.95	7.50
	12H	9.15	9.64	10.30	10.76	12.35	4.34	4.82	5.49	5.95	7.53
4H	2H	6.31	6.90	7.46	8.02	9.57	2.86	3.45	4.01	4.57	6.12
	3H	8.12	8.61	9.27	9.75	11.32	4.20	4.68	5.34	5.83	7.39
	4H	8.80	9.25	9.95	10.38	11.97	4.73	5.18	5.88	6.31	7.90
	6H	9.30	9.69	10.46	10.84	12.42	5.14	5.52	6.30	6.68	8.26
	8H	9.47	9.83	10.63	10.97	12.57	5.26	5.62	6.42	6.77	8.36
	12H	9.55	9.88	10.73	11.04	12.63	5.32	5.64	6.49	6.80	8.40
8H	4H	8.76	9.12	9.91	10.26	11.86	5.00	5.36	6.15	6.50	8.10
	6H	9.31	9.61	10.49	10.79	12.38	5.51	5.80	6.68	6.99	8.58
	8H	9.52	9.78	10.70	10.95	12.56	5.69	5.95	6.87	7.12	8.73
	12H	9.65	9.88	10.83	11.04	12.68	5.80	6.03	6.99	7.19	8.84
12H	4H	8.70	9.03	9.87	10.19	11.78	5.00	5.32	6.17	6.48	8.08
	6H	9.29	9.54	10.47	10.71	12.32	5.55	5.81	6.73	6.98	8.59
	8H	9.49	9.72	10.68	10.88	12.53	5.75	5.98	6.94	7.14	8.79

END OF REPORT