

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907961

Luminaire Tested: DFN2DIP-HX2F0-060D030US840-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907961
REPORT IS A COMBINATION OF REPORTS P900690 AND P897595
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-060D030US840-RLONL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8149.7 lumens
Efficiency: N/A
Efficacy: 100.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 81.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907961
CATALOG NUMBER: DFN2DIP-HX2F0-060D030US840-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P907961

CATALOG NUMBER: DFN2DIP-HX2F0-060D030US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	68	68	68	63
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	61	60	59	61	60	59	54
2	93	86	80	75	87	81	75	71	71	67	64	63	60	57	55	52	51	55	52	51	47
3	85	76	69	63	80	72	65	60	63	58	54	56	52	49	49	46	44	49	46	44	40
4	78	68	60	54	73	64	57	52	57	51	47	50	46	43	44	41	38	44	41	38	35
5	72	61	53	47	67	57	50	45	51	45	41	46	41	37	40	37	34	40	37	34	31
6	67	55	47	41	62	52	45	39	46	41	36	41	37	33	37	33	30	37	33	30	27
7	62	50	42	36	58	47	40	35	42	36	32	38	33	30	34	30	27	34	30	27	25
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	24	31	27	24	22
9	54	42	34	29	51	40	33	28	36	30	26	32	27	24	29	25	22	29	25	22	20
10	50	38	31	26	47	37	30	25	33	28	24	30	25	22	27	23	20	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5900	5900	5900
5°	5901	5793	5833
10°	5833	5665	5632
15°	5743	5464	5329
20°	5627	5193	4961
25°	5509	4892	4605
30°	5353	4584	4158
35°	5200	4255	3765
40°	5044	3915	3317
45°	4863	3541	2912
50°	4675	3164	2516
55°	4478	2764	2137
60°	4250	2347	1749
65°	3987	1925	1562
70°	3667	1531	1399
75°	3265	1323	1252
80°	2687	1072	1054
85°	1758	661	738

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4863 cd/sqm



TEST NUMBER: P907961

CATALOG NUMBER: DFN2DIP-HX2F0-060D030US840-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	234.7	2.9
10°-20°	644.3	7.9
20°-30°	904.6	11.1
30°-40°	986.1	12.1
40°-50°	906.3	11.1
50°-60°	711.7	8.7
60°-70°	463.3	5.7
70°-80°	238.5	2.9
80°-90°	62.7	0.8
90°-100°	33.7	0.4
100°-110°	125.7	1.5
110°-120°	333.3	4.1
120°-130°	552.9	6.8
130°-140°	587.3	7.2
140°-150°	545.8	6.7
150°-160°	438.8	5.4
160°-170°	282.8	3.5
170°-180°	97.3	1.2
0°-30°	1783.6	21.9
0°-40°	2769.6	34.0
0°-60°	4387.7	53.8
0°-90°	5152.1	63.2
90°-120°	492.7	6.0
90°-150°	2178.7	26.7
90°-180°	2998.0	36.8
0°-180°	8149.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2504	2504	2504	2504	2504	
5°	2504	2493	2463	2484	2477	237
15°	2382	2357	2280	2237	2214	671
25°	2162	2090	1940	1847	1813	994
35°	1863	1747	1548	1405	1355	1166
45°	1523	1371	1133	972	918	1176
55°	1158	981	736	601	558	1035
65°	782	598	394	317	310	775
75°	417	258	181	165	163	441
85°	97	50	43	43	43	112
90°	1	9	15	19	20	8
95°	48	24	29	33	32	57
105°	225	247	45	53	56	240
115°	425	438	456	114	61	419
125°	602	611	625	630	633	536
135°	744	756	763	770	769	575
145°	863	863	875	880	877	540
155°	951	944	953	957	952	438
165°	1002	997	1000	1005	1000	283
175°	1025	1020	1021	1026	1019	98
180°	1022	1022	1022	1022	1022	



TEST NUMBER: P907961

CATALOG NUMBER: DFN2DIP-HX2F0-060D030US840-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2504.3	2504.3	2504.3	2504.3	2504.3
2.5°	2515.6	2504.3	2479.2	2502.0	2497.5
5°	2504.3	2493.0	2463.4	2483.9	2477.1
7.5°	2483.9	2470.3	2438.6	2447.5	2436.2
10°	2456.6	2440.7	2395.6	2388.6	2375.1
12.5°	2422.8	2402.3	2341.0	2327.5	2302.5
15°	2381.9	2356.8	2279.9	2236.9	2214.2
17.5°	2334.3	2297.9	2202.7	2152.9	2116.7
20°	2279.9	2234.4	2121.2	2064.7	2014.7
22.5°	2221.0	2168.8	2037.3	1960.4	1926.4
25°	2162.1	2089.5	1940.0	1847.1	1813.0
27.5°	2091.9	2014.7	1849.3	1742.7	1690.6
30°	2017.1	1930.8	1749.5	1634.1	1572.8
32.5°	1944.5	1840.2	1654.6	1518.4	1461.7
35°	1863.0	1747.4	1548.0	1405.1	1355.1
37.5°	1783.6	1658.8	1448.2	1291.7	1235.2
40°	1699.7	1563.9	1343.8	1183.0	1124.1
42.5°	1613.7	1468.6	1239.7	1071.9	1015.4
45°	1523.0	1371.0	1133.3	972.1	917.8
47.5°	1436.9	1276.1	1031.3	870.2	820.4
50°	1341.7	1180.8	931.5	775.0	727.6
52.5°	1248.6	1078.6	836.3	686.7	643.7
55°	1158.0	981.3	736.5	600.7	557.5
57.5°	1065.2	883.8	648.2	521.3	484.9
60°	970.0	788.7	555.2	439.8	403.4
62.5°	877.2	695.9	475.8	367.2	349.1
65°	781.9	598.2	394.4	317.4	310.4
67.5°	691.3	507.6	317.4	278.7	272.0
70°	596.0	419.3	262.8	240.2	231.1
72.5°	505.4	337.6	219.7	201.8	197.1
75°	417.0	258.2	181.3	165.4	163.3
77.5°	328.7	183.5	142.8	133.7	129.2
80°	246.9	131.5	108.7	99.8	99.8
82.5°	172.2	88.5	74.7	70.2	70.2
85°	97.4	49.8	43.0	43.0	43.0
87.5°	36.4	18.1	18.1	15.9	15.9
90°	0.7	8.9	14.7	18.6	19.9
92.5°	18.6	15.6	17.8	19.3	19.9
95°	48.1	23.6	28.8	32.6	31.8
97.5°	86.5	26.0	37.7	40.0	40.7
100°	131.0	29.6	42.2	48.1	49.6
102.5°	179.8	178.3	43.6	51.7	54.0
105°	224.9	247.1	45.1	53.2	56.2
107.5°	277.4	295.9	46.7	54.7	57.8
110°	327.8	343.3	129.5	55.5	58.5



TEST NUMBER: P907961

CATALOG NUMBER: DFN2DIP-HX2F0-060D030US840-RLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.2	388.4	375.9	57.0	59.2
115°	425.4	438.0	456.5	113.9	60.7
117.5°	469.1	483.8	496.4	390.6	196.8
120°	517.9	529.0	542.3	551.2	451.3
122.5°	559.3	571.2	586.0	590.4	591.2
125°	601.5	611.1	625.2	630.4	632.6
127.5°	640.0	650.3	661.5	668.8	669.5
130°	676.2	688.1	696.2	704.3	703.7
132.5°	713.2	722.9	730.9	737.6	736.9
135°	744.3	756.2	762.8	770.2	768.7
137.5°	776.8	785.7	793.1	800.5	798.3
140°	808.6	814.6	822.6	829.3	825.7
142.5°	835.4	840.5	850.1	856.0	852.3
145°	863.4	862.6	875.3	880.4	876.7
147.5°	887.8	885.6	898.2	901.8	898.9
150°	911.5	906.4	918.2	922.5	918.9
152.5°	931.4	925.5	936.7	941.1	935.9
155°	950.7	944.1	952.9	957.4	951.5
157.5°	966.2	960.4	967.0	972.2	966.2
160°	979.6	975.1	979.6	984.0	978.8
162.5°	991.4	986.9	990.7	995.8	989.2
165°	1001.7	997.3	999.6	1004.7	999.6
167.5°	1009.9	1005.4	1007.6	1012.9	1006.2
170°	1016.5	1012.1	1013.6	1018.8	1012.1
172.5°	1021.0	1016.5	1018.0	1023.2	1016.5
175°	1024.6	1019.5	1021.0	1026.1	1018.8
177.5°	1026.1	1021.0	1021.8	1026.9	1020.3
180°	1022.5	1022.5	1022.5	1022.5	1022.5



TEST NUMBER: P907961
 CATALOG NUMBER: DFN2DIP-HX2F0-060D030US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.33	15.28	15.17	16.14	17.21	10.31	11.26	11.15	12.12	13.19
	3H	15.99	16.84	16.85	17.71	18.81	11.49	12.34	12.35	13.21	14.31
	4H	16.59	17.39	17.46	18.27	19.38	11.94	12.74	12.81	13.62	14.73
	6H	17.00	17.73	17.88	18.62	19.74	12.25	12.99	13.13	13.87	14.99
	8H	17.11	17.82	18.01	18.72	19.84	12.34	13.04	13.23	13.94	15.06
	12H	17.17	17.84	18.07	18.73	19.88	12.38	13.05	13.27	13.94	15.09
4H	2H	14.36	15.16	15.23	16.04	17.15	10.91	11.71	11.78	12.59	13.70
	3H	16.17	16.84	17.06	17.74	18.87	12.25	12.92	13.14	13.82	14.95
	4H	16.85	17.45	17.75	18.36	19.51	12.79	13.39	13.69	14.30	15.45
	6H	17.34	17.87	18.26	18.79	19.95	13.20	13.72	14.11	14.65	15.80
	8H	17.51	18.00	18.42	18.92	20.08	13.32	13.81	14.23	14.73	15.89
	12H	17.60	18.03	18.53	18.97	20.15	13.38	13.82	14.31	14.76	15.93
8H	4H	16.82	17.31	17.74	18.23	19.40	13.06	13.55	13.98	14.47	15.64
	6H	17.36	17.77	18.30	18.73	19.90	13.56	13.96	14.50	14.93	16.09
	8H	17.56	17.92	18.52	18.88	20.06	13.74	14.10	14.69	15.05	16.23
	12H	17.69	18.00	18.64	18.95	20.19	13.85	14.16	14.80	15.11	16.34
12H	4H	16.78	17.22	17.71	18.16	19.33	13.07	13.51	14.00	14.45	15.62
	6H	17.34	17.69	18.29	18.65	19.83	13.60	13.96	14.56	14.92	16.10
	8H	17.55	17.86	18.50	18.81	20.04	13.80	14.12	14.76	15.07	16.30