

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913522

Luminaire Tested: DFN2DIP-HX3F0-060D080US927-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913522
REPORT IS A COMBINATION OF REPORTS P899277 AND P896089
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-060D080US927-FLLFLL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10314.2 lumens
Efficiency: N/A
Efficacy: 87.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 118
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913522

CATALOG NUMBER: DFN2DIP-HX3F0-060D080US927-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P913522

CATALOG NUMBER: DFN2DIP-HX3F0-060D080US927-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46		
1	97	93	89	85	89	85	82	79	71	69	66	58	56	55	46	45	44	38		
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	41	39	37	32		
3	80	71	64	58	73	65	59	54	55	50	46	45	42	39	36	34	32	27		
4	74	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27	23		
5	67	56	48	42	62	52	45	39	44	38	34	36	32	29	29	26	24	20		
6	62	50	42	36	57	46	39	34	39	34	30	33	28	25	26	23	21	18		
7	57	45	37	32	53	42	35	30	36	30	26	30	25	22	24	21	19	16		
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17	14		
9	50	37	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15	13		
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	14	12		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2142	2142	2142
5°	2145	2111	2126
10°	2126	2081	2095
15°	2094	2045	2049
20°	2051	1996	2002
25°	2008	1938	1948
30°	1954	1883	1879
35°	1903	1819	1806
40°	1841	1755	1737
45°	1778	1690	1666
50°	1710	1622	1584
55°	1638	1542	1508
60°	1557	1449	1421
65°	1469	1352	1319
70°	1356	1233	1208
75°	1200	1091	1104
80°	1012	911	909
85°	717	602	590

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1886 cd/sqm

TEST NUMBER: P913522

CATALOG NUMBER: DFN2DIP-HX3F0-060D080US927-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.1	1.7
10°-20°	489.8	4.7
20°-30°	719.8	7.0
30°-40°	836.0	8.1
40°-50°	834.9	8.1
50°-60°	728.0	7.1
60°-70°	538.2	5.2
70°-80°	304.5	3.0
80°-90°	86.1	0.8
90°-100°	124.0	1.2
100°-110°	394.1	3.8
110°-120°	674.4	6.5
120°-130°	886.9	8.6
130°-140°	995.5	9.7
140°-150°	976.2	9.5
150°-160°	818.9	7.9
160°-170°	543.1	5.3
170°-180°	189.8	1.8
0°-30°	1383.6	13.4
0°-40°	2219.6	21.5
0°-60°	3782.5	36.7
0°-90°	4711.2	45.7
90°-120°	1192.5	11.6
90°-150°	4051.1	39.3
90°-180°	5603.0	54.3
0°-180°	10314.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1849	1849	1849	1849	1849	
5°	1849	1842	1823	1837	1834	176
15°	1760	1750	1727	1734	1725	496
25°	1593	1579	1549	1552	1549	733
35°	1375	1357	1328	1318	1309	858
45°	1119	1106	1079	1060	1053	863
55°	847	836	814	793	784	757
65°	571	560	542	526	518	564
75°	299	295	286	276	279	319
85°	73	71	69	64	62	81
90°	2	22	59	56	57	10
95°	88	105	108	108	105	98
105°	364	369	372	375	375	384
115°	677	686	683	682	677	669
125°	984	999	995	989	987	880
135°	1273	1292	1296	1294	1289	984
145°	1546	1558	1567	1569	1563	966
155°	1767	1772	1778	1786	1781	813
165°	1923	1921	1921	1933	1924	542
175°	2001	1996	1992	2004	1994	190
180°	2004	2004	2004	2004	2004	

TEST NUMBER: P913522

CATALOG NUMBER: DFN2DIP-HX3F0-060D080US927-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1849.4	1849.4	1849.4	1849.4	1849.4
2.5°	1860.2	1851.3	1831.7	1849.4	1846.0
5°	1849.4	1842.5	1822.8	1837.0	1833.6
7.5°	1837.0	1826.5	1806.8	1821.1	1817.6
10°	1817.6	1805.1	1783.8	1797.9	1792.6
12.5°	1790.8	1780.2	1758.9	1767.8	1764.2
15°	1760.5	1750.0	1726.8	1734.0	1725.1
17.5°	1723.2	1712.7	1689.5	1698.3	1689.5
20°	1682.3	1671.7	1646.8	1652.1	1645.1
22.5°	1641.6	1625.5	1602.3	1602.3	1598.7
25°	1593.4	1579.3	1549.0	1552.4	1549.0
27.5°	1540.0	1527.6	1504.5	1499.3	1490.4
30°	1486.8	1472.4	1445.9	1440.6	1433.4
32.5°	1429.8	1419.3	1390.8	1380.0	1372.8
35°	1374.8	1357.0	1328.5	1317.7	1308.8
37.5°	1312.5	1296.4	1268.0	1255.4	1246.6
40°	1248.5	1234.1	1205.7	1189.9	1182.6
42.5°	1186.2	1171.9	1143.6	1125.7	1115.1
45°	1118.7	1106.2	1079.4	1060.0	1052.8
47.5°	1052.8	1040.4	1011.9	992.3	981.7
50°	983.4	974.5	949.7	924.7	915.8
52.5°	915.8	903.4	880.4	860.8	848.3
55°	846.6	835.8	814.5	793.2	784.3
57.5°	777.2	768.3	745.1	723.8	716.6
60°	707.7	700.8	675.9	656.2	650.9
62.5°	640.2	627.7	610.0	592.2	585.1
65°	570.9	560.2	542.5	526.4	517.5
67.5°	499.8	490.8	474.9	462.5	455.3
70°	434.0	426.8	410.7	398.3	391.3
72.5°	366.4	359.3	350.4	337.9	332.6
75°	298.7	295.3	286.2	275.7	279.2
77.5°	238.3	231.2	227.5	222.3	217.0
80°	177.9	176.0	172.5	167.2	163.6
82.5°	121.0	121.0	119.2	112.1	112.1
85°	72.8	71.1	69.4	63.9	62.3
87.5°	32.1	28.5	24.9	19.6	17.7
90°	1.8	21.8	59.3	55.6	57.4
92.5°	37.5	50.8	52.6	54.3	54.3
95°	88.2	105.1	108.1	108.1	105.1
97.5°	146.9	162.6	169.2	169.2	169.2
100°	214.5	228.4	233.2	233.2	231.4
102.5°	285.8	296.1	302.7	304.5	302.7
105°	363.8	368.6	372.2	375.3	375.3
107.5°	441.1	448.4	448.4	449.6	441.1
110°	516.0	525.7	525.7	525.7	520.9

TEST NUMBER: P913522

CATALOG NUMBER: DFN2DIP-HX3F0-060D080US927-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	597.0	607.3	605.5	600.6	597.0
115°	676.8	686.4	683.4	681.6	676.8
117.5°	755.9	769.2	760.7	755.9	751.1
120°	835.7	849.0	835.7	835.7	830.2
122.5°	908.2	925.1	916.6	911.8	908.2
125°	984.3	999.4	994.6	989.1	987.4
127.5°	1058.7	1077.4	1070.7	1063.5	1058.7
130°	1128.1	1149.9	1146.8	1143.3	1136.6
132.5°	1206.1	1223.0	1224.2	1215.8	1210.9
135°	1273.1	1291.9	1295.5	1293.7	1288.9
137.5°	1348.1	1363.2	1366.2	1365.0	1357.7
140°	1414.0	1429.0	1437.5	1437.5	1430.8
142.5°	1481.6	1496.7	1501.6	1503.4	1496.7
145°	1545.7	1557.7	1567.4	1569.2	1562.6
147.5°	1603.1	1618.2	1625.4	1628.5	1621.8
150°	1662.3	1672.5	1679.2	1684.7	1679.2
152.5°	1714.8	1725.1	1733.6	1740.3	1733.6
155°	1767.4	1772.3	1777.7	1786.1	1780.7
157.5°	1812.7	1816.4	1819.4	1831.4	1823.0
160°	1853.2	1856.9	1858.7	1868.9	1861.7
162.5°	1890.7	1890.7	1892.5	1904.0	1895.5
165°	1922.7	1920.9	1920.9	1933.0	1924.5
167.5°	1951.7	1946.3	1946.3	1958.4	1949.9
170°	1973.5	1968.6	1966.8	1978.9	1968.6
172.5°	1988.6	1983.8	1982.0	1994.0	1983.8
175°	2000.7	1995.8	1992.2	2004.3	1994.0
177.5°	2007.3	2002.5	1998.8	2009.1	1998.8
180°	2004.3	2004.3	2004.3	2004.3	2004.3

TEST NUMBER: P913522

CATALOG NUMBER: DFN2DIP-HX3F0-060D080US927-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.46	10.28	10.45	11.29	12.62	9.03	9.86	10.02	10.86	12.19
	3H	11.11	11.85	12.11	12.86	14.22	10.64	11.38	11.65	12.39	13.75
	4H	11.69	12.39	12.71	13.41	14.77	11.22	11.92	12.24	12.94	14.30
	6H	12.08	12.73	13.11	13.75	15.12	11.61	12.26	12.64	13.28	14.65
	8H	12.18	12.80	13.22	13.83	15.20	11.71	12.33	12.75	13.37	14.73
	12H	12.23	12.81	13.27	13.84	15.24	11.75	12.34	12.79	13.37	14.76
4H	2H	9.91	10.61	10.94	11.63	12.99	9.57	10.27	10.59	11.29	12.65
	3H	11.77	12.35	12.80	13.40	14.77	11.38	11.96	12.41	13.01	14.38
	4H	12.47	13.01	13.51	14.05	15.44	12.07	12.61	13.11	13.65	15.04
	6H	12.98	13.44	14.03	14.50	15.89	12.58	13.04	13.62	14.10	15.49
	8H	13.13	13.56	14.18	14.61	16.02	12.72	13.15	13.77	14.20	15.61
	12H	13.19	13.58	14.26	14.65	16.06	12.78	13.17	13.84	14.23	15.65
8H	4H	12.67	13.09	13.71	14.15	15.56	12.31	12.74	13.36	13.79	15.20
	6H	13.29	13.64	14.36	14.74	16.14	12.93	13.28	14.00	14.38	15.78
	8H	13.50	13.81	14.58	14.89	16.32	13.14	13.45	14.22	14.53	15.95
	12H	13.63	13.90	14.71	14.97	16.44	13.25	13.52	14.33	14.60	16.06
12H	4H	12.65	13.04	13.72	14.10	15.52	12.30	12.69	13.37	13.76	15.17
	6H	13.31	13.63	14.39	14.71	16.13	12.97	13.28	14.05	14.36	15.78
	8H	13.55	13.82	14.63	14.90	16.36	13.19	13.47	14.28	14.54	16.01