

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913530

Luminaire Tested: DFN2DIP-HX3F0-070D040US927-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913530
REPORT IS A COMBINATION OF REPORTS P899223 AND P896089
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-070D040US927-FLLFLL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8294.2 lumens
Efficiency: N/A
Efficacy: 83.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 98.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913530
CATALOG NUMBER: DFN2DIP-HX3F0-070D040US927-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P913530
 CATALOG NUMBER: DFN2DIP-HX3F0-070D040US927-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66			
1	101	97	93	89	95	91	88	85	81	78	76	72	70	68	63	61	60	56			
2	92	85	78	73	87	80	74	70	71	67	63	63	60	57	55	53	51	47			
3	84	75	67	61	79	70	64	58	63	57	53	56	51	48	49	46	43	40			
4	77	66	58	52	72	63	55	50	56	50	45	50	45	41	44	40	37	34			
5	71	59	51	44	67	56	48	43	50	44	39	45	40	36	40	36	32	30			
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	36	32	29	26			
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	25	23			
8	56	44	36	30	53	42	34	29	38	31	27	34	29	25	30	26	23	21			
9	53	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	21	19			
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19	17			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2499	2499	2499
5°	2502	2463	2480
10°	2481	2428	2445
15°	2443	2386	2391
20°	2393	2329	2336
25°	2343	2261	2273
30°	2280	2197	2192
35°	2220	2123	2107
40°	2148	2047	2026
45°	2075	1971	1944
50°	1995	1892	1848
55°	1911	1800	1759
60°	1817	1691	1658
65°	1714	1577	1539
70°	1582	1439	1410
75°	1400	1273	1289
80°	1180	1062	1061
85°	837	703	688

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2075 cd/sqm



TEST NUMBER: P913530

CATALOG NUMBER: DFN2DIP-HX3F0-070D040US927-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.1	2.4
10°-20°	571.4	6.9
20°-30°	839.7	10.1
30°-40°	975.3	11.8
40°-50°	974.1	11.7
50°-60°	849.4	10.2
60°-70°	627.9	7.6
70°-80°	355.2	4.3
80°-90°	96.6	1.2
90°-100°	62.0	0.7
100°-110°	197.0	2.4
110°-120°	337.2	4.1
120°-130°	443.5	5.3
130°-140°	497.8	6.0
140°-150°	488.1	5.9
150°-160°	409.5	4.9
160°-170°	271.5	3.3
170°-180°	94.9	1.1
0°-30°	1614.2	19.5
0°-40°	2589.5	31.2
0°-60°	4412.9	53.2
0°-90°	5492.7	66.2
90°-120°	596.2	7.2
90°-150°	2025.6	24.4
90°-180°	2801.0	33.8
0°-180°	8294.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2158	2158	2158	2158	2158	
5°	2158	2150	2127	2143	2139	205
15°	2054	2042	2015	2023	2013	578
25°	1859	1842	1807	1811	1807	855
35°	1604	1583	1550	1537	1527	1002
45°	1305	1291	1259	1237	1228	1007
55°	988	975	950	925	915	883
65°	666	654	633	614	604	659
75°	348	344	334	322	326	372
85°	85	83	81	75	73	95
90°	1	11	30	28	29	8
95°	44	53	54	54	53	49
105°	182	184	186	188	188	192
115°	338	343	342	341	338	335
125°	492	500	497	495	494	440
135°	637	646	648	647	644	492
145°	773	779	784	785	781	483
155°	884	886	889	893	890	407
165°	961	960	960	966	962	271
175°	1000	998	996	1002	997	95
180°	1002	1002	1002	1002	1002	



TEST NUMBER: P913530

CATALOG NUMBER: DFN2DIP-HX3F0-070D040US927-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2157.7	2157.7	2157.7	2157.7	2157.7
2.5°	2170.3	2159.9	2137.0	2157.7	2153.7
5°	2157.7	2149.6	2126.7	2143.2	2139.2
7.5°	2143.2	2130.8	2107.9	2124.7	2120.5
10°	2120.5	2105.9	2081.1	2097.6	2091.4
12.5°	2089.2	2076.9	2052.1	2062.4	2058.2
15°	2054.0	2041.7	2014.6	2023.0	2012.6
17.5°	2010.4	1998.1	1971.0	1981.4	1971.0
20°	1962.6	1950.4	1921.3	1927.5	1919.3
22.5°	1915.1	1896.4	1869.3	1869.3	1865.1
25°	1859.0	1842.5	1807.3	1811.2	1807.3
27.5°	1796.7	1782.2	1755.3	1749.1	1738.8
30°	1734.6	1717.8	1686.9	1680.7	1672.3
32.5°	1668.1	1655.8	1622.5	1610.0	1601.6
35°	1603.8	1583.2	1549.9	1537.4	1527.0
37.5°	1531.2	1512.5	1479.2	1464.7	1454.4
40°	1456.6	1439.9	1406.6	1388.1	1379.7
42.5°	1383.9	1367.2	1334.2	1313.3	1300.9
45°	1305.1	1290.6	1259.3	1236.7	1228.3
47.5°	1228.3	1213.8	1180.5	1157.6	1145.3
50°	1147.3	1136.9	1107.9	1078.9	1068.5
52.5°	1068.5	1054.0	1027.1	1004.2	989.7
55°	987.7	975.2	950.3	925.4	915.0
57.5°	906.7	896.4	869.3	844.4	836.1
60°	825.7	817.5	788.5	765.6	759.5
62.5°	746.9	732.4	711.7	691.0	682.6
65°	666.1	653.5	632.9	614.2	603.8
67.5°	583.1	572.6	554.1	539.6	531.2
70°	506.3	498.0	479.2	464.7	456.5
72.5°	427.5	419.1	408.8	394.3	388.1
75°	348.5	344.5	333.9	321.6	325.8
77.5°	278.1	269.7	265.5	259.3	253.2
80°	207.6	205.4	201.2	195.0	190.8
82.5°	141.1	141.1	139.1	130.8	130.8
85°	85.0	83.0	81.0	74.6	72.6
87.5°	37.4	33.3	29.1	22.9	20.7
90°	0.9	10.9	29.6	27.8	28.7
92.5°	18.7	25.3	26.3	27.2	27.2
95°	44.1	52.6	54.1	54.1	52.6
97.5°	73.4	81.3	84.6	84.6	84.6
100°	107.3	114.2	116.6	116.6	115.7
102.5°	142.9	148.1	151.4	152.3	151.4
105°	181.9	184.3	186.1	187.6	187.6
107.5°	220.5	224.2	224.2	224.7	220.5
110°	258.0	262.8	262.8	262.8	260.5



TEST NUMBER: P913530

CATALOG NUMBER: DFN2DIP-HX3F0-070D040US927-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	298.5	303.6	302.7	300.3	298.5
115°	338.3	343.3	341.7	340.8	338.3
117.5°	377.9	384.6	380.4	377.9	375.6
120°	417.9	424.5	417.9	417.9	415.1
122.5°	454.1	462.6	458.4	455.9	454.1
125°	492.2	499.7	497.3	494.6	493.7
127.5°	529.3	538.7	535.4	531.7	529.3
130°	564.0	575.0	573.5	571.6	568.3
132.5°	603.0	611.5	612.1	607.8	605.5
135°	636.6	645.9	647.8	646.8	644.4
137.5°	674.1	681.6	683.1	682.5	678.9
140°	706.9	714.5	718.7	718.7	715.4
142.5°	740.8	748.4	750.8	751.7	748.4
145°	772.9	778.9	783.7	784.7	781.3
147.5°	801.5	809.1	812.7	814.2	810.9
150°	831.2	836.3	839.6	842.3	839.6
152.5°	857.5	862.5	866.8	870.1	866.8
155°	883.7	886.1	888.8	893.1	890.3
157.5°	906.4	908.2	909.7	915.8	911.5
160°	926.6	928.4	929.3	934.5	930.8
162.5°	945.3	945.3	946.3	952.0	947.8
165°	961.4	960.4	960.4	966.5	962.3
167.5°	975.9	973.1	973.1	979.2	974.9
170°	986.7	984.3	983.4	989.4	984.3
172.5°	994.3	991.9	990.9	997.0	991.9
175°	1000.4	997.9	996.1	1002.1	997.0
177.5°	1003.7	1001.2	999.4	1004.6	999.4
180°	1002.1	1002.1	1002.1	1002.1	1002.1



TEST NUMBER: P913530
 CATALOG NUMBER: DFN2DIP-HX3F0-070D040US927-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.79	12.82	12.59	13.64	14.66	11.36	12.39	12.16	13.21	14.23
	3H	13.45	14.38	14.27	15.21	16.26	12.98	13.91	13.80	14.74	15.79
	4H	14.04	14.91	14.88	15.76	16.82	13.57	14.45	14.41	15.29	16.35
	6H	14.44	15.25	15.29	16.10	17.17	13.97	14.78	14.82	15.63	16.70
	8H	14.55	15.32	15.41	16.19	17.26	14.08	14.85	14.94	15.72	16.79
	12H	14.60	15.33	15.46	16.20	17.30	14.13	14.86	14.99	15.72	16.82
4H	2H	12.27	13.14	13.10	13.98	15.04	11.92	12.80	12.76	13.64	14.70
	3H	14.14	14.87	14.99	15.74	16.82	13.75	14.48	14.60	15.35	16.43
	4H	14.85	15.52	15.72	16.39	17.49	14.45	15.11	15.31	15.99	17.09
	6H	15.37	15.94	16.25	16.84	17.95	14.96	15.54	15.84	16.44	17.54
	8H	15.52	16.06	16.40	16.95	18.07	15.11	15.65	15.99	16.54	17.66
	12H	15.60	16.08	16.50	16.99	18.12	15.18	15.66	16.08	16.58	17.70
8H	4H	15.06	15.60	15.94	16.49	17.61	14.70	15.24	15.58	16.13	17.25
	6H	15.69	16.13	16.60	17.07	18.19	15.33	15.77	16.24	16.71	17.83
	8H	15.91	16.30	16.83	17.23	18.36	15.54	15.94	16.46	16.86	18.00
	12H	16.04	16.39	16.96	17.31	18.49	15.66	16.01	16.58	16.93	18.11
12H	4H	15.05	15.54	15.95	16.45	17.57	14.70	15.19	15.60	16.10	17.22
	6H	15.72	16.11	16.64	17.04	18.18	15.37	15.76	16.29	16.69	17.83
	8H	15.96	16.31	16.89	17.23	18.42	15.61	15.96	16.53	16.88	18.06