

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913549

Luminaire Tested: DFN2DIP-HX3F0-070D090US927-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913549
REPORT IS A COMBINATION OF REPORTS P899294 AND P896089
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-070D090US927-RLLFLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11023.2 lumens
Efficiency: N/A
Efficacy: 78.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 140.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913549

CATALOG NUMBER: DFN2DIP-HX3F0-070D090US927-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P913549

CATALOG NUMBER: DFN2DIP-HX3F0-070D090US927-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	97	92	89	85	88	85	82	79	70	68	66	57	55	54	44	43	43
2	88	81	75	70	80	74	69	65	62	58	55	50	48	46	40	38	36
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	35	33	32
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28
5	68	57	49	43	62	52	46	41	44	39	35	36	32	30	29	26	24
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	26	24	22
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	35	29	49	39	32	28	33	28	24	28	24	21	22	19	17
9	50	38	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16
10	47	35	28	24	43	33	27	22	28	23	20	23	20	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2655	2655	2655
5°	2658	2611	2628
10°	2630	2558	2541
15°	2593	2471	2407
20°	2544	2353	2244
25°	2493	2221	2086
30°	2426	2086	1887
35°	2360	1940	1712
40°	2293	1790	1511
45°	2216	1623	1329
50°	2135	1456	1152
55°	2051	1276	981
60°	1953	1089	806
65°	1841	899	724
70°	1705	722	653
75°	1533	633	591
80°	1285	525	508
85°	878	342	373

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2216 cd/sqm

TEST NUMBER: P913549

CATALOG NUMBER: DFN2DIP-HX3F0-070D090US927-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.8	1.9
10°-20°	589.7	5.3
20°-30°	827.9	7.5
30°-40°	902.4	8.2
40°-50°	829.4	7.5
50°-60°	651.4	5.9
60°-70°	424.0	3.8
70°-80°	218.2	2.0
80°-90°	62.1	0.6
90°-100°	139.5	1.3
100°-110°	443.3	4.0
110°-120°	758.7	6.9
120°-130°	997.8	9.1
130°-140°	1120.0	10.2
140°-150°	1098.2	10.0
150°-160°	921.3	8.4
160°-170°	611.0	5.5
170°-180°	213.5	1.9
0°-30°	1632.3	14.8
0°-40°	2534.7	23.0
0°-60°	4015.5	36.4
0°-90°	4719.9	42.8
90°-120°	1341.5	12.2
90°-150°	4557.5	41.3
90°-180°	6303.0	57.2
0°-180°	11023.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2292	2292	2292	2292	2292	
5°	2292	2282	2254	2273	2267	217
15°	2180	2157	2086	2047	2026	614
25°	1979	1912	1775	1690	1659	910
35°	1705	1599	1417	1286	1240	1067
45°	1394	1255	1037	890	840	1076
55°	1060	898	674	550	510	947
65°	716	548	361	290	284	709
75°	382	236	166	151	149	404
85°	89	46	39	39	39	102
90°	2	24	67	62	65	11
95°	99	118	122	122	118	110
105°	409	415	419	422	422	432
115°	761	772	769	767	761	753
125°	1107	1124	1119	1113	1111	990
135°	1432	1453	1458	1455	1450	1107
145°	1739	1752	1763	1765	1758	1086
155°	1988	1994	2000	2009	2003	915
165°	2163	2161	2161	2175	2165	610
175°	2251	2245	2241	2255	2243	214
180°	2255	2255	2255	2255	2255	

TEST NUMBER: P913549

CATALOG NUMBER: DFN2DIP-HX3F0-070D090US927-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2291.9	2291.9	2291.9	2291.9	2291.9
2.5°	2302.2	2291.9	2269.0	2289.9	2285.7
5°	2291.9	2281.5	2254.5	2273.2	2267.0
7.5°	2273.2	2260.8	2231.8	2239.9	2229.6
10°	2248.3	2233.8	2192.4	2186.0	2173.7
12.5°	2217.2	2198.5	2142.5	2130.1	2107.2
15°	2179.8	2157.0	2086.5	2047.2	2026.5
17.5°	2136.3	2103.1	2015.9	1970.3	1937.1
20°	2086.5	2044.9	1941.3	1889.6	1843.8
22.5°	2032.7	1984.9	1864.5	1794.1	1763.1
25°	1978.7	1912.2	1775.4	1690.4	1659.2
27.5°	1914.5	1843.8	1692.4	1595.0	1547.2
30°	1846.0	1767.0	1601.1	1495.5	1439.4
32.5°	1779.6	1684.1	1514.2	1389.6	1337.7
35°	1704.9	1599.1	1416.7	1286.0	1240.2
37.5°	1632.4	1518.1	1325.4	1182.1	1130.4
40°	1555.5	1431.2	1229.9	1082.7	1028.7
42.5°	1476.8	1344.1	1134.6	981.0	929.3
45°	1393.8	1254.7	1037.1	889.7	839.9
47.5°	1315.0	1167.8	943.8	796.4	750.8
50°	1227.9	1080.7	852.5	709.2	665.9
52.5°	1142.7	987.1	765.3	628.4	589.1
55°	1059.8	898.0	674.0	549.7	510.3
57.5°	974.9	808.9	593.3	477.1	443.9
60°	887.7	721.8	508.1	402.5	369.2
62.5°	802.7	636.8	435.5	336.0	319.5
65°	715.6	547.5	360.9	290.5	284.1
67.5°	632.6	464.5	290.5	255.0	248.9
70°	545.5	383.7	240.5	219.8	211.4
72.5°	462.6	309.0	201.1	184.7	180.5
75°	381.6	236.3	165.9	151.4	149.4
77.5°	300.8	167.9	130.7	122.3	118.2
80°	226.0	120.3	99.5	91.3	91.3
82.5°	157.6	81.0	68.4	64.2	64.2
85°	89.1	45.6	39.4	39.4	39.4
87.5°	33.2	16.5	16.5	14.5	14.5
90°	2.1	24.5	66.6	62.5	64.6
92.5°	42.1	57.1	59.2	61.2	61.2
95°	99.3	118.3	121.7	121.7	118.3
97.5°	165.2	182.8	190.4	190.4	190.4
100°	241.3	257.0	262.4	262.4	260.4
102.5°	321.5	333.1	340.6	342.6	340.6
105°	409.2	414.6	418.7	422.2	422.2
107.5°	496.2	504.4	504.4	505.7	496.2
110°	580.5	591.4	591.4	591.4	586.0

TEST NUMBER: P913549

CATALOG NUMBER: DFN2DIP-HX3F0-070D090US927-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	671.6	683.2	681.1	675.7	671.6
115°	761.4	772.2	768.8	766.8	761.4
117.5°	850.4	865.4	855.9	850.4	844.9
120°	940.2	955.1	940.2	940.2	934.0
122.5°	1021.7	1040.8	1031.3	1025.8	1021.7
125°	1107.4	1124.3	1119.0	1112.8	1110.8
127.5°	1191.0	1212.0	1204.6	1196.4	1191.0
130°	1269.2	1293.6	1290.2	1286.1	1278.7
132.5°	1356.8	1375.9	1377.2	1367.7	1362.3
135°	1432.3	1453.3	1457.5	1455.4	1450.0
137.5°	1516.6	1533.6	1537.0	1535.6	1527.5
140°	1590.7	1607.7	1617.2	1617.2	1609.7
142.5°	1666.8	1683.8	1689.2	1691.3	1683.8
145°	1738.9	1752.5	1763.3	1765.4	1757.9
147.5°	1803.5	1820.4	1828.6	1832.0	1824.6
150°	1870.1	1881.7	1889.1	1895.2	1889.1
152.5°	1929.2	1940.8	1950.3	1957.8	1950.3
155°	1988.4	1993.8	1999.9	2009.4	2003.3
157.5°	2039.3	2043.4	2046.8	2060.4	2050.9
160°	2084.9	2089.0	2091.0	2102.5	2094.4
162.5°	2127.0	2127.0	2129.1	2142.0	2132.5
165°	2163.1	2161.0	2161.0	2174.6	2165.1
167.5°	2195.7	2189.6	2189.6	2203.1	2193.6
170°	2220.2	2214.7	2212.7	2226.3	2214.7
172.5°	2237.1	2231.7	2229.7	2243.3	2231.7
175°	2250.7	2245.3	2241.2	2254.9	2243.3
177.5°	2258.2	2252.8	2248.7	2260.3	2248.7
180°	2254.9	2254.9	2254.9	2254.9	2254.9

TEST NUMBER: P913549

CATALOG NUMBER: DFN2DIP-HX3F0-070D090US927-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.78	10.56	10.81	11.59	12.96	5.76	6.54	6.78	7.56	8.94
	3H	11.45	12.14	12.48	13.18	14.57	6.94	7.63	7.97	8.67	10.06
	4H	12.05	12.71	13.10	13.74	15.14	7.39	8.04	8.43	9.08	10.48
	6H	12.46	13.07	13.52	14.11	15.52	7.70	8.30	8.75	9.35	10.76
	8H	12.58	13.16	13.64	14.22	15.62	7.79	8.36	8.85	9.42	10.83
	12H	12.64	13.19	13.70	14.24	15.67	7.83	8.37	8.89	9.42	10.85
4H	2H	9.79	10.45	10.85	11.49	12.89	6.34	7.00	7.40	8.04	9.44
	3H	11.61	12.16	12.67	13.22	14.63	7.68	8.23	8.74	9.30	10.71
	4H	12.29	12.79	13.36	13.85	15.29	8.23	8.73	9.29	9.78	11.22
	6H	12.80	13.23	13.87	14.31	15.74	8.64	9.07	9.71	10.15	11.58
	8H	12.97	13.37	14.04	14.44	15.89	8.76	9.16	9.84	10.24	11.68
	12H	13.06	13.42	14.15	14.50	15.95	8.82	9.18	9.91	10.27	11.72
8H	4H	12.26	12.66	13.33	13.73	15.17	8.50	8.90	9.57	9.97	11.42
	6H	12.81	13.14	13.91	14.26	15.70	9.01	9.34	10.10	10.45	11.89
	8H	13.02	13.31	14.13	14.41	15.87	9.19	9.48	10.30	10.58	12.04
	12H	13.15	13.41	14.26	14.50	16.00	9.31	9.56	10.41	10.65	12.16
12H	4H	12.21	12.57	13.30	13.65	15.10	8.50	8.86	9.59	9.95	11.40
	6H	12.79	13.08	13.89	14.17	15.64	9.05	9.34	10.16	10.44	11.90
	8H	13.00	13.25	14.11	14.35	15.85	9.26	9.51	10.37	10.61	12.11

END OF REPORT