

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910605

Luminaire Tested: DFN2DIP-HX2F0-020D020US850-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910605
REPORT IS A COMBINATION OF REPORTS P900672 AND P897595
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-020D020US850-RLLONL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4081.1 lumens
Efficiency: N/A
Efficacy: 133.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 30.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910605

CATALOG NUMBER: DFN2DIP-HX2F0-020D020US850-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P910605

CATALOG NUMBER: DFN2DIP-HX2F0-020D020US850-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53			46
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45			40
2	89	82	76	71	82	76	70	66	63	60	57	52	50	48	42	40	39			34
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	34			29
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29			26
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26			23
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23			20
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21			18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19			16
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17			15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	18	15			13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2160	2160	2160
5°	2160	2120	2135
10°	2135	2074	2062
15°	2102	2000	1951
20°	2060	1901	1816
25°	2017	1791	1686
30°	1960	1678	1522
35°	1903	1558	1378
40°	1846	1433	1214
45°	1780	1296	1066
50°	1712	1158	921
55°	1639	1012	782
60°	1556	859	640
65°	1459	705	572
70°	1342	561	512
75°	1195	484	458
80°	984	392	385
85°	643	241	270

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1780 cd/sqm

TEST NUMBER: P910605

CATALOG NUMBER: DFN2DIP-HX2F0-020D020US850-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.9	2.1
10°-20°	235.8	5.8
20°-30°	331.1	8.1
30°-40°	361.0	8.8
40°-50°	331.8	8.1
50°-60°	260.6	6.4
60°-70°	169.6	4.2
70°-80°	87.3	2.1
80°-90°	23.6	0.6
90°-100°	24.7	0.6
100°-110°	92.0	2.3
110°-120°	244.0	6.0
120°-130°	404.8	9.9
130°-140°	429.9	10.5
140°-150°	399.6	9.8
150°-160°	321.3	7.9
160°-170°	207.0	5.1
170°-180°	71.2	1.7
0°-30°	652.9	16.0
0°-40°	1013.8	24.8
0°-60°	1606.2	39.4
0°-90°	1886.6	46.2
90°-120°	360.7	8.8
90°-150°	1595.0	39.1
90°-180°	2194.0	53.8
0°-180°	4081.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	917	917	917	917	917	
5°	917	913	902	909	907	87
15°	872	863	834	819	811	246
25°	792	765	710	676	664	364
35°	682	640	567	514	496	427
45°	558	502	415	356	336	431
55°	424	359	270	220	204	379
65°	286	219	144	116	114	284
75°	153	94	66	61	60	161
85°	36	18	16	16	16	41
90°	1	6	11	14	15	4
95°	35	17	21	24	23	42
105°	165	181	33	39	41	176
115°	311	321	334	83	44	307
125°	440	447	458	462	463	393
135°	545	554	558	564	563	421
145°	632	632	641	645	642	395
155°	696	691	698	701	697	321
165°	733	730	732	736	732	207
175°	750	746	748	751	746	71
180°	749	749	749	749	749	

TEST NUMBER: P910605

CATALOG NUMBER: DFN2DIP-HX2F0-020D020US850-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	916.7	916.7	916.7	916.7	916.7
2.5°	920.8	916.7	907.5	915.9	914.3
5°	916.7	912.6	901.7	909.3	906.7
7.5°	909.3	904.3	892.6	896.0	891.7
10°	899.3	893.4	876.9	874.3	869.5
12.5°	886.9	879.3	856.9	852.0	842.8
15°	871.9	862.7	834.5	818.8	810.6
17.5°	854.5	841.2	806.4	788.1	774.9
20°	834.5	817.9	776.5	755.8	737.5
22.5°	813.0	793.9	745.8	717.6	705.2
25°	791.5	764.9	710.1	676.2	663.6
27.5°	765.8	737.5	676.9	637.9	618.8
30°	738.4	706.8	640.4	598.2	575.7
32.5°	711.8	673.6	605.6	555.8	535.1
35°	681.9	639.7	566.7	514.4	496.1
37.5°	652.9	607.2	530.1	472.9	452.1
40°	622.1	572.5	492.0	433.1	411.4
42.5°	590.7	537.6	453.8	392.4	371.7
45°	557.5	501.8	414.9	355.9	335.9
47.5°	526.0	467.1	377.5	318.5	300.3
50°	491.2	432.3	341.0	283.7	266.4
52.5°	457.0	394.8	306.1	251.4	235.7
55°	423.9	359.2	269.6	219.9	204.1
57.5°	389.9	323.5	237.3	190.9	177.6
60°	355.1	288.7	203.3	161.0	147.7
62.5°	321.1	254.7	174.2	134.4	127.8
65°	286.2	219.0	144.4	116.2	113.7
67.5°	253.1	185.8	116.2	102.0	99.6
70°	218.1	153.5	96.2	87.9	84.6
72.5°	185.0	123.5	80.4	73.9	72.2
75°	152.6	94.5	66.3	60.6	59.8
77.5°	120.3	67.2	52.2	48.9	47.2
80°	90.4	48.1	39.8	36.5	36.5
82.5°	63.0	32.4	27.4	25.7	25.7
85°	35.6	18.2	15.7	15.7	15.7
87.5°	13.3	6.7	6.7	5.8	5.8
90°	0.6	6.5	10.8	13.5	14.6
92.5°	13.5	11.4	13.0	14.1	14.6
95°	35.2	17.3	21.1	23.8	23.3
97.5°	63.3	19.0	27.6	29.3	29.8
100°	95.9	21.6	30.8	35.2	36.3
102.5°	131.6	130.5	31.9	37.9	39.6
105°	164.7	180.9	33.0	38.9	41.1
107.5°	203.2	216.6	34.2	40.0	42.3
110°	240.0	251.3	94.8	40.7	42.8

TEST NUMBER: P910605

CATALOG NUMBER: DFN2DIP-HX2F0-020D020US850-RLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	274.6	284.3	275.1	41.7	43.4
115°	311.4	320.6	334.3	83.4	44.5
117.5°	343.3	354.2	363.4	286.0	144.1
120°	379.2	387.3	397.0	403.6	330.4
122.5°	409.4	418.1	429.0	432.2	432.8
125°	440.4	447.4	457.7	461.5	463.1
127.5°	468.6	476.1	484.3	489.6	490.2
130°	495.1	503.7	509.7	515.7	515.1
132.5°	522.1	529.2	535.1	540.0	539.5
135°	545.0	553.6	558.4	563.9	562.8
137.5°	568.7	575.2	580.7	586.1	584.4
140°	592.0	596.4	602.3	607.2	604.5
142.5°	611.5	615.4	622.4	626.7	623.9
145°	632.1	631.6	640.8	644.6	641.9
147.5°	650.0	648.3	657.5	660.2	658.1
150°	667.3	663.5	672.2	675.4	672.7
152.5°	681.9	677.6	685.7	689.0	685.1
155°	696.0	691.1	697.7	700.9	696.6
157.5°	707.4	703.1	708.0	711.8	707.4
160°	717.2	713.9	717.2	720.4	716.6
162.5°	725.7	722.5	725.3	729.1	724.2
165°	733.4	730.2	731.7	735.6	731.7
167.5°	739.4	736.0	737.7	741.6	736.6
170°	744.2	740.9	742.0	745.8	740.9
172.5°	747.5	744.2	745.4	749.1	744.2
175°	750.1	746.4	747.5	751.2	745.8
177.5°	751.2	747.5	748.0	751.8	746.9
180°	748.6	748.6	748.6	748.6	748.6

TEST NUMBER: P910605

CATALOG NUMBER: DFN2DIP-HX2F0-020D020US850-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.32	10.12	10.32	11.12	12.45	5.31	6.11	6.30	7.11	8.44
	3H	10.97	11.69	11.98	12.70	14.05	6.48	7.19	7.48	8.20	9.55
	4H	11.56	12.24	12.58	13.25	14.61	6.91	7.59	7.93	8.61	9.96
	6H	11.96	12.58	12.99	13.60	14.97	7.22	7.84	8.25	8.86	10.23
	8H	12.08	12.67	13.11	13.70	15.07	7.30	7.89	8.33	8.93	10.29
	12H	12.13	12.69	13.17	13.72	15.11	7.33	7.90	8.37	8.93	10.31
4H	2H	9.33	10.01	10.36	11.02	12.38	5.89	6.56	6.91	7.58	8.93
	3H	11.13	11.69	12.16	12.74	14.11	7.21	7.77	8.25	8.82	10.19
	4H	11.80	12.32	12.84	13.35	14.74	7.74	8.26	8.78	9.29	10.69
	6H	12.29	12.73	13.34	13.79	15.18	8.14	8.58	9.19	9.64	11.03
	8H	12.45	12.86	13.50	13.92	15.32	8.26	8.67	9.31	9.72	11.13
	12H	12.53	12.90	13.60	13.97	15.38	8.32	8.69	9.38	9.75	11.16
8H	4H	11.76	12.18	12.81	13.23	14.63	8.01	8.42	9.06	9.47	10.87
	6H	12.30	12.64	13.38	13.73	15.13	8.50	8.84	9.57	9.93	11.33
	8H	12.50	12.80	13.58	13.88	15.30	8.68	8.98	9.76	10.05	11.47
	12H	12.62	12.88	13.71	13.96	15.42	8.78	9.04	9.86	10.12	11.58
12H	4H	11.71	12.08	12.78	13.15	14.56	8.01	8.38	9.08	9.44	10.85
	6H	12.27	12.57	13.36	13.65	15.07	8.54	8.84	9.62	9.92	11.34
	8H	12.48	12.74	13.56	13.81	15.27	8.74	9.00	9.82	10.07	11.53