

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910618

Luminaire Tested: DFN2DIP-HX2F0-020D060US850-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910618
REPORT IS A COMBINATION OF REPORTS P899191 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-020D060US850-FLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8084.6 lumens
Efficiency: N/A
Efficacy: 127.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 63.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910618

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US850-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P910618

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US850-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35
1	93	88	85	81	83	79	76	73	62	60	58	46	44	43	31	30	30
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25
3	77	68	61	55	68	61	55	50	48	44	40	35	33	30	24	23	21
4	70	60	52	47	62	54	47	42	42	38	34	32	29	26	22	20	18
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	18	16	14
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	14	11	10
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2033	2033	2033
5°	2033	2000	2015
10°	2014	1968	1984
15°	1981	1931	1938
20°	1938	1881	1890
25°	1895	1823	1836
30°	1841	1768	1768
35°	1791	1704	1697
40°	1729	1639	1628
45°	1667	1574	1559
50°	1599	1506	1478
55°	1528	1426	1403
60°	1447	1333	1317
65°	1358	1236	1215
70°	1246	1116	1106
75°	1092	974	999
80°	904	794	806
85°	612	498	500

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2821 cd/sqm

TEST NUMBER: P910618

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US850-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.2	1.0
10°-20°	228.6	2.8
20°-30°	335.9	4.2
30°-40°	390.1	4.8
40°-50°	389.6	4.8
50°-60°	339.7	4.2
60°-70°	251.1	3.1
70°-80°	142.1	1.8
80°-90°	43.5	0.5
90°-100°	130.2	1.6
100°-110°	413.7	5.1
110°-120°	708.0	8.8
120°-130°	931.2	11.5
130°-140°	1045.3	12.9
140°-150°	1025.0	12.7
150°-160°	859.8	10.6
160°-170°	570.2	7.1
170°-180°	199.3	2.5
0°-30°	645.7	8.0
0°-40°	1035.8	12.8
0°-60°	1765.1	21.8
0°-90°	2201.8	27.2
90°-120°	1252.0	15.5
90°-150°	4253.5	52.6
90°-180°	5883.0	72.8
0°-180°	8084.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	863	863	863	863	863	
5°	863	860	851	857	856	82
15°	822	817	806	809	805	231
25°	744	737	723	724	723	342
35°	642	633	620	615	611	401
45°	522	516	504	495	491	403
55°	395	390	380	370	366	353
65°	266	261	253	246	242	263
75°	139	138	134	129	130	149
85°	34	33	32	30	29	38
90°	2	23	62	58	60	8
95°	93	110	114	114	110	103
105°	382	387	391	394	394	403
115°	710	721	718	716	710	703
125°	1034	1049	1044	1039	1037	924
135°	1337	1356	1360	1358	1353	1033
145°	1623	1636	1646	1648	1641	1014
155°	1856	1861	1866	1875	1870	854
165°	2019	2017	2017	2030	2021	569
175°	2101	2096	2092	2104	2094	200
180°	2104	2104	2104	2104	2104	

TEST NUMBER: P910618

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US850-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	863.0	863.0	863.0	863.0	863.0
2.5°	868.0	863.9	854.7	863.0	861.5
5°	863.0	859.8	850.6	857.3	855.6
7.5°	857.3	852.3	843.2	849.8	848.2
10°	848.2	842.4	832.4	839.0	836.5
12.5°	835.6	830.8	820.8	824.9	823.2
15°	821.5	816.7	805.8	809.1	805.0
17.5°	804.1	799.3	788.4	792.5	788.4
20°	785.1	780.1	768.4	771.0	767.6
22.5°	766.0	758.6	747.7	747.7	746.0
25°	743.6	736.9	722.8	724.4	722.8
27.5°	718.6	712.9	702.1	699.7	695.5
30°	693.8	687.1	674.7	672.3	668.8
32.5°	667.2	662.3	649.0	644.0	640.7
35°	641.6	633.2	619.9	614.9	610.7
37.5°	612.5	605.0	591.7	585.9	581.7
40°	582.6	575.9	562.6	555.3	551.8
42.5°	553.5	546.8	533.7	525.3	520.3
45°	522.0	516.2	503.7	494.6	491.3
47.5°	491.3	485.5	472.2	463.0	458.1
50°	458.9	454.8	443.2	431.5	427.4
52.5°	427.4	421.5	410.8	401.7	395.9
55°	395.0	390.0	380.1	370.2	366.0
57.5°	362.6	358.5	347.7	337.8	334.4
60°	330.3	327.0	315.4	306.2	303.8
62.5°	298.8	292.9	284.7	276.4	273.0
65°	266.4	261.4	253.2	245.6	241.5
67.5°	233.2	229.0	221.6	215.8	212.5
70°	202.5	199.2	191.6	185.9	182.7
72.5°	171.0	167.7	163.5	157.7	155.3
75°	139.4	137.8	133.5	128.6	130.3
77.5°	111.2	107.9	106.1	103.7	101.3
80°	83.1	82.2	80.5	78.0	76.3
82.5°	56.4	56.4	55.7	52.3	52.3
85°	33.9	33.2	32.4	29.8	29.1
87.5°	15.0	13.3	11.6	9.2	8.3
90°	1.9	22.8	62.2	58.3	60.2
92.5°	39.4	53.3	55.2	57.1	57.1
95°	92.6	110.3	113.6	113.6	110.3
97.5°	154.2	170.7	177.7	177.7	177.7
100°	225.2	239.8	244.9	244.9	243.0
102.5°	300.1	310.9	317.8	319.7	317.8
105°	381.9	387.0	390.8	394.0	394.0
107.5°	463.1	470.8	470.8	472.0	463.1
110°	541.9	551.9	551.9	551.9	546.8

TEST NUMBER: P910618

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US850-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	626.8	637.6	635.7	630.6	626.8
115°	710.5	720.7	717.5	715.6	710.5
117.5°	793.7	807.7	798.7	793.7	788.6
120°	877.4	891.4	877.4	877.4	871.7
122.5°	953.5	971.3	962.4	957.4	953.5
125°	1033.5	1049.3	1044.2	1038.6	1036.7
127.5°	1111.6	1131.2	1124.2	1116.7	1111.6
130°	1184.5	1207.4	1204.2	1200.4	1193.4
132.5°	1266.4	1284.1	1285.3	1276.5	1271.4
135°	1336.8	1356.4	1360.2	1358.3	1353.2
137.5°	1415.4	1431.3	1434.5	1433.2	1425.6
140°	1484.6	1500.5	1509.3	1509.3	1502.4
142.5°	1555.6	1571.5	1576.6	1578.4	1571.5
145°	1622.9	1635.6	1645.8	1647.6	1640.7
147.5°	1683.1	1699.0	1706.6	1709.7	1702.8
150°	1745.3	1756.1	1763.1	1768.7	1763.1
152.5°	1800.5	1811.3	1820.2	1827.2	1820.2
155°	1855.7	1860.8	1866.4	1875.4	1869.7
157.5°	1903.3	1907.1	1910.3	1923.0	1914.1
160°	1945.9	1949.6	1951.5	1962.3	1954.7
162.5°	1985.1	1985.1	1987.0	1999.1	1990.2
165°	2018.7	2016.8	2016.8	2029.6	2020.7
167.5°	2049.2	2043.6	2043.6	2056.2	2047.3
170°	2072.1	2067.0	2065.1	2077.7	2067.0
172.5°	2087.9	2082.8	2080.9	2093.6	2082.8
175°	2100.6	2095.6	2091.7	2104.4	2093.6
177.5°	2107.5	2102.6	2098.7	2109.4	2098.7
180°	2104.4	2104.4	2104.4	2104.4	2104.4



TEST NUMBER: P910618

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US850-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.99	7.68	8.12	8.80	10.36	6.57	7.26	7.70	8.38	9.94
	3H	8.61	9.23	9.75	10.36	11.94	8.15	8.77	9.29	9.90	11.48
	4H	9.17	9.76	10.32	10.89	12.48	8.72	9.30	9.86	10.43	12.02
	6H	9.55	10.09	10.70	11.22	12.81	9.09	9.63	10.24	10.76	12.36
	8H	9.64	10.15	10.80	11.30	12.89	9.18	9.69	10.34	10.84	12.43
	12H	9.67	10.16	10.83	11.30	12.91	9.21	9.69	10.37	10.84	12.45
4H	2H	7.42	8.01	8.58	9.14	10.72	7.08	7.67	8.24	8.80	10.38
	3H	9.24	9.73	10.40	10.89	12.48	8.86	9.35	10.02	10.50	12.10
	4H	9.93	10.38	11.09	11.52	13.14	9.54	9.99	10.70	11.13	12.75
	6H	10.41	10.80	11.58	11.96	13.57	10.02	10.40	11.18	11.57	13.17
	8H	10.54	10.90	11.71	12.06	13.69	10.15	10.51	11.31	11.67	13.29
	12H	10.60	10.92	11.78	12.09	13.72	10.19	10.52	11.38	11.69	13.32
8H	4H	10.10	10.46	11.27	11.62	13.24	9.75	10.11	10.92	11.27	12.89
	6H	10.69	10.99	11.88	12.19	13.81	10.34	10.64	11.53	11.84	13.46
	8H	10.90	11.16	12.09	12.34	13.98	10.54	10.80	11.73	11.98	13.62
	12H	11.00	11.23	12.20	12.41	14.08	10.64	10.86	11.83	12.04	13.71
12H	4H	10.07	10.40	11.26	11.57	13.20	9.73	10.06	10.92	11.23	12.86
	6H	10.72	10.98	11.91	12.16	13.80	10.38	10.64	11.57	11.82	13.46
	8H	10.93	11.16	12.13	12.34	14.01	10.59	10.82	11.78	11.99	13.66