

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910640

Luminaire Tested: DFN2DIP-HX2F0-030D060US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910640
REPORT IS A COMBINATION OF REPORTS P899194 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-030D060US850-RLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8716.7 lumens
Efficiency: N/A
Efficacy: 118.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 73.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910640

CATALOG NUMBER: DFN2DIP-HX2F0-030D060US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P910640

CATALOG NUMBER: DFN2DIP-HX2F0-030D060US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	31	29
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	29	27	25
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	26	24	22
5	66	55	47	42	59	50	43	38	40	36	32	32	28	26	23	21	19
6	61	49	42	36	55	45	38	33	36	32	28	29	25	23	21	19	17
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13
10	45	34	27	22	41	31	25	21	25	21	18	20	17	15	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3240	3240	3240
5°	3240	3181	3203
10°	3203	3111	3093
15°	3153	3000	2926
20°	3090	2851	2724
25°	3025	2686	2528
30°	2939	2517	2283
35°	2855	2336	2067
40°	2769	2150	1822
45°	2670	1945	1599
50°	2567	1738	1382
55°	2459	1517	1174
60°	2333	1289	961
65°	2189	1057	858
70°	2014	841	768
75°	1792	727	687
80°	1476	589	579
85°	966	363	405

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2821 cd/sqm

TEST NUMBER: P910640

CATALOG NUMBER: DFN2DIP-HX2F0-030D060US850-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.9	1.5
10°-20°	353.8	4.1
20°-30°	496.7	5.7
30°-40°	541.4	6.2
40°-50°	497.6	5.7
50°-60°	390.8	4.5
60°-70°	254.4	2.9
70°-80°	130.9	1.5
80°-90°	39.4	0.5
90°-100°	130.2	1.5
100°-110°	413.7	4.7
110°-120°	708.0	8.1
120°-130°	931.2	10.7
130°-140°	1045.3	12.0
140°-150°	1025.0	11.8
150°-160°	859.8	9.9
160°-170°	570.2	6.5
170°-180°	199.3	2.3
0°-30°	979.3	11.2
0°-40°	1520.7	17.4
0°-60°	2409.2	27.6
0°-90°	2833.9	32.5
90°-120°	1252.0	14.4
90°-150°	4253.5	48.8
90°-180°	5883.0	67.5
0°-180°	8716.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1375	1375	1375	1375	1375	
5°	1375	1369	1353	1364	1360	130
15°	1308	1294	1252	1228	1216	369
25°	1187	1147	1065	1014	995	546
35°	1023	959	850	772	744	640
45°	836	753	622	534	504	646
55°	636	539	404	330	306	568
65°	429	328	216	174	170	426
75°	229	142	100	91	90	242
85°	54	27	24	24	24	61
90°	2	23	62	58	60	9
95°	93	110	114	114	110	103
105°	382	387	391	394	394	403
115°	710	721	718	716	710	703
125°	1034	1049	1044	1039	1037	924
135°	1337	1356	1360	1358	1353	1033
145°	1623	1636	1646	1648	1641	1014
155°	1856	1861	1866	1875	1870	854
165°	2019	2017	2017	2030	2021	569
175°	2101	2096	2092	2104	2094	200
180°	2104	2104	2104	2104	2104	

TEST NUMBER: P910640

CATALOG NUMBER: DFN2DIP-HX2F0-030D060US850-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1375.0	1375.0	1375.0	1375.0	1375.0
2.5°	1381.3	1375.0	1361.3	1373.8	1371.4
5°	1375.0	1368.8	1352.6	1363.8	1360.1
7.5°	1363.8	1356.4	1339.0	1343.9	1337.7
10°	1348.9	1340.2	1315.4	1311.5	1304.2
12.5°	1330.2	1319.0	1285.4	1278.0	1264.3
15°	1307.8	1294.1	1251.8	1228.2	1215.8
17.5°	1281.7	1261.8	1209.5	1182.2	1162.2
20°	1251.8	1226.9	1164.7	1133.7	1106.2
22.5°	1219.6	1190.8	1118.6	1076.4	1057.8
25°	1187.2	1147.3	1065.2	1014.2	995.4
27.5°	1148.6	1106.2	1015.4	957.0	928.2
30°	1107.6	1060.2	960.6	897.3	863.6
32.5°	1067.6	1010.4	908.5	833.7	802.6
35°	1022.9	959.4	849.9	771.5	744.1
37.5°	979.4	910.8	795.2	709.2	678.3
40°	933.3	858.7	737.9	649.5	617.3
42.5°	886.0	806.5	680.7	588.5	557.5
45°	836.3	752.8	622.3	533.8	503.9
47.5°	788.9	700.7	566.3	477.8	450.5
50°	736.7	648.3	511.5	425.5	399.5
52.5°	685.6	592.3	459.2	377.1	353.4
55°	635.8	538.8	404.3	329.8	306.2
57.5°	584.9	485.3	356.0	286.2	266.3
60°	532.5	433.1	304.9	241.4	221.6
62.5°	481.6	382.1	261.3	201.6	191.7
65°	429.3	328.5	216.5	174.2	170.5
67.5°	379.6	278.7	174.2	153.0	149.3
70°	327.3	230.2	144.3	131.9	126.9
72.5°	277.5	185.3	120.7	110.8	108.2
75°	228.9	141.8	99.6	90.8	89.6
77.5°	180.4	100.7	78.4	73.4	70.9
80°	135.6	72.2	59.7	54.8	54.8
82.5°	94.5	48.6	41.0	38.6	38.6
85°	53.5	27.3	23.6	23.6	23.6
87.5°	20.0	9.9	9.9	8.8	8.8
90°	1.9	22.8	62.2	58.3	60.2
92.5°	39.4	53.3	55.2	57.1	57.1
95°	92.6	110.3	113.6	113.6	110.3
97.5°	154.2	170.7	177.7	177.7	177.7
100°	225.2	239.8	244.9	244.9	243.0
102.5°	300.1	310.9	317.8	319.7	317.8
105°	381.9	387.0	390.8	394.0	394.0
107.5°	463.1	470.8	470.8	472.0	463.1
110°	541.9	551.9	551.9	551.9	546.8

TEST NUMBER: P910640

CATALOG NUMBER: DFN2DIP-HX2F0-030D060US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	626.8	637.6	635.7	630.6	626.8
115°	710.5	720.7	717.5	715.6	710.5
117.5°	793.7	807.7	798.7	793.7	788.6
120°	877.4	891.4	877.4	877.4	871.7
122.5°	953.5	971.3	962.4	957.4	953.5
125°	1033.5	1049.3	1044.2	1038.6	1036.7
127.5°	1111.6	1131.2	1124.2	1116.7	1111.6
130°	1184.5	1207.4	1204.2	1200.4	1193.4
132.5°	1266.4	1284.1	1285.3	1276.5	1271.4
135°	1336.8	1356.4	1360.2	1358.3	1353.2
137.5°	1415.4	1431.3	1434.5	1433.2	1425.6
140°	1484.6	1500.5	1509.3	1509.3	1502.4
142.5°	1555.6	1571.5	1576.6	1578.4	1571.5
145°	1622.9	1635.6	1645.8	1647.6	1640.7
147.5°	1683.1	1699.0	1706.6	1709.7	1702.8
150°	1745.3	1756.1	1763.1	1768.7	1763.1
152.5°	1800.5	1811.3	1820.2	1827.2	1820.2
155°	1855.7	1860.8	1866.4	1875.4	1869.7
157.5°	1903.3	1907.1	1910.3	1923.0	1914.1
160°	1945.9	1949.6	1951.5	1962.3	1954.7
162.5°	1985.1	1985.1	1987.0	1999.1	1990.2
165°	2018.7	2016.8	2016.8	2029.6	2020.7
167.5°	2049.2	2043.6	2043.6	2056.2	2047.3
170°	2072.1	2067.0	2065.1	2077.7	2067.0
172.5°	2087.9	2082.8	2080.9	2093.6	2082.8
175°	2100.6	2095.6	2091.7	2104.4	2093.6
177.5°	2107.5	2102.6	2098.7	2109.4	2098.7
180°	2104.4	2104.4	2104.4	2104.4	2104.4

TEST NUMBER: P910640

CATALOG NUMBER: DFN2DIP-HX2F0-030D060US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.19	9.90	10.29	10.99	12.49	5.17	5.88	6.27	6.97	8.48
	3H	10.84	11.47	11.94	12.57	14.09	6.34	6.97	7.45	8.07	9.59
	4H	11.42	12.02	12.54	13.12	14.65	6.77	7.37	7.89	8.47	10.00
	6H	11.82	12.37	12.94	13.47	15.01	7.07	7.62	8.20	8.73	10.26
	8H	11.93	12.45	13.06	13.57	15.10	7.15	7.67	8.28	8.79	10.32
	12H	11.97	12.47	13.11	13.59	15.14	7.18	7.68	8.31	8.79	10.35
4H	2H	9.19	9.79	10.32	10.89	12.42	5.74	6.34	6.87	7.44	8.97
	3H	10.98	11.48	12.11	12.61	14.15	7.06	7.56	8.19	8.69	10.22
	4H	11.65	12.11	12.78	13.22	14.78	7.59	8.05	8.72	9.16	10.72
	6H	12.13	12.52	13.27	13.66	15.21	7.98	8.37	9.12	9.52	11.06
	8H	12.29	12.66	13.43	13.79	15.36	8.10	8.46	9.24	9.60	11.16
	12H	12.37	12.70	13.52	13.84	15.41	8.15	8.48	9.31	9.62	11.20
8H	4H	11.60	11.97	12.74	13.10	14.67	7.84	8.21	8.98	9.34	10.91
	6H	12.14	12.44	13.30	13.61	15.18	8.33	8.64	9.50	9.81	11.37
	8H	12.34	12.60	13.50	13.75	15.34	8.51	8.78	9.68	9.93	11.51
	12H	12.45	12.68	13.62	13.83	15.45	8.61	8.84	9.78	9.99	11.61
12H	4H	11.55	11.88	12.70	13.02	14.59	7.84	8.17	9.00	9.31	10.89
	6H	12.11	12.37	13.28	13.53	15.11	8.38	8.64	9.54	9.79	11.38
	8H	12.31	12.54	13.48	13.69	15.31	8.57	8.80	9.74	9.95	11.57