

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916159

Luminaire Tested: DFN2DIP-HX3F0-030D030US930-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916159
REPORT IS A COMBINATION OF REPORTS P900721 AND P897645
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-030D030US930-FLLONL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4842.9 lumens
Efficiency: N/A
Efficacy: 103.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 46.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916159

CATALOG NUMBER: DFN2DIP-HX3F0-030D030US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P916159

CATALOG NUMBER: DFN2DIP-HX3F0-030D030US930-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1102	1102	1102
5°	1104	1086	1094
10°	1094	1071	1078
15°	1078	1053	1055
20°	1055	1027	1030
25°	1033	997	1002
30°	1006	969	967
35°	979	936	929
40°	947	903	894
45°	915	870	857
50°	880	834	815
55°	843	794	776
60°	801	746	731
65°	756	696	679
70°	698	635	622
75°	618	562	568
80°	521	468	468
85°	369	310	303

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 915 cd/sqm

TEST NUMBER: P916159

CATALOG NUMBER: DFN2DIP-HX3F0-030D030US930-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.6	1.8
10°-20°	252.0	5.2
20°-30°	370.4	7.6
30°-40°	430.2	8.9
40°-50°	429.7	8.9
50°-60°	374.6	7.7
60°-70°	277.0	5.7
70°-80°	156.7	3.2
80°-90°	42.8	0.9
90°-100°	27.2	0.6
100°-110°	101.5	2.1
110°-120°	269.1	5.6
120°-130°	446.3	9.2
130°-140°	474.1	9.8
140°-150°	440.6	9.1
150°-160°	354.3	7.3
160°-170°	228.3	4.7
170°-180°	78.6	1.6
0°-30°	712.0	14.7
0°-40°	1142.2	23.6
0°-60°	1946.5	40.2
0°-90°	2422.9	50.0
90°-120°	397.8	8.2
90°-150°	1758.9	36.3
90°-180°	2420.0	50.0
0°-180°	4842.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	952	952	952	952	952	
5°	952	948	938	945	944	90
15°	906	901	889	892	888	255
25°	820	813	797	799	797	377
35°	707	698	684	678	674	442
45°	576	569	556	545	542	444
55°	436	430	419	408	404	390
65°	294	288	279	271	266	290
75°	154	152	147	142	144	164
85°	38	37	36	33	32	42
90°	1	7	12	15	16	4
95°	39	19	23	26	26	46
105°	182	200	36	43	45	194
115°	343	354	368	92	49	338
125°	486	493	505	509	511	433
135°	601	610	616	622	621	464
145°	697	696	707	711	708	436
155°	768	762	769	773	768	354
165°	809	805	807	811	807	228
175°	827	823	824	828	822	79
180°	826	826	826	826	826	

TEST NUMBER: P916159

CATALOG NUMBER: DFN2DIP-HX3F0-030D030US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	951.7	951.7	951.7	951.7	951.7
2.5°	957.2	952.7	942.6	951.7	950.0
5°	951.7	948.1	938.0	945.3	943.5
7.5°	945.3	939.9	929.8	937.2	935.3
10°	935.3	928.9	917.9	925.2	922.5
12.5°	921.5	916.1	905.1	909.6	907.8
15°	906.0	900.6	888.6	892.3	887.7
17.5°	886.7	881.3	869.4	873.9	869.4
20°	865.7	860.2	847.4	850.1	846.5
22.5°	844.7	836.5	824.5	824.5	822.6
25°	819.9	812.7	797.1	798.9	797.1
27.5°	792.5	786.0	774.2	771.5	767.0
30°	765.1	757.7	744.0	741.3	737.6
32.5°	735.8	730.3	715.7	710.1	706.5
35°	707.4	698.3	683.6	678.1	673.5
37.5°	675.4	667.2	652.5	646.0	641.5
40°	642.5	635.1	620.4	612.3	608.6
42.5°	610.4	603.1	588.5	579.3	573.8
45°	575.7	569.2	555.5	545.4	541.8
47.5°	541.8	535.4	520.7	510.6	505.2
50°	506.1	501.5	488.7	475.9	471.3
52.5°	471.3	464.9	453.1	443.0	436.5
55°	435.7	430.2	419.1	408.2	403.7
57.5°	399.9	395.3	383.4	372.4	368.8
60°	364.2	360.6	347.8	337.7	335.0
62.5°	329.5	323.0	313.9	304.8	301.1
65°	293.8	288.3	279.2	270.9	266.4
67.5°	257.2	252.6	244.3	238.0	234.3
70°	223.3	219.6	211.4	205.0	201.4
72.5°	188.6	184.8	180.3	173.9	171.2
75°	153.7	152.0	147.3	141.9	143.7
77.5°	122.6	119.0	117.1	114.4	111.7
80°	91.6	90.6	88.7	86.0	84.2
82.5°	62.2	62.2	61.4	57.6	57.6
85°	37.5	36.6	35.7	32.9	32.0
87.5°	16.5	14.7	12.8	10.1	9.1
90°	0.6	7.2	11.9	15.0	16.1
92.5°	15.0	12.6	14.3	15.6	16.1
95°	38.8	19.1	23.2	26.3	25.7
97.5°	69.9	21.0	30.4	32.3	32.9
100°	105.7	23.9	34.1	38.8	40.0
102.5°	145.1	144.0	35.2	41.7	43.6
105°	181.6	199.5	36.4	43.0	45.4
107.5°	224.0	238.9	37.7	44.2	46.6
110°	264.6	277.1	104.5	44.8	47.2

TEST NUMBER: P916159

CATALOG NUMBER: DFN2DIP-HX3F0-030D030US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	302.9	313.6	303.5	46.0	47.8
115°	343.4	353.6	368.5	92.0	49.0
117.5°	378.7	390.6	400.8	315.4	158.9
120°	418.1	427.1	437.8	445.0	364.4
122.5°	451.5	461.1	473.1	476.6	477.3
125°	485.6	493.3	504.8	508.9	510.7
127.5°	516.7	525.0	534.0	540.0	540.5
130°	545.9	555.5	562.1	568.6	568.1
132.5°	575.8	583.6	590.1	595.5	594.9
135°	600.9	610.5	615.8	621.8	620.6
137.5°	627.1	634.3	640.3	646.3	644.5
140°	652.8	657.6	664.1	669.5	666.6
142.5°	674.4	678.6	686.3	691.0	688.1
145°	697.1	696.4	706.6	710.8	707.8
147.5°	716.7	714.9	725.1	728.1	725.7
150°	735.9	731.7	741.3	744.8	741.8
152.5°	751.9	747.2	756.2	759.8	755.6
155°	767.5	762.2	769.3	772.9	768.2
157.5°	780.1	775.3	780.7	784.9	780.1
160°	790.8	787.3	790.8	794.4	790.2
162.5°	800.4	796.8	799.8	804.0	798.6
165°	808.7	805.2	807.0	811.1	807.0
167.5°	815.3	811.7	813.5	817.7	812.4
170°	820.7	817.1	818.3	822.5	817.1
172.5°	824.3	820.7	821.9	826.1	820.7
175°	827.2	823.0	824.3	828.4	822.5
177.5°	828.4	824.3	824.9	829.1	823.7
180°	825.5	825.5	825.5	825.5	825.5

TEST NUMBER: P916159

CATALOG NUMBER: DFN2DIP-HX3F0-030D030US930-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.57	8.43	8.53	9.40	10.67	7.14	8.00	8.10	8.97	10.25
	3H	9.22	10.00	10.19	10.98	12.27	8.75	9.53	9.72	10.51	11.80
	4H	9.80	10.54	10.79	11.52	12.82	9.34	10.07	10.32	11.05	12.35
	6H	10.20	10.87	11.19	11.86	13.18	9.73	10.40	10.72	11.39	12.71
	8H	10.30	10.94	11.30	11.95	13.26	9.83	10.47	10.83	11.48	12.79
	12H	10.35	10.96	11.35	11.96	13.29	9.87	10.48	10.88	11.48	12.82
4H	2H	8.03	8.76	9.02	9.75	11.05	7.69	8.42	8.67	9.40	10.70
	3H	9.89	10.50	10.88	11.51	12.83	9.50	10.11	10.49	11.12	12.44
	4H	10.59	11.15	11.60	12.16	13.50	10.19	10.75	11.20	11.76	13.10
	6H	11.10	11.58	12.12	12.61	13.95	10.70	11.18	11.71	12.21	13.55
	8H	11.25	11.70	12.27	12.72	14.07	10.84	11.29	11.86	12.31	13.66
	12H	11.32	11.72	12.35	12.76	14.12	10.90	11.31	11.94	12.35	13.70
8H	4H	10.79	11.24	11.81	12.26	13.61	10.43	10.88	11.45	11.90	13.25
	6H	11.41	11.78	12.45	12.85	14.20	11.05	11.42	12.09	12.49	13.84
	8H	11.63	11.95	12.68	13.00	14.37	11.26	11.59	12.31	12.64	14.01
	12H	11.75	12.04	12.81	13.09	14.50	11.37	11.66	12.43	12.71	14.12
12H	4H	10.77	11.18	11.81	12.22	13.57	10.42	10.83	11.46	11.87	13.22
	6H	11.44	11.77	12.49	12.82	14.18	11.09	11.42	12.14	12.47	13.84
	8H	11.67	11.96	12.73	13.01	14.42	11.32	11.61	12.37	12.65	14.06

END OF REPORT