

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913333

Luminaire Tested: DFN2DIP-HX2F0-020D020US927-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913333
REPORT IS A COMBINATION OF REPORTS P900672 AND P897595
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-020D020US927-RLONL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2915.2 lumens
Efficiency: N/A
Efficacy: 95.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 30.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913333

CATALOG NUMBER: DFN2DIP-HX2F0-020D020US927-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P913333

CATALOG NUMBER: DFN2DIP-HX2F0-020D020US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45
2	89	82	76	71	82	76	70	66	63	60	57	52	50	48	42	40	39
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	34
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1543	1543	1543
5°	1543	1515	1525
10°	1525	1481	1473
15°	1502	1429	1394
20°	1471	1358	1297
25°	1441	1279	1204
30°	1400	1199	1087
35°	1360	1113	984
40°	1319	1024	867
45°	1271	926	761
50°	1223	827	658
55°	1171	723	559
60°	1112	614	457
65°	1043	503	409
70°	959	400	366
75°	854	346	327
80°	703	280	276
85°	458	172	192

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1271 cd/sqm

TEST NUMBER: P913333

CATALOG NUMBER: DFN2DIP-HX2F0-020D020US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.4	2.1
10°-20°	168.5	5.8
20°-30°	236.5	8.1
30°-40°	257.8	8.8
40°-50°	237.0	8.1
50°-60°	186.1	6.4
60°-70°	121.2	4.2
70°-80°	62.3	2.1
80°-90°	16.9	0.6
90°-100°	17.6	0.6
100°-110°	65.7	2.3
110°-120°	174.3	6.0
120°-130°	289.1	9.9
130°-140°	307.1	10.5
140°-150°	285.4	9.8
150°-160°	229.5	7.9
160°-170°	147.9	5.1
170°-180°	50.9	1.7
0°-30°	466.4	16.0
0°-40°	724.2	24.8
0°-60°	1147.3	39.4
0°-90°	1347.6	46.2
90°-120°	257.7	8.8
90°-150°	1139.3	39.1
90°-180°	1568.0	53.8
0°-180°	2915.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	655	655	655	655	655	
5°	655	652	644	650	648	62
15°	623	616	596	585	579	176
25°	565	546	507	483	474	260
35°	487	457	405	367	354	305
45°	398	358	296	254	240	308
55°	303	257	193	157	146	271
65°	204	156	103	83	81	203
75°	109	68	47	43	43	115
85°	25	13	11	11	11	29
90°	0	5	8	10	10	3
95°	25	12	15	17	17	30
105°	118	129	24	28	29	126
115°	222	229	239	60	32	219
125°	315	320	327	330	331	281
135°	389	396	399	403	402	301
145°	452	451	458	460	458	282
155°	497	494	498	501	498	229
165°	524	522	523	526	523	148
175°	536	533	534	537	533	51
180°	535	535	535	535	535	

TEST NUMBER: P913333

CATALOG NUMBER: DFN2DIP-HX2F0-020D020US927-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	654.8	654.8	654.8	654.8	654.8
2.5°	657.7	654.8	648.2	654.3	653.1
5°	654.8	651.9	644.1	649.5	647.7
7.5°	649.5	645.9	637.6	640.0	637.0
10°	642.4	638.2	626.4	624.6	621.1
12.5°	633.5	628.1	612.1	608.6	602.1
15°	622.8	616.2	596.1	584.9	579.0
17.5°	610.4	600.9	576.0	562.9	553.5
20°	596.1	584.2	554.7	539.9	526.8
22.5°	580.7	567.1	532.7	512.6	503.7
25°	565.4	546.4	507.2	483.0	474.0
27.5°	547.0	526.8	483.5	455.7	442.0
30°	527.4	504.9	457.5	427.3	411.2
32.5°	508.4	481.2	432.6	397.0	382.2
35°	487.1	456.9	404.8	367.4	354.3
37.5°	466.4	433.7	378.7	337.8	323.0
40°	444.4	408.9	351.4	309.3	293.9
42.5°	421.9	384.0	324.2	280.3	265.5
45°	398.2	358.5	296.4	254.2	240.0
47.5°	375.7	333.7	269.7	227.5	214.5
50°	350.9	308.8	243.6	202.6	190.3
52.5°	326.5	282.0	218.6	179.6	168.3
55°	302.8	256.6	192.6	157.1	145.8
57.5°	278.5	231.1	169.5	136.3	126.8
60°	253.7	206.2	145.2	115.0	105.5
62.5°	229.3	182.0	124.5	96.0	91.3
65°	204.5	156.5	103.1	83.0	81.2
67.5°	180.8	132.7	83.0	72.9	71.1
70°	155.8	109.6	68.7	62.8	60.4
72.5°	132.1	88.2	57.4	52.8	51.6
75°	109.0	67.5	47.4	43.3	42.7
77.5°	86.0	48.0	37.3	34.9	33.7
80°	64.6	34.4	28.4	26.1	26.1
82.5°	45.0	23.1	19.6	18.4	18.4
85°	25.4	13.0	11.2	11.2	11.2
87.5°	9.5	4.8	4.8	4.1	4.1
90°	0.4	4.7	7.7	9.7	10.5
92.5°	9.7	8.2	9.3	10.1	10.5
95°	25.1	12.4	15.1	17.0	16.6
97.5°	45.2	13.5	19.7	20.9	21.3
100°	68.5	15.4	22.0	25.1	25.9
102.5°	94.0	93.2	22.8	27.1	28.3
105°	117.6	129.2	23.6	27.8	29.4
107.5°	145.1	154.7	24.4	28.6	30.2
110°	171.4	179.5	67.7	29.1	30.6

TEST NUMBER: P913333

CATALOG NUMBER: DFN2DIP-HX2F0-020D020US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	196.1	203.1	196.5	29.8	31.0
115°	222.4	229.0	238.8	59.6	31.8
117.5°	245.3	253.0	259.6	204.3	102.9
120°	270.8	276.6	283.6	288.3	236.0
122.5°	292.5	298.7	306.4	308.7	309.2
125°	314.6	319.6	326.9	329.6	330.8
127.5°	334.7	340.1	345.9	349.7	350.1
130°	353.6	359.8	364.1	368.4	368.0
132.5°	373.0	378.0	382.2	385.7	385.4
135°	389.3	395.5	398.9	402.8	402.0
137.5°	406.2	410.9	414.8	418.7	417.5
140°	422.9	426.0	430.2	433.7	431.8
142.5°	436.8	439.6	444.6	447.7	445.7
145°	451.5	451.1	457.7	460.4	458.5
147.5°	464.3	463.1	469.7	471.6	470.1
150°	476.7	474.0	480.1	482.4	480.5
152.5°	487.1	484.0	489.8	492.2	489.4
155°	497.2	493.7	498.4	500.7	497.6
157.5°	505.3	502.2	505.7	508.4	505.3
160°	512.3	509.9	512.3	514.6	511.9
162.5°	518.4	516.1	518.1	520.8	517.3
165°	523.9	521.6	522.7	525.5	522.7
167.5°	528.1	525.8	527.0	529.7	526.2
170°	531.6	529.3	530.0	532.7	529.3
172.5°	533.9	531.6	532.4	535.1	531.6
175°	535.8	533.1	533.9	536.6	532.7
177.5°	536.6	533.9	534.3	537.0	533.5
180°	534.7	534.7	534.7	534.7	534.7

TEST NUMBER: P913333

CATALOG NUMBER: DFN2DIP-HX2F0-020D020US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.15	8.95	9.15	9.96	11.28	4.14	4.94	5.13	5.94	7.26
	3H	9.80	10.52	10.81	11.53	12.88	5.31	6.02	6.31	7.03	8.38
	4H	10.39	11.07	11.41	12.08	13.44	5.74	6.42	6.76	7.43	8.79
	6H	10.79	11.42	11.82	12.44	13.80	6.05	6.67	7.08	7.69	9.06
	8H	10.91	11.50	11.94	12.54	13.90	6.13	6.72	7.16	7.76	9.12
	12H	10.96	11.52	12.00	12.55	13.94	6.16	6.73	7.20	7.76	9.14
4H	2H	8.16	8.84	9.19	9.86	11.21	4.71	5.39	5.74	6.40	7.76
	3H	9.96	10.52	10.99	11.57	12.94	6.04	6.60	7.07	7.65	9.02
	4H	10.63	11.15	11.67	12.18	13.57	6.57	7.09	7.61	8.12	9.52
	6H	11.12	11.56	12.17	12.62	14.01	6.97	7.41	8.02	8.47	9.86
	8H	11.28	11.70	12.33	12.75	14.15	7.09	7.50	8.14	8.56	9.96
	12H	11.36	11.74	12.43	12.80	14.21	7.15	7.52	8.21	8.58	9.99
8H	4H	10.59	11.01	11.64	12.06	13.46	6.84	7.25	7.89	8.30	9.70
	6H	11.13	11.47	12.21	12.57	13.97	7.33	7.67	8.40	8.76	10.16
	8H	11.33	11.63	12.41	12.71	14.13	7.51	7.81	8.59	8.88	10.30
	12H	11.45	11.71	12.54	12.79	14.25	7.61	7.87	8.70	8.95	10.41
12H	4H	10.54	10.92	11.61	11.98	13.39	6.84	7.21	7.90	8.27	9.68
	6H	11.11	11.41	12.19	12.48	13.90	7.37	7.67	8.45	8.75	10.17
	8H	11.31	11.57	12.39	12.64	14.10	7.57	7.83	8.65	8.90	10.36

END OF REPORT