

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916198

Luminaire Tested: DFN2DIP-HX3F0-040D070US930-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916198
REPORT IS A COMBINATION OF REPORTS P899259 AND P896089
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-040D070US930-FLLFLL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8279.4 lumens
Efficiency: N/A
Efficacy: 94.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 87.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916198
CATALOG NUMBER: DFN2DIP-HX3F0-040D070US930-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P916198

CATALOG NUMBER: DFN2DIP-HX3F0-040D070US930-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39				39
1	95	91	87	84	86	83	80	77	68	65	63	54	52	51	41	40	39	33				33
2	87	79	73	68	79	72	67	63	59	56	52	47	45	42	36	34	33	28				28
3	79	70	63	57	72	64	58	53	52	48	44	42	38	36	32	30	28	23				23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	31	28	26	24	20				20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	26	23	21	17				17
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15				15
7	56	44	37	31	51	41	34	29	34	28	25	27	23	20	21	18	16	14				14
8	52	40	33	27	47	37	30	26	31	26	22	25	21	18	19	17	15	12				12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11				11
10	45	34	26	22	41	31	25	20	26	21	18	21	17	15	17	14	12	10				10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1470	1470	1470
5°	1472	1448	1458
10°	1459	1428	1438
15°	1437	1403	1406
20°	1407	1370	1374
25°	1378	1330	1336
30°	1341	1292	1289
35°	1306	1248	1239
40°	1263	1204	1192
45°	1220	1159	1143
50°	1173	1113	1087
55°	1124	1058	1035
60°	1068	994	975
65°	1008	928	905
70°	930	846	829
75°	824	749	758
80°	694	624	624
85°	493	413	405

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 1699 cd/sqm



TEST NUMBER: P916198

CATALOG NUMBER: DFN2DIP-HX3F0-040D070US930-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.4	1.4
10°-20°	336.0	4.1
20°-30°	493.8	6.0
30°-40°	573.6	6.9
40°-50°	572.9	6.9
50°-60°	499.5	6.0
60°-70°	369.3	4.5
70°-80°	208.9	2.5
80°-90°	60.3	0.7
90°-100°	111.7	1.3
100°-110°	354.9	4.3
110°-120°	607.3	7.3
120°-130°	798.7	9.6
130°-140°	896.5	10.8
140°-150°	879.1	10.6
150°-160°	737.5	8.9
160°-170°	489.1	5.9
170°-180°	170.9	2.1
0°-30°	949.3	11.5
0°-40°	1522.9	18.4
0°-60°	2595.3	31.3
0°-90°	3233.7	39.1
90°-120°	1073.9	13.0
90°-150°	3648.2	44.1
90°-180°	5046.0	60.9
0°-180°	8279.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1269	1269	1269	1269	1269	
5°	1269	1264	1251	1260	1258	120
15°	1208	1201	1185	1190	1184	340
25°	1093	1084	1063	1065	1063	503
35°	943	931	912	904	898	589
45°	768	759	741	727	722	592
55°	581	574	559	544	538	519
65°	392	384	372	361	355	387
75°	205	203	196	189	192	219
85°	50	49	48	44	43	56
90°	2	20	53	50	52	8
95°	79	95	97	97	95	88
105°	328	332	335	338	338	346
115°	609	618	616	614	609	603
125°	886	900	896	891	889	792
135°	1147	1163	1167	1165	1161	886
145°	1392	1403	1412	1413	1407	870
155°	1592	1596	1601	1608	1604	733
165°	1731	1730	1730	1741	1733	488
175°	1802	1797	1794	1805	1796	171
180°	1805	1805	1805	1805	1805	



TEST NUMBER: P916198

CATALOG NUMBER: DFN2DIP-HX3F0-040D070US930-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1268.9	1268.9	1268.9	1268.9	1268.9
2.5°	1276.3	1270.2	1256.8	1268.9	1266.6
5°	1268.9	1264.1	1250.7	1260.4	1258.1
7.5°	1260.4	1253.1	1239.7	1249.5	1247.1
10°	1247.1	1238.5	1223.9	1233.6	1230.0
12.5°	1228.7	1221.4	1206.8	1212.9	1210.4
15°	1207.9	1200.7	1184.8	1189.7	1183.6
17.5°	1182.3	1175.1	1159.2	1165.2	1159.2
20°	1154.2	1147.0	1129.9	1133.5	1128.8
22.5°	1126.3	1115.2	1099.3	1099.3	1096.9
25°	1093.2	1083.5	1062.8	1065.2	1062.8
27.5°	1056.6	1048.1	1032.3	1028.7	1022.6
30°	1020.1	1010.3	992.1	988.4	983.5
32.5°	981.0	973.8	954.2	946.9	941.9
35°	943.2	931.1	911.5	904.2	898.1
37.5°	900.5	889.5	869.9	861.4	855.3
40°	856.6	846.8	827.2	816.4	811.5
42.5°	813.9	804.0	784.6	772.3	765.1
45°	767.5	759.0	740.6	727.3	722.4
47.5°	722.4	713.8	694.3	680.9	673.6
50°	674.7	668.6	651.6	634.5	628.4
52.5°	628.4	619.9	604.1	590.6	582.0
55°	580.9	573.5	558.9	544.2	538.2
57.5°	533.2	527.2	511.2	496.6	491.7
60°	485.6	480.8	463.7	450.3	446.6
62.5°	439.3	430.7	418.6	406.3	401.5
65°	391.8	384.3	372.2	361.2	355.1
67.5°	342.9	336.7	325.9	317.3	312.4
70°	297.7	292.9	281.8	273.3	268.5
72.5°	251.4	246.5	240.4	231.9	228.2
75°	205.0	202.6	196.4	189.1	191.6
77.5°	163.5	158.6	156.1	152.5	148.9
80°	122.1	120.7	118.3	114.7	112.3
82.5°	83.0	83.0	81.9	76.9	76.9
85°	50.0	48.8	47.6	43.9	42.7
87.5°	22.0	19.6	17.1	13.5	12.1
90°	1.6	19.6	53.3	50.1	51.7
92.5°	33.8	45.7	47.4	49.0	49.0
95°	79.4	94.7	97.4	97.4	94.7
97.5°	132.2	146.3	152.4	152.4	152.4
100°	193.1	205.7	210.0	210.0	208.4
102.5°	257.4	266.6	272.6	274.3	272.6
105°	327.6	331.9	335.2	337.9	337.9
107.5°	397.2	403.7	403.7	404.9	397.2
110°	464.7	473.4	473.4	473.4	469.0



TEST NUMBER: P916198

CATALOG NUMBER: DFN2DIP-HX3F0-040D070US930-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	537.6	546.9	545.3	540.9	537.6
115°	609.4	618.2	615.5	613.8	609.4
117.5°	680.7	692.7	685.1	680.7	676.4
120°	752.5	764.5	752.5	752.5	747.6
122.5°	817.8	833.1	825.5	821.1	817.8
125°	886.4	900.0	895.7	890.8	889.2
127.5°	953.3	970.2	964.3	957.7	953.3
130°	1015.9	1035.5	1032.8	1029.6	1023.5
132.5°	1086.1	1101.4	1102.4	1094.9	1090.5
135°	1146.6	1163.3	1166.7	1165.0	1160.7
137.5°	1214.0	1227.6	1230.3	1229.2	1222.7
140°	1273.3	1286.9	1294.5	1294.5	1288.6
142.5°	1334.2	1347.9	1352.2	1353.8	1347.9
145°	1392.0	1402.8	1411.5	1413.2	1407.2
147.5°	1443.6	1457.3	1463.8	1466.5	1460.5
150°	1497.0	1506.2	1512.2	1517.1	1512.2
152.5°	1544.3	1553.6	1561.1	1567.2	1561.1
155°	1591.6	1595.9	1600.9	1608.5	1603.6
157.5°	1632.5	1635.7	1638.4	1649.3	1641.7
160°	1668.9	1672.2	1673.8	1683.0	1676.5
162.5°	1702.7	1702.7	1704.3	1714.6	1707.0
165°	1731.4	1729.8	1729.8	1740.7	1733.1
167.5°	1757.6	1752.7	1752.7	1763.6	1756.0
170°	1777.2	1772.9	1771.2	1782.1	1772.9
172.5°	1790.8	1786.4	1784.8	1795.7	1786.4
175°	1801.6	1797.3	1794.1	1804.9	1795.7
177.5°	1807.7	1803.3	1800.0	1809.3	1800.0
180°	1804.9	1804.9	1804.9	1804.9	1804.9



TEST NUMBER: P916198
 CATALOG NUMBER: DFN2DIP-HX3F0-040D070US930-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.46	8.23	8.51	9.28	10.70	7.03	7.80	8.08	8.85	10.27
	3H	9.11	9.80	10.16	10.86	12.29	8.64	9.33	9.69	10.39	11.83
	4H	9.68	10.34	10.75	11.40	12.85	9.21	9.87	10.28	10.93	12.38
	6H	10.07	10.68	11.15	11.74	13.20	9.60	10.21	10.68	11.27	12.73
	8H	10.17	10.75	11.25	11.83	13.28	9.70	10.28	10.78	11.36	12.81
	12H	10.21	10.76	11.30	11.84	13.31	9.74	10.28	10.83	11.36	12.84
4H	2H	7.91	8.56	8.98	9.62	11.07	7.56	8.22	8.64	9.28	10.73
	3H	9.76	10.30	10.84	11.39	12.85	9.37	9.91	10.45	11.00	12.46
	4H	10.46	10.96	11.55	12.04	13.52	10.06	10.56	11.15	11.64	13.12
	6H	10.96	11.39	12.06	12.50	13.97	10.56	10.99	11.65	12.09	13.56
	8H	11.11	11.51	12.20	12.60	14.09	10.70	11.10	11.79	12.20	13.69
	12H	11.17	11.54	12.28	12.64	14.14	10.76	11.12	11.87	12.23	13.72
8H	4H	10.65	11.05	11.74	12.14	13.63	10.29	10.69	11.38	11.79	13.27
	6H	11.26	11.60	12.38	12.73	14.22	10.91	11.24	12.02	12.38	13.86
	8H	11.48	11.77	12.60	12.89	14.39	11.11	11.41	12.24	12.52	14.03
	12H	11.60	11.86	12.73	12.97	14.52	11.22	11.48	12.35	12.59	14.14
12H	4H	10.63	10.99	11.74	12.10	13.59	10.28	10.64	11.39	11.75	13.24
	6H	11.29	11.58	12.42	12.70	14.21	10.94	11.24	12.07	12.35	13.86
	8H	11.52	11.78	12.65	12.90	14.44	11.17	11.43	12.30	12.54	14.08