

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916199

Luminaire Tested: DFN2DIP-HX3F0-040D070US930-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916199
REPORT IS A COMBINATION OF REPORTS P900779 AND P897645
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-040D070US930-FLLONL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8878.6 lumens
Efficiency: N/A
Efficacy: 101.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 87.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916199

CATALOG NUMBER: DFN2DIP-HX3F0-040D070US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P916199

CATALOG NUMBER: DFN2DIP-HX3F0-040D070US930-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	95	90	87	83	86	82	79	76	66	64	62	52	50	49	39	38	37
2	86	79	73	68	78	72	67	62	58	54	51	46	43	41	34	32	31
3	79	69	62	57	71	63	57	52	51	47	43	40	37	35	30	28	26
4	72	61	54	48	65	56	49	44	45	41	37	36	32	30	27	25	23
5	66	55	47	41	59	50	43	38	41	35	32	32	28	26	24	22	20
6	61	49	41	35	55	45	38	33	37	31	27	29	25	22	22	19	17
7	56	44	36	31	51	40	33	29	33	28	24	26	23	20	20	17	15
8	52	40	32	27	47	37	30	25	30	25	21	24	20	18	18	16	14
9	48	36	29	24	44	33	27	22	28	23	19	22	18	16	17	14	12
10	45	33	26	21	41	31	24	20	25	20	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1470	1470	1470
5°	1472	1448	1458
10°	1459	1428	1438
15°	1437	1403	1406
20°	1407	1370	1374
25°	1378	1330	1336
30°	1341	1292	1289
35°	1306	1248	1239
40°	1263	1204	1192
45°	1220	1159	1143
50°	1173	1113	1087
55°	1124	1058	1035
60°	1068	994	975
65°	1008	928	905
70°	930	846	829
75°	824	749	758
80°	694	624	624
85°	493	413	405

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1235 cd/sqm

TEST NUMBER: P916199

CATALOG NUMBER: DFN2DIP-HX3F0-040D070US930-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.4	1.3
10°-20°	336.0	3.8
20°-30°	493.8	5.6
30°-40°	573.6	6.5
40°-50°	572.9	6.5
50°-60°	499.5	5.6
60°-70°	369.3	4.2
70°-80°	208.9	2.4
80°-90°	58.5	0.7
90°-100°	63.5	0.7
100°-110°	236.8	2.7
110°-120°	627.9	7.1
120°-130°	1041.5	11.7
130°-140°	1106.3	12.5
140°-150°	1028.1	11.6
150°-160°	826.6	9.3
160°-170°	532.6	6.0
170°-180°	183.3	2.1
0°-30°	949.3	10.7
0°-40°	1522.9	17.2
0°-60°	2595.3	29.2
0°-90°	3232.0	36.4
90°-120°	928.2	10.5
90°-150°	4104.1	46.2
90°-180°	5647.0	63.6
0°-180°	8878.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1269	1269	1269	1269	1269	
5°	1269	1264	1251	1260	1258	120
15°	1208	1201	1185	1190	1184	340
25°	1093	1084	1063	1065	1063	503
35°	943	931	912	904	898	589
45°	768	759	741	727	722	592
55°	581	574	559	544	538	519
65°	392	384	372	361	355	387
75°	205	203	196	189	192	219
85°	50	49	48	44	43	56
90°	1	17	28	35	38	8
95°	90	44	54	61	60	107
105°	424	466	85	100	106	453
115°	801	825	860	215	114	789
125°	1133	1151	1178	1188	1192	1010
135°	1402	1424	1437	1451	1448	1083
145°	1626	1625	1649	1658	1652	1017
155°	1791	1778	1795	1803	1792	825
165°	1887	1879	1883	1893	1883	533
175°	1930	1920	1923	1933	1919	184
180°	1926	1926	1926	1926	1926	

TEST NUMBER: P916199

CATALOG NUMBER: DFN2DIP-HX3F0-040D070US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1268.9	1268.9	1268.9	1268.9	1268.9
2.5°	1276.3	1270.2	1256.8	1268.9	1266.6
5°	1268.9	1264.1	1250.7	1260.4	1258.1
7.5°	1260.4	1253.1	1239.7	1249.5	1247.1
10°	1247.1	1238.5	1223.9	1233.6	1230.0
12.5°	1228.7	1221.4	1206.8	1212.9	1210.4
15°	1207.9	1200.7	1184.8	1189.7	1183.6
17.5°	1182.3	1175.1	1159.2	1165.2	1159.2
20°	1154.2	1147.0	1129.9	1133.5	1128.8
22.5°	1126.3	1115.2	1099.3	1099.3	1096.9
25°	1093.2	1083.5	1062.8	1065.2	1062.8
27.5°	1056.6	1048.1	1032.3	1028.7	1022.6
30°	1020.1	1010.3	992.1	988.4	983.5
32.5°	981.0	973.8	954.2	946.9	941.9
35°	943.2	931.1	911.5	904.2	898.1
37.5°	900.5	889.5	869.9	861.4	855.3
40°	856.6	846.8	827.2	816.4	811.5
42.5°	813.9	804.0	784.6	772.3	765.1
45°	767.5	759.0	740.6	727.3	722.4
47.5°	722.4	713.8	694.3	680.9	673.6
50°	674.7	668.6	651.6	634.5	628.4
52.5°	628.4	619.9	604.1	590.6	582.0
55°	580.9	573.5	558.9	544.2	538.2
57.5°	533.2	527.2	511.2	496.6	491.7
60°	485.6	480.8	463.7	450.3	446.6
62.5°	439.3	430.7	418.6	406.3	401.5
65°	391.8	384.3	372.2	361.2	355.1
67.5°	342.9	336.7	325.9	317.3	312.4
70°	297.7	292.9	281.8	273.3	268.5
72.5°	251.4	246.5	240.4	231.9	228.2
75°	205.0	202.6	196.4	189.1	191.6
77.5°	163.5	158.6	156.1	152.5	148.9
80°	122.1	120.7	118.3	114.7	112.3
82.5°	83.0	83.0	81.9	76.9	76.9
85°	50.0	48.8	47.6	43.9	42.7
87.5°	22.0	19.6	17.1	13.5	12.1
90°	1.3	16.7	27.8	34.9	37.6
92.5°	34.9	29.3	33.4	36.3	37.6
95°	90.5	44.5	54.3	61.4	59.9
97.5°	163.0	48.8	71.0	75.3	76.6
100°	246.8	55.8	79.4	90.5	93.4
102.5°	338.6	336.0	82.3	97.5	101.7
105°	423.7	465.5	85.0	100.3	105.9
107.5°	522.6	557.4	87.9	103.1	108.8
110°	617.5	646.6	243.9	104.6	110.1

TEST NUMBER: P916199

CATALOG NUMBER: DFN2DIP-HX3F0-040D070US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	706.7	731.6	708.0	107.2	111.5
115°	801.4	825.0	859.9	214.7	114.4
117.5°	883.6	911.4	935.2	735.8	370.7
120°	975.6	996.5	1021.7	1038.4	850.2
122.5°	1053.5	1075.9	1103.9	1112.1	1113.6
125°	1133.0	1151.2	1177.7	1187.5	1191.6
127.5°	1205.5	1225.0	1246.0	1260.0	1261.3
130°	1273.8	1296.2	1311.4	1326.8	1325.5
132.5°	1343.5	1361.7	1377.0	1389.5	1388.2
135°	1402.1	1424.4	1436.9	1450.9	1448.1
137.5°	1463.3	1480.1	1494.1	1508.1	1503.9
140°	1523.2	1534.5	1549.7	1562.3	1555.3
142.5°	1573.5	1583.3	1601.3	1612.4	1605.5
145°	1626.5	1625.1	1648.7	1658.5	1651.5
147.5°	1672.3	1668.3	1691.9	1698.8	1693.4
150°	1717.0	1707.3	1729.7	1737.9	1731.0
152.5°	1754.6	1743.5	1764.4	1772.8	1763.1
155°	1790.9	1778.4	1795.1	1803.4	1792.4
157.5°	1820.2	1809.1	1821.6	1831.4	1820.2
160°	1845.3	1836.9	1845.3	1853.6	1843.8
162.5°	1867.5	1859.2	1866.1	1875.9	1863.4
165°	1887.0	1878.8	1882.8	1892.6	1882.8
167.5°	1902.4	1893.9	1898.3	1908.0	1895.5
170°	1915.0	1906.6	1909.3	1919.1	1906.6
172.5°	1923.3	1915.0	1917.8	1927.5	1915.0
175°	1930.2	1920.4	1923.3	1933.0	1919.1
177.5°	1933.0	1923.3	1924.8	1934.5	1921.9
180°	1926.1	1926.1	1926.1	1926.1	1926.1



TEST NUMBER: P916199

CATALOG NUMBER: DFN2DIP-HX3F0-040D070US930-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.16	7.91	8.23	8.98	10.43	6.73	7.48	7.80	8.55	10.00
	3H	8.80	9.48	9.88	10.55	12.03	8.34	9.01	9.41	10.09	11.56
	4H	9.38	10.02	10.47	11.10	12.58	8.91	9.55	10.00	10.63	12.11
	6H	9.77	10.36	10.87	11.44	12.93	9.30	9.89	10.39	10.97	12.46
	8H	9.87	10.43	10.97	11.53	13.01	9.40	9.96	10.50	11.06	12.54
	12H	9.91	10.44	11.01	11.53	13.04	9.44	9.97	10.54	11.06	12.56
4H	2H	7.61	8.24	8.70	9.32	10.80	7.26	7.90	8.36	8.98	10.46
	3H	9.45	9.99	10.55	11.09	12.58	9.06	9.60	10.16	10.70	12.19
	4H	10.16	10.65	11.26	11.74	13.25	9.75	10.24	10.86	11.34	12.85
	6H	10.66	11.08	11.77	12.20	13.70	10.25	10.67	11.36	11.79	13.29
	8H	10.80	11.19	11.91	12.30	13.82	10.39	10.79	11.51	11.90	13.42
	12H	10.86	11.22	11.99	12.34	13.87	10.45	10.80	11.58	11.93	13.45
8H	4H	10.34	10.73	11.45	11.84	13.36	9.98	10.37	11.10	11.49	13.01
	6H	10.96	11.28	12.09	12.43	13.95	10.60	10.92	11.73	12.07	13.59
	8H	11.17	11.46	12.31	12.59	14.13	10.81	11.09	11.95	12.22	13.76
	12H	11.29	11.54	12.44	12.67	14.25	10.91	11.16	12.06	12.29	13.87
12H	4H	10.32	10.67	11.45	11.80	13.32	9.97	10.33	11.10	11.45	12.97
	6H	10.99	11.27	12.13	12.40	13.94	10.64	10.92	11.78	12.05	13.59
	8H	11.22	11.47	12.36	12.59	14.17	10.86	11.11	12.01	12.24	13.81