

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913387

Luminaire Tested: DFN2DIP-HX2F0-040D060US927-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913387
REPORT IS A COMBINATION OF REPORTS P900715 AND P897595
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-040D060US927-FLLONL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7842.6 lumens
Efficiency: N/A
Efficacy: 92.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 84.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913387

CATALOG NUMBER: DFN2DIP-HX2F0-040D060US927-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P913387

CATALOG NUMBER: DFN2DIP-HX2F0-040D060US927-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	47	47	47
1	96	91	87	84	87	83	80	77	68	66	64	54	53	51	41	41	40	40	40	40
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	37	35	33	33	33	33
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28	28	28	28
4	73	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24	24	24	24
5	67	55	47	41	60	50	44	38	42	37	33	34	30	27	26	23	21	21	21	21
6	61	49	41	36	56	45	38	33	38	32	28	30	26	23	24	21	19	19	19	19
7	57	45	37	31	51	41	34	29	34	29	25	28	24	21	22	19	17	17	17	17
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	15	15	15
9	49	37	29	24	44	34	27	23	28	23	20	23	19	17	18	15	13	13	13	13
10	46	34	27	22	41	31	25	20	26	21	18	21	18	15	17	14	12	12	12	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2905	2905	2905
5°	2905	2858	2878
10°	2877	2812	2834
15°	2830	2759	2768
20°	2768	2688	2701
25°	2706	2604	2623
30°	2631	2526	2527
35°	2558	2434	2425
40°	2470	2342	2327
45°	2381	2249	2227
50°	2285	2151	2111
55°	2183	2038	2004
60°	2067	1905	1881
65°	1941	1765	1737
70°	1780	1596	1579
75°	1560	1392	1427
80°	1291	1133	1152
85°	877	712	712

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2381 cd/sqm

TEST NUMBER: P913387

CATALOG NUMBER: DFN2DIP-HX2F0-040D060US927-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.0	1.5
10°-20°	326.5	4.2
20°-30°	479.8	6.1
30°-40°	557.3	7.1
40°-50°	556.6	7.1
50°-60°	485.3	6.2
60°-70°	358.8	4.6
70°-80°	203.0	2.6
80°-90°	56.4	0.7
90°-100°	52.9	0.7
100°-110°	197.2	2.5
110°-120°	523.0	6.7
120°-130°	867.4	11.1
130°-140°	921.3	11.7
140°-150°	856.3	10.9
150°-160°	688.4	8.8
160°-170°	443.6	5.7
170°-180°	152.7	1.9
0°-30°	922.4	11.8
0°-40°	1479.7	18.9
0°-60°	2521.7	32.2
0°-90°	3139.8	40.0
90°-120°	773.0	9.9
90°-150°	3418.0	43.6
90°-180°	4703.0	60.0
0°-180°	7842.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1233	1233	1233	1233	1233	
5°	1233	1228	1215	1225	1222	117
15°	1174	1167	1151	1156	1150	331
25°	1062	1053	1033	1035	1033	489
35°	916	905	886	878	873	572
45°	746	738	720	707	702	576
55°	564	557	543	529	523	505
65°	381	373	362	351	345	376
75°	199	197	191	184	186	213
85°	49	48	46	43	42	54
90°	1	14	23	29	31	7
95°	75	37	45	51	50	89
105°	353	388	71	84	88	377
115°	667	687	716	179	95	657
125°	944	959	981	989	992	842
135°	1168	1186	1197	1208	1206	902
145°	1355	1353	1373	1381	1376	847
155°	1492	1481	1495	1502	1493	687
165°	1572	1565	1568	1576	1568	444
175°	1608	1599	1602	1610	1598	153
180°	1604	1604	1604	1604	1604	

TEST NUMBER: P913387

CATALOG NUMBER: DFN2DIP-HX2F0-040D060US927-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1233.0	1233.0	1233.0	1233.0	1233.0
2.5°	1240.2	1234.2	1221.1	1233.0	1230.7
5°	1233.0	1228.3	1215.2	1224.6	1222.4
7.5°	1224.6	1217.6	1204.5	1214.1	1211.7
10°	1211.7	1203.4	1189.2	1198.6	1195.1
12.5°	1193.8	1186.8	1172.6	1178.5	1176.1
15°	1173.7	1166.6	1151.2	1156.0	1150.1
17.5°	1148.8	1141.8	1126.3	1132.2	1126.3
20°	1121.5	1114.4	1097.9	1101.4	1096.8
22.5°	1094.3	1083.6	1068.2	1068.2	1065.8
25°	1062.2	1052.8	1032.7	1035.0	1032.7
27.5°	1026.7	1018.3	1003.1	999.5	993.6
30°	991.2	981.7	963.9	960.4	955.6
32.5°	953.2	946.2	927.2	920.0	915.2
35°	916.5	904.7	885.7	878.5	872.6
37.5°	875.0	864.3	845.3	837.0	831.1
40°	832.3	822.8	803.7	793.2	788.5
42.5°	790.8	781.2	762.4	750.4	743.4
45°	745.8	737.5	719.6	706.7	701.9
47.5°	701.9	693.6	674.6	661.6	654.5
50°	655.6	649.7	633.1	616.5	610.5
52.5°	610.5	602.3	586.9	573.9	565.5
55°	564.4	557.2	543.0	528.8	522.9
57.5°	518.1	512.2	496.7	482.5	477.8
60°	471.8	467.1	450.6	437.5	434.0
62.5°	426.8	418.5	406.7	394.8	390.1
65°	380.6	373.4	361.6	350.9	345.1
67.5°	333.2	327.2	316.6	308.3	303.6
70°	289.3	284.6	273.9	265.5	260.9
72.5°	244.3	239.5	233.6	225.3	221.7
75°	199.2	196.9	190.8	183.8	186.2
77.5°	158.8	154.1	151.7	148.1	144.7
80°	118.6	117.3	114.9	111.5	109.1
82.5°	80.6	80.6	79.5	74.7	74.7
85°	48.6	47.5	46.3	42.6	41.5
87.5°	21.4	19.0	16.6	13.1	11.8
90°	1.1	13.9	23.1	29.1	31.3
92.5°	29.1	24.4	27.8	30.2	31.3
95°	75.4	37.1	45.2	51.2	49.9
97.5°	135.8	40.6	59.1	62.7	63.8
100°	205.5	46.4	66.1	75.4	77.7
102.5°	282.0	279.8	68.5	81.2	84.8
105°	352.8	387.7	70.8	83.5	88.2
107.5°	435.3	464.2	73.2	85.9	90.5
110°	514.3	538.5	203.2	87.1	91.7

TEST NUMBER: P913387

CATALOG NUMBER: DFN2DIP-HX2F0-040D060US927-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	588.5	609.3	589.6	89.3	92.9
115°	667.4	687.1	716.2	178.8	95.2
117.5°	735.9	759.1	778.9	612.8	308.7
120°	812.5	829.9	850.9	864.7	708.1
122.5°	877.4	896.0	919.3	926.2	927.5
125°	943.6	958.8	980.8	989.0	992.4
127.5°	1004.0	1020.3	1037.8	1049.3	1050.4
130°	1060.9	1079.5	1092.2	1105.0	1103.9
132.5°	1119.0	1134.1	1146.8	1157.2	1156.1
135°	1167.8	1186.4	1196.7	1208.4	1206.0
137.5°	1218.7	1232.6	1244.4	1255.9	1252.5
140°	1268.6	1278.0	1290.7	1301.2	1295.4
142.5°	1310.5	1318.7	1333.7	1342.9	1337.1
145°	1354.6	1353.4	1373.1	1381.2	1375.5
147.5°	1392.8	1389.3	1409.1	1414.8	1410.3
150°	1430.0	1421.9	1440.5	1447.4	1441.6
152.5°	1461.3	1452.1	1469.4	1476.5	1468.3
155°	1491.5	1481.1	1495.1	1502.0	1492.7
157.5°	1515.9	1506.6	1517.1	1525.3	1515.9
160°	1536.8	1529.8	1536.8	1543.7	1535.6
162.5°	1555.3	1548.4	1554.2	1562.3	1551.9
165°	1571.6	1564.7	1568.1	1576.3	1568.1
167.5°	1584.4	1577.4	1581.0	1589.1	1578.6
170°	1594.9	1587.8	1590.2	1598.3	1587.8
172.5°	1601.8	1594.9	1597.2	1605.4	1594.9
175°	1607.6	1599.4	1601.8	1609.9	1598.3
177.5°	1609.9	1601.8	1603.0	1611.1	1600.7
180°	1604.1	1604.1	1604.1	1604.1	1604.1

TEST NUMBER: P913387

CATALOG NUMBER: DFN2DIP-HX2F0-040D060US927-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.84	10.62	10.88	11.67	13.07	9.42	10.20	10.46	11.24	12.65
	3H	11.47	12.17	12.52	13.22	14.65	11.01	11.71	12.06	12.76	14.19
	4H	12.04	12.70	13.10	13.76	15.19	11.58	12.24	12.64	13.30	14.73
	6H	12.42	13.02	13.48	14.08	15.53	11.96	12.57	13.03	13.62	15.07
	8H	12.51	13.09	13.58	14.16	15.60	12.05	12.63	13.12	13.71	15.14
	12H	12.54	13.10	13.62	14.16	15.63	12.08	12.63	13.16	13.70	15.17
4H	2H	10.28	10.95	11.35	12.00	13.43	9.95	10.61	11.01	11.66	13.10
	3H	12.11	12.67	13.19	13.75	15.19	11.73	12.28	12.80	13.37	14.81
	4H	12.81	13.31	13.89	14.38	15.85	12.41	12.92	13.49	13.99	15.46
	6H	13.29	13.73	14.38	14.82	16.28	12.90	13.33	13.98	14.43	15.89
	8H	13.43	13.83	14.52	14.92	16.40	13.03	13.44	14.12	14.53	16.00
	12H	13.48	13.85	14.59	14.95	16.44	13.08	13.45	14.19	14.55	16.03
8H	4H	12.98	13.39	14.07	14.48	15.96	12.63	13.04	13.72	14.13	15.60
	6H	13.58	13.92	14.69	15.05	16.52	13.23	13.57	14.34	14.70	16.17
	8H	13.79	14.08	14.90	15.19	16.69	13.43	13.72	14.55	14.84	16.33
	12H	13.90	14.16	15.02	15.26	16.80	13.53	13.79	14.65	14.90	16.43
12H	4H	12.96	13.33	14.07	14.43	15.92	12.62	12.99	13.73	14.09	15.57
	6H	13.61	13.90	14.72	15.01	16.51	13.27	13.56	14.38	14.67	16.17
	8H	13.83	14.08	14.95	15.19	16.72	13.48	13.74	14.60	14.85	16.38