

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916275

Luminaire Tested: DFN2DIP-HX3F0-070D080US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916275
REPORT IS A COMBINATION OF REPORTS P899280 AND P896089
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-070D080US930-RLLFLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10623.3 lumens
Efficiency: N/A
Efficacy: 81.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 130.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916275

CATALOG NUMBER: DFN2DIP-HX3F0-070D080US930-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P916275

CATALOG NUMBER: DFN2DIP-HX3F0-070D080US930-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	93	89	86	89	86	82	80	72	69	67	59	57	56	47	46	45
2	89	82	76	71	81	75	70	66	63	60	56	52	49	47	42	40	38
3	81	72	65	60	74	67	61	56	56	52	48	46	43	40	37	35	33
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29
5	69	57	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23
7	59	47	39	34	54	43	37	32	37	32	28	31	27	24	26	23	20
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	18
9	51	39	32	27	47	36	30	25	31	26	22	26	22	20	22	19	17
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2732	2732	2732
5°	2735	2687	2705
10°	2707	2632	2615
15°	2669	2543	2478
20°	2618	2422	2310
25°	2566	2286	2147
30°	2497	2146	1942
35°	2429	1997	1761
40°	2360	1842	1555
45°	2280	1671	1368
50°	2197	1498	1185
55°	2111	1314	1010
60°	2010	1121	830
65°	1895	926	745
70°	1754	743	672
75°	1578	651	608
80°	1323	540	523
85°	903	351	384

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2280 cd/sqm

TEST NUMBER: P916275

CATALOG NUMBER: DFN2DIP-HX3F0-070D080US930-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.1	2.1
10°-20°	606.9	5.7
20°-30°	852.0	8.0
30°-40°	928.8	8.7
40°-50°	853.6	8.0
50°-60°	670.4	6.3
60°-70°	436.4	4.1
70°-80°	224.6	2.1
80°-90°	63.2	0.6
90°-100°	127.6	1.2
100°-110°	405.6	3.8
110°-120°	694.1	6.5
120°-130°	912.8	8.6
130°-140°	1024.6	9.6
140°-150°	1004.7	9.5
150°-160°	842.8	7.9
160°-170°	558.9	5.3
170°-180°	195.4	1.8
0°-30°	1679.9	15.8
0°-40°	2608.7	24.6
0°-60°	4132.7	38.9
0°-90°	4856.9	45.7
90°-120°	1227.3	11.6
90°-150°	4169.4	39.2
90°-180°	5766.0	54.3
0°-180°	10623.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2359	2359	2359	2359	2359	
5°	2359	2348	2320	2340	2333	224
15°	2244	2220	2147	2107	2086	632
25°	2036	1968	1827	1740	1708	937
35°	1755	1646	1458	1324	1276	1098
45°	1434	1291	1067	916	864	1108
55°	1091	924	694	566	525	975
65°	736	564	371	299	292	730
75°	393	243	171	156	154	415
85°	92	47	40	40	40	105
90°	2	22	61	57	59	10
95°	91	108	111	111	108	101
105°	374	379	383	386	386	395
115°	696	706	703	702	696	689
125°	1013	1029	1024	1018	1016	905
135°	1310	1330	1333	1332	1326	1013
145°	1591	1603	1613	1615	1608	994
155°	1819	1824	1830	1838	1833	837
165°	1979	1977	1977	1989	1981	558
175°	2059	2054	2050	2063	2052	196
180°	2063	2063	2063	2063	2063	

TEST NUMBER: P916275

CATALOG NUMBER: DFN2DIP-HX3F0-070D080US930-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2358.7	2358.7	2358.7	2358.7	2358.7
2.5°	2369.3	2358.7	2335.2	2356.7	2352.4
5°	2358.7	2348.1	2320.3	2339.5	2333.1
7.5°	2339.5	2326.8	2296.9	2305.3	2294.7
10°	2313.9	2299.0	2256.3	2249.8	2237.1
12.5°	2281.9	2262.7	2205.0	2192.3	2168.7
15°	2243.5	2219.9	2147.4	2106.9	2085.6
17.5°	2198.6	2164.5	2074.8	2027.8	1993.6
20°	2147.4	2104.6	1998.0	1944.7	1897.6
22.5°	2092.0	2042.8	1918.9	1846.4	1814.5
25°	2036.5	1968.0	1827.2	1739.8	1707.6
27.5°	1970.3	1897.6	1741.8	1641.5	1592.4
30°	1899.9	1818.6	1647.8	1539.1	1481.4
32.5°	1831.5	1733.2	1558.4	1430.2	1376.7
35°	1754.7	1645.8	1458.1	1323.6	1276.4
37.5°	1680.0	1562.4	1364.1	1216.6	1163.4
40°	1600.9	1473.0	1265.8	1114.3	1058.7
42.5°	1519.9	1383.3	1167.7	1009.6	956.4
45°	1434.5	1291.4	1067.4	915.7	864.5
47.5°	1353.4	1201.9	971.3	819.6	772.7
50°	1263.7	1112.2	877.3	729.9	685.3
52.5°	1176.1	1015.9	787.7	646.8	606.3
55°	1090.7	924.2	693.7	565.7	525.2
57.5°	1003.3	832.5	610.6	491.0	456.8
60°	913.6	742.8	522.9	414.3	380.0
62.5°	826.1	655.4	448.2	345.8	328.8
65°	736.5	563.5	371.4	299.0	292.4
67.5°	651.1	478.1	299.0	262.4	256.2
70°	561.4	394.9	247.5	226.2	217.6
72.5°	476.1	318.0	207.0	190.0	185.7
75°	392.7	243.2	170.7	155.8	153.8
77.5°	309.6	172.8	134.5	125.9	121.6
80°	232.6	123.8	102.4	94.0	94.0
82.5°	162.2	83.3	70.4	66.1	66.1
85°	91.7	46.9	40.5	40.5	40.5
87.5°	34.2	17.0	17.0	14.9	14.9
90°	1.9	22.4	61.0	57.2	59.1
92.5°	38.6	52.3	54.1	55.9	55.9
95°	90.8	108.2	111.3	111.3	108.2
97.5°	151.2	167.3	174.1	174.1	174.1
100°	220.8	235.1	240.0	240.0	238.1
102.5°	294.2	304.8	311.5	313.4	311.5
105°	374.4	379.4	383.1	386.2	386.2
107.5°	454.0	461.5	461.5	462.7	454.0
110°	531.1	541.0	541.0	541.0	536.1

TEST NUMBER: P916275

CATALOG NUMBER: DFN2DIP-HX3F0-070D080US930-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	614.4	625.0	623.1	618.2	614.4
115°	696.5	706.5	703.4	701.5	696.5
117.5°	778.0	791.7	782.9	778.0	773.0
120°	860.1	873.8	860.1	860.1	854.4
122.5°	934.7	952.1	943.4	938.4	934.7
125°	1013.0	1028.6	1023.6	1018.0	1016.2
127.5°	1089.6	1108.8	1102.0	1094.5	1089.6
130°	1161.1	1183.4	1180.3	1176.6	1169.8
132.5°	1241.3	1258.7	1260.0	1251.2	1246.3
135°	1310.3	1329.6	1333.3	1331.5	1326.5
137.5°	1387.4	1403.0	1406.1	1404.8	1397.3
140°	1455.2	1470.7	1479.4	1479.4	1472.6
142.5°	1524.9	1540.4	1545.4	1547.3	1540.4
145°	1590.8	1603.2	1613.1	1615.0	1608.2
147.5°	1649.8	1665.4	1672.8	1676.0	1669.2
150°	1710.8	1721.3	1728.2	1733.8	1728.2
152.5°	1764.9	1775.5	1784.2	1791.0	1784.2
155°	1819.0	1824.0	1829.6	1838.3	1832.7
157.5°	1865.6	1869.4	1872.5	1884.9	1876.2
160°	1907.3	1911.1	1912.9	1923.5	1916.0
162.5°	1945.9	1945.9	1947.7	1959.6	1950.8
165°	1978.8	1976.9	1976.9	1989.4	1980.7
167.5°	2008.7	2003.1	2003.1	2015.5	2006.8
170°	2031.1	2026.1	2024.2	2036.7	2026.1
172.5°	2046.6	2041.7	2039.8	2052.2	2041.7
175°	2059.0	2054.1	2050.3	2062.8	2052.2
177.5°	2065.9	2060.9	2057.2	2067.8	2057.2
180°	2062.8	2062.8	2062.8	2062.8	2062.8

TEST NUMBER: P916275

CATALOG NUMBER: DFN2DIP-HX3F0-070D080US930-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.18	10.98	11.18	11.98	13.32	6.16	6.95	7.16	7.96	9.29
	3H	11.85	12.56	12.86	13.57	14.93	7.34	8.05	8.35	9.07	10.42
	4H	12.45	13.12	13.47	14.14	15.50	7.78	8.46	8.81	9.48	10.84
	6H	12.86	13.48	13.90	14.51	15.88	8.10	8.72	9.13	9.74	11.12
	8H	12.98	13.57	14.02	14.61	15.98	8.19	8.78	9.22	9.81	11.19
	12H	13.04	13.60	14.08	14.63	16.03	8.23	8.79	9.27	9.82	11.21
4H	2H	10.19	10.87	11.22	11.88	13.25	6.74	7.42	7.77	8.44	9.80
	3H	12.01	12.57	13.05	13.62	14.99	8.08	8.64	9.12	9.69	11.07
	4H	12.70	13.21	13.74	14.25	15.64	8.63	9.14	9.67	10.18	11.58
	6H	13.20	13.64	14.25	14.70	16.10	9.04	9.48	10.09	10.54	11.94
	8H	13.37	13.78	14.43	14.84	16.24	9.17	9.58	10.22	10.63	12.04
	12H	13.46	13.83	14.53	14.90	16.31	9.23	9.60	10.30	10.67	12.08
8H	4H	12.66	13.07	13.71	14.12	15.53	8.90	9.31	9.96	10.37	11.77
	6H	13.22	13.55	14.29	14.65	16.06	9.41	9.75	10.49	10.85	12.25
	8H	13.43	13.72	14.51	14.80	16.23	9.60	9.90	10.68	10.98	12.40
	12H	13.56	13.82	14.65	14.90	16.36	9.71	9.97	10.80	11.05	12.52
12H	4H	12.61	12.98	13.68	14.05	15.46	8.90	9.27	9.97	10.34	11.76
	6H	13.19	13.49	14.28	14.57	15.99	9.46	9.76	10.54	10.84	12.26
	8H	13.40	13.67	14.49	14.74	16.21	9.66	9.92	10.75	11.00	12.47