

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913404

Luminaire Tested: DFN2DIP-HX2F0-050D050US927-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P913404  
REPORT IS A COMBINATION OF REPORTS P899188 AND P896039  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX2F0-050D050US927-RLLFLL  
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6872.2 lumens  
Efficiency: N/A  
Efficacy: 79.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 86  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9789  
Total Harmonic Distortion (THDi): 0.074  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P913404  
CATALOG NUMBER: DFN2DIP-HX2F0-050D050US927-RLFL

### Luminous Intensity Polar Plot





TEST NUMBER: P913404  
 CATALOG NUMBER: DFN2DIP-HX2F0-050D050US927-RLFL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55	49			49
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48	42			42
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41	36			36
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35	31			31
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31	27			27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27	24			24
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24	21			21
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22	19			19
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20	17			17
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18	16			16
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16	14			14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3857	3857	3857
5°	3857	3787	3813
10°	3813	3703	3682
15°	3754	3572	3484
20°	3679	3395	3243
25°	3601	3198	3010
30°	3499	2997	2718
35°	3399	2781	2461
40°	3297	2559	2169
45°	3179	2315	1903
50°	3056	2068	1645
55°	2928	1806	1397
60°	2779	1534	1143
65°	2606	1258	1022
70°	2398	1001	915
75°	2135	865	818
80°	1756	701	688
85°	1150	432	482

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3179 cd/sqm



TEST NUMBER: P913404

CATALOG NUMBER: DFN2DIP-HX2F0-050D050US927-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	153.4	2.2
10°-20°	421.2	6.1
20°-30°	591.3	8.6
30°-40°	644.6	9.4
40°-50°	592.4	8.6
50°-60°	465.3	6.8
60°-70°	302.9	4.4
70°-80°	155.9	2.3
80°-90°	43.4	0.6
90°-100°	77.5	1.1
100°-110°	246.3	3.6
110°-120°	421.5	6.1
120°-130°	554.3	8.1
130°-140°	622.2	9.1
140°-150°	610.1	8.9
150°-160°	511.8	7.4
160°-170°	339.4	4.9
170°-180°	118.6	1.7
0°-30°	1165.9	17.0
0°-40°	1810.5	26.3
0°-60°	2868.2	41.7
0°-90°	3370.3	49.0
90°-120°	745.3	10.8
90°-150°	2532.0	36.8
90°-180°	3502.0	51.0
0°-180°	6872.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1637	1637	1637	1637	1637	
5°	1637	1630	1610	1624	1619	155
15°	1557	1541	1490	1462	1448	439
25°	1413	1366	1268	1207	1185	650
35°	1218	1142	1012	918	886	762
45°	996	896	741	636	600	769
55°	757	641	481	393	364	676
65°	511	391	258	208	203	507
75°	273	169	118	108	107	288
85°	64	33	28	28	28	73
90°	1	14	37	35	36	7
95°	55	66	68	68	66	61
105°	227	230	233	234	234	240
115°	423	429	427	426	423	418
125°	615	625	622	618	617	550
135°	796	807	810	809	806	615
145°	966	974	980	981	977	604
155°	1105	1108	1111	1116	1113	508
165°	1202	1201	1201	1208	1203	339
175°	1250	1247	1245	1253	1246	119
180°	1253	1253	1253	1253	1253	



TEST NUMBER: P913404

CATALOG NUMBER: DFN2DIP-HX2F0-050D050US927-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1637.0	1637.0	1637.0	1637.0	1637.0
2.5°	1644.4	1637.0	1620.7	1635.6	1632.6
5°	1637.0	1629.7	1610.3	1623.7	1619.3
7.5°	1623.7	1614.9	1594.1	1600.0	1592.5
10°	1605.9	1595.5	1566.0	1561.5	1552.6
12.5°	1583.7	1570.4	1530.3	1521.5	1505.1
15°	1557.0	1540.7	1490.4	1462.3	1447.5
17.5°	1525.9	1502.2	1439.9	1407.4	1383.6
20°	1490.4	1460.7	1386.6	1349.7	1317.0
22.5°	1451.9	1417.8	1331.8	1281.5	1259.3
25°	1413.3	1365.9	1268.1	1207.4	1185.1
27.5°	1367.5	1317.0	1208.9	1139.2	1105.2
30°	1318.6	1262.2	1143.7	1068.2	1028.1
32.5°	1271.1	1202.9	1081.6	992.6	955.5
35°	1217.8	1142.2	1011.9	918.5	885.9
37.5°	1165.9	1084.4	946.7	844.4	807.5
40°	1111.1	1022.3	878.4	773.3	734.8
42.5°	1054.9	960.0	810.4	700.7	663.8
45°	995.6	896.3	740.8	635.5	599.9
47.5°	939.3	834.2	674.1	568.9	536.3
50°	877.1	771.9	608.9	506.6	475.6
52.5°	816.3	705.1	546.7	448.9	420.8
55°	757.0	641.4	481.4	392.6	364.5
57.5°	696.3	577.8	423.7	340.8	317.0
60°	634.1	515.6	362.9	287.5	263.7
62.5°	573.4	454.9	311.1	240.0	228.2
65°	511.1	391.1	257.8	207.5	203.0
67.5°	451.9	331.8	207.5	182.2	177.8
70°	389.7	274.1	171.8	157.0	151.1
72.5°	330.4	220.7	143.7	131.9	128.9
75°	272.6	168.8	118.5	108.1	106.7
77.5°	214.8	119.9	93.4	87.4	84.4
80°	161.4	86.0	71.1	65.2	65.2
82.5°	112.6	57.8	48.9	45.9	45.9
85°	63.7	32.6	28.1	28.1	28.1
87.5°	23.8	11.8	11.8	10.4	10.4
90°	1.1	13.6	37.0	34.8	35.9
92.5°	23.4	31.7	32.9	34.0	34.0
95°	55.1	65.8	67.6	67.6	65.8
97.5°	91.7	101.6	105.8	105.8	105.8
100°	134.0	142.8	145.8	145.8	144.7
102.5°	178.6	185.1	189.2	190.4	189.2
105°	227.4	230.4	232.7	234.5	234.5
107.5°	275.7	280.2	280.2	281.0	275.7
110°	322.5	328.6	328.6	328.6	325.5



TEST NUMBER: P913404

CATALOG NUMBER: DFN2DIP-HX2F0-050D050US927-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	373.1	379.5	378.4	375.4	373.1
115°	422.9	429.0	427.1	426.0	422.9
117.5°	472.5	480.8	475.5	472.5	469.4
120°	522.3	530.6	522.3	522.3	518.9
122.5°	567.6	578.2	572.9	569.9	567.6
125°	615.2	624.6	621.6	618.2	617.1
127.5°	661.6	673.4	669.2	664.6	661.6
130°	705.1	718.7	716.8	714.5	710.3
132.5°	753.8	764.4	765.2	759.9	756.8
135°	795.7	807.4	809.7	808.6	805.6
137.5°	842.6	852.0	853.9	853.1	848.6
140°	883.7	893.2	898.4	898.4	894.3
142.5°	926.0	935.5	938.5	939.6	935.5
145°	966.1	973.6	979.6	980.8	976.6
147.5°	1002.0	1011.4	1015.9	1017.8	1013.6
150°	1038.9	1045.4	1049.5	1052.9	1049.5
152.5°	1071.8	1078.2	1083.5	1087.7	1083.5
155°	1104.6	1107.6	1111.0	1116.3	1112.9
157.5°	1133.0	1135.2	1137.1	1144.7	1139.4
160°	1158.2	1160.5	1161.7	1168.1	1163.6
162.5°	1181.7	1181.7	1182.8	1190.0	1184.7
165°	1201.7	1200.6	1200.6	1208.2	1202.8
167.5°	1219.8	1216.4	1216.4	1224.0	1218.7
170°	1233.4	1230.4	1229.3	1236.8	1230.4
172.5°	1242.9	1239.8	1238.7	1246.3	1239.8
175°	1250.5	1247.4	1245.2	1252.7	1246.3
177.5°	1254.6	1251.6	1249.3	1255.7	1249.3
180°	1252.7	1252.7	1252.7	1252.7	1252.7



TEST NUMBER: P913404  
 CATALOG NUMBER: DFN2DIP-HX2F0-050D050US927-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.61	12.43	12.58	13.41	14.70	7.59	8.41	8.56	9.39	10.68
	3H	13.26	14.00	14.24	14.99	16.30	8.76	9.50	9.75	10.49	11.80
	4H	13.85	14.55	14.85	15.54	16.86	9.20	9.90	10.20	10.89	12.21
	6H	14.25	14.89	15.26	15.89	17.22	9.51	10.15	10.51	11.15	12.48
	8H	14.37	14.98	15.38	15.99	17.32	9.59	10.20	10.60	11.21	12.54
	12H	14.42	15.00	15.44	16.01	17.36	9.62	10.20	10.64	11.21	12.56
4H	2H	11.62	12.32	12.62	13.31	14.63	8.17	8.87	9.17	9.86	11.18
	3H	13.42	14.00	14.43	15.02	16.35	9.50	10.08	10.51	11.10	12.43
	4H	14.09	14.62	15.11	15.64	16.99	10.03	10.56	11.05	11.58	12.93
	6H	14.58	15.04	15.61	16.08	17.43	10.43	10.89	11.46	11.93	13.28
	8H	14.75	15.17	15.78	16.20	17.57	10.55	10.98	11.58	12.01	13.37
	12H	14.83	15.21	15.88	16.26	17.63	10.61	10.99	11.66	12.04	13.41
8H	4H	14.06	14.48	15.09	15.51	16.88	10.30	10.72	11.33	11.75	13.12
	6H	14.60	14.95	15.65	16.02	17.38	10.79	11.14	11.85	12.22	13.58
	8H	14.80	15.10	15.86	16.16	17.54	10.97	11.28	12.03	12.34	13.72
	12H	14.92	15.19	15.98	16.24	17.67	11.08	11.35	12.14	12.40	13.82
12H	4H	14.01	14.39	15.06	15.44	16.81	10.30	10.68	11.35	11.73	13.10
	6H	14.57	14.88	15.63	15.94	17.32	10.84	11.14	11.90	12.20	13.59
	8H	14.77	15.04	15.84	16.10	17.52	11.03	11.30	12.10	12.35	13.78