

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916064

Luminaire Tested: DFN2DIP-HX2F0-020D030US930-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P916064  
REPORT IS A COMBINATION OF REPORTS P899162 AND P896039  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX2F0-020D030US930-RLLFLL  
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3550.6 lumens  
Efficiency: N/A  
Efficacy: 96.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 37  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9968  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P916064  
CATALOG NUMBER: DFN2DIP-HX2F0-020D030US930-RLFL

### Luminous Intensity Polar Plot





TEST NUMBER: P916064

CATALOG NUMBER: DFN2DIP-HX2F0-020D030US930-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39			
1	96	92	88	85	87	83	80	78	68	66	64	54	53	51	41	40	40	34			
2	87	80	75	70	79	73	68	64	60	57	54	48	46	44	37	35	34	29			
3	80	71	64	58	73	65	59	54	53	49	46	43	40	37	33	31	29	25			
4	73	63	55	50	66	58	51	46	48	43	39	38	35	32	30	27	26	22			
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	24	22	19			
6	62	51	43	37	56	46	40	35	39	33	30	31	28	25	25	22	20	17			
7	57	46	38	33	52	42	35	30	35	30	26	29	25	22	22	20	18	15			
8	53	41	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16	14			
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15	12			
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1588	1588	1588
5°	1588	1559	1570
10°	1570	1525	1516
15°	1546	1470	1434
20°	1514	1398	1335
25°	1483	1316	1239
30°	1441	1234	1119
35°	1399	1145	1013
40°	1357	1054	893
45°	1309	953	784
50°	1258	852	677
55°	1205	744	575
60°	1144	631	471
65°	1073	518	421
70°	987	412	376
75°	879	356	337
80°	723	289	283
85°	473	178	199

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1309 cd/sqm



TEST NUMBER: P916064

CATALOG NUMBER: DFN2DIP-HX2F0-020D030US930-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	63.2	1.8
10°-20°	173.4	4.9
20°-30°	243.4	6.9
30°-40°	265.4	7.5
40°-50°	243.9	6.9
50°-60°	191.5	5.4
60°-70°	124.7	3.5
70°-80°	64.2	1.8
80°-90°	18.6	0.5
90°-100°	47.9	1.3
100°-110°	152.1	4.3
110°-120°	260.3	7.3
120°-130°	342.3	9.6
130°-140°	384.2	10.8
140°-150°	376.8	10.6
150°-160°	316.1	8.9
160°-170°	209.6	5.9
170°-180°	73.3	2.1
0°-30°	480.0	13.5
0°-40°	745.3	21.0
0°-60°	1180.8	33.3
0°-90°	1388.2	39.1
90°-120°	460.2	13.0
90°-150°	1563.5	44.0
90°-180°	2162.0	60.9
0°-180°	3550.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	674	674	674	674	674	
5°	674	671	663	668	667	64
15°	641	634	614	602	596	181
25°	582	562	522	497	488	268
35°	501	470	417	378	365	314
45°	410	369	305	262	247	317
55°	312	264	198	162	150	278
65°	210	161	106	85	84	209
75°	112	70	49	44	44	119
85°	26	13	12	12	12	30
90°	1	8	23	21	22	4
95°	34	41	42	42	41	38
105°	140	142	144	145	145	148
115°	261	265	264	263	261	258
125°	380	386	384	382	381	339
135°	491	499	500	499	497	380
145°	597	601	605	606	603	373
155°	682	684	686	689	687	314
165°	742	741	741	746	743	209
175°	772	770	769	774	770	73
180°	774	774	774	774	774	



TEST NUMBER: P916064

CATALOG NUMBER: DFN2DIP-HX2F0-020D030US930-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	673.9	673.9	673.9	673.9	673.9
2.5°	676.9	673.9	667.2	673.4	672.1
5°	673.9	670.9	662.9	668.5	666.6
7.5°	668.5	664.8	656.2	658.7	655.6
10°	661.1	656.8	644.7	642.8	639.2
12.5°	652.0	646.4	630.0	626.4	619.6
15°	641.0	634.2	613.5	601.9	595.9
17.5°	628.2	618.4	592.8	579.4	569.6
20°	613.5	601.3	570.9	555.6	542.2
22.5°	597.7	583.7	548.3	527.6	518.4
25°	581.9	562.3	522.0	497.1	487.9
27.5°	563.0	542.2	497.7	469.0	454.9
30°	542.8	519.6	470.8	439.8	423.2
32.5°	523.3	495.2	445.2	408.6	393.4
35°	501.3	470.3	416.6	378.1	364.7
37.5°	480.0	446.4	389.7	347.6	332.4
40°	457.4	420.9	361.7	318.4	302.5
42.5°	434.2	395.3	333.6	288.5	273.3
45°	409.9	368.9	305.0	261.6	247.0
47.5°	386.7	343.4	277.5	234.2	220.8
50°	361.1	317.8	250.7	208.6	195.8
52.5°	336.0	290.2	225.0	184.8	173.3
55°	311.6	264.1	198.2	161.7	150.0
57.5°	286.7	237.8	174.5	140.3	130.5
60°	261.1	212.2	149.4	118.4	108.6
62.5°	236.0	187.3	128.1	98.8	93.9
65°	210.4	161.0	106.2	85.4	83.6
67.5°	186.1	136.6	85.4	75.0	73.2
70°	160.4	112.8	70.7	64.7	62.2
72.5°	136.0	90.8	59.1	54.3	53.1
75°	112.2	69.5	48.8	44.5	43.9
77.5°	88.5	49.4	38.4	36.0	34.7
80°	66.4	35.4	29.3	26.8	26.8
82.5°	46.3	23.8	20.1	18.9	18.9
85°	26.2	13.4	11.6	11.6	11.6
87.5°	9.8	4.9	4.9	4.2	4.2
90°	0.7	8.4	22.8	21.4	22.2
92.5°	14.4	19.6	20.3	21.0	21.0
95°	34.1	40.6	41.7	41.7	40.6
97.5°	56.7	62.7	65.3	65.3	65.3
100°	82.8	88.1	90.0	90.0	89.4
102.5°	110.3	114.3	116.8	117.6	116.8
105°	140.4	142.3	143.7	144.8	144.8
107.5°	170.2	173.0	173.0	173.5	170.2
110°	199.2	202.9	202.9	202.9	201.1



TEST NUMBER: P916064

CATALOG NUMBER: DFN2DIP-HX2F0-020D030US930-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	230.4	234.4	233.7	231.8	230.4
115°	261.2	264.9	263.7	263.1	261.2
117.5°	291.7	296.9	293.6	291.7	289.8
120°	322.5	327.7	322.5	322.5	320.4
122.5°	350.5	357.0	353.8	351.9	350.5
125°	379.9	385.7	383.8	381.7	381.1
127.5°	408.5	415.8	413.3	410.4	408.5
130°	435.4	443.8	442.6	441.2	438.6
132.5°	465.5	472.0	472.5	469.2	467.3
135°	491.4	498.6	500.0	499.3	497.4
137.5°	520.2	526.1	527.3	526.8	524.0
140°	545.7	551.5	554.8	554.8	552.2
142.5°	571.9	577.6	579.5	580.2	577.6
145°	596.6	601.2	605.0	605.6	603.1
147.5°	618.7	624.5	627.3	628.5	625.9
150°	641.6	645.6	648.1	650.2	648.1
152.5°	661.9	665.8	669.0	671.6	669.0
155°	682.2	684.0	686.1	689.3	687.3
157.5°	699.6	701.0	702.2	706.9	703.6
160°	715.3	716.6	717.4	721.3	718.5
162.5°	729.7	729.7	730.4	734.8	731.6
165°	742.1	741.4	741.4	746.0	742.7
167.5°	753.3	751.1	751.1	755.8	752.5
170°	761.7	759.8	759.1	763.8	759.8
172.5°	767.4	765.6	764.9	769.6	765.6
175°	772.2	770.3	768.9	773.6	769.6
177.5°	774.7	772.8	771.4	775.4	771.4
180°	773.6	773.6	773.6	773.6	773.6



TEST NUMBER: P916064  
 CATALOG NUMBER: DFN2DIP-HX2F0-020D030US930-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.50	8.25	8.55	9.30	10.72	3.49	4.24	4.54	5.29	6.71
	3H	9.15	9.82	10.21	10.88	12.32	4.65	5.32	5.71	6.38	7.82
	4H	9.74	10.37	10.81	11.43	12.88	5.09	5.72	6.16	6.78	8.23
	6H	10.13	10.72	11.22	11.78	13.24	5.39	5.97	6.47	7.04	8.50
	8H	10.25	10.80	11.33	11.88	13.34	5.47	6.02	6.55	7.11	8.56
	12H	10.30	10.82	11.39	11.90	13.37	5.50	6.03	6.59	7.10	8.58
4H	2H	7.51	8.14	8.59	9.20	10.65	4.06	4.69	5.14	5.76	7.20
	3H	9.30	9.83	10.39	10.92	12.38	5.38	5.91	6.47	7.00	8.46
	4H	9.97	10.45	11.06	11.53	13.01	5.91	6.39	7.00	7.48	8.96
	6H	10.46	10.87	11.56	11.97	13.45	6.31	6.72	7.41	7.82	9.30
	8H	10.62	11.00	11.72	12.10	13.59	6.42	6.81	7.52	7.91	9.40
	12H	10.69	11.04	11.81	12.15	13.65	6.48	6.83	7.59	7.93	9.43
8H	4H	9.93	10.31	11.03	11.41	12.90	6.17	6.56	7.27	7.65	9.14
	6H	10.46	10.78	11.58	11.92	13.41	6.66	6.98	7.78	8.12	9.60
	8H	10.66	10.94	11.79	12.06	13.57	6.84	7.12	7.97	8.24	9.74
	12H	10.78	11.03	11.91	12.14	13.69	6.94	7.19	8.07	8.30	9.85
12H	4H	9.87	10.22	10.99	11.33	12.83	6.17	6.52	7.28	7.63	9.12
	6H	10.44	10.72	11.56	11.84	13.34	6.70	6.98	7.83	8.10	9.61
	8H	10.64	10.88	11.77	12.00	13.54	6.90	7.14	8.03	8.26	9.80