

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918888

Luminaire Tested: DFN2DIP-HX3F0-030D030US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918888
REPORT IS A COMBINATION OF REPORTS P899202 AND P896089
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-030D030US935-RLLFLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4481.4 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 46.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918888

CATALOG NUMBER: DFN2DIP-HX3F0-030D030US935-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P918888

CATALOG NUMBER: DFN2DIP-HX3F0-030D030US935-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1237	1237	1237
5°	1238	1216	1224
10°	1225	1191	1184
15°	1208	1151	1121
20°	1185	1096	1045
25°	1161	1035	972
30°	1130	971	879
35°	1100	904	797
40°	1068	834	704
45°	1032	756	619
50°	995	678	536
55°	955	594	457
60°	910	507	376
65°	857	419	337
70°	794	336	304
75°	714	295	275
80°	599	244	236
85°	409	159	173

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1032 cd/sqm

TEST NUMBER: P918888

CATALOG NUMBER: DFN2DIP-HX3F0-030D030US935-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.1	2.2
10°-20°	274.7	6.1
20°-30°	385.6	8.6
30°-40°	420.3	9.4
40°-50°	386.3	8.6
50°-60°	303.4	6.8
60°-70°	197.5	4.4
70°-80°	101.7	2.3
80°-90°	28.3	0.6
90°-100°	50.6	1.1
100°-110°	160.6	3.6
110°-120°	274.9	6.1
120°-130°	361.5	8.1
130°-140°	405.7	9.1
140°-150°	397.9	8.9
150°-160°	333.8	7.4
160°-170°	221.3	4.9
170°-180°	77.4	1.7
0°-30°	760.3	17.0
0°-40°	1180.7	26.3
0°-60°	1870.4	41.7
0°-90°	2197.8	49.0
90°-120°	486.0	10.8
90°-150°	1651.1	36.8
90°-180°	2284.0	51.0
0°-180°	4481.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1068	1068	1068	1068	1068	
5°	1068	1063	1050	1059	1056	101
15°	1015	1005	972	954	944	286
25°	922	891	827	787	773	424
35°	794	745	660	599	578	497
45°	649	584	483	414	391	501
55°	494	418	314	256	238	441
65°	333	255	168	135	132	330
75°	178	110	77	70	70	188
85°	42	21	18	18	18	48
90°	1	9	24	23	23	4
95°	36	43	44	44	43	40
105°	148	150	152	153	153	156
115°	276	280	278	278	276	273
125°	401	407	405	403	402	358
135°	519	526	528	527	525	401
145°	630	635	639	640	637	394
155°	720	722	724	728	726	332
165°	784	783	783	788	784	221
175°	816	814	812	817	813	77
180°	817	817	817	817	817	

TEST NUMBER: P918888

CATALOG NUMBER: DFN2DIP-HX3F0-030D030US935-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1067.6	1067.6	1067.6	1067.6	1067.6
2.5°	1072.4	1067.6	1056.9	1066.6	1064.7
5°	1067.6	1062.7	1050.2	1058.9	1055.9
7.5°	1058.9	1053.1	1039.6	1043.4	1038.5
10°	1047.2	1040.5	1021.2	1018.2	1012.5
12.5°	1032.8	1024.1	998.0	992.2	981.5
15°	1015.4	1004.7	971.9	953.6	943.9
17.5°	995.1	979.6	939.0	917.8	902.3
20°	971.9	952.5	904.2	880.2	858.8
22.5°	946.8	924.5	868.5	835.7	821.2
25°	921.7	890.7	827.0	787.4	772.8
27.5°	891.7	858.8	788.3	743.0	720.7
30°	859.9	823.1	745.8	696.6	670.5
32.5°	828.9	784.5	705.3	647.3	623.1
35°	794.2	744.8	659.9	599.0	577.7
37.5°	760.3	707.1	617.3	550.6	526.6
40°	724.6	666.7	572.9	504.3	479.2
42.5°	687.9	626.1	528.5	456.9	432.8
45°	649.3	584.4	483.1	414.4	391.2
47.5°	612.5	544.0	439.6	370.9	349.7
50°	572.0	503.3	397.1	330.4	310.1
52.5°	532.3	459.9	356.5	292.7	274.4
55°	493.6	418.3	313.9	256.1	237.7
57.5°	454.1	376.8	276.4	222.2	206.7
60°	413.5	336.2	236.7	187.4	172.0
62.5°	373.9	296.6	202.9	156.5	148.9
65°	333.3	255.0	168.1	135.3	132.3
67.5°	294.7	216.4	135.3	118.8	115.9
70°	254.1	178.7	112.0	102.4	98.5
72.5°	215.4	143.9	93.7	86.0	84.0
75°	177.7	110.1	77.3	70.5	69.6
77.5°	140.1	78.2	60.9	57.0	55.0
80°	105.3	56.1	46.3	42.5	42.5
82.5°	73.4	37.7	31.9	30.0	30.0
85°	41.5	21.2	18.3	18.3	18.3
87.5°	15.5	7.7	7.7	6.8	6.8
90°	0.8	8.9	24.1	22.6	23.4
92.5°	15.2	20.7	21.4	22.1	22.1
95°	36.0	42.9	44.1	44.1	42.9
97.5°	59.8	66.2	69.0	69.0	69.0
100°	87.4	93.1	95.1	95.1	94.4
102.5°	116.5	120.7	123.4	124.2	123.4
105°	148.3	150.2	151.7	152.9	152.9
107.5°	179.8	182.7	182.7	183.2	179.8
110°	210.3	214.3	214.3	214.3	212.3

TEST NUMBER: P918888

CATALOG NUMBER: DFN2DIP-HX3F0-030D030US935-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	243.3	247.5	246.8	244.8	243.3
115°	275.9	279.7	278.5	277.8	275.9
117.5°	308.1	313.5	310.0	308.1	306.1
120°	340.6	346.0	340.6	340.6	338.4
122.5°	370.1	377.0	373.6	371.6	370.1
125°	401.2	407.3	405.4	403.1	402.4
127.5°	431.4	439.1	436.4	433.4	431.4
130°	459.8	468.6	467.4	466.0	463.2
132.5°	491.5	498.4	498.9	495.5	493.5
135°	518.9	526.5	528.0	527.3	525.3
137.5°	549.4	555.6	556.8	556.4	553.4
140°	576.3	582.5	585.9	585.9	583.2
142.5°	603.9	610.0	612.0	612.8	610.0
145°	630.0	634.9	638.9	639.5	636.9
147.5°	653.4	659.5	662.5	663.7	661.0
150°	677.5	681.7	684.4	686.6	684.4
152.5°	699.0	703.1	706.5	709.3	706.5
155°	720.4	722.3	724.5	728.0	725.8
157.5°	738.8	740.3	741.6	746.5	743.0
160°	755.4	756.8	757.6	761.7	758.8
162.5°	770.6	770.6	771.4	776.0	772.6
165°	783.7	782.9	782.9	787.8	784.4
167.5°	795.5	793.2	793.2	798.1	794.7
170°	804.3	802.4	801.7	806.6	802.4
172.5°	810.5	808.6	807.8	812.7	808.6
175°	815.5	813.5	812.0	816.9	812.7
177.5°	818.1	816.1	814.7	818.9	814.7
180°	816.9	816.9	816.9	816.9	816.9

TEST NUMBER: P918888

CATALOG NUMBER: DFN2DIP-HX3F0-030D030US935-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.75	8.57	8.72	9.55	10.84	3.72	4.55	4.70	5.53	6.82
	3H	9.42	10.15	10.40	11.14	12.45	4.91	5.64	5.89	6.63	7.94
	4H	10.02	10.72	11.02	11.71	13.03	5.36	6.05	6.35	7.04	8.36
	6H	10.44	11.08	11.44	12.08	13.41	5.67	6.31	6.68	7.31	8.64
	8H	10.56	11.17	11.57	12.18	13.51	5.76	6.37	6.77	7.38	8.71
	12H	10.62	11.20	11.63	12.20	13.56	5.80	6.38	6.82	7.39	8.74
4H	2H	7.77	8.46	8.77	9.46	10.77	4.32	5.01	5.32	6.00	7.32
	3H	9.59	10.16	10.60	11.19	12.52	5.66	6.24	6.67	7.26	8.59
	4H	10.27	10.80	11.29	11.82	13.17	6.20	6.73	7.22	7.75	9.10
	6H	10.78	11.23	11.81	12.27	13.62	6.62	7.07	7.65	8.11	9.46
	8H	10.95	11.37	11.98	12.40	13.77	6.74	7.17	7.77	8.20	9.56
	12H	11.04	11.42	12.09	12.47	13.84	6.81	7.19	7.85	8.23	9.61
8H	4H	10.24	10.66	11.27	11.69	13.06	6.48	6.90	7.51	7.93	9.30
	6H	10.79	11.14	11.85	12.22	13.58	6.99	7.34	8.04	8.41	9.78
	8H	11.01	11.31	12.07	12.37	13.76	7.18	7.48	8.24	8.54	9.93
	12H	11.14	11.41	12.20	12.46	13.89	7.29	7.56	8.36	8.62	10.04
12H	4H	10.19	10.57	11.24	11.62	12.99	6.48	6.86	7.53	7.91	9.28
	6H	10.77	11.08	11.83	12.14	13.52	7.04	7.34	8.10	8.40	9.79
	8H	10.98	11.26	12.05	12.31	13.73	7.24	7.51	8.31	8.57	9.99

END OF REPORT