

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916097

Luminaire Tested: DFN2DIP-HX2F0-030D060US930-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916097
REPORT IS A COMBINATION OF REPORTS P900714 AND P897595
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-030D060US930-RLLONL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6921.9 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 73.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916097

CATALOG NUMBER: DFN2DIP-HX2F0-030D060US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P916097

CATALOG NUMBER: DFN2DIP-HX2F0-030D060US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38
1	94	90	86	83	84	81	77	75	64	62	60	48	47	46	34	33	32
2	85	78	73	68	76	71	66	62	56	53	50	43	40	39	30	29	28
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21
5	66	55	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15
8	52	40	33	28	46	36	30	25	29	25	21	23	20	17	17	15	13
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12
10	45	33	27	22	40	30	24	20	25	20	17	20	16	14	14	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2382	2382	2382
5°	2382	2338	2355
10°	2354	2287	2274
15°	2318	2206	2151
20°	2272	2096	2003
25°	2224	1975	1859
30°	2161	1850	1679
35°	2099	1717	1520
40°	2036	1581	1339
45°	1963	1430	1175
50°	1887	1277	1016
55°	1808	1116	863
60°	1715	947	706
65°	1609	777	631
70°	1480	618	565
75°	1318	534	505
80°	1085	433	425
85°	709	268	299

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1963 cd/sqm

TEST NUMBER: P916097

CATALOG NUMBER: DFN2DIP-HX2F0-030D060US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.7	1.4
10°-20°	260.1	3.8
20°-30°	365.1	5.3
30°-40°	398.0	5.8
40°-50°	365.8	5.3
50°-60°	287.3	4.2
60°-70°	187.0	2.7
70°-80°	96.3	1.4
80°-90°	27.5	0.4
90°-100°	54.4	0.8
100°-110°	202.9	2.9
110°-120°	538.2	7.8
120°-130°	892.7	12.9
130°-140°	948.2	13.7
140°-150°	881.3	12.7
150°-160°	708.5	10.2
160°-170°	456.5	6.6
170°-180°	157.1	2.3
0°-30°	720.0	10.4
0°-40°	1118.0	16.2
0°-60°	1771.2	25.6
0°-90°	2081.9	30.1
90°-120°	795.6	11.5
90°-150°	3517.8	50.8
90°-180°	4840.0	69.9
0°-180°	6921.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1011	1011	1011	1011	1011	
5°	1011	1006	994	1003	1000	96
15°	962	951	920	903	894	271
25°	873	843	783	746	732	401
35°	752	705	625	567	547	471
45°	615	553	458	392	370	475
55°	467	396	297	242	225	418
65°	316	242	159	128	125	313
75°	168	104	73	67	66	178
85°	39	20	17	17	17	45
90°	1	14	24	30	32	6
95°	78	38	47	53	51	92
105°	363	399	73	86	91	388
115°	687	707	737	184	98	676
125°	971	987	1009	1018	1021	866
135°	1202	1221	1232	1244	1241	928
145°	1394	1393	1413	1422	1416	872
155°	1535	1524	1539	1546	1536	707
165°	1618	1610	1614	1622	1614	457
175°	1654	1646	1648	1657	1645	157
180°	1651	1651	1651	1651	1651	

TEST NUMBER: P916097

CATALOG NUMBER: DFN2DIP-HX2F0-030D060US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1010.9	1010.9	1010.9	1010.9	1010.9
2.5°	1015.5	1010.9	1000.8	1010.0	1008.2
5°	1010.9	1006.3	994.4	1002.7	999.9
7.5°	1002.7	997.2	984.4	988.0	983.4
10°	991.6	985.3	967.0	964.2	958.8
12.5°	978.0	969.7	945.0	939.5	929.4
15°	961.5	951.4	920.3	902.9	893.8
17.5°	942.2	927.6	889.2	869.1	854.4
20°	920.3	902.0	856.2	833.5	813.3
22.5°	896.6	875.5	822.4	791.3	777.6
25°	872.8	843.4	783.1	745.6	731.8
27.5°	844.4	813.3	746.5	703.5	682.4
30°	814.2	779.4	706.2	659.7	634.9
32.5°	784.9	742.8	667.9	612.9	590.0
35°	752.0	705.3	624.8	567.2	547.1
37.5°	720.0	669.6	584.6	521.4	498.6
40°	686.2	631.3	542.5	477.5	453.8
42.5°	651.3	592.9	500.4	432.7	409.9
45°	614.8	553.4	457.5	392.4	370.5
47.5°	580.0	515.1	416.3	351.2	331.2
50°	541.6	476.6	376.0	312.8	293.7
52.5°	504.0	435.5	337.6	277.2	259.8
55°	467.4	396.1	297.3	242.5	225.1
57.5°	430.0	356.8	261.7	210.4	195.8
60°	391.5	318.4	224.1	177.5	162.9
62.5°	354.1	280.9	192.1	148.2	141.0
65°	315.6	241.5	159.1	128.1	125.3
67.5°	279.1	204.9	128.1	112.5	109.7
70°	240.6	169.3	106.1	96.9	93.3
72.5°	204.0	136.2	88.7	81.4	79.6
75°	168.3	104.3	73.2	66.8	65.9
77.5°	132.6	74.0	57.6	54.0	52.1
80°	99.7	53.1	43.9	40.3	40.3
82.5°	69.5	35.7	30.2	28.4	28.4
85°	39.3	20.1	17.4	17.4	17.4
87.5°	14.7	7.3	7.3	6.4	6.4
90°	1.1	14.3	23.8	29.9	32.2
92.5°	29.9	25.1	28.6	31.1	32.2
95°	77.6	38.2	46.6	52.7	51.4
97.5°	139.7	41.8	60.8	64.6	65.7
100°	211.5	47.8	68.1	77.6	80.0
102.5°	290.2	288.0	70.5	83.6	87.2
105°	363.1	399.0	72.9	85.9	90.8
107.5°	448.0	477.8	75.3	88.4	93.2
110°	529.3	554.2	209.1	89.7	94.3

TEST NUMBER: P916097

CATALOG NUMBER: DFN2DIP-HX2F0-030D060US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	605.7	627.1	606.8	91.9	95.6
115°	686.9	707.2	737.1	184.0	98.0
117.5°	757.3	781.2	801.6	630.7	317.7
120°	836.3	854.1	875.7	890.0	728.7
122.5°	903.0	922.2	946.2	953.2	954.6
125°	971.2	986.8	1009.4	1017.8	1021.3
127.5°	1033.3	1050.0	1068.0	1079.9	1081.1
130°	1091.8	1111.0	1124.1	1137.3	1136.1
132.5°	1151.6	1167.2	1180.2	1191.0	1189.8
135°	1201.8	1221.0	1231.6	1243.7	1241.2
137.5°	1254.3	1268.6	1280.7	1292.6	1289.1
140°	1305.6	1315.3	1328.4	1339.1	1333.2
142.5°	1348.7	1357.1	1372.6	1382.1	1376.1
145°	1394.2	1392.9	1413.2	1421.6	1415.6
147.5°	1433.5	1429.9	1450.2	1456.1	1451.5
150°	1471.8	1463.4	1482.5	1489.6	1483.7
152.5°	1504.0	1494.4	1512.3	1519.6	1511.2
155°	1535.0	1524.4	1538.7	1545.8	1536.3
157.5°	1560.2	1550.6	1561.4	1569.8	1560.2
160°	1581.7	1574.4	1581.7	1588.8	1580.5
162.5°	1600.7	1593.6	1599.5	1607.9	1597.2
165°	1617.5	1610.4	1613.9	1622.3	1613.9
167.5°	1630.6	1623.4	1627.1	1635.5	1624.6
170°	1641.4	1634.2	1636.6	1644.9	1634.2
172.5°	1648.5	1641.4	1643.8	1652.2	1641.4
175°	1654.5	1646.1	1648.5	1656.8	1644.9
177.5°	1656.8	1648.5	1649.8	1658.2	1647.4
180°	1650.9	1650.9	1650.9	1650.9	1650.9

TEST NUMBER: P916097

CATALOG NUMBER: DFN2DIP-HX2F0-030D060US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.80	8.50	8.92	9.60	11.13	3.79	4.48	4.90	5.58	7.12
	3H	9.45	10.06	10.57	11.18	12.73	4.95	5.56	6.07	6.68	8.23
	4H	10.03	10.62	11.16	11.73	13.29	5.38	5.96	6.51	7.08	8.63
	6H	10.42	10.96	11.57	12.08	13.65	5.68	6.22	6.82	7.34	8.90
	8H	10.54	11.05	11.68	12.18	13.74	5.76	6.27	6.90	7.40	8.96
	12H	10.58	11.07	11.73	12.20	13.78	5.79	6.27	6.94	7.40	8.98
4H	2H	7.80	8.39	8.94	9.50	11.06	4.35	4.94	5.49	6.05	7.61
	3H	9.59	10.08	10.74	11.22	12.78	5.67	6.15	6.81	7.30	8.86
	4H	10.26	10.70	11.41	11.84	13.42	6.19	6.64	7.34	7.77	9.36
	6H	10.74	11.12	11.89	12.28	13.85	6.59	6.97	7.74	8.13	9.70
	8H	10.90	11.26	12.05	12.40	13.99	6.71	7.06	7.86	8.21	9.80
	12H	10.97	11.30	12.14	12.45	14.05	6.76	7.08	7.93	8.24	9.83
8H	4H	10.21	10.57	11.36	11.71	13.31	6.45	6.81	7.60	7.95	9.55
	6H	10.74	11.04	11.92	12.23	13.82	6.94	7.24	8.12	8.42	10.01
	8H	10.94	11.20	12.12	12.37	13.98	7.12	7.38	8.30	8.54	10.15
	12H	11.06	11.28	12.24	12.45	14.09	7.22	7.44	8.40	8.61	10.25
12H	4H	10.15	10.48	11.32	11.64	13.23	6.44	6.77	7.61	7.93	9.52
	6H	10.72	10.97	11.90	12.14	13.75	6.98	7.24	8.16	8.41	10.02
	8H	10.91	11.14	12.10	12.30	13.95	7.17	7.40	8.36	8.56	10.21

END OF REPORT