

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918967

Luminaire Tested: DFN2DIP-HX3F0-060D050US935-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918967
REPORT IS A COMBINATION OF REPORTS P900755 AND P897645
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-060D050US935-FLLONL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9376.3 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 93.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918967
CATALOG NUMBER: DFN2DIP-HX3F0-060D050US935-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P918967

CATALOG NUMBER: DFN2DIP-HX3F0-060D050US935-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55			
1	99	94	91	87	92	88	84	81	75	73	71	64	62	60	53	52	51	46			
2	90	82	76	71	83	77	71	67	66	62	58	56	53	51	47	45	43	39			
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33			
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32	28			
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	34	30	27	24			
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	30	27	24	21			
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	22	19			
8	55	42	34	29	51	40	33	28	35	29	25	30	25	22	26	22	19	17			
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17	15			
10	48	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16	14			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2328	2328	2328
5°	2331	2294	2310
10°	2311	2262	2278
15°	2276	2223	2227
20°	2229	2170	2176
25°	2182	2106	2117
30°	2124	2047	2042
35°	2069	1977	1963
40°	2001	1907	1888
45°	1933	1836	1811
50°	1858	1762	1721
55°	1781	1677	1639
60°	1693	1575	1545
65°	1596	1469	1433
70°	1474	1341	1313
75°	1304	1186	1200
80°	1100	989	988
85°	779	654	641

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1933 cd/sqm



TEST NUMBER: P918967

CATALOG NUMBER: DFN2DIP-HX3F0-060D050US935-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.2	2.0
10°-20°	532.3	5.7
20°-30°	782.3	8.3
30°-40°	908.6	9.7
40°-50°	907.5	9.7
50°-60°	791.3	8.4
60°-70°	584.9	6.2
70°-80°	330.9	3.5
80°-90°	89.9	1.0
90°-100°	47.9	0.5
100°-110°	178.6	1.9
110°-120°	473.7	5.1
120°-130°	785.6	8.4
130°-140°	834.5	8.9
140°-150°	775.6	8.3
150°-160°	623.5	6.7
160°-170°	401.8	4.3
170°-180°	138.3	1.5
0°-30°	1503.8	16.0
0°-40°	2412.4	25.7
0°-60°	4111.1	43.8
0°-90°	5116.9	54.6
90°-120°	700.2	7.5
90°-150°	3095.8	33.0
90°-180°	4259.0	45.4
0°-180°	9376.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2010	2010	2010	2010	2010	
5°	2010	2002	1981	1997	1993	191
15°	1914	1902	1877	1885	1875	539
25°	1732	1716	1684	1687	1684	797
35°	1494	1475	1444	1432	1422	933
45°	1216	1202	1173	1152	1144	938
55°	920	908	885	862	852	823
65°	620	609	590	572	562	614
75°	325	321	311	300	304	347
85°	79	77	75	70	68	88
90°	1	13	21	26	28	9
95°	68	34	41	46	45	81
105°	320	351	64	76	80	342
115°	604	622	649	162	86	595
125°	855	868	888	896	899	762
135°	1058	1074	1084	1094	1092	817
145°	1227	1226	1244	1251	1246	767
155°	1351	1342	1354	1360	1352	622
165°	1423	1417	1420	1428	1420	402
175°	1456	1449	1451	1458	1448	139
180°	1453	1453	1453	1453	1453	



TEST NUMBER: P918967

CATALOG NUMBER: DFN2DIP-HX3F0-060D050US935-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2010.1	2010.1	2010.1	2010.1	2010.1
2.5°	2021.8	2012.2	1990.8	2010.1	2006.4
5°	2010.1	2002.5	1981.2	1996.6	1992.9
7.5°	1996.6	1985.1	1963.8	1979.3	1975.5
10°	1975.5	1962.0	1938.7	1954.1	1948.4
12.5°	1946.4	1934.8	1911.7	1921.3	1917.4
15°	1913.5	1902.0	1876.8	1884.6	1875.0
17.5°	1872.9	1861.5	1836.3	1845.8	1836.3
20°	1828.4	1817.0	1789.8	1795.6	1788.0
22.5°	1784.2	1766.7	1741.5	1741.5	1737.6
25°	1731.8	1716.5	1683.6	1687.3	1683.6
27.5°	1673.8	1660.3	1635.2	1629.5	1619.9
30°	1616.0	1600.3	1571.5	1565.7	1557.9
32.5°	1554.0	1542.6	1511.6	1499.9	1492.1
35°	1494.2	1474.9	1443.9	1432.2	1422.5
37.5°	1426.5	1409.0	1378.1	1364.5	1354.9
40°	1356.9	1341.3	1310.4	1293.2	1285.4
42.5°	1289.3	1273.7	1242.9	1223.5	1211.9
45°	1215.9	1202.3	1173.2	1152.1	1144.3
47.5°	1144.3	1130.7	1099.8	1078.5	1066.9
50°	1068.8	1059.2	1032.2	1005.0	995.4
52.5°	995.4	981.9	956.8	935.6	922.0
55°	920.1	908.4	885.3	862.1	852.5
57.5°	844.7	835.1	809.9	786.7	778.9
60°	769.2	761.6	734.6	713.3	707.5
62.5°	695.8	682.3	663.0	643.7	635.9
65°	620.5	608.9	589.6	572.1	562.5
67.5°	543.2	533.4	516.2	502.7	494.8
70°	471.7	463.9	446.4	432.9	425.3
72.5°	398.2	390.5	380.8	367.3	361.5
75°	324.6	321.0	311.1	299.6	303.5
77.5°	259.0	251.2	247.3	241.6	235.8
80°	193.4	191.3	187.4	181.7	177.8
82.5°	131.5	131.5	129.6	121.8	121.8
85°	79.1	77.3	75.4	69.5	67.7
87.5°	34.9	31.0	27.0	21.4	19.3
90°	1.0	12.6	21.0	26.3	28.3
92.5°	26.3	22.1	25.2	27.4	28.3
95°	68.3	33.6	41.0	46.3	45.2
97.5°	123.0	36.9	53.6	56.8	57.8
100°	186.1	42.1	59.9	68.3	70.4
102.5°	255.5	253.4	62.1	73.5	76.8
105°	319.6	351.2	64.1	75.7	79.9
107.5°	394.3	420.4	66.3	77.7	82.1
110°	465.8	487.8	184.0	78.9	83.0



TEST NUMBER: P918967

CATALOG NUMBER: DFN2DIP-HX3F0-060D050US935-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	533.0	551.9	534.1	80.9	84.1
115°	604.5	622.3	648.7	162.0	86.3
117.5°	666.5	687.5	705.5	555.0	279.7
120°	735.9	751.7	770.6	783.2	641.3
122.5°	794.7	811.6	832.7	839.0	840.1
125°	854.6	868.4	888.4	895.7	898.9
127.5°	909.3	924.0	940.0	950.4	951.4
130°	960.9	977.7	989.2	1000.8	999.9
132.5°	1013.5	1027.2	1038.6	1048.2	1047.1
135°	1057.6	1074.5	1083.8	1094.5	1092.3
137.5°	1103.8	1116.5	1127.0	1137.6	1134.5
140°	1149.0	1157.5	1169.0	1178.4	1173.3
142.5°	1187.0	1194.4	1208.0	1216.3	1211.1
145°	1226.9	1225.8	1243.6	1251.0	1245.8
147.5°	1261.5	1258.3	1276.3	1281.5	1277.4
150°	1295.2	1287.9	1304.7	1311.0	1305.7
152.5°	1323.5	1315.2	1330.9	1337.3	1329.9
155°	1350.9	1341.5	1354.1	1360.4	1352.0
157.5°	1372.9	1364.6	1374.1	1381.5	1372.9
160°	1392.0	1385.6	1392.0	1398.2	1390.9
162.5°	1408.7	1402.5	1407.6	1415.0	1405.6
165°	1423.4	1417.2	1420.3	1427.6	1420.3
167.5°	1435.0	1428.7	1431.9	1439.2	1429.8
170°	1444.5	1438.1	1440.3	1447.6	1438.1
172.5°	1450.8	1444.5	1446.6	1454.0	1444.5
175°	1456.0	1448.6	1450.8	1458.1	1447.6
177.5°	1458.1	1450.8	1451.9	1459.2	1449.7
180°	1452.8	1452.8	1452.8	1452.8	1452.8



TEST NUMBER: P918967
 CATALOG NUMBER: DFN2DIP-HX3F0-060D050US935-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.58	11.48	11.49	12.42	13.62	10.15	11.05	11.07	11.99	13.19
	3H	12.23	13.04	13.16	13.99	15.22	11.76	12.58	12.69	13.52	14.75
	4H	12.82	13.58	13.76	14.53	15.77	12.35	13.12	13.29	14.07	15.30
	6H	13.21	13.92	14.17	14.88	16.13	12.74	13.45	13.70	14.41	15.66
	8H	13.32	13.99	14.28	14.96	16.21	12.85	13.52	13.81	14.49	15.74
	12H	13.36	14.00	14.33	14.97	16.24	12.89	13.53	13.86	14.50	15.77
4H	2H	11.04	11.81	11.99	12.76	14.00	10.70	11.47	11.65	12.42	13.65
	3H	12.90	13.54	13.86	14.52	15.77	12.51	13.15	13.47	14.13	15.38
	4H	13.61	14.20	14.58	15.17	16.45	13.21	13.80	14.18	14.77	16.05
	6H	14.12	14.63	15.10	15.62	16.90	13.72	14.22	14.70	15.22	16.49
	8H	14.27	14.74	15.25	15.73	17.02	13.86	14.33	14.84	15.32	16.61
	12H	14.34	14.77	15.34	15.77	17.07	13.92	14.35	14.93	15.36	16.65
8H	4H	13.81	14.28	14.79	15.27	16.56	13.45	13.92	14.43	14.91	16.20
	6H	14.43	14.82	15.44	15.86	17.14	14.07	14.46	15.08	15.50	16.78
	8H	14.65	14.99	15.67	16.01	17.32	14.28	14.63	15.30	15.65	16.95
	12H	14.78	15.08	15.80	16.09	17.45	14.40	14.70	15.42	15.71	17.07
12H	4H	13.80	14.22	14.80	15.23	16.52	13.45	13.87	14.45	14.88	16.17
	6H	14.46	14.81	15.48	15.83	17.13	14.11	14.46	15.13	15.48	16.78
	8H	14.70	15.00	15.72	16.02	17.37	14.35	14.65	15.37	15.66	17.01