

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918991

Luminaire Tested: DFN2DIP-HX3F0-070D050US935-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918991
REPORT IS A COMBINATION OF REPORTS P900757 AND P897645
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-070D050US935-FLLONL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10228.7 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 105.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918991

CATALOG NUMBER: DFN2DIP-HX3F0-070D050US935-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P918991

CATALOG NUMBER: DFN2DIP-HX3F0-070D050US935-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64
1	100	95	91	88	93	89	86	82	77	75	72	66	65	63	56	55	54
2	91	83	77	72	84	78	72	68	68	64	60	58	55	53	50	47	45
3	83	73	66	60	77	69	62	57	60	55	50	52	48	44	44	41	39
4	76	65	57	51	70	61	54	48	53	47	43	46	42	38	39	36	33
5	70	58	50	43	65	54	47	41	48	42	37	41	37	33	35	32	29
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	29	26
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	26	23
8	55	43	35	29	51	40	33	28	36	30	26	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2716	2716	2716
5°	2720	2677	2695
10°	2696	2639	2657
15°	2656	2593	2599
20°	2601	2531	2539
25°	2546	2457	2470
30°	2478	2388	2383
35°	2413	2307	2290
40°	2334	2225	2202
45°	2255	2142	2112
50°	2168	2056	2008
55°	2077	1956	1912
60°	1975	1837	1802
65°	1862	1714	1672
70°	1720	1564	1532
75°	1522	1384	1401
80°	1283	1154	1153
85°	910	764	748

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2255 cd/sqm

TEST NUMBER: P918991

CATALOG NUMBER: DFN2DIP-HX3F0-070D050US935-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	220.7	2.2
10°-20°	621.0	6.1
20°-30°	912.7	8.9
30°-40°	1060.0	10.4
40°-50°	1058.7	10.4
50°-60°	923.2	9.0
60°-70°	682.4	6.7
70°-80°	386.1	3.8
80°-90°	104.5	1.0
90°-100°	47.9	0.5
100°-110°	178.6	1.7
110°-120°	473.7	4.6
120°-130°	785.6	7.7
130°-140°	834.5	8.2
140°-150°	775.6	7.6
150°-160°	623.5	6.1
160°-170°	401.8	3.9
170°-180°	138.3	1.4
0°-30°	1754.4	17.2
0°-40°	2814.4	27.5
0°-60°	4796.3	46.9
0°-90°	5969.3	58.4
90°-120°	700.2	6.8
90°-150°	3095.8	30.3
90°-180°	4259.0	41.6
0°-180°	10228.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2345	2345	2345	2345	2345	
5°	2345	2336	2311	2329	2325	223
15°	2232	2219	2190	2199	2188	629
25°	2020	2002	1964	1969	1964	930
35°	1743	1721	1684	1671	1660	1089
45°	1418	1403	1369	1344	1335	1095
55°	1074	1060	1033	1006	994	960
65°	724	710	688	668	656	716
75°	379	374	363	350	354	404
85°	92	90	88	81	79	103
90°	1	13	21	26	28	9
95°	68	34	41	46	45	81
105°	320	351	64	76	80	342
115°	604	622	649	162	86	595
125°	855	868	888	896	899	762
135°	1058	1074	1084	1094	1092	817
145°	1227	1226	1244	1251	1246	767
155°	1351	1342	1354	1360	1352	622
165°	1423	1417	1420	1428	1420	402
175°	1456	1449	1451	1458	1448	139
180°	1453	1453	1453	1453	1453	

TEST NUMBER: P918991

CATALOG NUMBER: DFN2DIP-HX3F0-070D050US935-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2345.1	2345.1	2345.1	2345.1	2345.1
2.5°	2358.8	2347.5	2322.6	2345.1	2340.8
5°	2345.1	2336.3	2311.4	2329.3	2325.0
7.5°	2329.3	2315.9	2291.0	2309.3	2304.7
10°	2304.7	2288.9	2261.8	2279.8	2273.1
12.5°	2270.7	2257.4	2230.3	2241.5	2237.0
15°	2232.5	2219.0	2189.6	2198.7	2187.5
17.5°	2185.0	2171.7	2142.2	2153.5	2142.2
20°	2133.1	2119.8	2088.2	2094.9	2086.0
22.5°	2081.5	2061.1	2031.7	2031.7	2027.1
25°	2020.5	2002.5	1964.3	1968.6	1964.3
27.5°	1952.7	1937.0	1907.8	1901.1	1889.8
30°	1885.3	1867.1	1833.4	1826.7	1817.6
32.5°	1813.0	1799.7	1763.5	1749.9	1740.8
35°	1743.2	1720.7	1684.5	1670.9	1659.7
37.5°	1664.2	1643.9	1607.7	1592.0	1580.7
40°	1583.1	1564.9	1528.8	1508.7	1499.6
42.5°	1504.2	1486.0	1450.1	1427.4	1413.9
45°	1418.5	1402.7	1368.7	1344.1	1335.0
47.5°	1335.0	1319.2	1283.1	1258.2	1244.8
50°	1247.0	1235.7	1204.1	1172.6	1161.3
52.5°	1161.3	1145.6	1116.4	1091.5	1075.6
55°	1073.5	1059.9	1032.9	1005.8	994.5
57.5°	985.5	974.2	944.8	917.7	908.7
60°	897.4	888.5	857.0	832.2	825.4
62.5°	811.7	796.0	773.5	751.0	741.9
65°	724.0	710.3	687.9	667.5	656.3
67.5°	633.8	622.3	602.2	586.4	577.3
70°	550.3	541.2	520.8	505.1	496.2
72.5°	464.6	455.6	444.3	428.5	421.8
75°	378.8	374.4	362.9	349.6	354.1
77.5°	302.2	293.1	288.5	281.8	275.2
80°	225.6	223.3	218.7	212.0	207.4
82.5°	153.3	153.3	151.2	142.2	142.2
85°	92.4	90.2	88.1	81.1	79.0
87.5°	40.6	36.2	31.6	24.9	22.5
90°	1.0	12.6	21.0	26.3	28.3
92.5°	26.3	22.1	25.2	27.4	28.3
95°	68.3	33.6	41.0	46.3	45.2
97.5°	123.0	36.9	53.6	56.8	57.8
100°	186.1	42.1	59.9	68.3	70.4
102.5°	255.5	253.4	62.1	73.5	76.8
105°	319.6	351.2	64.1	75.7	79.9
107.5°	394.3	420.4	66.3	77.7	82.1
110°	465.8	487.8	184.0	78.9	83.0



TEST NUMBER: P918991

CATALOG NUMBER: DFN2DIP-HX3F0-070D050US935-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	533.0	551.9	534.1	80.9	84.1
115°	604.5	622.3	648.7	162.0	86.3
117.5°	666.5	687.5	705.5	555.0	279.7
120°	735.9	751.7	770.6	783.2	641.3
122.5°	794.7	811.6	832.7	839.0	840.1
125°	854.6	868.4	888.4	895.7	898.9
127.5°	909.3	924.0	940.0	950.4	951.4
130°	960.9	977.7	989.2	1000.8	999.9
132.5°	1013.5	1027.2	1038.6	1048.2	1047.1
135°	1057.6	1074.5	1083.8	1094.5	1092.3
137.5°	1103.8	1116.5	1127.0	1137.6	1134.5
140°	1149.0	1157.5	1169.0	1178.4	1173.3
142.5°	1187.0	1194.4	1208.0	1216.3	1211.1
145°	1226.9	1225.8	1243.6	1251.0	1245.8
147.5°	1261.5	1258.3	1276.3	1281.5	1277.4
150°	1295.2	1287.9	1304.7	1311.0	1305.7
152.5°	1323.5	1315.2	1330.9	1337.3	1329.9
155°	1350.9	1341.5	1354.1	1360.4	1352.0
157.5°	1372.9	1364.6	1374.1	1381.5	1372.9
160°	1392.0	1385.6	1392.0	1398.2	1390.9
162.5°	1408.7	1402.5	1407.6	1415.0	1405.6
165°	1423.4	1417.2	1420.3	1427.6	1420.3
167.5°	1435.0	1428.7	1431.9	1439.2	1429.8
170°	1444.5	1438.1	1440.3	1447.6	1438.1
172.5°	1450.8	1444.5	1446.6	1454.0	1444.5
175°	1456.0	1448.6	1450.8	1458.1	1447.6
177.5°	1458.1	1450.8	1451.9	1459.2	1449.7
180°	1452.8	1452.8	1452.8	1452.8	1452.8

TEST NUMBER: P918991

CATALOG NUMBER: DFN2DIP-HX3F0-070D050US935-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.44	12.38	12.32	13.28	14.43	11.01	11.95	11.89	12.85	14.00
	3H	13.10	13.94	13.99	14.85	16.03	12.63	13.47	13.52	14.38	15.56
	4H	13.68	14.48	14.59	15.40	16.58	13.21	14.01	14.12	14.93	16.11
	6H	14.08	14.82	15.00	15.74	16.94	13.61	14.35	14.53	15.27	16.47
	8H	14.18	14.89	15.11	15.83	17.02	13.72	14.42	14.64	15.36	16.55
	12H	14.23	14.90	15.17	15.84	17.06	13.76	14.43	14.69	15.36	16.58
4H	2H	11.91	12.71	12.82	13.62	14.81	11.56	12.36	12.48	13.28	14.46
	3H	13.77	14.44	14.70	15.39	16.58	13.38	14.05	14.31	15.00	16.19
	4H	14.48	15.09	15.42	16.04	17.26	14.08	14.69	15.02	15.63	16.85
	6H	15.00	15.52	15.94	16.49	17.71	14.59	15.12	15.54	16.08	17.30
	8H	15.14	15.63	16.09	16.59	17.83	14.74	15.23	15.69	16.19	17.42
	12H	15.22	15.66	16.19	16.64	17.88	14.80	15.24	15.77	16.22	17.46
8H	4H	14.68	15.17	15.63	16.13	17.37	14.32	14.82	15.28	15.78	17.01
	6H	15.31	15.71	16.29	16.72	17.95	14.95	15.36	15.93	16.36	17.59
	8H	15.52	15.88	16.51	16.88	18.13	15.16	15.52	16.15	16.51	17.76
	12H	15.65	15.97	16.64	16.96	18.26	15.28	15.59	16.27	16.58	17.88
12H	4H	14.67	15.11	15.64	16.09	17.33	14.32	14.76	15.29	15.74	16.98
	6H	15.34	15.70	16.32	16.69	17.94	14.99	15.35	15.98	16.34	17.59
	8H	15.58	15.89	16.57	16.88	18.18	15.22	15.54	16.21	16.53	17.82