

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919014

Luminaire Tested: DFN2DIP-HX3F0-080D050US935-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919014
REPORT IS A COMBINATION OF REPORTS P899239 AND P896089
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-080D050US935-FLLFLL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10629.0 lumens
Efficiency: N/A
Efficacy: 91.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 116.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919014
CATALOG NUMBER: DFN2DIP-HX3F0-080D050US935-FLLFL

Luminous Intensity Polar Plot





TEST NUMBER: P919014

CATALOG NUMBER: DFN2DIP-HX3F0-080D050US935-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	69	69	69	64
1	101	97	93	89	95	91	87	84	80	77	75	70	68	66	61	60	58	61	60	58	54
2	92	84	78	73	86	79	74	69	70	66	62	62	58	56	54	51	49	54	51	49	45
3	84	74	67	61	79	70	63	58	62	57	52	55	50	47	48	45	42	48	45	42	38
4	77	66	58	51	72	62	55	49	55	49	45	49	44	40	43	39	36	43	39	36	33
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	38	35	32	38	35	32	29
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28	35	31	28	25
7	60	48	40	34	56	45	38	32	40	34	30	36	31	27	32	28	25	32	28	25	22
8	56	43	35	30	53	41	34	29	37	31	27	33	28	24	29	25	22	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	26	22	27	23	20	27	23	20	18
10	49	37	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3104	3104	3104
5°	3108	3059	3080
10°	3082	3016	3037
15°	3035	2964	2970
20°	2972	2893	2902
25°	2910	2808	2823
30°	2832	2729	2723
35°	2758	2637	2618
40°	2668	2543	2517
45°	2577	2449	2414
50°	2478	2350	2295
55°	2374	2235	2185
60°	2257	2100	2060
65°	2128	1959	1911
70°	1965	1788	1751
75°	1739	1582	1601
80°	1466	1319	1318
85°	1040	874	854

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2577 cd/sqm



TEST NUMBER: P919014

CATALOG NUMBER: DFN2DIP-HX3F0-080D050US935-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	252.3	2.4
10°-20°	709.8	6.7
20°-30°	1043.1	9.8
30°-40°	1211.4	11.4
40°-50°	1209.9	11.4
50°-60°	1055.0	9.9
60°-70°	779.9	7.3
70°-80°	441.2	4.2
80°-90°	120.3	1.1
90°-100°	84.2	0.8
100°-110°	267.7	2.5
110°-120°	458.1	4.3
120°-130°	602.5	5.7
130°-140°	676.3	6.4
140°-150°	663.1	6.2
150°-160°	556.3	5.2
160°-170°	368.9	3.5
170°-180°	128.9	1.2
0°-30°	2005.1	18.9
0°-40°	3216.5	30.3
0°-60°	5481.5	51.6
0°-90°	6823.0	64.2
90°-120°	810.0	7.6
90°-150°	2751.9	25.9
90°-180°	3806.0	35.8
0°-180°	10629.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2680	2680	2680	2680	2680	
5°	2680	2670	2642	2662	2657	254
15°	2551	2536	2502	2513	2500	719
25°	2309	2289	2245	2250	2245	1063
35°	1992	1966	1925	1910	1897	1244
45°	1621	1603	1564	1536	1526	1251
55°	1227	1211	1180	1150	1137	1097
65°	827	812	786	763	750	818
75°	433	428	415	400	405	462
85°	106	103	101	93	90	118
90°	1	15	40	38	39	10
95°	60	72	73	73	72	67
105°	247	250	253	255	255	261
115°	460	466	464	463	460	455
125°	669	679	676	672	671	598
135°	865	878	880	879	876	669
145°	1050	1058	1065	1066	1061	656
155°	1201	1204	1208	1213	1210	553
165°	1306	1305	1305	1313	1307	368
175°	1359	1356	1353	1362	1354	129
180°	1362	1362	1362	1362	1362	



TEST NUMBER: P919014

CATALOG NUMBER: DFN2DIP-HX3F0-080D050US935-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2680.1	2680.1	2680.1	2680.1	2680.1
2.5°	2695.7	2682.9	2654.5	2680.1	2675.2
5°	2680.1	2670.0	2641.6	2662.1	2657.2
7.5°	2662.1	2646.8	2618.4	2639.1	2634.0
10°	2634.0	2615.9	2585.0	2605.5	2597.9
12.5°	2595.1	2579.8	2548.9	2561.7	2556.6
15°	2551.4	2536.1	2502.4	2512.8	2500.0
17.5°	2497.2	2481.9	2448.2	2461.2	2448.2
20°	2437.9	2422.6	2386.5	2394.2	2384.0
22.5°	2378.9	2355.6	2321.9	2321.9	2316.8
25°	2309.1	2288.6	2244.9	2249.8	2244.9
27.5°	2231.7	2213.7	2180.3	2172.6	2159.8
30°	2154.6	2133.8	2095.3	2087.7	2077.2
32.5°	2072.1	2056.8	2015.4	1999.8	1989.5
35°	1992.2	1966.5	1925.2	1909.6	1896.8
37.5°	1901.9	1878.7	1837.5	1819.4	1806.5
40°	1809.3	1788.5	1747.2	1724.2	1713.8
42.5°	1719.1	1698.2	1657.2	1631.2	1616.0
45°	1621.2	1603.1	1564.3	1536.1	1525.8
47.5°	1525.8	1507.7	1466.4	1438.0	1422.6
50°	1425.1	1412.3	1376.1	1340.1	1327.2
52.5°	1327.2	1309.1	1275.8	1247.4	1229.3
55°	1226.8	1211.3	1180.4	1149.5	1136.6
57.5°	1126.3	1113.4	1079.8	1048.9	1038.4
60°	1025.6	1015.5	979.4	951.0	943.3
62.5°	927.7	909.7	884.0	858.3	847.9
65°	827.4	811.8	786.1	762.8	750.0
67.5°	724.3	711.2	688.2	670.2	659.8
70°	628.9	618.5	595.3	577.2	567.1
72.5°	531.0	520.6	507.7	489.7	482.1
75°	432.8	427.9	414.8	399.5	404.7
77.5°	345.3	334.9	329.8	322.1	314.4
80°	257.9	255.1	249.9	242.3	237.0
82.5°	175.3	175.3	172.8	162.4	162.4
85°	105.6	103.1	100.7	92.7	90.2
87.5°	46.5	41.3	36.1	28.4	25.7
90°	1.2	14.8	40.2	37.8	39.0
92.5°	25.5	34.4	35.7	36.9	36.9
95°	59.9	71.5	73.4	73.4	71.5
97.5°	99.7	110.4	114.9	114.9	114.9
100°	145.7	155.2	158.4	158.4	157.2
102.5°	194.2	201.1	205.6	206.9	205.6
105°	247.1	250.4	252.9	254.9	254.9
107.5°	299.6	304.5	304.5	305.4	299.6
110°	350.5	357.1	357.1	357.1	353.8



TEST NUMBER: P919014

CATALOG NUMBER: DFN2DIP-HX3F0-080D050US935-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	405.5	412.5	411.3	408.0	405.5
115°	459.7	466.3	464.3	463.0	459.7
117.5°	513.5	522.5	516.8	513.5	510.2
120°	567.7	576.7	567.7	567.7	564.0
122.5°	616.9	628.4	622.7	619.4	616.9
125°	668.7	678.9	675.6	671.9	670.7
127.5°	719.1	731.8	727.4	722.4	719.1
130°	766.4	781.1	779.0	776.6	772.1
132.5°	819.3	830.8	831.6	825.9	822.6
135°	864.9	877.5	880.0	878.8	875.5
137.5°	915.8	926.0	928.1	927.2	922.3
140°	960.4	970.8	976.5	976.5	972.0
142.5°	1006.4	1016.8	1020.0	1021.2	1016.8
145°	1050.0	1058.2	1064.7	1066.0	1061.4
147.5°	1089.0	1099.2	1104.1	1106.2	1101.6
150°	1129.2	1136.2	1140.6	1144.4	1140.6
152.5°	1164.9	1171.9	1177.6	1182.2	1177.6
155°	1200.6	1203.8	1207.5	1213.3	1209.6
157.5°	1231.4	1233.8	1235.9	1244.1	1238.4
160°	1258.9	1261.4	1262.6	1269.5	1264.6
162.5°	1284.4	1284.4	1285.6	1293.4	1287.6
165°	1306.1	1304.8	1304.8	1313.1	1307.3
167.5°	1325.8	1322.1	1322.1	1330.3	1324.6
170°	1340.6	1337.3	1336.1	1344.3	1337.3
172.5°	1350.8	1347.5	1346.3	1354.5	1347.5
175°	1359.1	1355.7	1353.3	1361.5	1354.5
177.5°	1363.6	1360.3	1357.8	1364.8	1357.8
180°	1361.5	1361.5	1361.5	1361.5	1361.5



TEST NUMBER: P919014
 CATALOG NUMBER: DFN2DIP-HX3F0-080D050US935-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.38	13.38	13.20	14.23	15.28	11.95	12.96	12.78	13.80	14.86
	3H	14.04	14.95	14.88	15.80	16.88	13.57	14.48	14.41	15.33	16.41
	4H	14.63	15.48	15.49	16.35	17.44	14.16	15.02	15.02	15.88	16.97
	6H	15.03	15.82	15.90	16.69	17.80	14.56	15.35	15.43	16.22	17.33
	8H	15.14	15.89	16.01	16.78	17.88	14.67	15.42	15.54	16.31	17.41
	12H	15.19	15.90	16.07	16.79	17.92	14.71	15.43	15.59	16.31	17.44
4H	2H	12.86	13.71	13.71	14.57	15.66	12.51	13.37	13.37	14.23	15.32
	3H	14.73	15.44	15.60	16.33	17.44	14.34	15.05	15.21	15.94	17.05
	4H	15.44	16.09	16.32	16.98	18.11	15.04	15.69	15.92	16.58	17.71
	6H	15.96	16.52	16.85	17.43	18.57	15.55	16.11	16.45	17.03	18.16
	8H	16.10	16.63	17.00	17.54	18.69	15.70	16.22	16.60	17.13	18.28
	12H	16.18	16.65	17.10	17.58	18.74	15.76	16.24	16.68	17.17	18.32
8H	4H	15.64	16.17	16.54	17.08	18.23	15.29	15.81	16.19	16.72	17.87
	6H	16.27	16.71	17.20	17.66	18.81	15.91	16.35	16.84	17.30	18.45
	8H	16.49	16.87	17.43	17.82	18.98	16.12	16.51	17.06	17.45	18.62
	12H	16.62	16.96	17.56	17.90	19.11	16.24	16.58	17.18	17.52	18.74
12H	4H	15.64	16.11	16.56	17.04	18.19	15.29	15.76	16.21	16.69	17.84
	6H	16.30	16.69	17.24	17.63	18.80	15.95	16.34	16.89	17.28	18.45
	8H	16.54	16.88	17.49	17.82	19.04	16.19	16.53	17.13	17.47	18.68