

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916152

Luminaire Tested: DFN2DIP-HX2F0-060D050US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916152
REPORT IS A COMBINATION OF REPORTS P899190 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-060D050US930-RLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7765.7 lumens
Efficiency: N/A
Efficacy: 79.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 97.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916152
CATALOG NUMBER: DFN2DIP-HX2F0-060D050US930-RLFL

Luminous Intensity Polar Plot





TEST NUMBER: P916152
 CATALOG NUMBER: DFN2DIP-HX2F0-060D050US930-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54			
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51	46			
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44	39			
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	43	40	38	34			
4	76	66	58	52	71	61	55	49	53	48	44	46	42	38	38	36	33	30			
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26			
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	29	26	23			
7	60	48	40	35	56	45	38	33	39	34	30	34	30	27	29	26	23	21			
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	24	21	19			
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	25	22	19	17			
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	18	16			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4764	4764	4764
5°	4764	4677	4709
10°	4709	4574	4547
15°	4637	4411	4302
20°	4543	4193	4005
25°	4448	3950	3718
30°	4322	3701	3357
35°	4198	3435	3040
40°	4072	3161	2678
45°	3926	2859	2351
50°	3775	2555	2031
55°	3616	2231	1725
60°	3431	1895	1412
65°	3219	1554	1261
70°	2961	1236	1129
75°	2636	1068	1010
80°	2169	865	851
85°	1419	534	596

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3926 cd/sqm



TEST NUMBER: P916152

CATALOG NUMBER: DFN2DIP-HX2F0-060D050US930-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.5	2.4
10°-20°	520.2	6.7
20°-30°	730.3	9.4
30°-40°	796.1	10.3
40°-50°	731.7	9.4
50°-60°	574.6	7.4
60°-70°	374.0	4.8
70°-80°	192.5	2.5
80°-90°	52.8	0.7
90°-100°	79.8	1.0
100°-110°	253.5	3.3
110°-120°	433.8	5.6
120°-130°	570.5	7.3
130°-140°	640.4	8.2
140°-150°	627.9	8.1
150°-160°	526.8	6.8
160°-170°	349.3	4.5
170°-180°	122.1	1.6
0°-30°	1439.9	18.5
0°-40°	2236.0	28.8
0°-60°	3542.3	45.6
0°-90°	4161.7	53.6
90°-120°	767.0	9.9
90°-150°	2605.8	33.6
90°-180°	3604.0	46.4
0°-180°	7765.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2022	2022	2022	2022	2022	
5°	2022	2013	1989	2005	2000	192
15°	1923	1903	1841	1806	1788	542
25°	1746	1687	1566	1491	1464	803
35°	1504	1411	1250	1134	1094	941
45°	1230	1107	915	785	741	950
55°	935	792	595	485	450	835
65°	631	483	318	256	251	626
75°	337	208	146	134	132	356
85°	79	40	35	35	35	90
90°	1	14	38	36	37	8
95°	57	68	70	70	68	63
105°	234	237	240	241	241	247
115°	435	442	440	438	435	431
125°	633	643	640	636	635	566
135°	819	831	833	832	829	633
145°	994	1002	1008	1009	1005	621
155°	1137	1140	1144	1149	1145	523
165°	1237	1236	1236	1243	1238	349
175°	1287	1284	1282	1289	1283	122
180°	1289	1289	1289	1289	1289	



TEST NUMBER: P916152

CATALOG NUMBER: DFN2DIP-HX2F0-060D050US930-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2021.8	2021.8	2021.8	2021.8	2021.8
2.5°	2030.9	2021.8	2001.6	2020.0	2016.3
5°	2021.8	2012.6	1988.8	2005.3	1999.8
7.5°	2005.3	1994.4	1968.8	1976.0	1966.8
10°	1983.3	1970.5	1934.1	1928.4	1917.5
12.5°	1956.0	1939.4	1889.9	1879.1	1858.9
15°	1923.0	1902.7	1840.6	1805.9	1787.6
17.5°	1884.6	1855.2	1778.3	1738.1	1708.9
20°	1840.6	1803.9	1712.5	1666.9	1626.5
22.5°	1793.1	1750.9	1644.8	1582.7	1555.3
25°	1745.6	1686.9	1566.2	1491.3	1463.7
27.5°	1688.9	1626.5	1493.0	1407.0	1364.9
30°	1628.5	1558.8	1412.4	1319.2	1269.7
32.5°	1569.9	1485.6	1335.8	1225.9	1180.1
35°	1504.1	1410.7	1249.8	1134.4	1094.0
37.5°	1440.0	1339.2	1169.2	1042.8	997.2
40°	1372.2	1262.6	1084.9	955.0	907.5
42.5°	1302.8	1185.7	1000.9	865.4	819.8
45°	1229.6	1106.8	914.9	784.8	740.9
47.5°	1160.1	1030.2	832.6	702.5	662.3
50°	1083.2	953.3	752.0	625.7	587.4
52.5°	1008.0	870.8	675.1	554.4	519.7
55°	934.9	792.2	594.6	484.9	450.1
57.5°	860.0	713.5	523.3	420.9	391.5
60°	783.1	636.7	448.3	355.1	325.7
62.5°	708.2	561.8	384.2	296.4	281.8
65°	631.3	483.0	318.4	256.2	250.6
67.5°	558.1	409.8	256.2	225.0	219.6
70°	481.2	338.5	212.1	194.0	186.5
72.5°	408.1	272.6	177.4	162.9	159.1
75°	336.6	208.5	146.3	133.5	131.8
77.5°	265.4	148.1	115.3	107.9	104.3
80°	199.3	106.2	87.7	80.6	80.6
82.5°	139.0	71.4	60.3	56.7	56.7
85°	78.6	40.2	34.7	34.7	34.7
87.5°	29.4	14.6	14.6	12.8	12.8
90°	1.1	14.0	38.1	35.8	36.9
92.5°	24.1	32.6	33.8	35.0	35.0
95°	56.7	67.7	69.5	69.5	67.7
97.5°	94.4	104.5	108.8	108.8	108.8
100°	137.9	146.9	150.0	150.0	148.9
102.5°	183.8	190.5	194.7	195.9	194.7
105°	234.0	237.1	239.5	241.3	241.3
107.5°	283.7	288.4	288.4	289.2	283.7
110°	331.9	338.2	338.2	338.2	335.0



TEST NUMBER: P916152

CATALOG NUMBER: DFN2DIP-HX2F0-060D050US930-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	384.0	390.6	389.5	386.4	384.0
115°	435.3	441.6	439.6	438.5	435.3
117.5°	486.2	494.8	489.3	486.2	483.1
120°	537.5	546.1	537.5	537.5	534.0
122.5°	584.2	595.1	589.6	586.5	584.2
125°	633.2	642.9	639.8	636.3	635.1
127.5°	680.9	693.0	688.8	684.0	680.9
130°	725.7	739.6	737.7	735.4	731.1
132.5°	775.8	786.7	787.5	782.0	778.9
135°	819.0	831.0	833.3	832.2	829.1
137.5°	867.2	876.9	878.8	878.0	873.3
140°	909.5	919.2	924.6	924.6	920.4
142.5°	953.0	962.8	965.9	967.0	962.8
145°	994.3	1002.0	1008.2	1009.4	1005.1
147.5°	1031.2	1040.9	1045.5	1047.5	1043.2
150°	1069.3	1075.9	1080.1	1083.6	1080.1
152.5°	1103.1	1109.7	1115.1	1119.4	1115.1
155°	1136.9	1140.0	1143.5	1148.9	1145.4
157.5°	1166.0	1168.3	1170.3	1178.1	1172.6
160°	1192.0	1194.4	1195.6	1202.2	1197.5
162.5°	1216.2	1216.2	1217.3	1224.7	1219.3
165°	1236.8	1235.6	1235.6	1243.4	1237.9
167.5°	1255.4	1251.9	1251.9	1259.7	1254.3
170°	1269.4	1266.3	1265.2	1272.9	1266.3
172.5°	1279.1	1276.0	1274.9	1282.6	1276.0
175°	1286.9	1283.8	1281.5	1289.2	1282.6
177.5°	1291.2	1288.1	1285.7	1292.3	1285.7
180°	1289.2	1289.2	1289.2	1289.2	1289.2



TEST NUMBER: P916152
 CATALOG NUMBER: DFN2DIP-HX2F0-060D050US930-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.76	13.62	13.69	14.57	15.79	8.74	9.61	9.68	10.55	11.77
	3H	14.42	15.19	15.36	16.14	17.39	9.92	10.69	10.86	11.64	12.89
	4H	15.01	15.74	15.97	16.70	17.95	10.36	11.09	11.32	12.04	13.30
	6H	15.41	16.08	16.38	17.05	18.31	10.67	11.34	11.64	12.30	13.57
	8H	15.53	16.16	16.50	17.15	18.41	10.75	11.39	11.73	12.37	13.63
	12H	15.58	16.19	16.56	17.16	18.45	10.79	11.39	11.77	12.37	13.66
4H	2H	12.78	13.51	13.74	14.47	15.72	9.33	10.06	10.29	11.02	12.27
	3H	14.58	15.19	15.56	16.18	17.44	10.66	11.27	11.64	12.26	13.52
	4H	15.26	15.81	16.24	16.79	18.08	11.20	11.75	12.18	12.73	14.02
	6H	15.75	16.22	16.74	17.23	18.52	11.60	12.07	12.60	13.08	14.37
	8H	15.91	16.35	16.91	17.35	18.66	11.72	12.16	12.72	13.16	14.47
	12H	15.99	16.39	17.01	17.41	18.72	11.78	12.18	12.79	13.19	14.50
8H	4H	15.22	15.67	16.22	16.66	17.97	11.46	11.91	12.46	12.91	14.21
	6H	15.76	16.13	16.78	17.17	18.47	11.96	12.33	12.98	13.37	14.67
	8H	15.96	16.28	16.99	17.31	18.63	12.14	12.46	13.17	13.49	14.81
	12H	16.09	16.37	17.12	17.39	18.76	12.25	12.53	13.28	13.55	14.92
12H	4H	15.17	15.57	16.19	16.59	17.90	11.47	11.87	12.48	12.88	14.19
	6H	15.74	16.06	16.77	17.09	18.41	12.00	12.33	13.03	13.35	14.68
	8H	15.94	16.22	16.97	17.25	18.61	12.20	12.48	13.23	13.51	14.87