

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916156

Luminaire Tested: DFN2DIP-HX2F0-060D060US930-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P916156  
REPORT IS A COMBINATION OF REPORTS P899200 AND P896039  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX2F0-060D060US930-RLLFLL  
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8487.2 lumens  
Efficiency: N/A  
Efficacy: 78.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 107.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9971  
Total Harmonic Distortion (THDi): 0.049  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P916156  
CATALOG NUMBER: DFN2DIP-HX2F0-060D060US930-RLFL

### Luminous Intensity Polar Plot





TEST NUMBER: P916156  
 CATALOG NUMBER: DFN2DIP-HX2F0-060D060US930-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55	49			49
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48	42			42
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41	36			36
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35	31			31
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31	27			27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27	24			24
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24	21			21
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22	19			19
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20	17			17
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18	16			16
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16	14			14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4764	4764	4764
5°	4764	4677	4709
10°	4709	4574	4547
15°	4637	4411	4302
20°	4543	4193	4005
25°	4448	3950	3718
30°	4322	3701	3357
35°	4198	3435	3040
40°	4072	3161	2678
45°	3926	2859	2351
50°	3775	2555	2031
55°	3616	2231	1725
60°	3431	1895	1412
65°	3219	1554	1261
70°	2961	1236	1129
75°	2636	1068	1010
80°	2169	865	851
85°	1419	534	596

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3926 cd/sqm



TEST NUMBER: P916156

CATALOG NUMBER: DFN2DIP-HX2F0-060D060US930-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	189.5	2.2
10°-20°	520.2	6.1
20°-30°	730.3	8.6
30°-40°	796.1	9.4
40°-50°	731.7	8.6
50°-60°	574.6	6.8
60°-70°	374.0	4.4
70°-80°	192.5	2.3
80°-90°	53.5	0.6
90°-100°	95.7	1.1
100°-110°	304.2	3.6
110°-120°	520.6	6.1
120°-130°	684.6	8.1
130°-140°	768.4	9.1
140°-150°	753.5	8.9
150°-160°	632.1	7.4
160°-170°	419.2	4.9
170°-180°	146.5	1.7
0°-30°	1439.9	17.0
0°-40°	2236.0	26.3
0°-60°	3542.3	41.7
0°-90°	4162.4	49.0
90°-120°	920.5	10.8
90°-150°	3127.0	36.8
90°-180°	4325.0	51.0
0°-180°	8487.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2022	2022	2022	2022	2022	
5°	2022	2013	1989	2005	2000	192
15°	1923	1903	1841	1806	1788	542
25°	1746	1687	1566	1491	1464	803
35°	1504	1411	1250	1134	1094	941
45°	1230	1107	915	785	741	950
55°	935	792	595	485	450	835
65°	631	483	318	256	251	626
75°	337	208	146	134	132	356
85°	79	40	35	35	35	90
90°	1	17	46	43	44	8
95°	68	81	84	84	81	76
105°	281	284	287	290	290	296
115°	522	530	528	526	522	517
125°	760	771	768	764	762	679
135°	983	997	1000	999	995	760
145°	1193	1202	1210	1211	1206	745
155°	1364	1368	1372	1379	1374	628
165°	1484	1483	1483	1492	1486	419
175°	1544	1541	1538	1547	1539	147
180°	1547	1547	1547	1547	1547	



TEST NUMBER: P916156

CATALOG NUMBER: DFN2DIP-HX2F0-060D060US930-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2021.8	2021.8	2021.8	2021.8	2021.8
2.5°	2030.9	2021.8	2001.6	2020.0	2016.3
5°	2021.8	2012.6	1988.8	2005.3	1999.8
7.5°	2005.3	1994.4	1968.8	1976.0	1966.8
10°	1983.3	1970.5	1934.1	1928.4	1917.5
12.5°	1956.0	1939.4	1889.9	1879.1	1858.9
15°	1923.0	1902.7	1840.6	1805.9	1787.6
17.5°	1884.6	1855.2	1778.3	1738.1	1708.9
20°	1840.6	1803.9	1712.5	1666.9	1626.5
22.5°	1793.1	1750.9	1644.8	1582.7	1555.3
25°	1745.6	1686.9	1566.2	1491.3	1463.7
27.5°	1688.9	1626.5	1493.0	1407.0	1364.9
30°	1628.5	1558.8	1412.4	1319.2	1269.7
32.5°	1569.9	1485.6	1335.8	1225.9	1180.1
35°	1504.1	1410.7	1249.8	1134.4	1094.0
37.5°	1440.0	1339.2	1169.2	1042.8	997.2
40°	1372.2	1262.6	1084.9	955.0	907.5
42.5°	1302.8	1185.7	1000.9	865.4	819.8
45°	1229.6	1106.8	914.9	784.8	740.9
47.5°	1160.1	1030.2	832.6	702.5	662.3
50°	1083.2	953.3	752.0	625.7	587.4
52.5°	1008.0	870.8	675.1	554.4	519.7
55°	934.9	792.2	594.6	484.9	450.1
57.5°	860.0	713.5	523.3	420.9	391.5
60°	783.1	636.7	448.3	355.1	325.7
62.5°	708.2	561.8	384.2	296.4	281.8
65°	631.3	483.0	318.4	256.2	250.6
67.5°	558.1	409.8	256.2	225.0	219.6
70°	481.2	338.5	212.1	194.0	186.5
72.5°	408.1	272.6	177.4	162.9	159.1
75°	336.6	208.5	146.3	133.5	131.8
77.5°	265.4	148.1	115.3	107.9	104.3
80°	199.3	106.2	87.7	80.6	80.6
82.5°	139.0	71.4	60.3	56.7	56.7
85°	78.6	40.2	34.7	34.7	34.7
87.5°	29.4	14.6	14.6	12.8	12.8
90°	1.4	16.8	45.7	42.9	44.3
92.5°	28.9	39.2	40.6	42.0	42.0
95°	68.1	81.1	83.5	83.5	81.1
97.5°	113.3	125.5	130.6	130.6	130.6
100°	165.6	176.3	180.0	180.0	178.6
102.5°	220.6	228.5	233.7	235.1	233.7
105°	280.8	284.5	287.3	289.7	289.7
107.5°	340.5	346.1	346.1	347.0	340.5
110°	398.4	405.8	405.8	405.8	402.0



TEST NUMBER: P916156

CATALOG NUMBER: DFN2DIP-HX2F0-060D060US930-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	460.8	468.7	467.3	463.6	460.8
115°	522.4	529.9	527.5	526.1	522.4
117.5°	583.5	593.8	587.2	583.5	579.8
120°	645.1	655.3	645.1	645.1	640.8
122.5°	701.0	714.0	707.5	703.8	701.0
125°	759.8	771.4	767.7	763.5	762.1
127.5°	817.2	831.6	826.5	820.9	817.2
130°	870.8	887.6	885.3	882.5	877.3
132.5°	931.0	944.0	944.9	938.4	934.7
135°	982.8	997.2	1000.0	998.6	994.8
137.5°	1040.6	1052.2	1054.6	1053.6	1048.1
140°	1091.4	1103.1	1109.6	1109.6	1104.5
142.5°	1143.6	1155.3	1159.0	1160.4	1155.3
145°	1193.1	1202.4	1209.9	1211.3	1206.2
147.5°	1237.4	1249.0	1254.7	1256.9	1251.8
150°	1283.1	1291.0	1296.2	1300.3	1296.2
152.5°	1323.6	1331.6	1338.1	1343.3	1338.1
155°	1364.2	1368.0	1372.1	1378.8	1374.5
157.5°	1399.2	1402.1	1404.4	1413.7	1407.2
160°	1430.5	1433.3	1434.7	1442.6	1437.0
162.5°	1459.4	1459.4	1460.8	1469.7	1463.1
165°	1484.1	1482.7	1482.7	1492.1	1485.6
167.5°	1506.5	1502.4	1502.4	1511.6	1505.1
170°	1523.3	1519.6	1518.2	1527.5	1519.6
172.5°	1535.0	1531.2	1529.8	1539.1	1531.2
175°	1544.3	1540.6	1537.7	1547.1	1539.1
177.5°	1549.4	1545.7	1542.9	1550.8	1542.9
180°	1547.1	1547.1	1547.1	1547.1	1547.1



TEST NUMBER: P916156  
 CATALOG NUMBER: DFN2DIP-HX2F0-060D060US930-RLFL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.34	13.16	13.31	14.15	15.43	8.32	9.15	9.30	10.13	11.42
	3H	13.99	14.73	14.98	15.72	17.03	9.50	10.23	10.48	11.22	12.53
	4H	14.58	15.28	15.58	16.27	17.59	9.93	10.63	10.93	11.62	12.94
	6H	14.99	15.63	15.99	16.62	17.95	10.24	10.88	11.25	11.88	13.21
	8H	15.10	15.71	16.11	16.72	18.05	10.32	10.93	11.34	11.95	13.27
	12H	15.15	15.73	16.17	16.74	18.09	10.36	10.94	11.38	11.95	13.30
4H	2H	12.35	13.05	13.36	14.04	15.36	8.91	9.60	9.91	10.59	11.91
	3H	14.15	14.73	15.17	15.76	17.09	10.23	10.81	11.25	11.84	13.17
	4H	14.83	15.36	15.85	16.37	17.73	10.77	11.30	11.79	12.31	13.67
	6H	15.32	15.77	16.35	16.81	18.16	11.17	11.62	12.20	12.66	14.01
	8H	15.48	15.90	16.51	16.93	18.30	11.29	11.71	12.32	12.74	14.11
	12H	15.56	15.94	16.61	16.99	18.36	11.34	11.72	12.39	12.77	14.14
8H	4H	14.79	15.21	15.82	16.25	17.61	11.03	11.46	12.06	12.49	13.85
	6H	15.33	15.68	16.38	16.75	18.12	11.53	11.88	12.58	12.95	14.31
	8H	15.53	15.84	16.59	16.90	18.28	11.70	12.01	12.77	13.07	14.45
	12H	15.65	15.92	16.71	16.97	18.40	11.81	12.08	12.87	13.13	14.56
12H	4H	14.74	15.12	15.79	16.17	17.54	11.03	11.41	12.08	12.46	13.83
	6H	15.30	15.61	16.36	16.67	18.05	11.57	11.88	12.63	12.94	14.32
	8H	15.50	15.78	16.57	16.83	18.25	11.76	12.03	12.83	13.09	14.51