

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918804

Luminaire Tested: DFN2DIP-HX2F0-020D060US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918804
REPORT IS A COMBINATION OF REPORTS P899192 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-020D060US935-RLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6035.6 lumens
Efficiency: N/A
Efficacy: 94.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 63.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918804
CATALOG NUMBER: DFN2DIP-HX2F0-020D060US935-RLLFLL

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P918804

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US935-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	24				24
1	92	88	85	81	82	79	76	73	61	59	57	44	43	42	29	28	28	21				21
2	84	77	71	67	75	69	64	60	53	50	47	39	37	35	26	25	24	18				18
3	77	68	61	56	68	61	55	50	47	43	40	35	32	30	23	22	20	15				15
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	21	19	18	13				13
5	64	54	46	40	57	48	42	37	38	33	29	28	25	22	19	17	16	12				12
6	59	48	40	35	53	43	37	32	34	29	26	25	22	20	17	15	14	11				11
7	55	43	36	30	49	39	32	28	31	26	23	23	20	17	16	14	12	9				9
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	14	12	11	8				8
9	47	36	29	24	42	32	26	22	25	21	18	19	16	14	13	11	10	8				8
10	44	33	26	21	39	29	23	19	23	19	16	18	15	13	12	10	9	7				7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1677	1677	1677
5°	1677	1646	1658
10°	1658	1610	1601
15°	1632	1553	1515
20°	1599	1476	1410
25°	1566	1390	1309
30°	1521	1303	1182
35°	1478	1209	1070
40°	1433	1113	943
45°	1382	1006	827
50°	1329	900	715
55°	1273	785	607
60°	1208	667	497
65°	1133	547	444
70°	1042	435	398
75°	928	376	356
80°	764	305	299
85°	498	188	209

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 2193 cd/sqm



TEST NUMBER: P918804

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US935-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.7	1.1
10°-20°	183.1	3.0
20°-30°	257.1	4.3
30°-40°	280.2	4.6
40°-50°	257.6	4.3
50°-60°	202.3	3.4
60°-70°	131.7	2.2
70°-80°	67.8	1.1
80°-90°	21.9	0.4
90°-100°	101.1	1.7
100°-110°	321.2	5.3
110°-120°	549.7	9.1
120°-130°	723.0	12.0
130°-140°	811.5	13.4
140°-150°	795.8	13.2
150°-160°	667.5	11.1
160°-170°	442.7	7.3
170°-180°	154.7	2.6
0°-30°	506.9	8.4
0°-40°	787.1	13.0
0°-60°	1247.0	20.7
0°-90°	1468.3	24.3
90°-120°	972.0	16.1
90°-150°	3302.3	54.7
90°-180°	4567.0	75.7
0°-180°	6035.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	712	712	712	712	712	
5°	712	708	700	706	704	67
15°	677	670	648	636	629	191
25°	614	594	551	525	515	283
35°	529	497	440	399	385	331
45°	433	390	322	276	261	334
55°	329	279	209	171	158	294
65°	222	170	112	90	88	220
75°	118	73	52	47	46	125
85°	28	14	12	12	12	32
90°	2	18	48	45	47	6
95°	72	86	88	88	86	80
105°	296	300	303	306	306	313
115°	552	560	557	556	552	546
125°	802	815	811	806	805	717
135°	1038	1053	1056	1055	1051	802
145°	1260	1270	1278	1279	1274	787
155°	1441	1445	1449	1456	1452	663
165°	1567	1566	1566	1576	1569	442
175°	1631	1627	1624	1634	1625	155
180°	1634	1634	1634	1634	1634	



TEST NUMBER: P918804

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US935-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	711.7	711.7	711.7	711.7	711.7
2.5°	714.9	711.7	704.6	711.1	709.8
5°	711.7	708.5	700.1	705.9	704.0
7.5°	705.9	702.1	693.0	695.6	692.3
10°	698.2	693.6	680.8	678.8	675.0
12.5°	688.5	682.7	665.3	661.5	654.4
15°	676.9	669.8	647.9	635.7	629.3
17.5°	663.4	653.1	626.0	611.8	601.6
20°	647.9	635.0	602.9	586.8	572.6
22.5°	631.2	616.4	579.0	557.2	547.5
25°	614.5	593.8	551.3	525.0	515.2
27.5°	594.5	572.6	525.6	495.2	480.4
30°	573.3	548.7	497.2	464.4	446.9
32.5°	552.6	523.0	470.2	431.5	415.4
35°	529.4	496.6	440.0	399.3	385.1
37.5°	506.9	471.4	411.6	367.1	351.0
40°	483.0	444.4	381.9	336.2	319.4
42.5°	458.6	417.4	352.3	304.6	288.6
45°	432.8	389.6	322.1	276.3	260.8
47.5°	408.4	362.7	293.1	247.3	233.2
50°	381.3	335.6	264.8	220.2	206.8
52.5°	354.8	306.5	237.6	195.2	183.0
55°	329.1	278.9	209.3	170.7	158.4
57.5°	302.7	251.2	184.3	148.2	137.8
60°	275.7	224.1	157.8	125.0	114.7
62.5°	249.3	197.8	135.3	104.4	99.2
65°	222.2	170.0	112.1	90.2	88.3
67.5°	196.5	144.2	90.2	79.2	77.3
70°	169.4	119.2	74.6	68.3	65.7
72.5°	143.6	95.9	62.4	57.3	56.1
75°	118.5	73.4	51.5	47.0	46.4
77.5°	93.4	52.2	40.6	38.0	36.7
80°	70.2	37.4	30.9	28.3	28.3
82.5°	48.9	25.1	21.3	20.0	20.0
85°	27.6	14.1	12.2	12.2	12.2
87.5°	10.3	5.2	5.2	4.5	4.5
90°	1.5	17.7	48.3	45.3	46.8
92.5°	30.6	41.4	42.9	44.3	44.3
95°	71.9	85.7	88.2	88.2	85.7
97.5°	119.7	132.5	137.9	137.9	137.9
100°	174.9	186.1	190.1	190.1	188.6
102.5°	233.0	241.3	246.8	248.2	246.8
105°	296.5	300.5	303.4	305.9	305.9
107.5°	359.6	365.5	365.5	366.4	359.6
110°	420.7	428.5	428.5	428.5	424.6



TEST NUMBER: P918804

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US935-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	486.6	495.0	493.5	489.6	486.6
115°	551.6	559.6	557.1	555.6	551.6
117.5°	616.2	627.1	620.1	616.2	612.3
120°	681.2	692.1	681.2	681.2	676.7
122.5°	740.3	754.1	747.2	743.3	740.3
125°	802.4	814.7	810.7	806.3	804.9
127.5°	863.0	878.2	872.8	866.9	863.0
130°	919.6	937.4	934.9	931.9	926.5
132.5°	983.2	996.9	997.9	991.0	987.0
135°	1037.8	1053.1	1056.0	1054.6	1050.6
137.5°	1098.9	1111.2	1113.7	1112.7	1106.8
140°	1152.6	1164.9	1171.8	1171.8	1166.4
142.5°	1207.7	1220.0	1224.0	1225.5	1220.0
145°	1260.0	1269.8	1277.7	1279.2	1273.8
147.5°	1306.7	1319.0	1325.0	1327.4	1322.0
150°	1355.0	1363.4	1368.8	1373.2	1368.8
152.5°	1397.8	1406.3	1413.2	1418.6	1413.2
155°	1440.7	1444.7	1449.1	1456.0	1451.6
157.5°	1477.6	1480.7	1483.1	1493.0	1486.1
160°	1510.7	1513.6	1515.1	1523.4	1517.6
162.5°	1541.2	1541.2	1542.6	1552.0	1545.1
165°	1567.3	1565.8	1565.8	1575.7	1568.8
167.5°	1591.0	1586.6	1586.6	1596.4	1589.5
170°	1608.7	1604.7	1603.3	1613.1	1604.7
172.5°	1621.0	1617.0	1615.6	1625.4	1617.0
175°	1630.8	1626.9	1623.9	1633.8	1625.4
177.5°	1636.2	1632.4	1629.4	1637.7	1629.4
180°	1633.8	1633.8	1633.8	1633.8	1633.8



TEST NUMBER: P918804
 CATALOG NUMBER: DFN2DIP-HX2F0-020D060US935-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.72	6.38	6.88	7.52	9.12	1.71	2.36	2.86	3.50	5.10
	3H	7.36	7.95	8.52	9.09	10.71	2.86	3.45	4.03	4.60	6.21
	4H	7.94	8.50	9.11	9.65	11.27	3.29	3.85	4.46	5.00	6.62
	6H	8.34	8.85	9.51	10.00	11.63	3.59	4.10	4.77	5.25	6.88
	8H	8.45	8.93	9.63	10.10	11.72	3.67	4.16	4.85	5.32	6.94
	12H	8.49	8.95	9.67	10.11	11.75	3.70	4.16	4.88	5.32	6.96
4H	2H	5.71	6.27	6.89	7.42	9.04	2.27	2.82	3.44	3.97	5.59
	3H	7.50	7.96	8.68	9.14	10.76	3.58	4.04	4.76	5.22	6.85
	4H	8.16	8.59	9.35	9.75	11.40	4.11	4.53	5.29	5.69	7.34
	6H	8.65	9.01	9.83	10.20	11.83	4.50	4.86	5.68	6.05	7.68
	8H	8.80	9.14	9.99	10.32	11.97	4.61	4.95	5.80	6.13	7.78
	12H	8.88	9.19	10.08	10.37	12.03	4.66	4.97	5.86	6.15	7.81
8H	4H	8.11	8.46	9.30	9.63	11.28	4.36	4.70	5.54	5.87	7.53
	6H	8.65	8.93	9.85	10.15	11.80	4.85	5.13	6.05	6.34	7.99
	8H	8.85	9.09	10.06	10.29	11.96	5.02	5.27	6.23	6.46	8.13
	12H	8.96	9.17	10.17	10.37	12.07	5.12	5.33	6.33	6.53	8.23
12H	4H	8.06	8.37	9.26	9.55	11.21	4.35	4.66	5.55	5.85	7.50
	6H	8.62	8.87	9.83	10.06	11.73	4.89	5.13	6.10	6.33	8.00
	8H	8.82	9.03	10.03	10.22	11.93	5.08	5.29	6.29	6.48	8.18