

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919043

Luminaire Tested: DFN2DIP-HX3F0-090D060US935-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919043
REPORT IS A COMBINATION OF REPORTS P900775 AND P897645
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-090D060US935-FLLONL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12785.8 lumens
Efficiency: N/A
Efficacy: 92.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 138
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919043
CATALOG NUMBER: DFN2DIP-HX3F0-090D060US935-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P919043

CATALOG NUMBER: DFN2DIP-HX3F0-090D060US935-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60			
1	100	96	92	88	93	90	86	83	78	75	73	67	66	64	58	56	55	51			
2	91	84	77	72	85	78	73	68	68	64	61	59	56	53	51	49	47	42			
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40	36			
4	76	65	57	51	71	61	54	48	54	48	44	47	42	39	40	37	34	31			
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30	27			
6	64	52	44	38	60	49	42	36	43	37	33	38	33	30	33	29	26	24			
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23	21			
8	55	43	35	30	52	40	33	28	36	30	26	32	27	23	28	24	21	19			
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19	17			
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17	15			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3493	3493	3493
5°	3497	3442	3465
10°	3467	3393	3416
15°	3414	3334	3341
20°	3344	3254	3264
25°	3274	3159	3176
30°	3186	3070	3063
35°	3103	2966	2945
40°	3001	2861	2832
45°	2899	2755	2716
50°	2788	2643	2582
55°	2671	2515	2459
60°	2539	2362	2317
65°	2394	2204	2150
70°	2211	2011	1970
75°	1957	1780	1801
80°	1650	1484	1483
85°	1170	982	962

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2899 cd/sqm



TEST NUMBER: P919043

CATALOG NUMBER: DFN2DIP-HX3F0-090D060US935-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	283.8	2.2
10°-20°	798.5	6.2
20°-30°	1173.4	9.2
30°-40°	1362.9	10.7
40°-50°	1361.2	10.6
50°-60°	1186.9	9.3
60°-70°	877.4	6.9
70°-80°	496.4	3.9
80°-90°	134.1	1.0
90°-100°	57.5	0.4
100°-110°	214.3	1.7
110°-120°	568.4	4.4
120°-130°	942.7	7.4
130°-140°	1001.4	7.8
140°-150°	930.7	7.3
150°-160°	748.2	5.9
160°-170°	482.1	3.8
170°-180°	165.9	1.3
0°-30°	2255.7	17.6
0°-40°	3618.6	28.3
0°-60°	6166.7	48.2
0°-90°	7674.6	60.0
90°-120°	840.2	6.6
90°-150°	3714.9	29.1
90°-180°	5111.0	40.0
0°-180°	12785.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3015	3015	3015	3015	3015	
5°	3015	3004	2972	2995	2989	286
15°	2870	2853	2815	2827	2812	808
25°	2598	2575	2526	2531	2526	1195
35°	2241	2212	2166	2148	2134	1400
45°	1824	1804	1760	1728	1716	1408
55°	1380	1363	1328	1293	1279	1234
65°	931	913	884	858	844	920
75°	487	481	467	449	455	520
85°	119	116	113	104	102	132
90°	1	15	25	32	34	12
95°	82	40	49	56	54	97
105°	384	421	77	91	96	410
115°	725	747	778	194	104	714
125°	1026	1042	1066	1075	1079	915
135°	1269	1289	1301	1313	1311	980
145°	1472	1471	1492	1501	1495	921
155°	1621	1610	1625	1632	1622	747
165°	1708	1701	1704	1713	1704	483
175°	1747	1738	1741	1750	1737	166
180°	1743	1743	1743	1743	1743	



TEST NUMBER: P919043

CATALOG NUMBER: DFN2DIP-HX3F0-090D060US935-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3015.1	3015.1	3015.1	3015.1	3015.1
2.5°	3032.7	3018.2	2986.3	3015.1	3009.6
5°	3015.1	3003.8	2971.8	2994.9	2989.3
7.5°	2994.9	2977.7	2945.6	2969.1	2963.2
10°	2963.2	2942.9	2908.1	2931.2	2922.6
12.5°	2919.5	2902.3	2867.6	2881.9	2876.2
15°	2870.3	2853.1	2815.2	2826.9	2812.4
17.5°	2809.3	2792.1	2754.3	2768.8	2754.3
20°	2742.6	2725.4	2684.8	2693.4	2682.0
22.5°	2676.2	2650.1	2612.2	2612.2	2606.3
25°	2597.7	2574.6	2525.5	2531.0	2525.5
27.5°	2510.7	2490.4	2452.9	2444.3	2429.8
30°	2424.0	2400.5	2357.2	2348.5	2336.9
32.5°	2331.1	2313.8	2267.4	2249.9	2238.2
35°	2241.3	2212.3	2165.8	2148.4	2133.9
37.5°	2139.8	2113.6	2067.1	2046.9	2032.4
40°	2035.4	2012.1	1965.6	1939.7	1928.1
42.5°	1933.9	1910.6	1864.4	1835.2	1818.0
45°	1823.8	1803.5	1759.8	1728.1	1716.5
47.5°	1716.5	1696.2	1649.7	1617.7	1600.5
50°	1603.3	1588.8	1548.2	1507.6	1493.1
52.5°	1493.1	1472.8	1435.3	1403.3	1383.0
55°	1380.3	1362.7	1327.9	1293.2	1278.8
57.5°	1267.0	1252.6	1214.8	1180.0	1168.3
60°	1153.8	1142.5	1101.8	1069.9	1061.3
62.5°	1043.7	1023.4	994.5	965.6	953.9
65°	930.8	913.3	884.3	858.2	843.8
67.5°	814.8	800.1	774.2	754.0	742.3
70°	707.5	695.8	669.7	649.4	638.0
72.5°	597.4	585.7	571.2	551.0	542.3
75°	487.0	481.4	466.7	449.4	455.3
77.5°	388.5	376.9	371.0	362.4	353.8
80°	290.1	287.0	281.1	272.5	266.7
82.5°	197.2	197.2	194.4	182.7	182.7
85°	118.7	116.0	113.2	104.3	101.5
87.5°	52.3	46.4	40.6	32.0	28.9
90°	1.2	15.2	25.1	31.6	34.0
92.5°	31.6	26.5	30.2	32.8	34.0
95°	82.0	40.3	49.2	55.6	54.2
97.5°	147.6	44.2	64.2	68.2	69.4
100°	223.3	50.5	71.9	82.0	84.5
102.5°	306.5	304.1	74.5	88.3	92.1
105°	383.5	421.4	77.0	90.7	95.9
107.5°	473.1	504.5	79.6	93.3	98.4
110°	559.0	585.3	220.8	94.7	99.6



TEST NUMBER: P919043

CATALOG NUMBER: DFN2DIP-HX3F0-090D060US935-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	639.6	662.3	640.8	97.0	101.0
115°	725.4	746.8	778.4	194.3	103.5
117.5°	799.8	825.0	846.5	666.1	335.5
120°	883.1	902.0	924.8	939.9	769.6
122.5°	953.6	973.9	999.2	1006.7	1008.1
125°	1025.6	1042.1	1066.0	1074.9	1078.6
127.5°	1091.2	1108.9	1127.9	1140.5	1141.7
130°	1153.0	1173.3	1187.1	1201.0	1199.8
132.5°	1216.2	1232.6	1246.4	1257.7	1256.5
135°	1269.2	1289.4	1300.6	1313.4	1310.8
137.5°	1324.6	1339.7	1352.5	1365.0	1361.3
140°	1378.8	1389.0	1402.8	1414.2	1407.9
142.5°	1424.3	1433.2	1449.6	1459.6	1453.3
145°	1472.3	1470.9	1492.4	1501.2	1495.0
147.5°	1513.8	1510.0	1531.5	1537.7	1532.8
150°	1554.3	1545.4	1565.6	1573.1	1566.8
152.5°	1588.3	1578.2	1597.1	1604.7	1595.9
155°	1621.1	1609.8	1625.0	1632.5	1622.4
157.5°	1647.6	1637.5	1648.9	1657.8	1647.6
160°	1670.3	1662.7	1670.3	1677.8	1669.0
162.5°	1690.4	1682.9	1689.2	1698.1	1686.7
165°	1708.1	1700.6	1704.3	1713.2	1704.3
167.5°	1722.0	1714.4	1718.3	1727.2	1715.7
170°	1733.4	1725.8	1728.4	1737.1	1725.8
172.5°	1740.9	1733.4	1735.9	1744.8	1733.4
175°	1747.2	1738.4	1740.9	1749.7	1737.1
177.5°	1749.7	1740.9	1742.2	1751.1	1739.7
180°	1743.4	1743.4	1743.4	1743.4	1743.4



TEST NUMBER: P919043
 CATALOG NUMBER: DFN2DIP-HX3F0-090D060US935-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.45	13.41	13.32	14.30	15.42	12.02	12.98	12.89	13.87	14.99
	3H	14.11	14.97	14.99	15.87	17.01	13.64	14.50	14.52	15.40	16.55
	4H	14.70	15.51	15.59	16.41	17.57	14.23	15.04	15.12	15.95	17.10
	6H	15.10	15.85	16.00	16.76	17.93	14.63	15.38	15.53	16.29	17.46
	8H	15.20	15.92	16.11	16.84	18.01	14.73	15.45	15.65	16.37	17.54
	12H	15.25	15.93	16.17	16.85	18.05	14.77	15.46	15.69	16.38	17.57
4H	2H	12.92	13.73	13.82	14.64	15.79	12.58	13.39	13.48	14.29	15.45
	3H	14.79	15.47	15.70	16.40	17.57	14.40	15.08	15.31	16.01	17.18
	4H	15.50	16.12	16.42	17.05	18.25	15.10	15.72	16.02	16.65	17.84
	6H	16.01	16.55	16.95	17.50	18.70	15.61	16.14	16.54	17.10	18.29
	8H	16.16	16.66	17.10	17.61	18.82	15.75	16.25	16.69	17.20	18.41
	12H	16.23	16.69	17.19	17.65	18.87	15.82	16.27	16.78	17.23	18.45
8H	4H	15.70	16.20	16.64	17.15	18.36	15.34	15.84	16.28	16.79	18.00
	6H	16.33	16.74	17.29	17.73	18.94	15.97	16.38	16.93	17.37	18.58
	8H	16.54	16.91	17.52	17.89	19.12	16.18	16.54	17.15	17.52	18.75
	12H	16.67	17.00	17.65	17.97	19.24	16.29	16.62	17.27	17.59	18.87
12H	4H	15.69	16.14	16.65	17.11	18.32	15.34	15.79	16.30	16.76	17.97
	6H	16.36	16.72	17.33	17.70	18.93	16.01	16.37	16.98	17.35	18.58
	8H	16.60	16.92	17.57	17.89	19.17	16.24	16.57	17.22	17.54	18.81