

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918847

Luminaire Tested: DFN2DIP-HX2F0-050D020US935-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918847
REPORT IS A COMBINATION OF REPORTS P900677 AND P897595
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-050D020US935-FLLONL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5966.7 lumens
Efficiency: N/A
Efficacy: 95.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918847

CATALOG NUMBER: DFN2DIP-HX2F0-050D020US935-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P918847

CATALOG NUMBER: DFN2DIP-HX2F0-050D020US935-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76
1	103	98	94	90	97	93	90	86	84	81	78	75	73	71	67	66	64
2	93	86	79	74	88	81	76	71	73	69	65	66	62	59	59	56	54
3	85	75	68	62	80	72	65	59	65	59	55	58	54	50	52	49	46
4	78	67	59	52	74	64	56	50	58	52	47	52	47	43	47	43	40
5	72	60	51	45	68	57	49	44	52	45	40	47	42	38	42	38	35
6	66	54	45	39	63	51	44	38	47	40	35	42	37	33	38	34	31
7	61	49	40	35	58	47	39	34	42	36	31	39	33	29	35	31	27
8	57	44	36	31	54	42	35	30	39	33	28	35	30	26	32	28	24
9	53	41	33	28	50	39	32	27	36	30	25	33	27	24	30	25	22
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	28	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3947	3947	3947
5°	3947	3882	3911
10°	3909	3821	3851
15°	3845	3748	3761
20°	3761	3652	3669
25°	3677	3538	3564
30°	3574	3432	3433
35°	3475	3307	3294
40°	3355	3182	3161
45°	3235	3055	3025
50°	3104	2922	2869
55°	2965	2768	2723
60°	2809	2588	2556
65°	2637	2398	2359
70°	2418	2168	2146
75°	2118	1891	1939
80°	1754	1540	1565
85°	1191	967	968

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3235 cd/sqm

TEST NUMBER: P918847

CATALOG NUMBER: DFN2DIP-HX2F0-050D020US935-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.7	2.6
10°-20°	443.6	7.4
20°-30°	651.9	10.9
30°-40°	757.2	12.7
40°-50°	756.2	12.7
50°-60°	659.4	11.1
60°-70°	487.4	8.2
70°-80°	275.8	4.6
80°-90°	73.8	1.2
90°-100°	19.2	0.3
100°-110°	71.4	1.2
110°-120°	189.5	3.2
120°-130°	314.2	5.3
130°-140°	333.8	5.6
140°-150°	310.2	5.2
150°-160°	249.4	4.2
160°-170°	160.7	2.7
170°-180°	55.3	0.9
0°-30°	1253.2	21.0
0°-40°	2010.3	33.7
0°-60°	3425.9	57.4
0°-90°	4263.0	71.4
90°-120°	280.0	4.7
90°-150°	1238.3	20.8
90°-180°	1704.0	28.6
0°-180°	5966.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1675	1675	1675	1675	1675	
5°	1675	1669	1651	1664	1661	159
15°	1595	1585	1564	1570	1562	449
25°	1443	1430	1403	1406	1403	664
35°	1245	1229	1203	1194	1186	778
45°	1013	1002	978	960	954	782
55°	767	757	738	718	710	686
65°	517	507	491	477	469	511
75°	270	267	259	250	253	289
85°	66	64	63	58	56	74
90°	0	5	8	10	11	6
95°	27	13	16	18	18	32
105°	128	140	26	30	32	137
115°	242	249	260	65	34	238
125°	342	347	355	358	360	305
135°	423	430	434	438	437	327
145°	491	490	498	500	498	307
155°	540	537	542	544	541	249
165°	569	567	568	571	568	161
175°	582	580	580	583	579	55
180°	581	581	581	581	581	

TEST NUMBER: P918847

CATALOG NUMBER: DFN2DIP-HX2F0-050D020US935-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1675.1	1675.1	1675.1	1675.1	1675.1
2.5°	1684.8	1676.8	1659.1	1675.1	1672.1
5°	1675.1	1668.8	1651.0	1663.8	1660.8
7.5°	1663.8	1654.2	1636.5	1649.5	1646.2
10°	1646.2	1634.9	1615.7	1628.4	1623.7
12.5°	1621.9	1612.4	1593.1	1601.1	1597.8
15°	1594.6	1585.0	1564.0	1570.5	1562.5
17.5°	1560.7	1551.2	1530.2	1538.2	1530.2
20°	1523.7	1514.2	1491.6	1496.3	1490.0
22.5°	1486.8	1472.2	1451.2	1451.2	1447.9
25°	1443.2	1430.4	1403.0	1406.1	1403.0
27.5°	1394.8	1383.5	1362.7	1357.9	1349.9
30°	1346.6	1333.7	1309.6	1304.8	1298.3
32.5°	1295.0	1285.5	1259.6	1249.9	1243.5
35°	1245.1	1229.1	1203.2	1193.5	1185.5
37.5°	1188.7	1174.2	1148.4	1137.1	1129.1
40°	1130.8	1117.8	1092.0	1077.6	1071.2
42.5°	1074.4	1061.4	1035.8	1019.5	1010.0
45°	1013.2	1001.9	977.7	960.1	953.6
47.5°	953.6	942.3	916.5	898.7	889.2
50°	890.7	882.7	860.1	837.6	829.5
52.5°	829.5	818.2	797.4	779.6	768.4
55°	766.8	757.1	737.7	718.4	710.4
57.5°	703.9	695.9	674.9	655.6	649.0
60°	641.0	634.7	612.2	594.3	589.6
62.5°	579.9	568.6	552.5	536.4	529.9
65°	517.1	507.4	491.3	476.8	468.7
67.5°	452.7	444.5	430.2	418.9	412.3
70°	393.0	386.6	372.0	360.8	354.5
72.5°	331.9	325.4	317.4	306.1	301.3
75°	270.5	267.4	259.2	249.7	253.0
77.5°	215.9	209.3	206.1	201.3	196.6
80°	161.2	159.5	156.2	151.4	148.2
82.5°	109.5	109.5	108.0	101.5	101.5
85°	66.0	64.4	62.9	57.9	56.4
87.5°	29.0	25.8	22.6	17.7	16.1
90°	0.4	5.1	8.4	10.5	11.4
92.5°	10.5	8.9	10.1	10.9	11.4
95°	27.3	13.4	16.4	18.5	18.1
97.5°	49.2	14.7	21.4	22.7	23.2
100°	74.5	16.8	23.9	27.3	28.2
102.5°	102.2	101.3	24.8	29.4	30.7
105°	127.9	140.4	25.7	30.2	31.9
107.5°	157.7	168.2	26.5	31.1	32.8
110°	186.3	195.1	73.6	31.6	33.2

TEST NUMBER: P918847

CATALOG NUMBER: DFN2DIP-HX2F0-050D020US935-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	213.2	220.8	213.6	32.4	33.7
115°	241.8	248.9	259.5	64.7	34.5
117.5°	266.6	275.0	282.1	222.1	111.8
120°	294.4	300.7	308.2	313.3	256.5
122.5°	317.9	324.6	333.0	335.5	336.0
125°	341.9	347.3	355.3	358.3	359.6
127.5°	363.8	369.6	376.0	380.1	380.6
130°	384.3	391.1	395.7	400.4	399.9
132.5°	405.4	410.9	415.4	419.2	418.9
135°	423.1	429.8	433.5	437.8	437.0
137.5°	441.5	446.6	450.8	455.0	453.7
140°	459.6	463.0	467.6	471.4	469.3
142.5°	474.8	477.8	483.2	486.5	484.4
145°	490.8	490.3	497.5	500.4	498.3
147.5°	504.6	503.3	510.5	512.6	510.9
150°	518.1	515.1	521.9	524.3	522.3
152.5°	529.4	526.1	532.4	534.9	531.9
155°	540.4	536.6	541.7	544.2	540.8
157.5°	549.2	545.9	549.7	552.6	549.2
160°	556.8	554.2	556.8	559.3	556.4
162.5°	563.4	560.9	563.1	566.0	562.2
165°	569.4	566.9	568.1	571.1	568.1
167.5°	574.0	571.4	572.7	575.7	571.9
170°	577.8	575.2	576.1	579.0	575.2
172.5°	580.3	577.8	578.7	581.6	577.8
175°	582.4	579.5	580.3	583.2	579.0
177.5°	583.2	580.3	580.7	583.7	579.9
180°	581.2	581.2	581.2	581.2	581.2

TEST NUMBER: P918847

CATALOG NUMBER: DFN2DIP-HX2F0-050D020US935-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.68	14.78	14.43	15.55	16.48	13.26	14.36	14.01	15.13	16.05
	3H	15.34	16.32	16.10	17.10	18.06	14.88	15.86	15.64	16.64	17.60
	4H	15.92	16.85	16.70	17.63	18.61	15.46	16.39	16.24	17.18	18.15
	6H	16.31	17.17	17.10	17.96	18.95	15.85	16.71	16.64	17.51	18.49
	8H	16.41	17.23	17.21	18.04	19.03	15.95	16.77	16.76	17.59	18.57
	12H	16.46	17.24	17.27	18.05	19.06	16.00	16.78	16.81	17.59	18.60
4H	2H	14.16	15.09	14.95	15.88	16.85	13.83	14.75	14.61	15.54	16.51
	3H	16.02	16.80	16.82	17.62	18.61	15.64	16.41	16.43	17.24	18.22
	4H	16.72	17.43	17.53	18.25	19.27	16.33	17.04	17.14	17.86	18.87
	6H	17.23	17.84	18.06	18.69	19.71	16.83	17.45	17.66	18.29	19.31
	8H	17.37	17.94	18.20	18.79	19.82	16.98	17.55	17.81	18.39	19.42
	12H	17.45	17.96	18.30	18.82	19.86	17.04	17.55	17.89	18.42	19.46
8H	4H	16.93	17.50	17.76	18.34	19.38	16.58	17.15	17.41	17.99	19.02
	6H	17.54	18.01	18.40	18.90	19.93	17.19	17.66	18.05	18.55	19.58
	8H	17.75	18.17	18.62	19.05	20.10	17.39	17.81	18.26	18.69	19.74
	12H	17.87	18.24	18.75	19.11	20.22	17.50	17.88	18.38	18.75	19.85
12H	4H	16.92	17.44	17.77	18.30	19.34	16.58	17.09	17.43	17.96	19.00
	6H	17.57	17.99	18.44	18.87	19.92	17.23	17.65	18.10	18.53	19.58
	8H	17.80	18.17	18.67	19.04	20.15	17.46	17.83	18.33	18.70	19.80