

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918856

Luminaire Tested: DFN2DIP-HX2F0-050D040US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918856
REPORT IS A COMBINATION OF REPORTS P899178 AND P896039
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-050D040US935-RLLFLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6707.2 lumens
Efficiency: N/A
Efficacy: 87.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 76.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918856

CATALOG NUMBER: DFN2DIP-HX2F0-050D040US935-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P918856

CATALOG NUMBER: DFN2DIP-HX2F0-050D040US935-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	54	53	52
2	91	84	78	73	84	78	73	69	67	63	60	57	55	52	48	46	45
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	41	39
4	76	66	58	52	71	62	55	50	54	48	44	46	42	39	39	36	34
5	70	59	51	45	65	55	48	43	48	43	38	42	37	34	35	32	30
6	65	53	45	40	60	50	43	38	44	38	34	38	33	30	32	29	26
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	26	24
8	56	44	36	31	52	41	34	30	36	31	27	32	27	24	27	24	21
9	52	40	33	28	49	38	31	27	34	28	24	29	25	22	25	22	19
10	49	37	30	25	46	35	28	24	31	26	22	27	23	20	24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4192	4192	4192
5°	4192	4116	4144
10°	4144	4025	4002
15°	4080	3882	3786
20°	3998	3690	3525
25°	3914	3476	3272
30°	3803	3257	2954
35°	3694	3023	2675
40°	3583	2782	2357
45°	3455	2516	2069
50°	3322	2248	1788
55°	3182	1963	1518
60°	3020	1667	1242
65°	2832	1368	1110
70°	2606	1088	994
75°	2320	940	889
80°	1910	761	749
85°	1249	470	525

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3455 cd/sqm

TEST NUMBER: P918856

CATALOG NUMBER: DFN2DIP-HX2F0-050D040US935-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.8	2.5
10°-20°	457.8	6.8
20°-30°	642.7	9.6
30°-40°	700.6	10.4
40°-50°	643.9	9.6
50°-60°	505.7	7.5
60°-70°	329.2	4.9
70°-80°	169.5	2.5
80°-90°	46.4	0.7
90°-100°	67.4	1.0
100°-110°	214.2	3.2
110°-120°	366.5	5.5
120°-130°	482.0	7.2
130°-140°	541.0	8.1
140°-150°	530.5	7.9
150°-160°	445.0	6.6
160°-170°	295.1	4.4
170°-180°	103.2	1.5
0°-30°	1267.2	18.9
0°-40°	1967.8	29.3
0°-60°	3117.4	46.5
0°-90°	3662.4	54.6
90°-120°	648.0	9.7
90°-150°	2201.5	32.8
90°-180°	3045.0	45.4
0°-180°	6707.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1779	1779	1779	1779	1779	
5°	1779	1771	1750	1765	1760	169
15°	1692	1675	1620	1589	1573	477
25°	1536	1484	1378	1312	1288	706
35°	1324	1242	1100	998	963	828
45°	1082	974	805	691	652	836
55°	823	697	523	427	396	735
65°	556	425	280	226	221	551
75°	296	184	129	118	116	313
85°	69	35	31	31	31	79
90°	1	12	32	30	31	7
95°	48	57	59	59	57	53
105°	198	200	202	204	204	209
115°	368	373	371	370	368	364
125°	535	543	540	538	537	478
135°	692	702	704	703	700	535
145°	840	846	852	853	849	525
155°	960	963	966	971	968	442
165°	1045	1044	1044	1050	1046	295
175°	1087	1085	1083	1089	1084	103
180°	1089	1089	1089	1089	1089	

TEST NUMBER: P918856

CATALOG NUMBER: DFN2DIP-HX2F0-050D040US935-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1779.3	1779.3	1779.3	1779.3	1779.3
2.5°	1787.3	1779.3	1761.5	1777.7	1774.4
5°	1779.3	1771.2	1750.2	1764.7	1760.0
7.5°	1764.7	1755.1	1732.6	1739.0	1730.9
10°	1745.4	1734.1	1702.0	1697.1	1687.5
12.5°	1721.3	1706.8	1663.3	1653.7	1635.9
15°	1692.3	1674.6	1619.9	1589.3	1573.2
17.5°	1658.5	1632.7	1565.0	1529.6	1503.8
20°	1619.9	1587.6	1507.1	1467.0	1431.4
22.5°	1578.0	1540.9	1447.5	1392.8	1368.7
25°	1536.1	1484.5	1378.3	1312.3	1288.1
27.5°	1486.3	1431.4	1313.9	1238.2	1201.2
30°	1433.1	1371.8	1243.0	1161.0	1117.4
32.5°	1381.6	1307.4	1175.5	1078.8	1038.5
35°	1323.6	1241.5	1099.8	998.3	962.9
37.5°	1267.2	1178.6	1029.0	917.7	877.6
40°	1207.6	1111.1	954.8	840.5	798.7
42.5°	1146.5	1043.4	880.8	761.6	721.4
45°	1082.1	974.1	805.1	690.7	652.0
47.5°	1020.9	906.6	732.7	618.3	582.9
50°	953.3	839.0	661.8	550.6	516.9
52.5°	887.2	766.4	594.2	487.9	457.4
55°	822.8	697.1	523.2	426.7	396.1
57.5°	756.8	628.0	460.5	370.4	344.6
60°	689.1	560.3	394.4	312.5	286.6
62.5°	623.2	494.4	338.1	260.9	248.1
65°	555.5	425.1	280.2	225.5	220.6
67.5°	491.1	360.7	225.5	198.0	193.2
70°	423.5	297.9	186.8	170.6	164.2
72.5°	359.1	239.9	156.2	143.4	140.1
75°	296.3	183.5	128.8	117.5	116.0
77.5°	233.5	130.4	101.5	95.0	91.7
80°	175.5	93.4	77.2	70.9	70.9
82.5°	122.3	62.9	53.1	49.9	49.9
85°	69.2	35.4	30.6	30.6	30.6
87.5°	25.8	12.8	12.8	11.3	11.3
90°	0.9	11.8	32.2	30.2	31.2
92.5°	20.3	27.6	28.6	29.5	29.5
95°	48.0	57.2	58.8	58.8	57.2
97.5°	79.8	88.3	92.0	92.0	92.0
100°	116.6	124.2	126.7	126.7	125.8
102.5°	155.3	160.9	164.5	165.5	164.5
105°	197.7	200.3	202.2	203.9	203.9
107.5°	239.7	243.7	243.7	244.3	239.7
110°	280.4	285.7	285.7	285.7	283.1



TEST NUMBER: P918856

CATALOG NUMBER: DFN2DIP-HX2F0-050D040US935-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	324.4	330.0	329.0	326.4	324.4
115°	367.7	373.1	371.3	370.4	367.7
117.5°	410.8	418.0	413.5	410.8	408.2
120°	454.2	461.3	454.2	454.2	451.2
122.5°	493.5	502.7	498.2	495.5	493.5
125°	534.9	543.1	540.5	537.5	536.6
127.5°	575.3	585.5	581.9	577.9	575.3
130°	613.0	624.9	623.3	621.3	617.7
132.5°	655.4	664.6	665.3	660.6	658.1
135°	691.9	702.1	704.0	703.0	700.4
137.5°	732.6	740.8	742.4	741.7	737.9
140°	768.4	776.6	781.2	781.2	777.6
142.5°	805.2	813.4	816.0	817.0	813.4
145°	840.0	846.5	851.8	852.8	849.2
147.5°	871.2	879.3	883.3	884.9	881.3
150°	903.4	909.0	912.6	915.5	912.6
152.5°	931.9	937.5	942.1	945.7	942.1
155°	960.4	963.1	966.0	970.7	967.7
157.5°	985.2	987.0	988.7	995.3	990.7
160°	1007.1	1009.1	1010.0	1015.6	1011.7
162.5°	1027.4	1027.4	1028.5	1034.7	1030.1
165°	1044.9	1043.9	1043.9	1050.4	1045.9
167.5°	1060.7	1057.6	1057.6	1064.3	1059.6
170°	1072.5	1069.8	1068.8	1075.4	1069.8
172.5°	1080.6	1078.1	1077.0	1083.7	1078.1
175°	1087.3	1084.6	1082.6	1089.2	1083.7
177.5°	1090.9	1088.2	1086.2	1091.8	1086.2
180°	1089.2	1089.2	1089.2	1089.2	1089.2

TEST NUMBER: P918856

CATALOG NUMBER: DFN2DIP-HX2F0-050D040US935-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.41	13.28	13.33	14.21	15.42	8.39	9.26	9.31	10.20	11.40
	3H	14.06	14.84	15.00	15.79	17.02	9.57	10.34	10.50	11.29	12.52
	4H	14.66	15.39	15.61	16.34	17.58	10.01	10.74	10.96	11.69	12.93
	6H	15.06	15.74	16.02	16.69	17.95	10.31	10.99	11.28	11.95	13.20
	8H	15.18	15.82	16.14	16.79	18.04	10.40	11.04	11.37	12.01	13.26
	12H	15.23	15.84	16.20	16.81	18.08	10.44	11.05	11.41	12.01	13.29
4H	2H	12.43	13.16	13.38	14.11	15.35	8.98	9.71	9.93	10.66	11.90
	3H	14.23	14.84	15.20	15.82	17.08	10.31	10.92	11.28	11.90	13.16
	4H	14.91	15.46	15.88	16.44	17.72	10.85	11.40	11.82	12.38	13.66
	6H	15.40	15.88	16.39	16.88	18.15	11.25	11.73	12.24	12.73	14.00
	8H	15.56	16.01	16.55	17.00	18.29	11.37	11.82	12.36	12.81	14.10
	12H	15.64	16.05	16.65	17.06	18.35	11.43	11.83	12.43	12.84	14.13
8H	4H	14.87	15.32	15.86	16.31	17.60	11.11	11.56	12.10	12.55	13.84
	6H	15.41	15.78	16.43	16.82	18.10	11.61	11.98	12.62	13.01	14.30
	8H	15.61	15.94	16.63	16.96	18.27	11.79	12.11	12.81	13.13	14.44
	12H	15.74	16.02	16.76	17.04	18.39	11.90	12.18	12.92	13.20	14.55
12H	4H	14.83	15.23	15.83	16.24	17.53	11.12	11.52	12.12	12.53	13.82
	6H	15.39	15.71	16.41	16.73	18.04	11.65	11.98	12.67	13.00	14.31
	8H	15.59	15.88	16.62	16.89	18.25	11.85	12.14	12.87	13.15	14.50