

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921663

Luminaire Tested: DFN2DIP-HX3F0-050D030US940-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921663
REPORT IS A COMBINATION OF REPORTS P900725 AND P897645
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-050D030US940-FLLONL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7062.4 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 67.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921663

CATALOG NUMBER: DFN2DIP-HX3F0-050D030US940-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P921663

CATALOG NUMBER: DFN2DIP-HX3F0-050D030US940-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57
2	92	84	78	72	86	79	73	69	69	65	62	61	58	55	53	50	48
3	84	74	66	60	78	70	63	57	61	56	52	54	50	46	47	44	41
4	77	65	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35
5	70	58	50	44	66	55	48	42	49	43	38	43	38	34	38	34	31
6	65	53	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27
7	60	47	39	34	56	45	38	32	40	34	30	35	31	27	31	27	24
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22
9	52	40	32	27	49	37	30	26	34	28	24	30	25	22	27	23	20
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2010	2010	2010
5°	2012	1980	1994
10°	1995	1952	1966
15°	1964	1919	1922
20°	1924	1873	1878
25°	1884	1818	1827
30°	1833	1767	1763
35°	1785	1707	1694
40°	1727	1646	1629
45°	1668	1585	1563
50°	1604	1521	1486
55°	1537	1447	1415
60°	1461	1359	1333
65°	1378	1268	1237
70°	1272	1157	1134
75°	1126	1024	1036
80°	949	854	853
85°	673	565	553

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1668 cd/sqm

TEST NUMBER: P921663

CATALOG NUMBER: DFN2DIP-HX3F0-050D030US940-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.3	2.3
10°-20°	459.4	6.5
20°-30°	675.2	9.6
30°-40°	784.2	11.1
40°-50°	783.2	11.1
50°-60°	682.9	9.7
60°-70°	504.8	7.1
70°-80°	285.6	4.0
80°-90°	77.0	1.1
90°-100°	29.8	0.4
100°-110°	111.0	1.6
110°-120°	294.3	4.2
120°-130°	488.2	6.9
130°-140°	518.5	7.3
140°-150°	481.9	6.8
150°-160°	387.5	5.5
160°-170°	249.7	3.5
170°-180°	85.9	1.2
0°-30°	1297.9	18.4
0°-40°	2082.0	29.5
0°-60°	3548.1	50.2
0°-90°	4415.6	62.5
90°-120°	435.1	6.2
90°-150°	1923.7	27.2
90°-180°	2647.0	37.5
0°-180°	7062.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1735	1735	1735	1735	1735	
5°	1735	1728	1710	1723	1720	165
15°	1651	1642	1620	1627	1618	465
25°	1495	1481	1453	1456	1453	688
35°	1290	1273	1246	1236	1228	805
45°	1049	1038	1012	994	988	810
55°	794	784	764	744	736	710
65°	536	526	509	494	485	530
75°	280	277	268	259	262	299
85°	68	67	65	60	58	76
90°	1	8	13	16	18	7
95°	42	21	25	29	28	50
105°	199	218	40	47	50	212
115°	376	387	403	101	54	370
125°	531	540	552	557	559	474
135°	657	668	674	680	679	508
145°	762	762	773	777	774	477
155°	840	834	841	845	840	387
165°	884	881	883	887	883	250
175°	905	900	902	906	900	86
180°	903	903	903	903	903	

TEST NUMBER: P921663

CATALOG NUMBER: DFN2DIP-HX3F0-050D030US940-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1734.8	1734.8	1734.8	1734.8	1734.8
2.5°	1744.9	1736.6	1718.2	1734.8	1731.7
5°	1734.8	1728.3	1709.9	1723.1	1720.0
7.5°	1723.1	1713.2	1694.9	1708.3	1705.0
10°	1705.0	1693.3	1673.3	1686.5	1681.6
12.5°	1679.8	1669.9	1649.9	1658.2	1654.8
15°	1651.4	1641.5	1619.8	1626.6	1618.2
17.5°	1616.4	1606.5	1584.7	1593.0	1584.7
20°	1578.1	1568.2	1544.8	1549.7	1543.2
22.5°	1539.8	1524.7	1503.0	1503.0	1499.6
25°	1494.7	1481.4	1453.0	1456.3	1453.0
27.5°	1444.6	1432.9	1411.3	1406.3	1398.0
30°	1394.6	1381.3	1356.3	1351.3	1344.6
32.5°	1341.2	1331.3	1304.6	1294.5	1287.8
35°	1289.5	1272.9	1246.2	1236.1	1227.8
37.5°	1231.1	1216.1	1189.4	1177.7	1169.4
40°	1171.2	1157.7	1131.0	1116.1	1109.4
42.5°	1112.8	1099.3	1072.7	1055.9	1046.0
45°	1049.4	1037.7	1012.5	994.3	987.6
47.5°	987.6	975.9	949.2	930.8	920.9
50°	922.5	914.2	890.8	867.5	859.1
52.5°	859.1	847.4	825.8	807.4	795.8
55°	794.2	784.1	764.0	744.0	735.8
57.5°	729.0	720.7	698.9	678.9	672.2
60°	663.9	657.4	634.0	615.5	610.6
62.5°	600.6	588.9	572.2	555.5	548.8
65°	535.6	525.5	508.8	493.8	485.4
67.5°	468.9	460.4	445.5	433.8	427.0
70°	407.1	400.4	385.3	373.6	367.1
72.5°	343.8	337.0	328.7	317.0	312.0
75°	280.2	277.0	268.5	258.6	262.0
77.5°	223.6	216.8	213.5	208.5	203.6
80°	166.9	165.1	161.8	156.9	153.5
82.5°	113.4	113.4	111.8	105.1	105.1
85°	68.3	66.7	65.1	60.0	58.4
87.5°	30.1	26.8	23.4	18.4	16.7
90°	0.6	7.8	13.0	16.4	17.6
92.5°	16.4	13.7	15.7	17.0	17.6
95°	42.4	20.9	25.4	28.8	28.1
97.5°	76.4	22.9	33.3	35.3	35.9
100°	115.7	26.1	37.3	42.4	43.8
102.5°	158.7	157.5	38.5	45.7	47.7
105°	198.6	218.2	39.9	47.0	49.7
107.5°	245.0	261.3	41.2	48.3	51.0
110°	289.4	303.1	114.3	49.0	51.6

TEST NUMBER: P921663

CATALOG NUMBER: DFN2DIP-HX3F0-050D030US940-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	331.3	343.0	331.9	50.3	52.3
115°	375.6	386.7	403.1	100.6	53.6
117.5°	414.2	427.2	438.4	344.9	173.8
120°	457.3	467.1	478.8	486.7	398.5
122.5°	493.8	504.4	517.5	521.3	522.0
125°	531.1	539.6	552.1	556.6	558.6
127.5°	565.1	574.2	584.1	590.6	591.2
130°	597.1	607.6	614.7	621.9	621.3
132.5°	629.7	638.3	645.4	651.3	650.7
135°	657.2	667.7	673.5	680.1	678.8
137.5°	685.9	693.8	700.3	706.9	704.9
140°	714.0	719.3	726.4	732.3	729.1
142.5°	737.6	742.2	750.6	755.8	752.6
145°	762.4	761.7	772.8	777.4	774.1
147.5°	783.9	781.9	793.1	796.3	793.7
150°	804.9	800.3	810.7	814.6	811.4
152.5°	822.4	817.3	827.1	831.0	826.4
155°	839.5	833.7	841.4	845.3	840.2
157.5°	853.2	848.0	853.9	858.4	853.2
160°	865.0	861.0	865.0	868.9	864.2
162.5°	875.4	871.5	874.8	879.3	873.4
165°	884.5	880.7	882.6	887.2	882.6
167.5°	891.7	887.8	889.7	894.4	888.5
170°	897.6	893.7	895.0	899.6	893.7
172.5°	901.5	897.6	898.9	903.5	897.6
175°	904.7	900.2	901.5	906.1	899.6
177.5°	906.1	901.5	902.2	906.8	900.9
180°	902.9	902.9	902.9	902.9	902.9

TEST NUMBER: P921663

CATALOG NUMBER: DFN2DIP-HX3F0-050D030US940-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.73	11.72	11.58	12.58	13.67	10.31	11.29	11.15	12.16	13.24
	3H	12.40	13.28	13.25	14.16	15.26	11.93	12.81	12.78	13.69	14.79
	4H	12.99	13.82	13.86	14.70	15.82	12.52	13.35	13.39	14.23	15.35
	6H	13.39	14.16	14.27	15.04	16.18	12.91	13.69	13.80	14.57	15.70
	8H	13.49	14.23	14.38	15.13	16.26	13.02	13.76	13.91	14.66	15.79
	12H	13.54	14.24	14.44	15.14	16.30	13.06	13.77	13.96	14.66	15.82
4H	2H	11.21	12.05	12.08	12.93	14.04	10.87	11.70	11.74	12.58	13.70
	3H	13.08	13.78	13.96	14.69	15.82	12.69	13.39	13.57	14.30	15.43
	4H	13.79	14.43	14.69	15.34	16.49	13.39	14.02	14.29	14.93	16.09
	6H	14.31	14.86	15.22	15.79	16.95	13.90	14.45	14.81	15.38	16.54
	8H	14.45	14.97	15.37	15.89	17.07	14.05	14.56	14.96	15.49	16.66
	12H	14.53	14.99	15.46	15.94	17.12	14.11	14.58	15.05	15.52	16.70
8H	4H	13.99	14.51	14.91	15.43	16.61	13.64	14.15	14.55	15.08	16.25
	6H	14.62	15.05	15.56	16.02	17.19	14.26	14.69	15.20	15.66	16.83
	8H	14.84	15.21	15.79	16.17	17.36	14.47	14.85	15.43	15.81	17.00
	12H	14.97	15.30	15.92	16.25	17.49	14.59	14.92	15.55	15.87	17.11
12H	4H	13.98	14.45	14.92	15.39	16.57	13.63	14.10	14.57	15.04	16.22
	6H	14.65	15.03	15.60	15.99	17.18	14.30	14.68	15.25	15.64	16.83
	8H	14.89	15.22	15.85	16.18	17.42	14.54	14.87	15.49	15.82	17.06