

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918873

Luminaire Tested: DFN2DIP-HX2F0-060D030US935-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918873
REPORT IS A COMBINATION OF REPORTS P900690 AND P897595
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-060D030US935-RLLONL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6948.3 lumens
Efficiency: N/A
Efficacy: 85.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 81.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918873

CATALOG NUMBER: DFN2DIP-HX2F0-060D030US935-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P918873

CATALOG NUMBER: DFN2DIP-HX2F0-060D030US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	61	60	59
2	93	86	80	75	87	81	75	71	71	67	64	63	60	57	55	52	51
3	85	76	69	63	80	72	65	60	63	58	54	56	52	49	49	46	44
4	78	68	60	54	73	64	57	52	57	51	47	50	46	43	44	41	38
5	72	61	53	47	67	57	50	45	51	45	41	46	41	37	40	37	34
6	67	55	47	41	62	52	45	39	46	41	36	41	37	33	37	33	30
7	62	50	42	36	58	47	40	35	42	36	32	38	33	30	34	30	27
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	24
9	54	42	34	29	51	40	33	28	36	30	26	32	27	24	29	25	22
10	50	38	31	26	47	37	30	25	33	28	24	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5031	5031	5031
5°	5031	4939	4973
10°	4973	4830	4802
15°	4896	4659	4544
20°	4798	4428	4229
25°	4697	4171	3926
30°	4564	3908	3545
35°	4434	3628	3210
40°	4300	3338	2828
45°	4146	3019	2483
50°	3986	2698	2145
55°	3818	2356	1822
60°	3624	2001	1491
65°	3399	1641	1332
70°	3127	1305	1192
75°	2784	1127	1067
80°	2291	913	899
85°	1498	564	630

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4146 cd/sqm

TEST NUMBER: P918873

CATALOG NUMBER: DFN2DIP-HX2F0-060D030US935-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.1	2.9
10°-20°	549.3	7.9
20°-30°	771.2	11.1
30°-40°	840.7	12.1
40°-50°	772.7	11.1
50°-60°	606.8	8.7
60°-70°	395.0	5.7
70°-80°	203.3	2.9
80°-90°	53.4	0.8
90°-100°	28.7	0.4
100°-110°	107.2	1.5
110°-120°	284.2	4.1
120°-130°	471.3	6.8
130°-140°	500.7	7.2
140°-150°	465.3	6.7
150°-160°	374.1	5.4
160°-170°	241.1	3.5
170°-180°	83.0	1.2
0°-30°	1520.7	21.9
0°-40°	2361.4	34.0
0°-60°	3740.9	53.8
0°-90°	4392.6	63.2
90°-120°	420.1	6.0
90°-150°	1857.5	26.7
90°-180°	2556.0	36.8
0°-180°	6948.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2135	2135	2135	2135	2135	
5°	2135	2126	2100	2118	2112	202
15°	2031	2009	1944	1907	1888	572
25°	1843	1782	1654	1575	1546	848
35°	1588	1490	1320	1198	1155	994
45°	1298	1169	966	829	782	1003
55°	987	837	628	512	475	882
65°	667	510	336	271	265	661
75°	356	220	154	141	139	376
85°	83	42	37	37	37	95
90°	1	8	13	16	17	7
95°	41	20	24	28	27	49
105°	192	211	38	45	48	205
115°	363	373	389	97	52	357
125°	513	521	533	537	539	457
135°	635	645	650	657	655	490
145°	736	736	746	751	747	460
155°	810	805	812	816	811	373
165°	854	850	852	857	852	241
175°	874	869	870	875	869	83
180°	872	872	872	872	872	

TEST NUMBER: P918873

CATALOG NUMBER: DFN2DIP-HX2F0-060D030US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2135.1	2135.1	2135.1	2135.1	2135.1
2.5°	2144.7	2135.1	2113.7	2133.2	2129.3
5°	2135.1	2125.5	2100.2	2117.7	2111.9
7.5°	2117.7	2106.2	2079.1	2086.7	2077.1
10°	2094.5	2080.9	2042.5	2036.5	2025.0
12.5°	2065.6	2048.1	1995.9	1984.4	1963.1
15°	2030.7	2009.4	1943.8	1907.1	1887.8
17.5°	1990.2	1959.2	1878.0	1835.6	1804.7
20°	1943.8	1905.0	1808.5	1760.3	1717.7
22.5°	1893.6	1849.1	1737.0	1671.4	1642.4
25°	1843.4	1781.5	1654.0	1574.9	1545.7
27.5°	1783.6	1717.7	1576.7	1485.8	1441.4
30°	1719.8	1646.1	1491.6	1393.2	1340.9
32.5°	1657.9	1568.9	1410.7	1294.6	1246.2
35°	1588.4	1489.8	1319.8	1198.0	1155.4
37.5°	1520.7	1414.3	1234.8	1101.3	1053.1
40°	1449.1	1333.3	1145.7	1008.6	958.4
42.5°	1375.8	1252.1	1057.0	913.9	865.7
45°	1298.5	1168.9	966.2	828.8	782.5
47.5°	1225.1	1088.0	879.3	741.9	699.5
50°	1143.9	1006.8	794.2	660.7	620.3
52.5°	1064.5	919.6	713.0	585.5	548.8
55°	987.3	836.6	627.9	512.1	475.4
57.5°	908.2	753.5	552.7	444.4	413.5
60°	827.0	672.4	473.4	375.0	344.0
62.5°	747.9	593.3	405.7	313.1	297.6
65°	666.7	510.1	336.2	270.6	264.7
67.5°	589.4	432.7	270.6	237.6	231.9
70°	508.2	357.5	224.0	204.8	197.0
72.5°	430.9	287.8	187.4	172.0	168.1
75°	355.5	220.2	154.5	141.0	139.2
77.5°	280.3	156.4	121.7	114.0	110.1
80°	210.5	112.1	92.6	85.1	85.1
82.5°	146.8	75.4	63.7	59.8	59.8
85°	83.0	42.4	36.7	36.7	36.7
87.5°	31.0	15.4	15.4	13.5	13.5
90°	0.6	7.6	12.6	15.8	17.0
92.5°	15.8	13.3	15.2	16.4	17.0
95°	41.0	20.1	24.5	27.8	27.1
97.5°	73.8	22.1	32.1	34.1	34.7
100°	111.7	25.2	36.0	41.0	42.3
102.5°	153.3	152.1	37.2	44.1	46.1
105°	191.7	210.7	38.5	45.4	48.0
107.5°	236.5	252.3	39.8	46.7	49.2
110°	279.5	292.7	110.4	47.4	49.9

TEST NUMBER: P918873

CATALOG NUMBER: DFN2DIP-HX2F0-060D030US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	319.9	331.1	320.5	48.6	50.5
115°	362.7	373.4	389.2	97.1	51.7
117.5°	399.9	412.5	423.3	333.0	167.8
120°	441.5	451.0	462.4	469.9	384.8
122.5°	476.8	487.0	499.6	503.3	504.0
125°	512.8	521.0	533.0	537.4	539.3
127.5°	545.6	554.4	564.0	570.2	570.8
130°	576.5	586.7	593.6	600.5	599.9
132.5°	608.0	616.3	623.2	628.9	628.3
135°	634.6	644.7	650.3	656.7	655.4
137.5°	662.3	669.9	676.2	682.5	680.6
140°	689.4	694.5	701.4	707.1	704.0
142.5°	712.2	716.6	724.8	729.8	726.7
145°	736.2	735.5	746.2	750.6	747.4
147.5°	756.9	755.0	765.8	768.9	766.4
150°	777.1	772.7	782.8	786.5	783.4
152.5°	794.1	789.1	798.6	802.4	798.0
155°	810.5	804.9	812.4	816.2	811.2
157.5°	823.8	818.8	824.5	828.9	823.8
160°	835.2	831.4	835.2	839.0	834.5
162.5°	845.2	841.5	844.6	849.0	843.3
165°	854.0	850.3	852.2	856.6	852.2
167.5°	861.0	857.2	859.1	863.6	857.9
170°	866.7	862.9	864.2	868.6	862.9
172.5°	870.5	866.7	868.0	872.4	866.7
175°	873.6	869.2	870.5	874.9	868.6
177.5°	874.9	870.5	871.2	875.5	869.9
180°	871.8	871.8	871.8	871.8	871.8

TEST NUMBER: P918873

CATALOG NUMBER: DFN2DIP-HX2F0-060D030US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.78	14.73	14.62	15.59	16.66	9.76	10.71	10.60	11.57	12.64
	3H	15.44	16.29	16.29	17.16	18.26	10.94	11.79	11.79	12.66	13.76
	4H	16.03	16.84	16.91	17.71	18.82	11.38	12.19	12.25	13.06	14.17
	6H	16.44	17.18	17.32	18.06	19.19	11.70	12.43	12.58	13.32	14.44
	8H	16.56	17.26	17.45	18.16	19.29	11.78	12.48	12.67	13.38	14.51
	12H	16.62	17.28	17.51	18.18	19.33	11.82	12.49	12.72	13.38	14.53
4H	2H	13.80	14.61	14.68	15.48	16.59	10.35	11.16	11.23	12.03	13.14
	3H	15.62	16.28	16.50	17.19	18.31	11.70	12.36	12.58	13.27	14.39
	4H	16.29	16.90	17.19	17.80	18.95	12.23	12.84	13.13	13.74	14.89
	6H	16.79	17.31	17.70	18.24	19.39	12.64	13.16	13.55	14.09	15.24
	8H	16.95	17.44	17.87	18.36	19.53	12.76	13.25	13.68	14.17	15.34
	12H	17.04	17.48	17.98	18.42	19.59	12.82	13.26	13.76	14.20	15.37
8H	4H	16.27	16.75	17.18	17.68	18.84	12.51	13.00	13.42	13.92	15.08
	6H	16.81	17.21	17.75	18.18	19.34	13.01	13.41	13.95	14.37	15.54
	8H	17.01	17.37	17.96	18.32	19.50	13.18	13.54	14.14	14.50	15.68
	12H	17.14	17.45	18.09	18.40	19.63	13.30	13.61	14.25	14.56	15.79
12H	4H	16.22	16.66	17.16	17.60	18.77	12.51	12.95	13.45	13.89	15.06
	6H	16.78	17.14	17.73	18.09	19.28	13.05	13.41	14.00	14.36	15.54
	8H	16.99	17.31	17.95	18.25	19.49	13.25	13.56	14.20	14.51	15.74