

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918876

Luminaire Tested: DFN2DIP-HX2F0-060D040US935-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P918876  
REPORT IS A COMBINATION OF REPORTS P899180 AND P896039  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX2F0-060D040US935-RLLFLL  
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7439.0 lumens  
Efficiency: N/A  
Efficacy: 83.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 88.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9971  
Total Harmonic Distortion (THDi): 0.049  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P918876  
CATALOG NUMBER: DFN2DIP-HX2F0-060D040US935-RLFL

### Luminous Intensity Polar Plot





TEST NUMBER: P918876

CATALOG NUMBER: DFN2DIP-HX2F0-060D040US935-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59			
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56	51			
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	52	50	48	44			
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	44	41	38			
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36	33			
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	34	32	29			
6	66	54	46	40	61	51	44	39	45	39	35	40	35	32	35	31	28	26			
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25	23			
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23	21			
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	24	21	19			
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	25	22	19	17			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5031	5031	5031
5°	5031	4939	4973
10°	4973	4830	4802
15°	4896	4659	4544
20°	4798	4428	4229
25°	4697	4171	3926
30°	4564	3908	3545
35°	4434	3628	3210
40°	4300	3338	2828
45°	4146	3019	2483
50°	3986	2698	2145
55°	3818	2356	1822
60°	3624	2001	1491
65°	3399	1641	1332
70°	3127	1305	1192
75°	2784	1127	1067
80°	2291	913	899
85°	1498	564	630

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4146 cd/sqm



TEST NUMBER: P918876

CATALOG NUMBER: DFN2DIP-HX2F0-060D040US935-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	200.1	2.7
10°-20°	549.3	7.4
20°-30°	771.2	10.4
30°-40°	840.7	11.3
40°-50°	772.7	10.4
50°-60°	606.8	8.2
60°-70°	395.0	5.3
70°-80°	203.3	2.7
80°-90°	55.0	0.7
90°-100°	67.4	0.9
100°-110°	214.2	2.9
110°-120°	366.5	4.9
120°-130°	482.0	6.5
130°-140°	541.0	7.3
140°-150°	530.5	7.1
150°-160°	445.0	6.0
160°-170°	295.1	4.0
170°-180°	103.2	1.4
0°-30°	1520.7	20.4
0°-40°	2361.4	31.7
0°-60°	3740.9	50.3
0°-90°	4394.2	59.1
90°-120°	648.0	8.7
90°-150°	2201.5	29.6
90°-180°	3045.0	40.9
0°-180°	7439.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2135	2135	2135	2135	2135	
5°	2135	2126	2100	2118	2112	202
15°	2031	2009	1944	1907	1888	572
25°	1843	1782	1654	1575	1546	848
35°	1588	1490	1320	1198	1155	994
45°	1298	1169	966	829	782	1003
55°	987	837	628	512	475	882
65°	667	510	336	271	265	661
75°	356	220	154	141	139	376
85°	83	42	37	37	37	95
90°	1	12	32	30	31	7
95°	48	57	59	59	57	53
105°	198	200	202	204	204	209
115°	368	373	371	370	368	364
125°	535	543	540	538	537	478
135°	692	702	704	703	700	535
145°	840	846	852	853	849	525
155°	960	963	966	971	968	442
165°	1045	1044	1044	1050	1046	295
175°	1087	1085	1083	1089	1084	103
180°	1089	1089	1089	1089	1089	



TEST NUMBER: P918876

CATALOG NUMBER: DFN2DIP-HX2F0-060D040US935-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2135.1	2135.1	2135.1	2135.1	2135.1
2.5°	2144.7	2135.1	2113.7	2133.2	2129.3
5°	2135.1	2125.5	2100.2	2117.7	2111.9
7.5°	2117.7	2106.2	2079.1	2086.7	2077.1
10°	2094.5	2080.9	2042.5	2036.5	2025.0
12.5°	2065.6	2048.1	1995.9	1984.4	1963.1
15°	2030.7	2009.4	1943.8	1907.1	1887.8
17.5°	1990.2	1959.2	1878.0	1835.6	1804.7
20°	1943.8	1905.0	1808.5	1760.3	1717.7
22.5°	1893.6	1849.1	1737.0	1671.4	1642.4
25°	1843.4	1781.5	1654.0	1574.9	1545.7
27.5°	1783.6	1717.7	1576.7	1485.8	1441.4
30°	1719.8	1646.1	1491.6	1393.2	1340.9
32.5°	1657.9	1568.9	1410.7	1294.6	1246.2
35°	1588.4	1489.8	1319.8	1198.0	1155.4
37.5°	1520.7	1414.3	1234.8	1101.3	1053.1
40°	1449.1	1333.3	1145.7	1008.6	958.4
42.5°	1375.8	1252.1	1057.0	913.9	865.7
45°	1298.5	1168.9	966.2	828.8	782.5
47.5°	1225.1	1088.0	879.3	741.9	699.5
50°	1143.9	1006.8	794.2	660.7	620.3
52.5°	1064.5	919.6	713.0	585.5	548.8
55°	987.3	836.6	627.9	512.1	475.4
57.5°	908.2	753.5	552.7	444.4	413.5
60°	827.0	672.4	473.4	375.0	344.0
62.5°	747.9	593.3	405.7	313.1	297.6
65°	666.7	510.1	336.2	270.6	264.7
67.5°	589.4	432.7	270.6	237.6	231.9
70°	508.2	357.5	224.0	204.8	197.0
72.5°	430.9	287.8	187.4	172.0	168.1
75°	355.5	220.2	154.5	141.0	139.2
77.5°	280.3	156.4	121.7	114.0	110.1
80°	210.5	112.1	92.6	85.1	85.1
82.5°	146.8	75.4	63.7	59.8	59.8
85°	83.0	42.4	36.7	36.7	36.7
87.5°	31.0	15.4	15.4	13.5	13.5
90°	0.9	11.8	32.2	30.2	31.2
92.5°	20.3	27.6	28.6	29.5	29.5
95°	48.0	57.2	58.8	58.8	57.2
97.5°	79.8	88.3	92.0	92.0	92.0
100°	116.6	124.2	126.7	126.7	125.8
102.5°	155.3	160.9	164.5	165.5	164.5
105°	197.7	200.3	202.2	203.9	203.9
107.5°	239.7	243.7	243.7	244.3	239.7
110°	280.4	285.7	285.7	285.7	283.1



TEST NUMBER: P918876

CATALOG NUMBER: DFN2DIP-HX2F0-060D040US935-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	324.4	330.0	329.0	326.4	324.4
115°	367.7	373.1	371.3	370.4	367.7
117.5°	410.8	418.0	413.5	410.8	408.2
120°	454.2	461.3	454.2	454.2	451.2
122.5°	493.5	502.7	498.2	495.5	493.5
125°	534.9	543.1	540.5	537.5	536.6
127.5°	575.3	585.5	581.9	577.9	575.3
130°	613.0	624.9	623.3	621.3	617.7
132.5°	655.4	664.6	665.3	660.6	658.1
135°	691.9	702.1	704.0	703.0	700.4
137.5°	732.6	740.8	742.4	741.7	737.9
140°	768.4	776.6	781.2	781.2	777.6
142.5°	805.2	813.4	816.0	817.0	813.4
145°	840.0	846.5	851.8	852.8	849.2
147.5°	871.2	879.3	883.3	884.9	881.3
150°	903.4	909.0	912.6	915.5	912.6
152.5°	931.9	937.5	942.1	945.7	942.1
155°	960.4	963.1	966.0	970.7	967.7
157.5°	985.2	987.0	988.7	995.3	990.7
160°	1007.1	1009.1	1010.0	1015.6	1011.7
162.5°	1027.4	1027.4	1028.5	1034.7	1030.1
165°	1044.9	1043.9	1043.9	1050.4	1045.9
167.5°	1060.7	1057.6	1057.6	1064.3	1059.6
170°	1072.5	1069.8	1068.8	1075.4	1069.8
172.5°	1080.6	1078.1	1077.0	1083.7	1078.1
175°	1087.3	1084.6	1082.6	1089.2	1083.7
177.5°	1090.9	1088.2	1086.2	1091.8	1086.2
180°	1089.2	1089.2	1089.2	1089.2	1089.2



TEST NUMBER: P918876  
 CATALOG NUMBER: DFN2DIP-HX2F0-060D040US935-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.43	14.34	14.31	15.24	16.38	9.41	10.32	10.29	11.22	12.36
	3H	15.09	15.90	15.98	16.81	17.97	10.59	11.40	11.48	12.31	13.48
	4H	15.68	16.45	16.59	17.36	18.54	11.03	11.80	11.94	12.71	13.89
	6H	16.09	16.80	17.01	17.71	18.90	11.34	12.05	12.26	12.97	14.16
	8H	16.21	16.88	17.13	17.82	19.00	11.43	12.10	12.36	13.04	14.22
	12H	16.26	16.90	17.19	17.83	19.04	11.47	12.11	12.40	13.04	14.25
4H	2H	13.45	14.22	14.37	15.13	16.31	10.00	10.77	10.92	11.68	12.86
	3H	15.26	15.90	16.19	16.84	18.03	11.34	11.98	12.27	12.92	14.11
	4H	15.94	16.52	16.87	17.46	18.67	11.88	12.46	12.81	13.40	14.61
	6H	16.43	16.93	17.38	17.90	19.11	12.28	12.78	13.23	13.75	14.96
	8H	16.59	17.06	17.55	18.02	19.25	12.40	12.87	13.35	13.83	15.05
	12H	16.68	17.10	17.65	18.07	19.31	12.46	12.88	13.43	13.86	15.09
8H	4H	15.91	16.37	16.86	17.33	18.56	12.15	12.62	13.10	13.57	14.80
	6H	16.45	16.83	17.42	17.83	19.06	12.65	13.03	13.62	14.03	15.26
	8H	16.65	16.99	17.63	17.98	19.22	12.82	13.16	13.81	14.15	15.40
	12H	16.77	17.07	17.76	18.05	19.35	12.93	13.23	13.92	14.21	15.51
12H	4H	15.86	16.28	16.83	17.26	18.49	12.15	12.57	13.12	13.55	14.78
	6H	16.42	16.76	17.41	17.75	19.00	12.69	13.03	13.67	14.02	15.26
	8H	16.63	16.93	17.62	17.91	19.20	12.89	13.19	13.88	14.17	15.46